

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026527

Luminaire Tested: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026527
REPORT IS A COMBINATION OF REPORTS P999617 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D810UB50-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4885.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026527

CATALOG NUMBER: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026527

CATALOG NUMBER: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	89	86	89	85	82	79	72	69	67	59	57	56	47	46	45
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	40	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7937	7937	7937
5°	7937	7701	7702
10°	7870	7459	7370
15°	7762	7156	6977
20°	7620	6811	6530
25°	7444	6439	6093
30°	7271	6059	5603
35°	7080	5674	5123
40°	6853	5260	4630
45°	6641	4849	4142
50°	6400	4400	3647
55°	6139	3940	3136
60°	5848	3451	2630
65°	5569	2890	2144
70°	5171	2301	1639
75°	4660	1674	1146
80°	3895	1028	824
85°	2925	592	453

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6641 cd/sqm

TEST NUMBER: P1026527

CATALOG NUMBER: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.9
10°-20°	255.2	5.2
20°-30°	368.4	7.5
30°-40°	417.6	8.5
40°-50°	403.2	8.3
50°-60°	335.2	6.9
60°-70°	231.3	4.7
70°-80°	116.9	2.4
80°-90°	31.7	0.6
90°-100°	61.9	1.3
100°-110°	185.3	3.8
110°-120°	314.8	6.4
120°-130°	415.2	8.5
130°-140°	466.4	9.5
140°-150°	458.4	9.4
150°-160°	385.5	7.9
160°-170°	256.5	5.3
170°-180°	89.8	1.8
0°-30°	715.2	14.6
0°-40°	1132.7	23.2
0°-60°	1871.1	38.3
0°-90°	2251.0	46.1
90°-120°	562.1	11.5
90°-150°	1902.1	38.9
90°-180°	2634.0	53.9
0°-180°	4885.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	973	973	973	973	973	
5°	972	969	960	967	966	92
15°	926	919	900	899	894	261
25°	837	824	793	780	773	386
35°	724	700	663	637	624	452
45°	590	563	518	482	468	455
55°	447	417	369	330	316	400
65°	304	272	224	192	183	300
75°	162	134	99	82	78	171
85°	40	25	23	22	22	44
90°	2	10	16	21	22	6
95°	44	51	56	58	58	48
105°	171	172	175	177	179	181
115°	320	320	319	318	317	316
125°	466	466	466	464	462	416
135°	601	606	606	604	602	465
145°	730	734	734	734	731	457
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1026527

CATALOG NUMBER: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	973.3	973.3	973.3	973.3	973.3
2.5°	976.3	973.3	965.1	973.3	972.6
5°	971.8	968.9	959.9	967.4	965.9
7.5°	965.1	962.2	951.0	956.2	954.0
10°	954.7	951.0	937.6	940.5	937.6
12.5°	941.3	936.8	920.4	921.9	917.4
15°	925.6	918.9	900.3	898.8	893.6
17.5°	907.8	898.1	876.5	872.7	865.3
20°	886.1	876.5	851.1	845.1	835.5
22.5°	862.3	851.1	823.5	813.8	806.4
25°	837.0	823.5	793.0	780.3	772.9
27.5°	810.9	794.5	762.4	747.5	737.1
30°	783.3	764.7	729.6	711.0	699.1
32.5°	754.2	732.6	696.1	673.7	662.6
35°	723.7	699.8	662.6	637.2	623.8
37.5°	691.6	667.0	626.0	598.5	585.0
40°	657.3	632.7	590.3	559.0	545.5
42.5°	624.5	598.5	553.7	521.7	507.5
45°	590.3	562.7	518.0	481.5	468.0
47.5°	555.2	526.9	480.7	442.7	427.8
50°	519.5	490.4	442.7	405.4	391.3
52.5°	482.9	454.6	405.4	367.4	352.5
55°	447.2	417.4	368.9	330.2	316.0
57.5°	412.1	380.8	333.1	293.6	283.2
60°	374.1	344.3	296.6	257.9	245.9
62.5°	339.8	308.5	259.4	224.3	215.4
65°	304.1	272.0	224.3	192.3	183.3
67.5°	266.8	236.3	191.5	163.2	152.8
70°	231.8	200.5	158.0	133.4	126.0
72.5°	194.5	166.9	127.4	107.3	100.6
75°	161.7	134.2	99.1	82.0	77.5
77.5°	127.4	103.6	73.8	61.9	60.4
80°	94.7	73.0	50.7	48.4	47.7
82.5°	66.3	47.0	36.5	35.0	34.3
85°	40.2	25.3	23.1	21.6	21.6
87.5°	17.1	11.2	10.4	9.7	10.4
90°	2.2	10.3	16.2	20.6	22.0
92.5°	19.1	28.6	32.3	34.5	35.2
95°	44.1	50.7	55.8	58.0	58.0
97.5°	70.5	76.4	82.2	85.2	85.2
100°	102.8	105.7	112.3	113.8	113.8
102.5°	136.6	137.3	143.2	145.4	146.1
105°	171.1	171.8	174.7	176.9	179.1
107.5°	207.0	207.8	208.5	211.4	210.7
110°	243.8	245.2	244.5	243.0	245.2

TEST NUMBER: P1026527

CATALOG NUMBER: S124RDIP-B575D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	281.9	280.5	280.5	280.5
115°	320.1	320.1	318.6	317.9	317.2
117.5°	356.1	356.1	355.3	353.1	350.9
120°	392.1	395.0	392.8	389.1	390.6
122.5°	429.5	430.2	429.5	427.3	423.6
125°	466.2	466.2	465.5	464.0	462.5
127.5°	499.2	501.5	500.0	498.5	497.8
130°	534.5	536.7	536.7	535.2	532.3
132.5°	570.5	571.9	571.2	569.7	569.0
135°	601.3	605.7	605.7	604.2	602.0
137.5°	635.8	638.0	639.5	637.3	638.0
140°	670.3	671.8	671.8	671.0	670.3
142.5°	701.9	703.4	702.6	702.6	702.6
145°	730.5	733.5	734.2	733.5	731.3
147.5°	759.9	763.6	762.8	762.1	761.4
150°	786.3	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)