

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026576

Luminaire Tested: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026576
REPORT IS A COMBINATION OF REPORTS P999686 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7575.6 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026576

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026576

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	50	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1026576

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	1.7
10°-20°	367.8	4.9
20°-30°	530.9	7.0
30°-40°	601.7	7.9
40°-50°	581.0	7.7
50°-60°	483.0	6.4
60°-70°	333.4	4.4
70°-80°	168.5	2.2
80°-90°	45.1	0.6
90°-100°	441.0	5.8
100°-110°	896.9	11.8
110°-120°	799.4	10.6
120°-130°	671.5	8.9
130°-140°	560.4	7.4
140°-150°	428.0	5.6
150°-160°	300.8	4.0
160°-170°	176.9	2.3
170°-180°	57.5	0.8
0°-30°	1030.6	13.6
0°-40°	1632.3	21.5
0°-60°	2696.4	35.6
0°-90°	3243.3	42.8
90°-120°	2137.3	28.2
90°-150°	3797.1	50.1
90°-180°	4332.0	57.2
0°-180°	7575.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	1	9	21	23	24	6
95°	38	121	950	471	285	42
105°	136	198	765	1647	1641	145
115°	240	301	682	1311	1576	238
125°	335	398	679	1116	1257	298
135°	398	474	673	990	1124	307
145°	458	525	670	835	918	288
155°	521	563	651	737	769	240
165°	568	586	624	661	671	160
175°	592	594	598	606	604	56
180°	594	594	594	594	594	

TEST NUMBER: P1026576

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	1.2	9.3	21.0	23.3	24.5
92.5°	16.3	89.8	457.2	151.0	106.1
95°	38.5	121.3	950.5	470.6	284.6
97.5°	64.1	134.1	1017.0	961.0	683.4
100°	88.6	151.6	937.7	1329.6	1069.5
102.5°	112.0	172.6	838.6	1560.5	1405.4
105°	136.5	197.7	765.1	1647.4	1641.0
107.5°	163.3	223.4	717.3	1621.2	1752.9
110°	190.1	249.0	695.1	1527.8	1755.3

TEST NUMBER: P1026576

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.8	274.6	684.6	1413.6	1686.5
115°	240.3	301.4	682.3	1310.9	1575.7
117.5°	265.9	326.5	681.1	1230.4	1467.2
120°	291.6	351.0	681.1	1176.2	1378.6
122.5°	314.9	375.0	680.0	1140.6	1308.6
125°	334.7	397.7	678.8	1115.6	1257.3
127.5°	353.4	418.7	676.5	1091.6	1224.6
130°	368.5	439.1	675.3	1063.1	1196.6
132.5°	383.7	456.6	674.1	1029.2	1165.1
135°	397.7	473.6	673.0	990.2	1124.3
137.5°	411.7	488.1	673.0	948.2	1076.5
140°	426.9	501.5	671.8	907.4	1024.0
142.5°	443.2	513.8	671.8	869.5	968.0
145°	458.4	524.8	669.5	835.0	917.9
147.5°	475.8	535.4	666.0	806.5	871.2
150°	492.2	545.2	662.5	780.2	832.7
152.5°	507.3	554.6	656.6	758.1	797.7
155°	521.3	562.8	650.8	737.1	768.6
157.5°	535.3	570.3	645.0	717.2	741.8
160°	548.2	576.7	638.0	697.4	717.3
162.5°	559.8	582.0	631.0	678.2	693.9
165°	568.0	585.5	624.0	660.7	670.6
167.5°	577.3	588.4	617.0	645.6	652.0
170°	583.1	590.8	610.0	630.4	634.5
172.5°	589.0	592.4	603.0	617.0	617.0
175°	592.5	593.6	598.3	606.5	604.1
177.5°	594.8	593.6	594.8	598.9	594.8
180°	593.6	593.6	593.6	593.6	593.6

(END OF REPORT)