

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026045

Luminaire Tested: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026045
REPORT IS A COMBINATION OF REPORTS P998975 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6185.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	93	89	86	82	80	78	73	71	70	64	63	62
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	51	48	46
4	79	68	60	54	74	65	58	52	58	52	48	52	48	44	46	43	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	43	38	34	38	34	31
7	62	50	42	36	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	32	55	43	36	31	40	34	29	36	31	27	32	28	25
9	54	42	34	29	51	40	33	28	36	31	26	33	28	25	30	26	23
10	51	38	31	26	48	37	30	26	34	28	24	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13374	13374	13374	13374
5°	13375	15113	13396	11551
10°	13303	17421	13293	10045
15°	13144	19606	13144	8410
20°	12979	21258	12911	7406
25°	12777	21349	12718	6689
30°	12561	18153	12463	6196
35°	12258	13697	12102	5828
40°	11919	9926	11685	5541
45°	11360	7544	11078	5287
50°	10697	6097	10403	4915
55°	9978	5049	9651	4420
60°	9256	4269	8842	3675
65°	8351	3478	8083	2921
70°	7518	2819	7164	2373
75°	6588	2032	6132	1739
80°	5437	1347	4948	1278
85°	3944	692	3267	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 16743 cd/sqm

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.8	2.6
10°-20°	479.6	7.8
20°-30°	751.2	12.1
30°-40°	834.2	13.5
40°-50°	739.2	12.0
50°-60°	576.1	9.3
60°-70°	376.8	6.1
70°-80°	184.9	3.0
80°-90°	46.1	0.7
90°-100°	202.8	3.3
100°-110°	423.4	6.8
110°-120°	376.4	6.1
120°-130°	316.8	5.1
130°-140°	264.3	4.3
140°-150°	201.8	3.3
150°-160°	141.9	2.3
160°-170°	83.4	1.3
170°-180°	27.1	0.4
0°-30°	1389.6	22.5
0°-40°	2223.9	36.0
0°-60°	3539.2	57.2
0°-90°	4147.1	67.1
90°-120°	1002.5	16.2
90°-150°	1785.4	28.9
90°-180°	2038.0	33.0
0°-180°	6185.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1640	1640	1640	1640	1640	
5°	1638	1895	1640	1448	1638	156
15°	1567	2511	1567	1077	1567	442
25°	1437	2708	1430	848	1437	662
35°	1253	1668	1237	710	1253	783
45°	1010	852	985	597	1010	779
55°	727	509	703	445	727	650
65°	456	297	441	250	456	455
75°	229	137	213	118	229	243
85°	54	33	45	33	54	61
90°	0	12	0	12	0	5
95°	18	134	18	134	18	20
105°	64	774	64	774	64	69
115°	113	743	113	743	113	112
125°	158	593	158	593	158	141
135°	188	530	188	530	188	145
145°	216	433	216	433	216	136
155°	246	362	246	362	246	113
165°	268	316	268	316	268	76
175°	279	285	279	285	279	27
180°	280	280	280	280	280	

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1642.8	1657.3	1665.2	1671.8	1685.0	1690.3	1700.9	1703.5	1714.1	1712.8	1708.8
5°	1637.5	1662.6	1681.1	1700.9	1724.7	1737.9	1752.4	1773.6	1784.2	1798.7	1808.0
7.5°	1628.2	1662.6	1693.0	1723.4	1761.7	1782.8	1801.3	1834.4	1862.1	1885.9	1912.4
10°	1613.7	1657.3	1702.2	1743.2	1796.1	1821.2	1848.9	1897.8	1936.1	1969.2	2011.5
12.5°	1591.2	1652.0	1702.2	1757.7	1825.1	1859.5	1896.5	1954.6	1999.6	2053.8	2106.6
15°	1567.4	1634.8	1700.9	1773.6	1850.2	1889.9	1926.9	2004.9	2073.6	2135.7	2193.9
17.5°	1541.0	1615.0	1687.7	1768.3	1860.8	1909.7	1953.3	2047.2	2122.5	2203.1	2261.3
20°	1509.3	1589.9	1673.1	1763.0	1867.4	1921.6	1970.5	2077.6	2160.8	2248.0	2320.7
22.5°	1474.9	1562.1	1653.3	1751.1	1859.5	1919.0	1975.8	2090.8	2187.3	2267.9	2365.7
25°	1436.6	1529.1	1622.9	1726.0	1847.6	1912.4	1970.5	2084.2	2187.3	2293.0	2388.1
27.5°	1396.9	1492.1	1589.9	1698.3	1822.5	1885.9	1952.0	2061.7	2182.0	2296.9	2393.4
30°	1353.3	1445.8	1548.9	1652.0	1784.2	1847.6	1915.0	2033.9	2164.8	2279.8	2384.2
32.5°	1305.7	1400.9	1498.7	1605.7	1735.3	1804.0	1866.1	2000.9	2134.4	2248.0	2345.8
35°	1252.9	1342.7	1435.3	1545.0	1673.1	1735.3	1809.3	1949.4	2084.2	2204.4	2267.9
37.5°	1196.0	1282.0	1367.9	1476.2	1599.1	1674.5	1747.2	1888.6	2031.3	2111.9	2145.0
40°	1143.2	1218.5	1293.8	1398.3	1522.5	1600.5	1674.5	1821.2	1946.7	2008.8	1983.7
42.5°	1075.8	1153.8	1221.2	1317.6	1443.2	1515.9	1591.2	1743.2	1845.0	1870.1	1808.0
45°	1009.7	1074.5	1139.2	1233.1	1365.2	1427.3	1507.9	1649.4	1733.9	1711.5	1620.3
47.5°	944.9	997.8	1058.6	1149.8	1268.7	1342.7	1418.1	1541.0	1600.5	1568.7	1441.9
50°	868.3	921.2	984.6	1063.9	1178.9	1250.2	1309.7	1423.4	1468.3	1390.3	1237.0
52.5°	795.6	841.9	896.0	970.1	1079.7	1144.5	1209.3	1307.1	1321.6	1231.7	1070.5
55°	726.9	763.9	820.7	880.2	980.6	1049.4	1094.3	1177.5	1173.6	1061.2	922.5
57.5°	655.5	689.9	728.2	790.3	885.5	937.0	985.9	1058.6	1020.3	925.1	787.7
60°	592.1	611.9	650.2	709.7	790.3	835.3	873.6	913.2	880.2	777.1	671.4
62.5°	522.0	544.5	572.3	619.8	691.2	733.5	761.2	778.4	744.1	664.8	568.3
65°	456.0	475.8	504.9	547.1	601.3	633.0	647.6	659.5	641.0	551.1	474.5
67.5°	396.5	409.7	436.1	463.9	522.0	530.0	549.8	555.1	518.1	449.3	388.6
70°	337.0	350.2	362.1	395.2	421.6	436.1	440.1	440.1	403.1	358.2	307.9
72.5°	281.5	289.4	301.3	323.8	338.3	348.9	354.2	347.6	313.2	276.2	239.2
75°	228.6	232.6	243.2	257.7	269.6	265.6	264.3	256.4	231.3	204.8	183.7
77.5°	175.8	178.4	190.3	194.3	194.3	198.2	193.0	185.0	163.9	144.1	134.8
80°	132.2	136.1	137.4	140.1	137.4	137.4	133.5	120.3	109.7	100.4	93.8
82.5°	91.2	93.8	95.2	91.2	93.8	89.9	83.3	74.0	67.4	66.1	63.4
85°	54.2	55.5	54.2	54.2	50.2	48.9	43.6	42.3	39.6	39.6	38.3
87.5°	26.4	25.1	22.5	19.8	19.8	18.5	19.8	17.2	19.8	18.5	17.2
90°	0.5	1.6	3.3	3.8	4.4	4.4	4.4	7.7	7.7	8.8	9.9
92.5°	7.7	11.0	17.0	25.3	35.2	42.4	49.5	83.6	136.9	188.6	215.5
95°	18.1	19.8	25.3	32.4	45.6	57.2	68.7	116.5	206.7	338.1	448.0
97.5°	30.2	30.2	35.2	41.8	53.3	63.2	73.1	111.0	188.6	323.8	479.4
100°	41.8	41.8	45.6	52.2	62.7	71.5	80.3	112.7	174.8	287.0	442.0
102.5°	52.8	53.9	57.2	63.2	73.1	81.4	89.6	118.2	171.0	262.2	395.2
105°	64.3	66.0	68.7	75.3	85.2	93.2	101.1	127.5	173.2	250.1	360.6
107.5°	77.0	78.1	80.8	88.0	97.3	105.2	113.2	137.4	179.8	246.8	338.1
110°	89.6	90.7	93.5	100.0	109.9	117.4	124.8	149.0	187.5	247.9	327.6

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	101.7	102.8	106.1	112.1	122.0	129.4	136.9	160.0	195.7	251.2	322.7
115°	113.2	114.9	118.7	124.2	134.7	142.1	149.5	171.5	204.5	255.6	321.6
117.5°	125.3	127.0	130.3	136.3	146.2	153.9	161.6	182.5	213.3	260.0	321.0
120°	137.4	138.5	142.4	148.4	157.8	165.5	173.2	194.1	222.6	265.0	321.0
122.5°	148.4	149.5	153.4	158.9	169.3	176.8	184.2	205.0	231.4	269.9	320.5
125°	157.8	160.0	163.3	169.3	179.8	187.4	195.1	214.9	240.2	274.9	319.9
127.5°	166.6	168.2	172.1	178.7	189.7	197.4	205.0	224.3	247.9	278.7	318.8
130°	173.7	175.9	180.3	188.6	199.0	207.0	214.9	233.6	255.1	283.1	318.3
132.5°	180.9	182.5	188.6	196.2	207.8	215.2	222.6	241.3	262.2	287.0	317.7
135°	187.5	189.7	195.1	204.5	216.0	223.2	230.3	248.5	268.3	290.8	317.2
137.5°	194.1	196.2	202.3	211.1	223.2	230.0	236.9	254.0	272.7	293.0	317.2
140°	201.2	202.8	208.9	218.2	229.8	236.4	243.0	259.5	277.1	295.7	316.6
142.5°	208.9	210.5	216.0	224.8	235.8	242.2	248.5	264.4	280.4	297.9	316.6
145°	216.0	217.7	223.2	230.9	241.3	247.4	253.4	267.7	282.6	298.5	315.5
147.5°	224.3	224.8	229.8	238.0	246.8	252.3	257.8	271.6	284.8	299.0	313.9
150°	232.0	232.5	236.9	243.5	251.8	257.0	262.2	274.3	286.4	299.0	312.2
152.5°	239.1	239.1	243.5	249.6	256.7	261.4	266.1	276.5	287.5	297.9	309.5
155°	245.7	246.3	249.6	255.1	261.1	265.2	269.4	278.7	288.1	296.8	306.7
157.5°	252.3	252.3	255.6	260.0	265.5	268.8	272.1	280.4	288.1	295.7	304.0
160°	258.4	258.4	260.6	264.4	268.8	271.8	274.9	281.5	288.1	294.1	300.7
162.5°	263.9	263.3	265.0	268.3	272.1	274.3	276.5	282.6	288.1	292.4	297.4
165°	267.7	267.7	268.8	271.6	274.3	276.0	277.6	282.6	287.0	290.3	294.1
167.5°	272.1	271.6	272.1	274.3	276.0	277.4	278.7	282.6	285.9	288.1	290.8
170°	274.9	274.3	274.9	276.5	277.6	278.5	279.3	282.0	284.8	285.9	287.5
172.5°	277.6	277.1	277.1	278.2	278.7	279.2	279.8	281.5	283.7	283.7	284.2
175°	279.3	278.7	278.7	279.3	279.8	279.8	279.8	280.9	282.6	282.0	282.0
177.5°	280.4	279.8	279.3	279.8	279.8	279.8	279.8	280.4	281.5	280.4	280.4
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1719.4	1733.9	1735.3	1748.5	1744.5	1737.9	1749.8	1741.9	1757.7	1752.4	1759.1
5°	1819.8	1839.7	1856.9	1867.4	1885.9	1882.0	1901.8	1895.2	1909.7	1895.2	1913.7
7.5°	1937.5	1970.5	1987.7	2015.4	2023.4	2024.7	2048.5	2053.8	2063.0	2053.8	2064.3
10°	2052.4	2092.1	2131.7	2154.2	2168.7	2188.6	2209.7	2219.0	2225.6	2216.3	2222.9
12.5°	2156.9	2219.0	2262.6	2307.5	2318.1	2335.3	2357.7	2355.1	2381.5	2376.2	2388.1
15°	2253.3	2322.1	2374.9	2410.6	2439.7	2454.2	2496.5	2499.1	2497.8	2511.0	2503.1
17.5°	2339.2	2397.4	2472.7	2519.0	2554.7	2554.7	2578.4	2627.3	2623.4	2622.1	2630.0
20°	2409.3	2475.4	2545.4	2623.4	2652.5	2657.7	2690.8	2715.9	2719.9	2719.9	2719.9
22.5°	2462.1	2540.1	2615.4	2671.0	2693.4	2711.9	2741.0	2756.9	2762.1	2759.5	2762.1
25°	2488.6	2562.6	2639.2	2689.5	2702.7	2713.2	2715.9	2725.1	2723.8	2708.0	2717.2
27.5°	2493.9	2565.2	2615.4	2628.7	2622.1	2615.4	2573.2	2577.1	2565.2	2541.4	2550.7
30°	2470.1	2508.4	2507.1	2466.1	2454.2	2426.5	2388.1	2331.3	2285.0	2265.2	2271.8
32.5°	2384.2	2384.2	2336.6	2244.1	2203.1	2152.9	2084.2	2032.6	1971.8	1958.6	1983.7
35°	2265.2	2197.8	2110.6	1989.0	1926.9	1889.9	1770.9	1733.9	1682.4	1667.9	1679.8
37.5°	2080.2	1967.9	1841.0	1727.3	1674.5	1608.4	1504.0	1451.1	1414.1	1389.0	1400.9
40°	1872.7	1736.6	1604.4	1464.3	1406.2	1352.0	1274.0	1226.4	1167.0	1169.6	1173.6
42.5°	1674.5	1514.6	1366.5	1237.0	1181.5	1136.6	1082.4	1024.2	1003.1	996.5	989.9
45°	1464.3	1293.8	1155.1	1058.6	1008.4	966.1	915.9	882.8	857.7	852.4	859.0
47.5°	1266.1	1122.0	989.9	900.0	859.0	837.9	798.2	767.9	752.0	738.8	746.7
50°	1086.4	951.6	845.8	770.5	741.4	726.9	689.9	674.0	658.2	654.2	652.9
52.5°	938.3	823.4	732.2	671.4	648.9	641.0	613.2	590.8	577.5	581.5	584.1
55°	803.5	705.7	634.4	585.5	567.0	557.7	537.9	522.0	512.8	508.8	511.5
57.5°	684.6	600.0	548.5	508.8	494.3	490.3	469.2	463.9	457.3	453.3	453.3
60°	576.2	516.7	469.2	446.7	430.8	426.9	411.0	404.4	403.1	399.1	396.5
62.5°	485.0	436.1	403.1	379.3	372.7	371.4	360.8	352.9	348.9	346.3	346.3
65°	405.7	370.0	342.3	325.1	319.8	317.2	305.3	302.6	300.0	297.4	296.0
67.5°	338.3	306.6	286.8	274.9	268.3	269.6	263.0	257.7	257.7	256.4	255.1
70°	273.6	253.7	236.6	230.0	227.3	224.7	222.0	218.1	216.7	216.7	216.7
72.5°	215.4	202.2	193.0	189.0	186.3	183.7	181.1	181.1	181.1	179.7	179.7
75°	165.2	159.9	153.3	149.3	149.3	152.0	148.0	144.1	140.1	137.4	138.8
77.5°	124.2	121.6	117.6	111.0	112.3	109.7	109.7	107.0	108.4	108.4	105.7
80°	91.2	87.2	85.9	81.9	83.3	81.9	80.6	80.6	78.0	78.0	78.0
82.5°	63.4	59.5	59.5	58.2	56.8	56.8	55.5	55.5	56.8	54.2	54.2
85°	38.3	37.0	37.0	34.4	34.4	34.4	34.4	35.7	34.4	33.0	33.0
87.5°	17.2	18.5	17.2	15.9	15.9	15.9	14.5	14.5	13.2	14.5	14.5
90°	9.3	9.9	10.4	11.0	11.0	11.0	11.5	12.1	11.5	11.5	11.5
92.5°	179.2	132.5	98.9	78.1	71.2	64.3	56.1	52.2	50.0	50.0	50.0
95°	460.7	407.3	322.1	248.5	221.8	195.1	168.2	151.2	141.3	134.1	141.3
97.5°	577.8	586.5	544.2	483.8	453.0	422.2	384.8	351.8	335.3	322.1	335.3
100°	582.7	663.0	674.0	647.0	626.6	606.3	558.5	525.0	508.5	504.1	508.5
102.5°	541.5	659.1	724.5	741.0	735.5	730.0	705.3	683.3	665.7	662.4	665.7
105°	489.8	615.7	710.8	765.2	776.4	787.7	788.8	784.4	776.8	773.5	776.8
107.5°	447.5	562.4	665.2	741.0	764.1	787.2	811.4	821.3	825.7	826.2	825.7
110°	417.2	515.1	610.2	689.9	720.2	750.4	789.4	812.5	822.4	827.3	822.4

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	400.2	480.5	561.8	636.0	666.2	696.5	742.1	771.3	786.1	794.9	786.1
115°	390.8	459.6	527.2	591.5	617.9	644.3	687.7	720.7	738.3	742.7	738.3
117.5°	385.9	447.5	504.6	556.9	580.0	603.0	641.5	670.1	688.8	691.5	688.8
120°	382.1	439.8	490.9	534.9	554.4	573.9	605.2	629.4	643.7	649.8	643.7
122.5°	377.7	433.2	482.1	521.1	537.6	554.1	579.4	599.2	610.7	616.8	610.7
125°	372.7	425.5	472.8	510.7	525.8	540.9	562.9	578.9	589.3	592.6	589.3
127.5°	366.1	416.7	462.3	500.2	514.5	528.8	550.8	565.1	573.9	577.2	573.9
130°	360.1	405.7	449.1	486.5	501.0	515.6	538.2	551.9	560.7	564.0	560.7
132.5°	354.6	394.1	434.3	470.6	485.2	499.7	521.7	537.6	545.9	549.2	545.9
135°	349.1	383.7	419.4	453.0	466.8	480.5	502.4	517.8	526.6	529.9	526.6
137.5°	344.1	373.8	405.1	434.3	447.0	459.6	480.5	496.4	503.5	507.4	503.5
140°	340.3	365.6	391.4	416.1	427.6	439.2	458.5	470.6	478.3	482.7	478.3
142.5°	337.0	357.9	379.9	400.2	409.8	419.4	435.9	446.9	453.5	456.3	453.5
145°	333.1	350.7	369.4	385.9	393.6	401.3	415.0	424.4	429.9	432.6	429.9
147.5°	329.8	344.7	360.1	373.8	380.2	386.5	396.9	405.1	409.5	410.6	409.5
150°	326.0	339.2	351.8	362.8	367.8	372.7	381.5	388.7	391.9	392.5	391.9
152.5°	321.6	333.1	343.6	353.5	357.4	361.2	368.3	373.8	375.5	376.0	375.5
155°	317.2	327.1	335.9	344.1	347.4	350.7	356.2	360.6	362.3	362.3	362.3
157.5°	312.8	320.5	328.2	335.3	338.0	340.8	345.2	348.5	349.6	349.6	349.6
160°	307.8	314.4	320.5	326.5	328.7	330.9	334.2	337.5	338.1	338.1	338.1
162.5°	303.4	308.4	313.3	317.7	319.6	321.6	323.8	327.1	327.6	327.1	327.6
165°	298.5	302.9	306.2	310.0	311.4	312.8	315.0	317.2	316.6	316.1	316.6
167.5°	294.1	297.4	300.1	303.4	304.2	305.1	306.2	307.8	307.8	307.3	307.8
170°	289.7	292.4	294.1	296.3	297.1	297.9	299.0	299.6	299.0	299.0	299.0
172.5°	285.9	288.1	289.2	290.3	290.8	291.4	291.9	292.4	291.9	290.8	291.9
175°	283.1	284.2	284.8	285.9	285.9	285.9	285.9	287.0	285.9	284.8	285.9
177.5°	280.9	281.5	282.0	282.0	282.3	282.6	282.0	282.6	281.5	280.4	281.5
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1763.0	1753.8	1752.4	1752.4	1737.9	1745.8	1730.0	1712.8	1704.9	1704.9	1690.3
5°	1909.7	1900.5	1891.2	1876.7	1876.7	1868.7	1843.6	1818.5	1800.0	1784.2	1767.0
7.5°	2060.4	2051.1	2024.7	2010.2	2018.1	2002.2	1969.2	1926.9	1895.2	1870.1	1834.4
10°	2224.3	2199.1	2185.9	2178.0	2150.2	2133.1	2094.7	2032.6	1993.0	1959.9	1913.7
12.5°	2357.7	2365.7	2315.4	2319.4	2291.7	2267.9	2208.4	2148.9	2089.5	2043.2	1974.5
15°	2501.8	2478.0	2447.6	2423.8	2414.6	2385.5	2335.3	2256.0	2191.2	2118.5	2040.6
17.5°	2615.4	2596.9	2567.9	2545.4	2525.6	2455.5	2413.2	2343.2	2254.7	2183.3	2088.1
20°	2711.9	2694.7	2653.8	2639.2	2603.6	2553.3	2492.5	2384.2	2304.9	2226.9	2134.4
22.5°	2752.9	2735.7	2700.0	2681.5	2659.1	2610.2	2552.0	2448.9	2351.1	2253.3	2155.5
25°	2718.5	2718.5	2701.4	2694.7	2674.9	2631.3	2571.8	2484.6	2380.2	2274.5	2158.2
27.5°	2552.0	2585.1	2596.9	2603.6	2603.6	2604.9	2563.9	2479.3	2377.6	2274.5	2152.9
30°	2311.5	2367.0	2415.9	2430.4	2455.5	2483.3	2500.5	2459.5	2368.3	2259.9	2138.4
32.5°	2008.8	2080.2	2171.4	2193.9	2228.2	2311.5	2357.7	2374.9	2324.7	2229.5	2100.0
35°	1707.5	1797.4	1852.9	1921.6	1953.3	2076.2	2179.3	2241.4	2229.5	2172.7	2055.1
37.5°	1444.5	1496.1	1563.5	1636.1	1699.6	1817.2	1945.4	2065.7	2114.6	2086.8	1998.3
40°	1192.1	1252.9	1333.5	1393.0	1436.6	1554.2	1712.8	1843.6	1950.7	1967.9	1913.7
42.5°	1013.7	1074.5	1123.4	1188.1	1222.5	1336.1	1476.2	1640.1	1767.0	1834.4	1810.6
45°	876.2	913.2	952.9	989.9	1032.2	1132.6	1262.1	1441.9	1584.6	1679.8	1689.0
47.5°	756.0	789.0	823.4	857.7	881.5	959.5	1078.4	1225.1	1381.1	1511.9	1563.5
50°	671.4	687.2	712.3	732.2	759.9	827.3	922.5	1049.4	1214.6	1356.0	1423.4
52.5°	588.1	607.9	627.8	644.9	663.4	711.0	798.2	907.9	1050.7	1196.0	1279.3
55°	518.1	533.9	552.4	564.3	574.9	617.2	683.3	767.9	890.8	1028.2	1131.3
57.5°	461.2	467.8	483.7	490.3	502.2	536.6	584.1	659.5	758.6	892.1	976.7
60°	399.1	412.3	424.2	429.5	438.8	462.6	495.6	565.6	651.5	749.3	845.8
62.5°	348.9	354.2	363.4	370.0	376.7	401.8	429.5	482.4	547.1	629.1	717.6
65°	302.6	305.3	310.6	319.8	323.8	342.3	358.2	396.5	457.3	519.4	607.9
67.5°	255.1	257.7	264.3	269.6	273.6	285.5	302.6	330.4	363.4	432.2	481.1
70°	218.1	218.1	222.0	224.7	228.6	233.9	243.2	264.3	294.7	338.3	383.3
72.5°	182.4	182.4	182.4	186.3	186.3	190.3	195.6	210.1	231.3	265.6	294.7
75°	141.4	142.7	145.4	145.4	146.7	152.0	155.9	159.9	170.5	193.0	219.4
77.5°	107.0	109.7	111.0	108.4	111.0	111.0	116.3	121.6	126.9	133.5	153.3
80°	79.3	80.6	78.0	79.3	79.3	81.9	84.6	83.3	85.9	93.8	99.1
82.5°	52.9	54.2	54.2	54.2	54.2	58.2	58.2	56.8	58.2	59.5	60.8
85°	33.0	31.7	31.7	33.0	31.7	31.7	33.0	34.4	33.0	34.4	35.7
87.5°	14.5	14.5	14.5	14.5	13.2	13.2	14.5	13.2	14.5	13.2	11.9
90°	12.1	11.5	11.0	11.0	11.0	10.4	9.9	9.3	9.9	8.8	7.7
92.5°	52.2	56.1	64.3	71.2	78.1	98.9	132.5	179.2	215.5	188.6	136.9
95°	151.2	168.2	195.1	221.8	248.5	322.1	407.3	460.7	448.0	338.1	206.7
97.5°	351.8	384.8	422.2	453.0	483.8	544.2	586.5	577.8	479.4	323.8	188.6
100°	525.0	558.5	606.3	626.6	647.0	674.0	663.0	582.7	442.0	287.0	174.8
102.5°	683.3	705.3	730.0	735.5	741.0	724.5	659.1	541.5	395.2	262.2	171.0
105°	784.4	788.8	787.7	776.4	765.2	710.8	615.7	489.8	360.6	250.1	173.2
107.5°	821.3	811.4	787.2	764.1	741.0	665.2	562.4	447.5	338.1	246.8	179.8
110°	812.5	789.4	750.4	720.2	689.9	610.2	515.1	417.2	327.6	247.9	187.5

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	771.3	742.1	696.5	666.2	636.0	561.8	480.5	400.2	322.7	251.2	195.7
115°	720.7	687.7	644.3	617.9	591.5	527.2	459.6	390.8	321.6	255.6	204.5
117.5°	670.1	641.5	603.0	580.0	556.9	504.6	447.5	385.9	321.0	260.0	213.3
120°	629.4	605.2	573.9	554.4	534.9	490.9	439.8	382.1	321.0	265.0	222.6
122.5°	599.2	579.4	554.1	537.6	521.1	482.1	433.2	377.7	320.5	269.9	231.4
125°	578.9	562.9	540.9	525.8	510.7	472.8	425.5	372.7	319.9	274.9	240.2
127.5°	565.1	550.8	528.8	514.5	500.2	462.3	416.7	366.1	318.8	278.7	247.9
130°	551.9	538.2	515.6	501.0	486.5	449.1	405.7	360.1	318.3	283.1	255.1
132.5°	537.6	521.7	499.7	485.2	470.6	434.3	394.1	354.6	317.7	287.0	262.2
135°	517.8	502.4	480.5	466.8	453.0	419.4	383.7	349.1	317.2	290.8	268.3
137.5°	496.4	480.5	459.6	447.0	434.3	405.1	373.8	344.1	317.2	293.0	272.7
140°	470.6	458.5	439.2	427.6	416.1	391.4	365.6	340.3	316.6	295.7	277.1
142.5°	446.9	435.9	419.4	409.8	400.2	379.9	357.9	337.0	316.6	297.9	280.4
145°	424.4	415.0	401.3	393.6	385.9	369.4	350.7	333.1	315.5	298.5	282.6
147.5°	405.1	396.9	386.5	380.2	373.8	360.1	344.7	329.8	313.9	299.0	284.8
150°	388.7	381.5	372.7	367.8	362.8	351.8	339.2	326.0	312.2	299.0	286.4
152.5°	373.8	368.3	361.2	357.4	353.5	343.6	333.1	321.6	309.5	297.9	287.5
155°	360.6	356.2	350.7	347.4	344.1	335.9	327.1	317.2	306.7	296.8	288.1
157.5°	348.5	345.2	340.8	338.0	335.3	328.2	320.5	312.8	304.0	295.7	288.1
160°	337.5	334.2	330.9	328.7	326.5	320.5	314.4	307.8	300.7	294.1	288.1
162.5°	327.1	323.8	321.6	319.6	317.7	313.3	308.4	303.4	297.4	292.4	288.1
165°	317.2	315.0	312.8	311.4	310.0	306.2	302.9	298.5	294.1	290.3	287.0
167.5°	307.8	306.2	305.1	304.2	303.4	300.1	297.4	294.1	290.8	288.1	285.9
170°	299.6	299.0	297.9	297.1	296.3	294.1	292.4	289.7	287.5	285.9	284.8
172.5°	292.4	291.9	291.4	290.8	290.3	289.2	288.1	285.9	284.2	283.7	283.7
175°	287.0	285.9	285.9	285.9	285.9	284.8	284.2	283.1	282.0	282.0	282.6
177.5°	282.6	282.0	282.6	282.3	282.0	282.0	281.5	280.9	280.4	280.4	281.5
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1682.4	1675.8	1671.8	1670.5	1658.6	1652.0	1648.0	1645.4	1641.4	1630.9	1621.6
5°	1745.8	1727.3	1718.1	1707.5	1689.0	1667.9	1650.7	1640.1	1626.9	1605.7	1585.9
7.5°	1805.3	1777.6	1759.1	1744.5	1712.8	1678.4	1650.7	1628.2	1603.1	1574.0	1546.3
10°	1867.4	1822.5	1798.7	1776.2	1730.0	1685.0	1645.4	1612.4	1576.7	1538.3	1507.9
12.5°	1916.3	1856.9	1830.4	1798.7	1741.9	1689.0	1638.8	1593.9	1547.6	1506.6	1463.0
15°	1973.2	1899.1	1868.7	1827.8	1749.8	1681.1	1616.3	1567.4	1519.8	1459.0	1412.8
17.5°	2006.2	1920.3	1876.7	1841.0	1756.4	1673.1	1597.8	1537.0	1481.5	1420.7	1371.8
20°	2039.2	1941.4	1892.5	1842.3	1741.9	1653.3	1574.0	1501.3	1443.2	1377.1	1326.9
22.5°	2049.8	1936.1	1884.6	1838.3	1732.6	1633.5	1542.3	1468.3	1400.9	1334.8	1278.0
25°	2049.8	1934.8	1874.0	1814.6	1703.5	1601.8	1510.6	1430.0	1354.6	1288.6	1231.7
27.5°	2028.7	1908.4	1845.0	1790.8	1675.8	1566.1	1472.3	1383.7	1311.0	1244.9	1180.2
30°	2002.2	1870.1	1806.6	1741.9	1630.9	1526.5	1424.7	1342.7	1266.1	1190.8	1132.6
32.5°	1969.2	1829.1	1759.1	1693.0	1575.3	1467.0	1373.1	1292.5	1219.8	1141.9	1077.1
35°	1921.6	1768.3	1690.3	1632.2	1518.5	1406.2	1316.3	1237.0	1167.0	1086.4	1016.3
37.5°	1860.8	1712.8	1633.5	1562.1	1444.5	1341.4	1256.8	1180.2	1111.5	1037.5	959.5
40°	1789.4	1634.8	1566.1	1490.8	1366.5	1268.7	1189.4	1120.7	1052.0	982.0	906.6
42.5°	1708.8	1555.5	1478.9	1406.2	1287.2	1190.8	1116.8	1054.6	991.2	926.4	845.8
45°	1612.4	1468.3	1394.3	1325.6	1210.6	1111.5	1044.1	984.6	930.4	864.3	793.0
47.5°	1504.0	1378.4	1303.1	1229.1	1116.8	1030.8	964.8	914.5	868.3	802.2	737.5
50°	1398.3	1274.0	1213.2	1137.9	1034.8	954.2	886.8	844.5	808.8	744.1	685.9
52.5°	1264.8	1170.9	1112.8	1048.0	948.9	867.0	814.1	777.1	734.8	684.6	633.0
55°	1147.2	1059.9	1013.7	952.9	855.1	782.4	737.5	703.1	670.1	625.1	584.1
57.5°	1013.7	959.5	913.2	860.4	763.9	701.8	662.1	633.0	602.7	565.6	532.6
60°	873.6	848.5	803.5	761.2	679.3	625.1	592.1	565.6	536.6	506.2	478.4
62.5°	749.3	734.8	708.4	675.3	598.7	552.4	519.4	499.6	478.4	450.7	424.2
65°	631.7	625.1	600.0	576.2	523.4	482.4	453.3	441.4	417.6	396.5	372.7
67.5°	527.3	519.4	504.9	494.3	449.3	411.0	396.5	380.6	360.8	344.9	325.1
70°	421.6	420.3	411.0	397.8	374.0	346.3	331.7	321.1	301.3	289.4	274.9
72.5°	327.8	334.4	326.4	321.1	305.3	285.5	272.2	265.6	249.8	240.5	230.0
75°	244.5	249.8	253.7	244.5	240.5	231.3	219.4	212.8	204.8	191.6	187.7
77.5°	166.5	178.4	178.4	181.1	182.4	177.1	167.8	162.6	153.3	150.7	145.4
80°	109.7	120.3	121.6	124.2	128.2	128.2	121.6	120.3	111.0	109.7	105.7
82.5°	63.4	72.7	78.0	81.9	80.6	85.9	80.6	79.3	74.0	74.0	71.4
85°	34.4	35.7	38.3	41.0	43.6	46.3	46.3	44.9	43.6	42.3	39.6
87.5°	13.2	13.2	14.5	13.2	14.5	17.2	18.5	18.5	17.2	15.9	13.2
90°	7.7	4.4	4.4	4.4	3.8	3.3	1.6	0.5	1.6	3.3	3.8
92.5°	83.6	49.5	42.4	35.2	25.3	17.0	11.0	7.7	11.0	17.0	25.3
95°	116.5	68.7	57.2	45.6	32.4	25.3	19.8	18.1	19.8	25.3	32.4
97.5°	111.0	73.1	63.2	53.3	41.8	35.2	30.2	30.2	30.2	35.2	41.8
100°	112.7	80.3	71.5	62.7	52.2	45.6	41.8	41.8	41.8	45.6	52.2
102.5°	118.2	89.6	81.4	73.1	63.2	57.2	53.9	52.8	53.9	57.2	63.2
105°	127.5	101.1	93.2	85.2	75.3	68.7	66.0	64.3	66.0	68.7	75.3
107.5°	137.4	113.2	105.2	97.3	88.0	80.8	78.1	77.0	78.1	80.8	88.0
110°	149.0	124.8	117.4	109.9	100.0	93.5	90.7	89.6	90.7	93.5	100.0

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	160.0	136.9	129.4	122.0	112.1	106.1	102.8	101.7	102.8	106.1	112.1
115°	171.5	149.5	142.1	134.7	124.2	118.7	114.9	113.2	114.9	118.7	124.2
117.5°	182.5	161.6	153.9	146.2	136.3	130.3	127.0	125.3	127.0	130.3	136.3
120°	194.1	173.2	165.5	157.8	148.4	142.4	138.5	137.4	138.5	142.4	148.4
122.5°	205.0	184.2	176.8	169.3	158.9	153.4	149.5	148.4	149.5	153.4	158.9
125°	214.9	195.1	187.4	179.8	169.3	163.3	160.0	157.8	160.0	163.3	169.3
127.5°	224.3	205.0	197.4	189.7	178.7	172.1	168.2	166.6	168.2	172.1	178.7
130°	233.6	214.9	207.0	199.0	188.6	180.3	175.9	173.7	175.9	180.3	188.6
132.5°	241.3	222.6	215.2	207.8	196.2	188.6	182.5	180.9	182.5	188.6	196.2
135°	248.5	230.3	223.2	216.0	204.5	195.1	189.7	187.5	189.7	195.1	204.5
137.5°	254.0	236.9	230.0	223.2	211.1	202.3	196.2	194.1	196.2	202.3	211.1
140°	259.5	243.0	236.4	229.8	218.2	208.9	202.8	201.2	202.8	208.9	218.2
142.5°	264.4	248.5	242.2	235.8	224.8	216.0	210.5	208.9	210.5	216.0	224.8
145°	267.7	253.4	247.4	241.3	230.9	223.2	217.7	216.0	217.7	223.2	230.9
147.5°	271.6	257.8	252.3	246.8	238.0	229.8	224.8	224.3	224.8	229.8	238.0
150°	274.3	262.2	257.0	251.8	243.5	236.9	232.5	232.0	232.5	236.9	243.5
152.5°	276.5	266.1	261.4	256.7	249.6	243.5	239.1	239.1	239.1	243.5	249.6
155°	278.7	269.4	265.2	261.1	255.1	249.6	246.3	245.7	246.3	249.6	255.1
157.5°	280.4	272.1	268.8	265.5	260.0	255.6	252.3	252.3	252.3	255.6	260.0
160°	281.5	274.9	271.8	268.8	264.4	260.6	258.4	258.4	258.4	260.6	264.4
162.5°	282.6	276.5	274.3	272.1	268.3	265.0	263.3	263.9	263.3	265.0	268.3
165°	282.6	277.6	276.0	274.3	271.6	268.8	267.7	267.7	267.7	268.8	271.6
167.5°	282.6	278.7	277.4	276.0	274.3	272.1	271.6	272.1	271.6	272.1	274.3
170°	282.0	279.3	278.5	277.6	276.5	274.9	274.3	274.9	274.3	274.9	276.5
172.5°	281.5	279.8	279.2	278.7	278.2	277.1	277.1	277.6	277.1	277.1	278.2
175°	280.9	279.8	279.8	279.8	279.3	278.7	278.7	279.3	278.7	278.7	279.3
177.5°	280.4	279.8	279.8	279.8	279.8	279.3	279.8	280.4	279.8	279.3	279.8
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1613.7	1611.0	1608.4	1597.8	1588.6	1572.7	1559.5	1554.2	1552.9	1554.2	1550.2
5°	1567.4	1566.1	1556.8	1538.3	1521.2	1502.7	1489.4	1476.2	1468.3	1468.3	1459.0
7.5°	1523.8	1514.6	1506.6	1482.8	1463.0	1437.9	1418.1	1406.2	1399.6	1385.0	1385.0
10°	1477.6	1464.3	1453.8	1431.3	1402.2	1377.1	1352.0	1337.5	1325.6	1315.0	1311.0
12.5°	1431.3	1420.7	1400.9	1377.1	1348.0	1316.3	1289.9	1279.3	1251.6	1229.1	1230.4
15°	1387.7	1363.9	1354.6	1320.3	1285.9	1255.5	1217.2	1186.8	1164.3	1149.8	1131.3
17.5°	1338.8	1315.0	1297.8	1268.7	1223.8	1176.2	1139.2	1098.3	1075.8	1050.7	1038.8
20°	1284.6	1264.8	1251.6	1205.3	1151.1	1094.3	1053.3	1028.2	1003.1	984.6	974.0
22.5°	1238.3	1213.2	1197.4	1135.3	1075.8	1019.0	987.2	966.1	944.9	929.1	923.8
25°	1178.9	1164.3	1126.0	1071.8	999.1	960.8	933.1	905.3	893.4	882.8	870.9
27.5°	1130.0	1094.3	1067.9	996.5	951.6	907.9	880.2	859.0	844.5	833.9	824.7
30°	1069.2	1036.1	999.1	939.7	898.7	857.7	832.6	815.4	799.6	793.0	785.0
32.5°	1005.7	975.3	939.7	892.1	841.9	810.1	790.3	771.8	761.2	754.6	745.4
35°	948.9	910.6	886.8	841.9	800.9	765.2	746.7	730.8	719.0	716.3	715.0
37.5°	888.1	859.0	836.6	790.3	756.0	725.6	708.4	691.2	684.6	683.3	678.0
40°	835.3	810.1	789.0	745.4	708.4	680.6	667.4	656.8	650.2	650.2	648.9
42.5°	789.0	762.6	741.4	701.8	668.7	643.6	629.1	618.5	615.9	617.2	615.9
45°	737.5	715.0	693.8	652.9	625.1	606.6	590.8	585.5	581.5	582.8	584.1
47.5°	688.6	670.1	648.9	615.9	584.1	564.3	555.1	549.8	549.8	549.8	552.4
50°	644.9	623.8	605.3	570.9	541.9	526.0	518.1	511.5	512.8	514.1	515.4
52.5°	593.4	574.9	561.7	527.3	506.2	486.3	477.1	478.4	477.1	477.1	479.7
55°	548.5	530.0	516.7	485.0	463.9	450.7	442.7	438.8	440.1	437.5	442.7
57.5°	498.2	482.4	473.1	442.7	424.2	412.3	405.7	399.1	401.8	400.4	399.1
60°	454.6	436.1	421.6	400.4	384.6	370.0	366.1	359.5	362.1	359.5	358.2
62.5°	404.4	389.9	379.3	358.2	344.9	333.0	323.8	319.8	318.5	314.5	310.6
65°	354.2	346.3	335.7	314.5	301.3	292.1	286.8	282.8	281.5	270.9	259.0
67.5°	307.9	302.6	292.1	276.2	264.3	255.1	247.1	240.5	232.6	224.7	218.1
70°	264.3	256.4	249.8	235.2	224.7	215.4	207.5	199.6	195.6	187.7	185.0
72.5°	222.0	214.1	207.5	194.3	185.0	175.8	173.1	163.9	159.9	158.6	158.6
75°	178.4	171.8	167.8	155.9	148.0	141.4	137.4	134.8	132.2	129.5	125.6
77.5°	136.1	132.2	129.5	121.6	115.0	111.0	109.7	100.4	97.8	95.2	92.5
80°	99.1	97.8	95.2	88.5	85.9	76.7	76.7	74.0	72.7	72.7	72.7
82.5°	67.4	64.8	63.4	56.8	55.5	54.2	52.9	51.5	52.9	51.5	52.9
85°	35.7	34.4	33.0	33.0	33.0	33.0	33.0	33.0	33.0	31.7	33.0
87.5°	13.2	13.2	13.2	13.2	11.9	13.2	13.2	11.9	13.2	13.2	13.2
90°	4.4	4.4	4.4	7.7	7.7	8.8	9.9	9.3	9.9	10.4	11.0
92.5°	35.2	42.4	49.5	83.6	136.9	188.6	215.5	179.2	132.5	98.9	78.1
95°	45.6	57.2	68.7	116.5	206.7	338.1	448.0	460.7	407.3	322.1	248.5
97.5°	53.3	63.2	73.1	111.0	188.6	323.8	479.4	577.8	586.5	544.2	483.8
100°	62.7	71.5	80.3	112.7	174.8	287.0	442.0	582.7	663.0	674.0	647.0
102.5°	73.1	81.4	89.6	118.2	171.0	262.2	395.2	541.5	659.1	724.5	741.0
105°	85.2	93.2	101.1	127.5	173.2	250.1	360.6	489.8	615.7	710.8	765.2
107.5°	97.3	105.2	113.2	137.4	179.8	246.8	338.1	447.5	562.4	665.2	741.0
110°	109.9	117.4	124.8	149.0	187.5	247.9	327.6	417.2	515.1	610.2	689.9

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	122.0	129.4	136.9	160.0	195.7	251.2	322.7	400.2	480.5	561.8	636.0
115°	134.7	142.1	149.5	171.5	204.5	255.6	321.6	390.8	459.6	527.2	591.5
117.5°	146.2	153.9	161.6	182.5	213.3	260.0	321.0	385.9	447.5	504.6	556.9
120°	157.8	165.5	173.2	194.1	222.6	265.0	321.0	382.1	439.8	490.9	534.9
122.5°	169.3	176.8	184.2	205.0	231.4	269.9	320.5	377.7	433.2	482.1	521.1
125°	179.8	187.4	195.1	214.9	240.2	274.9	319.9	372.7	425.5	472.8	510.7
127.5°	189.7	197.4	205.0	224.3	247.9	278.7	318.8	366.1	416.7	462.3	500.2
130°	199.0	207.0	214.9	233.6	255.1	283.1	318.3	360.1	405.7	449.1	486.5
132.5°	207.8	215.2	222.6	241.3	262.2	287.0	317.7	354.6	394.1	434.3	470.6
135°	216.0	223.2	230.3	248.5	268.3	290.8	317.2	349.1	383.7	419.4	453.0
137.5°	223.2	230.0	236.9	254.0	272.7	293.0	317.2	344.1	373.8	405.1	434.3
140°	229.8	236.4	243.0	259.5	277.1	295.7	316.6	340.3	365.6	391.4	416.1
142.5°	235.8	242.2	248.5	264.4	280.4	297.9	316.6	337.0	357.9	379.9	400.2
145°	241.3	247.4	253.4	267.7	282.6	298.5	315.5	333.1	350.7	369.4	385.9
147.5°	246.8	252.3	257.8	271.6	284.8	299.0	313.9	329.8	344.7	360.1	373.8
150°	251.8	257.0	262.2	274.3	286.4	299.0	312.2	326.0	339.2	351.8	362.8
152.5°	256.7	261.4	266.1	276.5	287.5	297.9	309.5	321.6	333.1	343.6	353.5
155°	261.1	265.2	269.4	278.7	288.1	296.8	306.7	317.2	327.1	335.9	344.1
157.5°	265.5	268.8	272.1	280.4	288.1	295.7	304.0	312.8	320.5	328.2	335.3
160°	268.8	271.8	274.9	281.5	288.1	294.1	300.7	307.8	314.4	320.5	326.5
162.5°	272.1	274.3	276.5	282.6	288.1	292.4	297.4	303.4	308.4	313.3	317.7
165°	274.3	276.0	277.6	282.6	287.0	290.3	294.1	298.5	302.9	306.2	310.0
167.5°	276.0	277.4	278.7	282.6	285.9	288.1	290.8	294.1	297.4	300.1	303.4
170°	277.6	278.5	279.3	282.0	284.8	285.9	287.5	289.7	292.4	294.1	296.3
172.5°	278.7	279.2	279.8	281.5	283.7	283.7	284.2	285.9	288.1	289.2	290.3
175°	279.8	279.8	279.8	280.9	282.6	282.0	282.0	283.1	284.2	284.8	285.9
177.5°	279.8	279.8	279.8	280.4	281.5	280.4	280.4	280.9	281.5	282.0	282.0
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1550.2	1555.5	1548.9	1552.9	1543.6	1542.3	1543.6	1543.6	1545.0	1546.3	1547.6
5°	1463.0	1461.7	1453.8	1448.5	1444.5	1448.5	1451.1	1453.8	1451.1	1453.8	1455.1
7.5°	1381.1	1377.1	1373.1	1363.9	1366.5	1363.9	1371.8	1367.9	1367.9	1374.5	1379.8
10°	1308.4	1300.5	1297.8	1287.2	1279.3	1278.0	1287.2	1291.2	1295.2	1297.8	1308.4
12.5°	1214.6	1202.7	1193.4	1197.4	1174.9	1184.2	1186.8	1181.5	1197.4	1215.9	1205.3
15°	1114.1	1115.4	1096.9	1090.3	1071.8	1077.1	1078.4	1091.6	1104.9	1103.5	1119.4
17.5°	1040.1	1032.2	1016.3	1015.0	1007.1	1011.0	1009.7	1020.3	1016.3	1022.9	1036.1
20°	971.4	966.1	952.9	947.6	950.2	947.6	948.9	950.2	954.2	968.7	966.1
22.5°	917.2	910.6	910.6	904.0	896.0	893.4	900.0	904.0	909.3	911.9	918.5
25°	869.6	864.3	857.7	853.8	847.1	848.5	852.4	857.7	861.7	867.0	872.3
27.5°	820.7	820.7	814.1	812.8	810.1	808.8	814.1	816.7	816.7	820.7	826.0
30°	782.4	782.4	775.8	774.5	773.1	773.1	777.1	778.4	779.7	783.7	786.4
32.5°	745.4	744.1	741.4	742.7	741.4	742.7	742.7	744.1	746.7	748.0	753.3
35°	711.0	712.3	709.7	709.7	708.4	709.7	712.3	713.7	715.0	717.6	717.6
37.5°	678.0	680.6	679.3	683.3	683.3	683.3	683.3	685.9	685.9	685.9	684.6
40°	648.9	648.9	647.6	650.2	652.9	652.9	654.2	654.2	655.5	655.5	654.2
42.5°	615.9	618.5	622.5	623.8	626.4	625.1	629.1	627.8	629.1	626.4	623.8
45°	585.5	585.5	590.8	596.0	597.4	597.4	597.4	600.0	597.4	593.4	592.1
47.5°	552.4	555.1	557.7	564.3	565.6	565.6	565.6	565.6	563.0	563.0	563.0
50°	519.4	520.7	522.0	524.7	528.6	527.3	527.3	527.3	532.6	527.3	528.6
52.5°	479.7	481.1	482.4	487.7	486.3	486.3	487.7	487.7	491.6	490.3	487.7
55°	440.1	440.1	442.7	442.7	442.7	445.4	446.7	449.3	448.0	449.3	450.7
57.5°	400.4	397.8	396.5	396.5	400.4	399.1	400.4	400.4	405.7	408.4	409.7
60°	354.2	354.2	352.9	344.9	344.9	343.6	347.6	350.2	352.9	364.8	363.4
62.5°	306.6	301.3	296.0	297.4	289.4	293.4	290.8	293.4	301.3	310.6	311.9
65°	259.0	255.1	249.8	248.5	245.8	249.8	248.5	249.8	253.7	259.0	265.6
67.5°	216.7	215.4	212.8	211.5	211.5	211.5	214.1	214.1	215.4	219.4	223.4
70°	185.0	183.7	185.0	182.4	183.7	182.4	183.7	185.0	186.3	187.7	191.6
72.5°	155.9	155.9	155.9	153.3	155.9	154.6	154.6	155.9	157.3	158.6	161.2
75°	124.2	121.6	118.9	116.3	115.0	117.6	118.9	117.6	121.6	126.9	126.9
77.5°	93.8	92.5	92.5	92.5	93.8	92.5	95.2	93.8	95.2	95.2	97.8
80°	72.7	71.4	72.7	72.7	71.4	74.0	72.7	72.7	74.0	75.3	74.0
82.5°	52.9	54.2	52.9	52.9	52.9	55.5	52.9	52.9	52.9	54.2	54.2
85°	33.0	33.0	33.0	33.0	34.4	33.0	34.4	33.0	35.7	34.4	34.4
87.5°	11.9	13.2	14.5	14.5	14.5	14.5	13.2	14.5	15.9	14.5	15.9
90°	11.0	11.0	11.5	12.1	11.5	11.5	11.5	12.1	11.5	11.0	11.0
92.5°	71.2	64.3	56.1	52.2	50.0	50.0	50.0	52.2	56.1	64.3	71.2
95°	221.8	195.1	168.2	151.2	141.3	134.1	141.3	151.2	168.2	195.1	221.8
97.5°	453.0	422.2	384.8	351.8	335.3	322.1	335.3	351.8	384.8	422.2	453.0
100°	626.6	606.3	558.5	525.0	508.5	504.1	508.5	525.0	558.5	606.3	626.6
102.5°	735.5	730.0	705.3	683.3	665.7	662.4	665.7	683.3	705.3	730.0	735.5
105°	776.4	787.7	788.8	784.4	776.8	773.5	776.8	784.4	788.8	787.7	776.4
107.5°	764.1	787.2	811.4	821.3	825.7	826.2	825.7	821.3	811.4	787.2	764.1
110°	720.2	750.4	789.4	812.5	822.4	827.3	822.4	812.5	789.4	750.4	720.2

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	666.2	696.5	742.1	771.3	786.1	794.9	786.1	771.3	742.1	696.5	666.2
115°	617.9	644.3	687.7	720.7	738.3	742.7	738.3	720.7	687.7	644.3	617.9
117.5°	580.0	603.0	641.5	670.1	688.8	691.5	688.8	670.1	641.5	603.0	580.0
120°	554.4	573.9	605.2	629.4	643.7	649.8	643.7	629.4	605.2	573.9	554.4
122.5°	537.6	554.1	579.4	599.2	610.7	616.8	610.7	599.2	579.4	554.1	537.6
125°	525.8	540.9	562.9	578.9	589.3	592.6	589.3	578.9	562.9	540.9	525.8
127.5°	514.5	528.8	550.8	565.1	573.9	577.2	573.9	565.1	550.8	528.8	514.5
130°	501.0	515.6	538.2	551.9	560.7	564.0	560.7	551.9	538.2	515.6	501.0
132.5°	485.2	499.7	521.7	537.6	545.9	549.2	545.9	537.6	521.7	499.7	485.2
135°	466.8	480.5	502.4	517.8	526.6	529.9	526.6	517.8	502.4	480.5	466.8
137.5°	447.0	459.6	480.5	496.4	503.5	507.4	503.5	496.4	480.5	459.6	447.0
140°	427.6	439.2	458.5	470.6	478.3	482.7	478.3	470.6	458.5	439.2	427.6
142.5°	409.8	419.4	435.9	446.9	453.5	456.3	453.5	446.9	435.9	419.4	409.8
145°	393.6	401.3	415.0	424.4	429.9	432.6	429.9	424.4	415.0	401.3	393.6
147.5°	380.2	386.5	396.9	405.1	409.5	410.6	409.5	405.1	396.9	386.5	380.2
150°	367.8	372.7	381.5	388.7	391.9	392.5	391.9	388.7	381.5	372.7	367.8
152.5°	357.4	361.2	368.3	373.8	375.5	376.0	375.5	373.8	368.3	361.2	357.4
155°	347.4	350.7	356.2	360.6	362.3	362.3	362.3	360.6	356.2	350.7	347.4
157.5°	338.0	340.8	345.2	348.5	349.6	349.6	349.6	348.5	345.2	340.8	338.0
160°	328.7	330.9	334.2	337.5	338.1	338.1	338.1	337.5	334.2	330.9	328.7
162.5°	319.6	321.6	323.8	327.1	327.6	327.1	327.6	327.1	323.8	321.6	319.6
165°	311.4	312.8	315.0	317.2	316.6	316.1	316.6	317.2	315.0	312.8	311.4
167.5°	304.2	305.1	306.2	307.8	307.8	307.3	307.8	307.8	306.2	305.1	304.2
170°	297.1	297.9	299.0	299.6	299.0	299.0	299.0	299.6	299.0	297.9	297.1
172.5°	290.8	291.4	291.9	292.4	291.9	290.8	291.9	292.4	291.9	291.4	290.8
175°	285.9	285.9	285.9	287.0	285.9	284.8	285.9	287.0	285.9	285.9	285.9
177.5°	282.3	282.6	282.0	282.6	281.5	280.4	281.5	282.6	282.0	282.6	282.3
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1552.9	1559.5	1556.8	1547.6	1551.6	1559.5	1567.4	1578.0	1584.6	1589.9	1592.5
5°	1461.7	1473.6	1470.9	1470.9	1476.2	1489.4	1502.7	1525.1	1533.1	1542.3	1555.5
7.5°	1381.1	1390.3	1398.3	1400.9	1408.8	1426.0	1443.2	1468.3	1488.1	1498.7	1506.6
10°	1309.7	1316.3	1328.2	1334.8	1342.7	1363.9	1389.0	1415.4	1435.3	1453.8	1464.3
12.5°	1218.5	1244.9	1260.8	1271.4	1282.0	1313.7	1333.5	1362.6	1386.4	1403.5	1419.4
15°	1116.8	1148.5	1157.7	1198.7	1225.1	1250.2	1280.6	1315.0	1337.5	1357.3	1378.4
17.5°	1030.8	1053.3	1063.9	1107.5	1130.0	1169.6	1213.2	1256.8	1291.2	1305.7	1326.9
20°	976.7	988.6	1009.7	1024.2	1048.0	1094.3	1141.9	1194.7	1246.3	1260.8	1282.0
22.5°	921.2	937.0	951.6	971.4	989.9	1021.6	1069.2	1127.3	1182.8	1209.3	1234.4
25°	870.9	886.8	896.0	917.2	934.4	966.1	999.1	1058.6	1124.7	1147.2	1186.8
27.5°	831.3	840.5	856.4	865.6	885.5	914.5	944.9	989.9	1054.6	1093.0	1131.3
30°	791.6	798.2	811.5	824.7	839.2	859.0	893.4	937.0	996.5	1029.5	1067.9
32.5°	752.0	762.6	770.5	779.7	795.6	819.4	843.2	885.5	933.1	970.1	1008.4
35°	719.0	722.9	733.5	744.1	754.6	775.8	800.9	841.9	884.2	913.2	947.6
37.5°	683.3	689.9	697.8	701.8	719.0	732.2	758.6	790.3	840.5	859.0	893.4
40°	655.5	654.2	662.1	668.7	676.7	697.8	713.7	748.0	787.7	816.7	837.9
42.5°	621.2	621.2	623.8	631.7	642.3	655.5	674.0	703.1	744.1	765.2	790.3
45°	593.4	589.4	590.8	596.0	602.7	615.9	634.4	659.5	700.4	717.6	744.1
47.5°	560.4	556.4	556.4	561.7	567.0	576.2	590.8	619.8	652.9	675.3	695.2
50°	523.4	524.7	523.4	527.3	530.0	539.2	555.1	578.9	609.3	627.8	650.2
52.5°	489.0	486.3	485.0	487.7	493.0	499.6	516.7	537.9	567.0	585.5	605.3
55°	446.7	449.3	449.3	449.3	457.3	459.9	473.1	494.3	523.4	537.9	556.4
57.5°	408.4	407.1	409.7	408.4	415.0	424.2	434.8	450.7	479.7	494.3	511.5
60°	366.1	367.4	368.7	368.7	374.0	383.3	395.2	409.7	433.5	448.0	463.9
62.5°	314.5	321.1	327.8	330.4	338.3	344.9	352.9	368.7	389.9	400.4	415.0
65°	265.6	274.9	284.1	290.8	296.0	302.6	313.2	327.8	344.9	355.5	370.0
67.5°	223.4	230.0	241.9	248.5	259.0	267.0	273.6	285.5	306.6	310.6	322.5
70°	193.0	195.6	200.9	206.2	218.1	224.7	232.6	244.5	260.4	269.6	276.2
72.5°	162.6	163.9	166.5	171.8	177.1	185.0	194.3	204.8	219.4	223.4	232.6
75°	129.5	137.4	137.4	141.4	145.4	149.3	157.3	167.8	177.1	183.7	189.0
77.5°	96.5	100.4	103.1	109.7	115.0	118.9	124.2	132.2	137.4	142.7	146.7
80°	75.3	76.7	78.0	78.0	80.6	85.9	91.2	96.5	103.1	105.7	109.7
82.5°	55.5	55.5	55.5	58.2	59.5	60.8	60.8	63.4	70.0	72.7	76.7
85°	35.7	35.7	35.7	35.7	37.0	38.3	39.6	41.0	41.0	41.0	43.6
87.5°	14.5	17.2	15.9	17.2	17.2	17.2	17.2	18.5	18.5	19.8	19.8
90°	11.0	10.4	9.9	9.3	9.9	8.8	7.7	7.7	4.4	4.4	4.4
92.5°	78.1	98.9	132.5	179.2	215.5	188.6	136.9	83.6	49.5	42.4	35.2
95°	248.5	322.1	407.3	460.7	448.0	338.1	206.7	116.5	68.7	57.2	45.6
97.5°	483.8	544.2	586.5	577.8	479.4	323.8	188.6	111.0	73.1	63.2	53.3
100°	647.0	674.0	663.0	582.7	442.0	287.0	174.8	112.7	80.3	71.5	62.7
102.5°	741.0	724.5	659.1	541.5	395.2	262.2	171.0	118.2	89.6	81.4	73.1
105°	765.2	710.8	615.7	489.8	360.6	250.1	173.2	127.5	101.1	93.2	85.2
107.5°	741.0	665.2	562.4	447.5	338.1	246.8	179.8	137.4	113.2	105.2	97.3
110°	689.9	610.2	515.1	417.2	327.6	247.9	187.5	149.0	124.8	117.4	109.9

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	636.0	561.8	480.5	400.2	322.7	251.2	195.7	160.0	136.9	129.4	122.0
115°	591.5	527.2	459.6	390.8	321.6	255.6	204.5	171.5	149.5	142.1	134.7
117.5°	556.9	504.6	447.5	385.9	321.0	260.0	213.3	182.5	161.6	153.9	146.2
120°	534.9	490.9	439.8	382.1	321.0	265.0	222.6	194.1	173.2	165.5	157.8
122.5°	521.1	482.1	433.2	377.7	320.5	269.9	231.4	205.0	184.2	176.8	169.3
125°	510.7	472.8	425.5	372.7	319.9	274.9	240.2	214.9	195.1	187.4	179.8
127.5°	500.2	462.3	416.7	366.1	318.8	278.7	247.9	224.3	205.0	197.4	189.7
130°	486.5	449.1	405.7	360.1	318.3	283.1	255.1	233.6	214.9	207.0	199.0
132.5°	470.6	434.3	394.1	354.6	317.7	287.0	262.2	241.3	222.6	215.2	207.8
135°	453.0	419.4	383.7	349.1	317.2	290.8	268.3	248.5	230.3	223.2	216.0
137.5°	434.3	405.1	373.8	344.1	317.2	293.0	272.7	254.0	236.9	230.0	223.2
140°	416.1	391.4	365.6	340.3	316.6	295.7	277.1	259.5	243.0	236.4	229.8
142.5°	400.2	379.9	357.9	337.0	316.6	297.9	280.4	264.4	248.5	242.2	235.8
145°	385.9	369.4	350.7	333.1	315.5	298.5	282.6	267.7	253.4	247.4	241.3
147.5°	373.8	360.1	344.7	329.8	313.9	299.0	284.8	271.6	257.8	252.3	246.8
150°	362.8	351.8	339.2	326.0	312.2	299.0	286.4	274.3	262.2	257.0	251.8
152.5°	353.5	343.6	333.1	321.6	309.5	297.9	287.5	276.5	266.1	261.4	256.7
155°	344.1	335.9	327.1	317.2	306.7	296.8	288.1	278.7	269.4	265.2	261.1
157.5°	335.3	328.2	320.5	312.8	304.0	295.7	288.1	280.4	272.1	268.8	265.5
160°	326.5	320.5	314.4	307.8	300.7	294.1	288.1	281.5	274.9	271.8	268.8
162.5°	317.7	313.3	308.4	303.4	297.4	292.4	288.1	282.6	276.5	274.3	272.1
165°	310.0	306.2	302.9	298.5	294.1	290.3	287.0	282.6	277.6	276.0	274.3
167.5°	303.4	300.1	297.4	294.1	290.8	288.1	285.9	282.6	278.7	277.4	276.0
170°	296.3	294.1	292.4	289.7	287.5	285.9	284.8	282.0	279.3	278.5	277.6
172.5°	290.3	289.2	288.1	285.9	284.2	283.7	283.7	281.5	279.8	279.2	278.7
175°	285.9	284.8	284.2	283.1	282.0	282.0	282.6	280.9	279.8	279.8	279.8
177.5°	282.0	282.0	281.5	280.9	280.4	280.4	281.5	280.4	279.8	279.8	279.8
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1640.1	1640.1	1640.1	1640.1
2.5°	1603.1	1611.0	1624.2	1642.8
5°	1566.1	1588.6	1609.7	1637.5
7.5°	1533.1	1559.5	1588.6	1628.2
10°	1494.7	1527.8	1564.8	1613.7
12.5°	1449.8	1496.1	1538.3	1591.2
15°	1416.8	1451.1	1505.3	1567.4
17.5°	1370.5	1416.8	1470.9	1541.0
20°	1326.9	1375.8	1436.6	1509.3
22.5°	1280.6	1336.1	1396.9	1474.9
25°	1233.1	1292.5	1353.3	1436.6
27.5°	1189.4	1243.6	1312.4	1396.9
30°	1136.6	1198.7	1264.8	1353.3
32.5°	1085.0	1149.8	1217.2	1305.7
35°	1029.5	1094.3	1168.3	1252.9
37.5°	975.3	1046.7	1114.1	1196.0
40°	915.9	989.9	1059.9	1143.2
42.5°	857.7	934.4	1004.4	1075.8
45°	803.5	878.9	942.3	1009.7
47.5°	752.0	819.4	884.2	944.9
50°	701.8	758.6	818.1	868.3
52.5°	648.9	703.1	750.7	795.6
55°	601.3	643.6	685.9	726.9
57.5°	544.5	586.8	623.8	655.5
60°	496.9	523.4	559.0	592.1
62.5°	442.7	473.1	500.9	522.0
65°	389.9	416.3	437.5	456.0
67.5°	344.9	360.8	376.7	396.5
70°	290.8	304.0	322.5	337.0
72.5°	244.5	255.1	264.3	281.5
75°	198.2	207.5	212.8	228.6
77.5°	153.3	162.6	166.5	175.8
80°	117.6	118.9	124.2	132.2
82.5°	80.6	83.3	84.6	91.2
85°	46.3	52.9	51.5	54.2
87.5°	19.8	21.1	23.8	26.4
90°	3.8	3.3	1.6	0.5
92.5°	25.3	17.0	11.0	7.7
95°	32.4	25.3	19.8	18.1
97.5°	41.8	35.2	30.2	30.2
100°	52.2	45.6	41.8	41.8
102.5°	63.2	57.2	53.9	52.8
105°	75.3	68.7	66.0	64.3
107.5°	88.0	80.8	78.1	77.0
110°	100.0	93.5	90.7	89.6

TEST NUMBER: P1026045

CATALOG NUMBER: S124RDIP-B1020D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	112.1	106.1	102.8	101.7
115°	124.2	118.7	114.9	113.2
117.5°	136.3	130.3	127.0	125.3
120°	148.4	142.4	138.5	137.4
122.5°	158.9	153.4	149.5	148.4
125°	169.3	163.3	160.0	157.8
127.5°	178.7	172.1	168.2	166.6
130°	188.6	180.3	175.9	173.7
132.5°	196.2	188.6	182.5	180.9
135°	204.5	195.1	189.7	187.5
137.5°	211.1	202.3	196.2	194.1
140°	218.2	208.9	202.8	201.2
142.5°	224.8	216.0	210.5	208.9
145°	230.9	223.2	217.7	216.0
147.5°	238.0	229.8	224.8	224.3
150°	243.5	236.9	232.5	232.0
152.5°	249.6	243.5	239.1	239.1
155°	255.1	249.6	246.3	245.7
157.5°	260.0	255.6	252.3	252.3
160°	264.4	260.6	258.4	258.4
162.5°	268.3	265.0	263.3	263.9
165°	271.6	268.8	267.7	267.7
167.5°	274.3	272.1	271.6	272.1
170°	276.5	274.9	274.3	274.9
172.5°	278.2	277.1	277.1	277.6
175°	279.3	278.7	278.7	279.3
177.5°	279.8	279.3	279.8	280.4
180°	279.8	279.8	279.8	279.8

(END OF REPORT)