

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026617

Luminaire Tested: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026617
REPORT IS A COMBINATION OF REPORTS P999737 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB50-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4330.0 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026617

CATALOG NUMBER: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026617

CATALOG NUMBER: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36
6	67	55	47	41	64	53	45	40	48	42	37	44	38	35	40	35	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1026617

CATALOG NUMBER: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.9
10°-20°	352.1	8.1
20°-30°	508.3	11.7
30°-40°	576.1	13.3
40°-50°	556.3	12.8
50°-60°	462.5	10.7
60°-70°	319.2	7.4
70°-80°	161.3	3.7
80°-90°	41.9	1.0
90°-100°	28.8	0.7
100°-110°	86.3	2.0
110°-120°	146.5	3.4
120°-130°	193.3	4.5
130°-140°	217.1	5.0
140°-150°	213.4	4.9
150°-160°	179.5	4.1
160°-170°	119.4	2.8
170°-180°	41.8	1.0
0°-30°	986.7	22.8
0°-40°	1562.8	36.1
0°-60°	2581.6	59.6
0°-90°	3103.9	71.7
90°-120°	261.6	6.0
90°-150°	885.4	20.4
90°-180°	1226.0	28.3
0°-180°	4330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	1	5	8	10	10	5
95°	20	24	26	27	27	22
105°	80	80	81	82	83	84
115°	149	149	148	148	148	147
125°	217	217	217	216	215	193
135°	280	282	282	281	280	217
145°	340	341	342	341	340	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1026617

CATALOG NUMBER: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	1.0	4.8	7.5	9.6	10.3
92.5°	8.9	13.3	15.0	16.1	16.4
95°	20.5	23.6	26.0	27.0	27.0
97.5°	32.8	35.5	38.3	39.6	39.6
100°	47.8	49.2	52.3	53.0	53.0
102.5°	63.6	63.9	66.6	67.7	68.0
105°	79.6	80.0	81.3	82.4	83.4
107.5°	96.4	96.7	97.1	98.4	98.1
110°	113.5	114.1	113.8	113.1	114.1



TEST NUMBER: P1026617

CATALOG NUMBER: S124RDIP-B795D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.2	131.2	130.5	130.5	130.5
115°	149.0	149.0	148.3	148.0	147.6
117.5°	165.7	165.7	165.4	164.4	163.4
120°	182.5	183.9	182.8	181.1	181.8
122.5°	199.9	200.3	199.9	198.9	197.2
125°	217.0	217.0	216.7	216.0	215.3
127.5°	232.4	233.4	232.7	232.0	231.7
130°	248.8	249.8	249.8	249.1	247.8
132.5°	265.5	266.2	265.9	265.2	264.9
135°	279.9	281.9	281.9	281.3	280.2
137.5°	296.0	297.0	297.7	296.6	297.0
140°	312.0	312.7	312.7	312.4	312.0
142.5°	326.7	327.4	327.1	327.1	327.1
145°	340.0	341.4	341.7	341.4	340.4
147.5°	353.7	355.4	355.1	354.7	354.4
150°	366.0	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)