

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026636

Luminaire Tested: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026636
REPORT IS A COMBINATION OF REPORTS P999766 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D590UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5374.3 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026636

CATALOG NUMBER: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026636

CATALOG NUMBER: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	28	25
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1026636

CATALOG NUMBER: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	2.5
10°-20°	367.8	6.8
20°-30°	530.9	9.9
30°-40°	601.7	11.2
40°-50°	581.0	10.8
50°-60°	483.0	9.0
60°-70°	333.4	6.2
70°-80°	168.5	3.1
80°-90°	43.9	0.8
90°-100°	217.0	4.0
100°-110°	441.4	8.2
110°-120°	393.4	7.3
120°-130°	330.5	6.1
130°-140°	275.8	5.1
140°-150°	210.6	3.9
150°-160°	148.0	2.8
160°-170°	87.1	1.6
170°-180°	28.3	0.5
0°-30°	1030.6	19.2
0°-40°	1632.3	30.4
0°-60°	2696.4	50.2
0°-90°	3242.1	60.3
90°-120°	1051.9	19.6
90°-150°	1868.7	34.8
90°-180°	2132.0	39.7
0°-180°	5374.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	1	5	10	12	12	5
95°	19	60	468	232	140	21
105°	67	97	376	811	808	72
115°	118	148	336	645	775	117
125°	165	196	334	549	619	147
135°	196	233	331	487	553	151
145°	226	258	330	411	452	142
155°	257	277	320	363	378	118
165°	280	288	307	325	330	79
175°	292	292	294	298	297	28
180°	292	292	292	292	292	

TEST NUMBER: P1026636

CATALOG NUMBER: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	0.6	4.6	10.3	11.5	12.1
92.5°	8.0	44.2	225.0	74.4	52.2
95°	18.9	59.6	467.8	231.6	140.1
97.5°	31.6	66.0	500.5	473.0	336.4
100°	43.6	74.6	461.5	654.4	526.3
102.5°	55.1	84.9	412.7	768.0	691.6
105°	67.2	97.3	376.5	810.8	807.6
107.5°	80.4	109.9	353.0	797.8	862.7
110°	93.6	122.6	342.1	751.9	863.8

TEST NUMBER: P1026636

CATALOG NUMBER: S124RDIP-B795D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.2	135.2	336.9	695.7	830.0
115°	118.2	148.4	335.8	645.2	775.4
117.5°	130.9	160.8	335.2	605.6	722.1
120°	143.5	172.8	335.2	578.8	678.4
122.5°	155.0	184.6	334.6	561.4	644.0
125°	164.7	195.8	334.1	549.0	618.8
127.5°	173.9	206.0	332.9	537.2	602.7
130°	181.4	216.1	332.3	523.2	588.9
132.5°	188.8	224.8	331.8	506.5	573.4
135°	195.7	233.0	331.2	487.4	553.3
137.5°	202.6	240.2	331.2	466.6	529.8
140°	210.1	246.8	330.6	446.6	504.0
142.5°	218.1	252.8	330.6	427.9	476.4
145°	225.6	258.3	329.5	411.0	451.7
147.5°	234.2	263.4	327.7	396.9	428.8
150°	242.2	268.4	326.0	384.0	409.8
152.5°	249.7	272.9	323.2	373.1	392.6
155°	256.6	277.0	320.3	362.8	378.3
157.5°	263.5	280.6	317.4	353.0	365.1
160°	269.8	283.8	314.0	343.2	353.0
162.5°	275.5	286.4	310.5	333.8	341.5
165°	279.5	288.2	307.1	325.2	330.0
167.5°	284.1	289.6	303.6	317.7	320.9
170°	287.0	290.8	300.2	310.2	312.2
172.5°	289.9	291.6	296.7	303.6	303.6
175°	291.6	292.2	294.5	298.5	297.3
177.5°	292.7	292.2	292.7	294.8	292.7
180°	292.2	292.2	292.2	292.2	292.2

(END OF REPORT)