

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026080

Luminaire Tested: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026080
REPORT IS A COMBINATION OF REPORTS P999020 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8494.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	27	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16055	16055	16055	16055
5°	16055	18141	16081	13866
10°	15969	20913	15956	12058
15°	15779	23536	15779	10096
20°	15581	25519	15499	8890
25°	15337	25627	15267	8029
30°	15080	21792	14962	7438
35°	14714	16443	14529	6996
40°	14308	11916	14026	6651
45°	13637	9056	13297	6347
50°	12840	7319	12489	5900
55°	11978	6061	11585	5305
60°	11111	5124	10614	4412
65°	10023	4175	9704	3506
70°	9027	3385	8600	2848
75°	7910	2440	7360	2088
80°	6523	1617	5939	1534
85°	4730	832	3922	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20099 cd/sqm

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.6	2.2
10°-20°	575.7	6.8
20°-30°	901.8	10.6
30°-40°	1001.4	11.8
40°-50°	887.4	10.4
50°-60°	691.6	8.1
60°-70°	452.4	5.3
70°-80°	222.0	2.6
80°-90°	56.8	0.7
90°-100°	82.6	1.0
100°-110°	247.3	2.9
110°-120°	420.1	4.9
120°-130°	554.0	6.5
130°-140°	622.3	7.3
140°-150°	611.6	7.2
150°-160°	514.4	6.1
160°-170°	342.3	4.0
170°-180°	119.8	1.4
0°-30°	1668.2	19.6
0°-40°	2669.6	31.4
0°-60°	4248.6	50.0
0°-90°	4979.7	58.6
90°-120°	749.9	8.8
90°-150°	2537.8	29.9
90°-180°	3514.0	41.4
0°-180°	8494.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1969	1969	1969	1969	1969	
5°	1966	2275	1969	1739	1966	187
15°	1882	3014	1882	1293	1882	531
25°	1724	3251	1717	1018	1724	795
35°	1504	2002	1485	852	1504	940
45°	1212	1023	1182	717	1212	935
55°	873	611	844	535	873	780
65°	547	357	530	300	547	546
75°	274	165	255	141	274	291
85°	65	40	54	40	65	73
90°	3	29	3	29	3	9
95°	59	77	59	77	59	64
105°	228	239	228	239	228	242
115°	427	423	427	423	427	421
125°	622	617	622	617	622	554
135°	802	803	802	803	802	621
145°	975	976	975	976	975	610
155°	1117	1116	1117	1116	1117	514
165°	1216	1213	1216	1213	1216	343
175°	1265	1259	1265	1259	1265	120
180°	1267	1267	1267	1267	1267	

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1972.0	1989.5	1999.0	2006.9	2022.8	2029.1	2041.8	2045.0	2057.7	2056.1	2051.3
5°	1965.7	1995.8	2018.0	2041.8	2070.4	2086.2	2103.7	2129.1	2141.8	2159.2	2170.3
7.5°	1954.6	1995.8	2032.3	2068.8	2114.8	2140.2	2162.4	2202.1	2235.4	2263.9	2295.7
10°	1937.1	1989.5	2043.4	2092.6	2156.0	2186.2	2219.5	2278.2	2324.2	2363.9	2414.6
12.5°	1910.1	1983.1	2043.4	2110.0	2191.0	2232.2	2276.6	2346.4	2400.4	2465.4	2528.9
15°	1881.6	1962.5	2041.8	2129.1	2221.1	2268.7	2313.1	2406.7	2489.2	2563.8	2633.6
17.5°	1849.9	1938.7	2026.0	2122.7	2233.8	2292.5	2344.8	2457.5	2547.9	2644.7	2714.5
20°	1811.8	1908.6	2008.5	2116.4	2241.7	2306.8	2365.5	2494.0	2593.9	2698.6	2785.9
22.5°	1770.5	1875.2	1984.7	2102.1	2232.2	2303.6	2371.8	2509.8	2625.7	2722.4	2839.8
25°	1724.5	1835.6	1948.2	2072.0	2217.9	2295.7	2365.5	2501.9	2625.7	2752.6	2866.8
27.5°	1676.9	1791.2	1908.6	2038.6	2187.8	2263.9	2343.3	2474.9	2619.3	2757.3	2873.1
30°	1624.6	1735.6	1859.4	1983.1	2141.8	2217.9	2298.8	2441.6	2598.7	2736.7	2862.0
32.5°	1567.5	1681.7	1799.1	1927.6	2083.1	2165.6	2240.1	2402.0	2562.2	2698.6	2816.0
35°	1504.0	1611.9	1722.9	1854.6	2008.5	2083.1	2171.9	2340.1	2501.9	2646.3	2722.4
37.5°	1435.8	1538.9	1642.0	1772.1	1919.7	2010.1	2097.3	2267.1	2438.4	2535.2	2574.9
40°	1372.3	1462.7	1553.2	1678.5	1827.6	1921.2	2010.1	2186.2	2336.9	2411.5	2381.3
42.5°	1291.4	1385.0	1465.9	1581.7	1732.5	1819.7	1910.1	2092.6	2214.7	2244.9	2170.3
45°	1212.1	1289.8	1367.6	1480.2	1638.9	1713.4	1810.2	1979.9	2081.5	2054.5	1945.0
47.5°	1134.3	1197.8	1270.8	1380.3	1523.0	1611.9	1702.3	1849.9	1921.2	1883.2	1730.9
50°	1042.3	1105.8	1181.9	1277.1	1415.2	1500.8	1572.2	1708.7	1762.6	1669.0	1485.0
52.5°	955.1	1010.6	1075.6	1164.5	1296.2	1373.9	1451.6	1569.0	1586.5	1478.6	1285.1
55°	872.6	917.0	985.2	1056.6	1177.2	1259.7	1313.6	1413.6	1408.8	1274.0	1107.4
57.5°	786.9	828.2	874.2	948.7	1063.0	1124.8	1183.5	1270.8	1224.8	1110.5	945.6
60°	710.8	734.5	780.6	851.9	948.7	1002.7	1048.7	1096.3	1056.6	932.9	805.9
62.5°	626.7	653.6	687.0	744.1	829.7	880.5	913.8	934.4	893.2	798.0	682.2
65°	547.3	571.1	606.0	656.8	721.9	759.9	777.4	791.7	769.5	661.6	569.6
67.5°	475.9	491.8	523.5	556.9	626.7	636.2	660.0	666.3	621.9	539.4	466.4
70°	404.6	420.4	434.7	474.4	506.1	523.5	528.3	528.3	483.9	429.9	369.7
72.5°	337.9	347.4	361.7	388.7	406.1	418.8	425.2	417.2	376.0	331.6	287.2
75°	274.5	279.2	291.9	309.4	323.6	318.9	317.3	307.8	277.6	245.9	220.5
77.5°	211.0	214.2	228.5	233.2	233.2	238.0	231.6	222.1	196.7	172.9	161.8
80°	158.6	163.4	165.0	168.2	165.0	165.0	160.2	144.4	131.7	120.6	112.6
82.5°	109.5	112.6	114.2	109.5	112.6	107.9	99.9	88.8	80.9	79.3	76.2
85°	65.0	66.6	65.0	65.0	60.3	58.7	52.4	50.8	47.6	47.6	46.0
87.5°	31.7	30.1	27.0	23.8	23.8	22.2	23.8	20.6	23.8	22.2	20.6
90°	2.9	5.3	7.7	10.1	12.5	13.7	14.6	16.3	18.1	19.8	21.6
92.5°	25.5	28.3	31.1	34.0	36.8	38.2	38.7	39.8	40.9	42.0	43.1
95°	58.8	60.8	62.7	64.7	66.6	67.6	68.4	69.9	71.4	72.9	74.4
97.5°	94.0	95.8	97.5	99.3	101.0	101.9	102.8	104.5	106.2	108.0	109.7
100°	137.1	138.0	138.9	139.8	140.7	141.1	142.1	144.0	146.0	147.9	149.9
102.5°	182.2	182.4	182.6	182.9	183.1	183.2	184.1	185.8	187.5	189.3	191.0
105°	228.2	228.4	228.6	228.9	229.1	229.2	229.6	230.5	231.4	232.2	233.1
107.5°	276.2	276.4	276.6	276.9	277.1	277.2	277.3	277.5	277.8	278.0	278.2
110°	325.2	325.6	326.1	326.5	327.0	327.2	327.1	326.9	326.6	326.4	326.2

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	376.2	376.2	376.2	376.2	376.2	376.2	376.0	375.5	375.1	374.6	374.2
115°	427.1	427.1	427.1	427.1	427.1	427.1	426.9	426.4	426.0	425.5	425.1
117.5°	475.1	475.1	475.1	475.1	475.1	475.1	475.0	474.8	474.5	474.3	474.1
120°	523.1	524.0	524.8	525.7	526.6	527.0	526.7	526.0	525.4	524.7	524.1
122.5°	573.0	573.2	573.4	573.7	573.9	574.0	573.9	573.7	573.4	573.2	573.0
125°	622.0	622.0	622.0	622.0	622.0	622.0	621.9	621.7	621.4	621.2	621.0
127.5°	666.1	666.7	667.4	668.0	668.7	669.0	668.8	668.4	667.9	667.5	667.1
130°	713.1	713.8	714.4	715.1	715.8	716.1	716.1	716.1	716.1	716.1	716.1
132.5°	761.1	761.5	762.0	762.4	762.9	763.1	763.0	762.8	762.5	762.3	762.1
135°	802.3	803.6	804.9	806.2	807.5	808.1	808.1	808.1	808.1	808.1	808.1
137.5°	848.3	848.9	849.6	850.2	850.9	851.2	851.4	851.9	852.3	852.8	853.2
140°	894.3	894.7	895.2	895.6	896.1	896.3	896.3	896.3	896.3	896.3	896.3
142.5°	936.5	936.9	937.3	937.8	938.2	938.4	938.3	938.1	937.8	937.6	937.4
145°	974.7	975.6	976.4	977.3	978.2	978.6	978.7	978.9	979.2	979.4	979.6
147.5°	1013.9	1015.0	1016.0	1017.1	1018.2	1018.7	1018.6	1018.4	1018.2	1018.0	1017.8
150°	1049.1	1050.0	1050.8	1051.7	1052.6	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
152.5°	1082.4	1082.8	1083.3	1083.7	1084.2	1084.4	1084.5	1084.7	1085.0	1085.2	1085.4
155°	1116.7	1116.7	1116.7	1116.7	1116.7	1116.7	1116.6	1116.4	1116.1	1115.9	1115.7
157.5°	1146.1	1145.7	1145.2	1144.8	1144.3	1144.1	1144.1	1144.1	1144.1	1144.1	1144.1
160°	1171.6	1171.4	1171.2	1170.9	1170.7	1170.6	1170.5	1170.3	1170.0	1169.8	1169.6
162.5°	1195.1	1194.4	1193.8	1193.1	1192.4	1192.1	1192.0	1191.8	1191.6	1191.4	1191.2
165°	1215.6	1215.0	1214.3	1213.7	1213.0	1212.7	1212.5	1212.0	1211.6	1211.1	1210.7
167.5°	1232.3	1231.4	1230.6	1229.7	1228.8	1228.4	1228.4	1228.4	1228.4	1228.4	1228.4
170°	1246.0	1244.9	1243.8	1242.7	1241.6	1241.1	1241.2	1241.4	1241.7	1241.9	1242.1
172.5°	1255.8	1254.9	1254.1	1253.2	1252.3	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9
175°	1264.6	1263.5	1262.4	1261.3	1260.2	1259.7	1259.6	1259.4	1259.1	1258.9	1258.7
177.5°	1268.5	1267.4	1266.3	1265.2	1264.1	1263.6	1263.6	1263.6	1263.6	1263.6	1263.6
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2064.0	2081.5	2083.1	2098.9	2094.2	2086.2	2100.5	2091.0	2110.0	2103.7	2111.6
5°	2184.6	2208.4	2229.0	2241.7	2263.9	2259.2	2283.0	2275.0	2292.5	2275.0	2297.2
7.5°	2325.8	2365.5	2386.1	2419.4	2428.9	2430.5	2459.1	2465.4	2476.5	2465.4	2478.1
10°	2463.8	2511.4	2559.0	2586.0	2603.4	2627.2	2652.6	2663.7	2671.7	2660.6	2668.5
12.5°	2589.2	2663.7	2716.1	2770.0	2782.7	2803.3	2830.3	2827.1	2858.9	2852.5	2866.8
15°	2705.0	2787.5	2850.9	2893.8	2928.7	2946.1	2996.9	3000.1	2998.5	3014.3	3004.8
17.5°	2808.1	2877.9	2968.3	3023.9	3066.7	3066.7	3095.3	3154.0	3149.2	3147.6	3157.1
20°	2892.2	2971.5	3055.6	3149.2	3184.1	3190.4	3230.1	3260.2	3265.0	3265.0	3265.0
22.5°	2955.6	3049.2	3139.7	3206.3	3233.3	3255.5	3290.4	3309.4	3315.8	3312.6	3315.8
25°	2987.4	3076.2	3168.2	3228.5	3244.4	3257.1	3260.2	3271.4	3269.8	3250.7	3261.8
27.5°	2993.7	3079.4	3139.7	3155.5	3147.6	3139.7	3088.9	3093.7	3079.4	3050.8	3061.9
30°	2965.2	3011.2	3009.6	2960.4	2946.1	2912.8	2866.8	2798.6	2743.1	2719.3	2727.2
32.5°	2862.0	2862.0	2804.9	2693.9	2644.7	2584.4	2501.9	2440.0	2367.1	2351.2	2381.3
35°	2719.3	2638.3	2533.6	2387.7	2313.1	2268.7	2125.9	2081.5	2019.6	2002.2	2016.4
37.5°	2497.1	2362.3	2210.0	2073.6	2010.1	1930.8	1805.4	1742.0	1697.6	1667.4	1681.7
40°	2248.1	2084.7	1926.0	1757.8	1688.0	1623.0	1529.4	1472.3	1400.9	1404.0	1408.8
42.5°	2010.1	1818.1	1640.4	1485.0	1418.3	1364.4	1299.3	1229.5	1204.2	1196.2	1188.3
45°	1757.8	1553.2	1386.6	1270.8	1210.5	1159.7	1099.4	1059.8	1029.6	1023.3	1031.2
47.5°	1519.9	1346.9	1188.3	1080.4	1031.2	1005.8	958.2	921.8	902.7	886.9	896.4
50°	1304.1	1142.3	1015.4	924.9	890.0	872.6	828.2	809.1	790.1	785.3	783.7
52.5°	1126.4	988.4	878.9	805.9	779.0	769.5	736.1	709.2	693.3	698.1	701.2
55°	964.6	847.2	761.5	702.8	680.6	669.5	645.7	626.7	615.6	610.8	614.0
57.5°	821.8	720.3	658.4	610.8	593.3	588.6	563.2	556.9	548.9	544.2	544.2
60°	691.7	620.3	563.2	536.2	517.2	512.4	493.4	485.5	483.9	479.1	475.9
62.5°	582.2	523.5	483.9	455.3	447.4	445.8	433.1	423.6	418.8	415.7	415.7
65°	487.1	444.2	410.9	390.3	383.9	380.8	366.5	363.3	360.1	357.0	355.4
67.5°	406.1	368.1	344.3	330.0	322.1	323.6	315.7	309.4	309.4	307.8	306.2
70°	328.4	304.6	284.0	276.1	272.9	269.7	266.5	261.8	260.2	260.2	260.2
72.5°	258.6	242.7	231.6	226.9	223.7	220.5	217.3	217.3	217.3	215.8	215.8
75°	198.3	192.0	184.0	179.3	179.3	182.4	177.7	172.9	168.2	165.0	166.6
77.5°	149.1	146.0	141.2	133.3	134.9	131.7	131.7	128.5	130.1	130.1	126.9
80°	109.5	104.7	103.1	98.4	99.9	98.4	96.8	96.8	93.6	93.6	93.6
82.5°	76.2	71.4	71.4	69.8	68.2	68.2	66.6	66.6	68.2	65.0	65.0
85°	46.0	44.4	44.4	41.2	41.2	41.2	41.2	42.8	41.2	39.7	39.7
87.5°	20.6	22.2	20.6	19.0	19.0	19.0	17.5	17.5	15.9	17.5	17.5
90°	22.9	24.2	25.5	26.8	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	43.7	44.4	45.0	45.7	46.0	46.1	46.3	46.6	46.8	47.0	46.8
95°	75.1	75.7	76.4	77.1	77.4	77.4	77.4	77.4	77.4	77.4	77.4
97.5°	110.6	111.4	112.3	113.2	113.6	113.6	113.6	113.6	113.6	113.6	113.6
100°	150.3	150.7	151.2	151.6	151.8	151.8	151.8	151.8	151.8	151.8	151.8
102.5°	191.7	192.3	193.0	193.7	194.0	194.1	194.3	194.5	194.7	194.9	194.7
105°	233.8	234.4	235.1	235.8	236.1	236.4	237.1	237.7	238.4	239.0	238.4
107.5°	279.1	279.9	280.8	281.7	282.1	282.0	281.8	281.5	281.3	281.1	281.3
110°	325.8	325.3	324.9	324.4	324.2	324.5	325.2	325.9	326.5	327.2	326.5

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
115°	424.9	424.7	424.5	424.3	424.2	424.1	423.9	423.6	423.4	423.2	423.4
117.5°	473.5	472.8	472.2	471.5	471.2	470.9	470.2	469.5	468.9	468.2	468.9
120°	523.0	521.9	520.8	519.7	519.2	519.4	519.8	520.3	520.7	521.1	520.7
122.5°	572.4	571.7	571.1	570.4	570.1	569.6	568.5	567.4	566.3	565.2	566.3
125°	620.6	620.2	619.7	619.3	619.1	618.9	618.4	618.0	617.5	617.1	617.5
127.5°	666.7	666.2	665.8	665.3	665.1	665.0	664.8	664.5	664.3	664.1	664.3
130°	715.7	715.2	714.8	714.3	714.1	713.7	712.8	711.9	711.1	710.2	711.1
132.5°	761.7	761.2	760.8	760.3	760.1	760.0	759.8	759.6	759.4	759.2	759.4
135°	807.7	807.3	806.8	806.4	806.2	805.9	805.2	804.5	803.9	803.2	803.9
137.5°	852.6	851.9	851.3	850.6	850.3	850.4	850.6	850.8	851.0	851.2	851.0
140°	896.1	895.9	895.6	895.4	895.3	895.2	895.0	894.7	894.5	894.3	894.5
142.5°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
145°	979.4	979.2	978.9	978.7	978.6	978.3	977.6	976.9	976.3	975.6	976.3
147.5°	1017.6	1017.4	1017.1	1016.9	1016.8	1016.7	1016.5	1016.2	1016.0	1015.8	1016.0
150°	1053.0	1053.0	1053.0	1053.0	1053.0	1052.9	1052.7	1052.5	1052.3	1052.1	1052.3
152.5°	1086.0	1086.7	1087.3	1088.0	1088.3	1088.0	1087.3	1086.7	1086.0	1085.4	1086.0
155°	1116.6	1117.4	1118.3	1119.2	1119.6	1119.2	1118.3	1117.4	1116.6	1115.7	1116.6
157.5°	1144.8	1145.4	1146.1	1146.8	1147.1	1146.8	1146.1	1145.4	1144.8	1144.1	1144.8
160°	1170.2	1170.9	1171.5	1172.2	1172.5	1172.0	1170.9	1169.8	1168.7	1167.6	1168.7
162.5°	1192.5	1193.8	1195.1	1196.4	1197.0	1196.5	1195.4	1194.3	1193.2	1192.1	1193.2
165°	1212.0	1213.3	1214.6	1215.9	1216.6	1216.2	1215.3	1214.4	1213.6	1212.7	1213.6
167.5°	1229.7	1231.0	1232.3	1233.6	1234.3	1233.6	1232.3	1231.0	1229.7	1228.4	1229.7
170°	1243.4	1244.7	1246.0	1247.3	1248.0	1247.2	1245.7	1244.2	1242.6	1241.1	1242.6
172.5°	1253.4	1254.9	1256.4	1257.9	1258.7	1257.9	1256.4	1254.9	1253.4	1251.9	1253.4
175°	1260.2	1261.8	1263.3	1264.8	1265.6	1264.8	1263.3	1261.8	1260.2	1258.7	1260.2
177.5°	1265.1	1266.7	1268.2	1269.7	1270.5	1269.6	1267.9	1266.2	1264.4	1262.7	1264.4
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2116.4	2105.3	2103.7	2103.7	2086.2	2095.8	2076.7	2056.1	2046.6	2046.6	2029.1
5°	2292.5	2281.4	2270.3	2252.8	2252.8	2243.3	2213.2	2183.0	2160.8	2141.8	2121.1
7.5°	2473.3	2462.2	2430.5	2413.1	2422.6	2403.5	2363.9	2313.1	2275.0	2244.9	2202.1
10°	2670.1	2639.9	2624.1	2614.5	2581.2	2560.6	2514.6	2440.0	2392.4	2352.8	2297.2
12.5°	2830.3	2839.8	2779.5	2784.3	2751.0	2722.4	2651.0	2579.6	2508.2	2452.7	2370.2
15°	3003.2	2974.7	2938.2	2909.6	2898.5	2863.6	2803.3	2708.1	2630.4	2543.2	2449.5
17.5°	3139.7	3117.5	3082.6	3055.6	3031.8	2947.7	2896.9	2812.9	2706.6	2620.9	2506.7
20°	3255.5	3234.9	3185.7	3168.2	3125.4	3065.1	2992.1	2862.0	2766.8	2673.2	2562.2
22.5°	3304.7	3284.0	3241.2	3219.0	3192.0	3133.3	3063.5	2939.8	2822.4	2705.0	2587.6
25°	3263.4	3263.4	3242.8	3234.9	3211.1	3158.7	3087.3	2982.6	2857.3	2730.4	2590.7
27.5°	3063.5	3103.2	3117.5	3125.4	3125.4	3127.0	3077.8	2976.3	2854.1	2730.4	2584.4
30°	2774.8	2841.4	2900.1	2917.6	2947.7	2981.0	3001.7	2952.5	2843.0	2712.9	2567.0
32.5°	2411.5	2497.1	2606.6	2633.6	2674.8	2774.8	2830.3	2850.9	2790.6	2676.4	2520.9
35°	2049.8	2157.6	2224.3	2306.8	2344.8	2492.4	2616.1	2690.7	2676.4	2608.2	2467.0
37.5°	1734.0	1795.9	1876.8	1964.1	2040.2	2181.4	2335.3	2479.7	2538.4	2505.1	2398.8
40°	1431.0	1504.0	1600.8	1672.2	1724.5	1865.7	2056.1	2213.2	2341.7	2362.3	2297.2
42.5°	1216.8	1289.8	1348.5	1426.3	1467.5	1603.9	1772.1	1968.8	2121.1	2202.1	2173.5
45°	1051.8	1096.3	1143.9	1188.3	1239.1	1359.6	1515.1	1730.9	1902.2	2016.4	2027.5
47.5°	907.5	947.1	988.4	1029.6	1058.2	1151.8	1294.6	1470.7	1657.9	1815.0	1876.8
50°	805.9	825.0	855.1	878.9	912.2	993.1	1107.4	1259.7	1458.0	1627.7	1708.7
52.5°	706.0	729.8	753.6	774.2	796.4	853.5	958.2	1089.9	1261.3	1435.8	1535.7
55°	621.9	640.9	663.2	677.4	690.1	740.9	820.2	921.8	1069.3	1234.3	1358.0
57.5°	553.7	561.6	580.7	588.6	602.9	644.1	701.2	791.7	910.6	1070.9	1172.4
60°	479.1	495.0	509.3	515.6	526.7	555.3	594.9	679.0	782.1	899.5	1015.4
62.5°	418.8	425.2	436.3	444.2	452.2	482.3	515.6	579.1	656.8	755.2	861.5
65°	363.3	366.5	372.8	383.9	388.7	410.9	429.9	475.9	548.9	623.5	729.8
67.5°	306.2	309.4	317.3	323.6	328.4	342.7	363.3	396.6	436.3	518.8	577.5
70°	261.8	261.8	266.5	269.7	274.5	280.8	291.9	317.3	353.8	406.1	460.1
72.5°	218.9	218.9	218.9	223.7	223.7	228.5	234.8	252.3	277.6	318.9	353.8
75°	169.8	171.3	174.5	174.5	176.1	182.4	187.2	192.0	204.7	231.6	263.4
77.5°	128.5	131.7	133.3	130.1	133.3	133.3	139.6	146.0	152.3	160.2	184.0
80°	95.2	96.8	93.6	95.2	95.2	98.4	101.5	99.9	103.1	112.6	119.0
82.5°	63.5	65.0	65.0	65.0	65.0	69.8	69.8	68.2	69.8	71.4	73.0
85°	39.7	38.1	38.1	39.7	38.1	38.1	39.7	41.2	39.7	41.2	42.8
87.5°	17.5	17.5	17.5	17.5	15.9	15.9	17.5	15.9	17.5	15.9	14.3
90°	28.5	28.1	27.6	27.4	26.8	25.5	24.2	22.9	21.6	19.8	18.1
92.5°	46.6	46.3	46.1	46.0	45.7	45.0	44.4	43.7	43.1	42.0	40.9
95°	77.4	77.4	77.4	77.4	77.1	76.4	75.7	75.1	74.4	72.9	71.4
97.5°	113.6	113.6	113.6	113.6	113.2	112.3	111.4	110.6	109.7	108.0	106.2
100°	151.8	151.8	151.8	151.8	151.6	151.2	150.7	150.3	149.9	147.9	146.0
102.5°	194.5	194.3	194.1	194.0	193.7	193.0	192.3	191.7	191.0	189.3	187.5
105°	237.7	237.1	236.4	236.1	235.8	235.1	234.4	233.8	233.1	232.2	231.4
107.5°	281.5	281.8	282.0	282.1	281.7	280.8	279.9	279.1	278.2	278.0	277.8
110°	325.9	325.2	324.5	324.2	324.4	324.9	325.3	325.8	326.2	326.4	326.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.6	375.1
115°	423.6	423.9	424.1	424.2	424.3	424.5	424.7	424.9	425.1	425.5	426.0
117.5°	469.5	470.2	470.9	471.2	471.5	472.2	472.8	473.5	474.1	474.3	474.5
120°	520.3	519.8	519.4	519.2	519.7	520.8	521.9	523.0	524.1	524.7	525.4
122.5°	567.4	568.5	569.6	570.1	570.4	571.1	571.7	572.4	573.0	573.2	573.4
125°	618.0	618.4	618.9	619.1	619.3	619.7	620.2	620.6	621.0	621.2	621.4
127.5°	664.5	664.8	665.0	665.1	665.3	665.8	666.2	666.7	667.1	667.5	667.9
130°	711.9	712.8	713.7	714.1	714.3	714.8	715.2	715.7	716.1	716.1	716.1
132.5°	759.6	759.8	760.0	760.1	760.3	760.8	761.2	761.7	762.1	762.3	762.5
135°	804.5	805.2	805.9	806.2	806.4	806.8	807.3	807.7	808.1	808.1	808.1
137.5°	850.8	850.6	850.4	850.3	850.6	851.3	851.9	852.6	853.2	852.8	852.3
140°	894.7	895.0	895.2	895.3	895.4	895.6	895.9	896.1	896.3	896.3	896.3
142.5°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.6	937.8
145°	976.9	977.6	978.3	978.6	978.7	978.9	979.2	979.4	979.6	979.4	979.2
147.5°	1016.2	1016.5	1016.7	1016.8	1016.9	1017.1	1017.4	1017.6	1017.8	1018.0	1018.2
150°	1052.5	1052.7	1052.9	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
152.5°	1086.7	1087.3	1088.0	1088.3	1088.0	1087.3	1086.7	1086.0	1085.4	1085.2	1085.0
155°	1117.4	1118.3	1119.2	1119.6	1119.2	1118.3	1117.4	1116.6	1115.7	1115.9	1116.1
157.5°	1145.4	1146.1	1146.8	1147.1	1146.8	1146.1	1145.4	1144.8	1144.1	1144.1	1144.1
160°	1169.8	1170.9	1172.0	1172.5	1172.2	1171.5	1170.9	1170.2	1169.6	1169.8	1170.0
162.5°	1194.3	1195.4	1196.5	1197.0	1196.4	1195.1	1193.8	1192.5	1191.2	1191.4	1191.6
165°	1214.4	1215.3	1216.2	1216.6	1215.9	1214.6	1213.3	1212.0	1210.7	1211.1	1211.6
167.5°	1231.0	1232.3	1233.6	1234.3	1233.6	1232.3	1231.0	1229.7	1228.4	1228.4	1228.4
170°	1244.2	1245.7	1247.2	1248.0	1247.3	1246.0	1244.7	1243.4	1242.1	1241.9	1241.7
172.5°	1254.9	1256.4	1257.9	1258.7	1257.9	1256.4	1254.9	1253.4	1251.9	1251.9	1251.9
175°	1261.8	1263.3	1264.8	1265.6	1264.8	1263.3	1261.8	1260.2	1258.7	1258.9	1259.1
177.5°	1266.2	1267.9	1269.6	1270.5	1269.7	1268.2	1266.7	1265.1	1263.6	1263.6	1263.6
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2019.6	2011.7	2006.9	2005.3	1991.1	1983.1	1978.4	1975.2	1970.4	1957.7	1946.6
5°	2095.8	2073.6	2062.4	2049.8	2027.5	2002.2	1981.5	1968.8	1953.0	1927.6	1903.8
7.5°	2167.2	2133.8	2111.6	2094.2	2056.1	2014.8	1981.5	1954.6	1924.4	1889.5	1856.2
10°	2241.7	2187.8	2159.2	2132.3	2076.7	2022.8	1975.2	1935.5	1892.7	1846.7	1810.2
12.5°	2300.4	2229.0	2197.3	2159.2	2091.0	2027.5	1967.3	1913.3	1857.8	1808.6	1756.3
15°	2368.6	2279.8	2243.3	2194.1	2100.5	2018.0	1940.3	1881.6	1824.5	1751.5	1696.0
17.5°	2408.3	2305.2	2252.8	2210.0	2108.5	2008.5	1918.1	1845.1	1778.5	1705.5	1646.8
20°	2448.0	2330.6	2271.9	2211.6	2091.0	1984.7	1889.5	1802.3	1732.5	1653.1	1592.8
22.5°	2460.7	2324.2	2262.3	2206.8	2079.9	1960.9	1851.4	1762.6	1681.7	1602.4	1534.1
25°	2460.7	2322.6	2249.7	2178.3	2045.0	1922.8	1813.4	1716.6	1626.2	1546.8	1478.6
27.5°	2435.3	2290.9	2214.7	2149.7	2011.7	1880.0	1767.4	1661.1	1573.8	1494.5	1416.7
30°	2403.5	2244.9	2168.7	2091.0	1957.7	1832.4	1710.2	1611.9	1519.9	1429.4	1359.6
32.5°	2363.9	2195.7	2111.6	2032.3	1891.1	1761.0	1648.4	1551.6	1464.3	1370.7	1293.0
35°	2306.8	2122.7	2029.1	1959.3	1822.9	1688.0	1580.1	1485.0	1400.9	1304.1	1220.0
37.5°	2233.8	2056.1	1960.9	1875.2	1734.0	1610.3	1508.8	1416.7	1334.2	1245.4	1151.8
40°	2148.1	1962.5	1880.0	1789.6	1640.4	1523.0	1427.8	1345.3	1262.9	1178.8	1088.3
42.5°	2051.3	1867.3	1775.3	1688.0	1545.2	1429.4	1340.6	1266.0	1189.9	1112.1	1015.4
45°	1935.5	1762.6	1673.8	1591.3	1453.2	1334.2	1253.3	1181.9	1116.9	1037.6	951.9
47.5°	1805.4	1654.7	1564.3	1475.4	1340.6	1237.5	1158.1	1097.9	1042.3	963.0	885.3
50°	1678.5	1529.4	1456.4	1366.0	1242.2	1145.5	1064.5	1013.8	970.9	893.2	823.4
52.5°	1518.3	1405.6	1335.8	1258.1	1139.1	1040.7	977.3	932.9	882.1	821.8	759.9
55°	1377.1	1272.4	1216.8	1143.9	1026.5	939.2	885.3	844.0	804.4	750.4	701.2
57.5°	1216.8	1151.8	1096.3	1032.8	917.0	842.4	794.8	759.9	723.4	679.0	639.4
60°	1048.7	1018.5	964.6	913.8	815.5	750.4	710.8	679.0	644.1	607.6	574.3
62.5°	899.5	882.1	850.4	810.7	718.7	663.2	623.5	599.7	574.3	541.0	509.3
65°	758.3	750.4	720.3	691.7	628.3	579.1	544.2	529.9	501.3	475.9	447.4
67.5°	633.0	623.5	606.0	593.3	539.4	493.4	475.9	456.9	433.1	414.1	390.3
70°	506.1	504.5	493.4	477.5	449.0	415.7	398.2	385.5	361.7	347.4	330.0
72.5°	393.5	401.4	391.9	385.5	366.5	342.7	326.8	318.9	299.8	288.7	276.1
75°	293.5	299.8	304.6	293.5	288.7	277.6	263.4	255.4	245.9	230.0	225.3
77.5°	199.9	214.2	214.2	217.3	218.9	212.6	201.5	195.1	184.0	180.9	174.5
80°	131.7	144.4	146.0	149.1	153.9	153.9	146.0	144.4	133.3	131.7	126.9
82.5°	76.2	87.3	93.6	98.4	96.8	103.1	96.8	95.2	88.8	88.8	85.7
85°	41.2	42.8	46.0	49.2	52.4	55.5	55.5	53.9	52.4	50.8	47.6
87.5°	15.9	15.9	17.5	15.9	17.5	20.6	22.2	22.2	20.6	19.0	15.9
90°	16.3	14.6	13.7	12.5	10.1	7.7	5.3	2.9	5.3	7.7	10.1
92.5°	39.8	38.7	38.2	36.8	34.0	31.1	28.3	25.5	28.3	31.1	34.0
95°	69.9	68.4	67.6	66.6	64.7	62.7	60.8	58.8	60.8	62.7	64.7
97.5°	104.5	102.8	101.9	101.0	99.3	97.5	95.8	94.0	95.8	97.5	99.3
100°	144.0	142.1	141.1	140.7	139.8	138.9	138.0	137.1	138.0	138.9	139.8
102.5°	185.8	184.1	183.2	183.1	182.9	182.6	182.4	182.2	182.4	182.6	182.9
105°	230.5	229.6	229.2	229.1	228.9	228.6	228.4	228.2	228.4	228.6	228.9
107.5°	277.5	277.3	277.2	277.1	276.9	276.6	276.4	276.2	276.4	276.6	276.9
110°	326.9	327.1	327.2	327.0	326.5	326.1	325.6	325.2	325.6	326.1	326.5

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	375.5	376.0	376.2	376.2	376.2	376.2	376.2	376.2	376.2	376.2	376.2
115°	426.4	426.9	427.1	427.1	427.1	427.1	427.1	427.1	427.1	427.1	427.1
117.5°	474.8	475.0	475.1	475.1	475.1	475.1	475.1	475.1	475.1	475.1	475.1
120°	526.0	526.7	527.0	526.6	525.7	524.8	524.0	523.1	524.0	524.8	525.7
122.5°	573.7	573.9	574.0	573.9	573.7	573.4	573.2	573.0	573.2	573.4	573.7
125°	621.7	621.9	622.0	622.0	622.0	622.0	622.0	622.0	622.0	622.0	622.0
127.5°	668.4	668.8	669.0	668.7	668.0	667.4	666.7	666.1	666.7	667.4	668.0
130°	716.1	716.1	716.1	715.8	715.1	714.4	713.8	713.1	713.8	714.4	715.1
132.5°	762.8	763.0	763.1	762.9	762.4	762.0	761.5	761.1	761.5	762.0	762.4
135°	808.1	808.1	808.1	807.5	806.2	804.9	803.6	802.3	803.6	804.9	806.2
137.5°	851.9	851.4	851.2	850.9	850.2	849.6	848.9	848.3	848.9	849.6	850.2
140°	896.3	896.3	896.3	896.1	895.6	895.2	894.7	894.3	894.7	895.2	895.6
142.5°	938.1	938.3	938.4	938.2	937.8	937.3	936.9	936.5	936.9	937.3	937.8
145°	978.9	978.7	978.6	978.2	977.3	976.4	975.6	974.7	975.6	976.4	977.3
147.5°	1018.4	1018.6	1018.7	1018.2	1017.1	1016.0	1015.0	1013.9	1015.0	1016.0	1017.1
150°	1053.0	1053.0	1053.0	1052.6	1051.7	1050.8	1050.0	1049.1	1050.0	1050.8	1051.7
152.5°	1084.7	1084.5	1084.4	1084.2	1083.7	1083.3	1082.8	1082.4	1082.8	1083.3	1083.7
155°	1116.4	1116.6	1116.7	1116.7	1116.7	1116.7	1116.7	1116.7	1116.7	1116.7	1116.7
157.5°	1144.1	1144.1	1144.1	1144.3	1144.8	1145.2	1145.7	1146.1	1145.7	1145.2	1144.8
160°	1170.3	1170.5	1170.6	1170.7	1170.9	1171.2	1171.4	1171.6	1171.4	1171.2	1170.9
162.5°	1191.8	1192.0	1192.1	1192.4	1193.1	1193.8	1194.4	1195.1	1194.4	1193.8	1193.1
165°	1212.0	1212.5	1212.7	1213.0	1213.7	1214.3	1215.0	1215.6	1215.0	1214.3	1213.7
167.5°	1228.4	1228.4	1228.4	1228.8	1229.7	1230.6	1231.4	1232.3	1231.4	1230.6	1229.7
170°	1241.4	1241.2	1241.1	1241.6	1242.7	1243.8	1244.9	1246.0	1244.9	1243.8	1242.7
172.5°	1251.9	1251.9	1251.9	1252.3	1253.2	1254.1	1254.9	1255.8	1254.9	1254.1	1253.2
175°	1259.4	1259.6	1259.7	1260.2	1261.3	1262.4	1263.5	1264.6	1263.5	1262.4	1261.3
177.5°	1263.6	1263.6	1263.6	1264.1	1265.2	1266.3	1267.4	1268.5	1267.4	1266.3	1265.2
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1937.1	1933.9	1930.8	1918.1	1907.0	1887.9	1872.1	1865.7	1864.1	1865.7	1861.0
5°	1881.6	1880.0	1868.9	1846.7	1826.1	1803.8	1788.0	1772.1	1762.6	1762.6	1751.5
7.5°	1829.2	1818.1	1808.6	1780.0	1756.3	1726.1	1702.3	1688.0	1680.1	1662.6	1662.6
10°	1773.7	1757.8	1745.1	1718.2	1683.3	1653.1	1623.0	1605.5	1591.3	1578.6	1573.8
12.5°	1718.2	1705.5	1681.7	1653.1	1618.2	1580.1	1548.4	1535.7	1502.4	1475.4	1477.0
15°	1665.8	1637.3	1626.2	1584.9	1543.7	1507.2	1461.2	1424.7	1397.7	1380.3	1358.0
17.5°	1607.1	1578.6	1557.9	1523.0	1469.1	1412.0	1367.6	1318.4	1291.4	1261.3	1247.0
20°	1542.1	1518.3	1502.4	1446.9	1381.8	1313.6	1264.4	1234.3	1204.2	1181.9	1169.2
22.5°	1486.5	1456.4	1437.4	1362.8	1291.4	1223.2	1185.1	1159.7	1134.3	1115.3	1109.0
25°	1415.2	1397.7	1351.7	1286.6	1199.4	1153.4	1120.1	1086.7	1072.5	1059.8	1045.5
27.5°	1356.5	1313.6	1281.9	1196.2	1142.3	1089.9	1056.6	1031.2	1013.8	1001.1	990.0
30°	1283.5	1243.8	1199.4	1128.0	1078.8	1029.6	999.5	978.9	959.8	951.9	942.4
32.5°	1207.3	1170.8	1128.0	1070.9	1010.6	972.5	948.7	926.5	913.8	905.9	894.8
35°	1139.1	1093.1	1064.5	1010.6	961.4	918.6	896.4	877.3	863.1	859.9	858.3
37.5°	1066.1	1031.2	1004.3	948.7	907.5	871.0	850.4	829.7	821.8	820.2	813.9
40°	1002.7	972.5	947.1	894.8	850.4	817.0	801.2	788.5	780.6	780.6	779.0
42.5°	947.1	915.4	890.0	842.4	802.8	772.6	755.2	742.5	739.3	740.9	739.3
45°	885.3	858.3	832.9	783.7	750.4	728.2	709.2	702.8	698.1	699.6	701.2
47.5°	826.6	804.4	779.0	739.3	701.2	677.4	666.3	660.0	660.0	660.0	663.2
50°	774.2	748.8	726.6	685.4	650.5	631.4	621.9	614.0	615.6	617.1	618.7
52.5°	712.3	690.1	674.3	633.0	607.6	583.8	572.7	574.3	572.7	572.7	575.9
55°	658.4	636.2	620.3	582.2	556.9	541.0	531.5	526.7	528.3	525.1	531.5
57.5°	598.1	579.1	568.0	531.5	509.3	495.0	487.1	479.1	482.3	480.7	479.1
60°	545.8	523.5	506.1	480.7	461.7	444.2	439.5	431.5	434.7	431.5	429.9
62.5°	485.5	468.0	455.3	429.9	414.1	399.8	388.7	383.9	382.3	377.6	372.8
65°	425.2	415.7	403.0	377.6	361.7	350.6	344.3	339.5	337.9	325.2	311.0
67.5°	369.7	363.3	350.6	331.6	317.3	306.2	296.7	288.7	279.2	269.7	261.8
70°	317.3	307.8	299.8	282.4	269.7	258.6	249.1	239.6	234.8	225.3	222.1
72.5°	266.5	257.0	249.1	233.2	222.1	211.0	207.8	196.7	192.0	190.4	190.4
75°	214.2	206.2	201.5	187.2	177.7	169.8	165.0	161.8	158.6	155.5	150.7
77.5°	163.4	158.6	155.5	146.0	138.0	133.3	131.7	120.6	117.4	114.2	111.1
80°	119.0	117.4	114.2	106.3	103.1	92.0	92.0	88.8	87.3	87.3	87.3
82.5°	80.9	77.7	76.2	68.2	66.6	65.0	63.5	61.9	63.5	61.9	63.5
85°	42.8	41.2	39.7	39.7	39.7	39.7	39.7	39.7	39.7	38.1	39.7
87.5°	15.9	15.9	15.9	15.9	14.3	15.9	15.9	14.3	15.9	15.9	15.9
90°	12.5	13.7	14.6	16.3	18.1	19.8	21.6	22.9	24.2	25.5	26.8
92.5°	36.8	38.2	38.7	39.8	40.9	42.0	43.1	43.7	44.4	45.0	45.7
95°	66.6	67.6	68.4	69.9	71.4	72.9	74.4	75.1	75.7	76.4	77.1
97.5°	101.0	101.9	102.8	104.5	106.2	108.0	109.7	110.6	111.4	112.3	113.2
100°	140.7	141.1	142.1	144.0	146.0	147.9	149.9	150.3	150.7	151.2	151.6
102.5°	183.1	183.2	184.1	185.8	187.5	189.3	191.0	191.7	192.3	193.0	193.7
105°	229.1	229.2	229.6	230.5	231.4	232.2	233.1	233.8	234.4	235.1	235.8
107.5°	277.1	277.2	277.3	277.5	277.8	278.0	278.2	279.1	279.9	280.8	281.7
110°	327.0	327.2	327.1	326.9	326.6	326.4	326.2	325.8	325.3	324.9	324.4

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	376.2	376.2	376.0	375.5	375.1	374.6	374.2	374.2	374.2	374.2	374.2
115°	427.1	427.1	426.9	426.4	426.0	425.5	425.1	424.9	424.7	424.5	424.3
117.5°	475.1	475.1	475.0	474.8	474.5	474.3	474.1	473.5	472.8	472.2	471.5
120°	526.6	527.0	526.7	526.0	525.4	524.7	524.1	523.0	521.9	520.8	519.7
122.5°	573.9	574.0	573.9	573.7	573.4	573.2	573.0	572.4	571.7	571.1	570.4
125°	622.0	622.0	621.9	621.7	621.4	621.2	621.0	620.6	620.2	619.7	619.3
127.5°	668.7	669.0	668.8	668.4	667.9	667.5	667.1	666.7	666.2	665.8	665.3
130°	715.8	716.1	716.1	716.1	716.1	716.1	716.1	715.7	715.2	714.8	714.3
132.5°	762.9	763.1	763.0	762.8	762.5	762.3	762.1	761.7	761.2	760.8	760.3
135°	807.5	808.1	808.1	808.1	808.1	808.1	808.1	807.7	807.3	806.8	806.4
137.5°	850.9	851.2	851.4	851.9	852.3	852.8	853.2	852.6	851.9	851.3	850.6
140°	896.1	896.3	896.3	896.3	896.3	896.3	896.3	896.1	895.9	895.6	895.4
142.5°	938.2	938.4	938.3	938.1	937.8	937.6	937.4	937.4	937.4	937.4	937.4
145°	978.2	978.6	978.7	978.9	979.2	979.4	979.6	979.4	979.2	978.9	978.7
147.5°	1018.2	1018.7	1018.6	1018.4	1018.2	1018.0	1017.8	1017.6	1017.4	1017.1	1016.9
150°	1052.6	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0
152.5°	1084.2	1084.4	1084.5	1084.7	1085.0	1085.2	1085.4	1086.0	1086.7	1087.3	1088.0
155°	1116.7	1116.7	1116.6	1116.4	1116.1	1115.9	1115.7	1116.6	1117.4	1118.3	1119.2
157.5°	1144.3	1144.1	1144.1	1144.1	1144.1	1144.1	1144.1	1144.8	1145.4	1146.1	1146.8
160°	1170.7	1170.6	1170.5	1170.3	1170.0	1169.8	1169.6	1170.2	1170.9	1171.5	1172.2
162.5°	1192.4	1192.1	1192.0	1191.8	1191.6	1191.4	1191.2	1192.5	1193.8	1195.1	1196.4
165°	1213.0	1212.7	1212.5	1212.0	1211.6	1211.1	1210.7	1212.0	1213.3	1214.6	1215.9
167.5°	1228.8	1228.4	1228.4	1228.4	1228.4	1228.4	1228.4	1229.7	1231.0	1232.3	1233.6
170°	1241.6	1241.1	1241.2	1241.4	1241.7	1241.9	1242.1	1243.4	1244.7	1246.0	1247.3
172.5°	1252.3	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1253.4	1254.9	1256.4	1257.9
175°	1260.2	1259.7	1259.6	1259.4	1259.1	1258.9	1258.7	1260.2	1261.8	1263.3	1264.8
177.5°	1264.1	1263.6	1263.6	1263.6	1263.6	1263.6	1263.6	1265.1	1266.7	1268.2	1269.7
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1861.0	1867.3	1859.4	1864.1	1853.0	1851.4	1853.0	1853.0	1854.6	1856.2	1857.8
5°	1756.3	1754.7	1745.1	1738.8	1734.0	1738.8	1742.0	1745.1	1742.0	1745.1	1746.7
7.5°	1657.9	1653.1	1648.4	1637.3	1640.4	1637.3	1646.8	1642.0	1642.0	1650.0	1656.3
10°	1570.6	1561.1	1557.9	1545.2	1535.7	1534.1	1545.2	1550.0	1554.8	1557.9	1570.6
12.5°	1458.0	1443.7	1432.6	1437.4	1410.4	1421.5	1424.7	1418.3	1437.4	1459.6	1446.9
15°	1337.4	1339.0	1316.8	1308.9	1286.6	1293.0	1294.6	1310.4	1326.3	1324.7	1343.8
17.5°	1248.6	1239.1	1220.0	1218.4	1208.9	1213.7	1212.1	1224.8	1220.0	1227.9	1243.8
20°	1166.1	1159.7	1143.9	1137.5	1140.7	1137.5	1139.1	1140.7	1145.5	1162.9	1159.7
22.5°	1101.0	1093.1	1093.1	1085.2	1075.6	1072.5	1080.4	1085.2	1091.5	1094.7	1102.6
25°	1043.9	1037.6	1029.6	1024.9	1016.9	1018.5	1023.3	1029.6	1034.4	1040.7	1047.1
27.5°	985.2	985.2	977.3	975.7	972.5	970.9	977.3	980.5	980.5	985.2	991.6
30°	939.2	939.2	931.3	929.7	928.1	928.1	932.9	934.4	936.0	940.8	944.0
32.5°	894.8	893.2	890.0	891.6	890.0	891.6	891.6	893.2	896.4	898.0	904.3
35°	853.5	855.1	851.9	851.9	850.4	851.9	855.1	856.7	858.3	861.5	861.5
37.5°	813.9	817.0	815.5	820.2	820.2	820.2	820.2	823.4	823.4	823.4	821.8
40°	779.0	779.0	777.4	780.6	783.7	783.7	785.3	785.3	786.9	786.9	785.3
42.5°	739.3	742.5	747.2	748.8	752.0	750.4	755.2	753.6	755.2	752.0	748.8
45°	702.8	702.8	709.2	715.5	717.1	717.1	717.1	720.3	717.1	712.3	710.8
47.5°	663.2	666.3	669.5	677.4	679.0	679.0	679.0	679.0	675.8	675.8	675.8
50°	623.5	625.1	626.7	629.8	634.6	633.0	633.0	633.0	639.4	633.0	634.6
52.5°	575.9	577.5	579.1	585.4	583.8	583.8	585.4	585.4	590.2	588.6	585.4
55°	528.3	528.3	531.5	531.5	531.5	534.6	536.2	539.4	537.8	539.4	541.0
57.5°	480.7	477.5	475.9	475.9	480.7	479.1	480.7	480.7	487.1	490.2	491.8
60°	425.2	425.2	423.6	414.1	414.1	412.5	417.2	420.4	423.6	437.9	436.3
62.5°	368.1	361.7	355.4	357.0	347.4	352.2	349.0	352.2	361.7	372.8	374.4
65°	311.0	306.2	299.8	298.3	295.1	299.8	298.3	299.8	304.6	311.0	318.9
67.5°	260.2	258.6	255.4	253.8	253.8	253.8	257.0	257.0	258.6	263.4	268.1
70°	222.1	220.5	222.1	218.9	220.5	218.9	220.5	222.1	223.7	225.3	230.0
72.5°	187.2	187.2	187.2	184.0	187.2	185.6	185.6	187.2	188.8	190.4	193.6
75°	149.1	146.0	142.8	139.6	138.0	141.2	142.8	141.2	146.0	152.3	152.3
77.5°	112.6	111.1	111.1	111.1	112.6	111.1	114.2	112.6	114.2	114.2	117.4
80°	87.3	85.7	87.3	87.3	85.7	88.8	87.3	87.3	88.8	90.4	88.8
82.5°	63.5	65.0	63.5	63.5	63.5	66.6	63.5	63.5	63.5	65.0	65.0
85°	39.7	39.7	39.7	39.7	41.2	39.7	41.2	39.7	42.8	41.2	41.2
87.5°	14.3	15.9	17.5	17.5	17.5	17.5	15.9	17.5	19.0	17.5	19.0
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	46.0	46.1	46.3	46.6	46.8	47.0	46.8	46.6	46.3	46.1	46.0
95°	77.4	77.4	77.4	77.4	77.4	77.4	77.4	77.4	77.4	77.4	77.4
97.5°	113.6	113.6	113.6	113.6	113.6	113.6	113.6	113.6	113.6	113.6	113.6
100°	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8	151.8
102.5°	194.0	194.1	194.3	194.5	194.7	194.9	194.7	194.5	194.3	194.1	194.0
105°	236.1	236.4	237.1	237.7	238.4	239.0	238.4	237.7	237.1	236.4	236.1
107.5°	282.1	282.0	281.8	281.5	281.3	281.1	281.3	281.5	281.8	282.0	282.1
110°	324.2	324.5	325.2	325.9	326.5	327.2	326.5	325.9	325.2	324.5	324.2

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
115°	424.2	424.1	423.9	423.6	423.4	423.2	423.4	423.6	423.9	424.1	424.2
117.5°	471.2	470.9	470.2	469.5	468.9	468.2	468.9	469.5	470.2	470.9	471.2
120°	519.2	519.4	519.8	520.3	520.7	521.1	520.7	520.3	519.8	519.4	519.2
122.5°	570.1	569.6	568.5	567.4	566.3	565.2	566.3	567.4	568.5	569.6	570.1
125°	619.1	618.9	618.4	618.0	617.5	617.1	617.5	618.0	618.4	618.9	619.1
127.5°	665.1	665.0	664.8	664.5	664.3	664.1	664.3	664.5	664.8	665.0	665.1
130°	714.1	713.7	712.8	711.9	711.1	710.2	711.1	711.9	712.8	713.7	714.1
132.5°	760.1	760.0	759.8	759.6	759.4	759.2	759.4	759.6	759.8	760.0	760.1
135°	806.2	805.9	805.2	804.5	803.9	803.2	803.9	804.5	805.2	805.9	806.2
137.5°	850.3	850.4	850.6	850.8	851.0	851.2	851.0	850.8	850.6	850.4	850.3
140°	895.3	895.2	895.0	894.7	894.5	894.3	894.5	894.7	895.0	895.2	895.3
142.5°	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4	937.4
145°	978.6	978.3	977.6	976.9	976.3	975.6	976.3	976.9	977.6	978.3	978.6
147.5°	1016.8	1016.7	1016.5	1016.2	1016.0	1015.8	1016.0	1016.2	1016.5	1016.7	1016.8
150°	1053.0	1052.9	1052.7	1052.5	1052.3	1052.1	1052.3	1052.5	1052.7	1052.9	1053.0
152.5°	1088.3	1088.0	1087.3	1086.7	1086.0	1085.4	1086.0	1086.7	1087.3	1088.0	1088.3
155°	1119.6	1119.2	1118.3	1117.4	1116.6	1115.7	1116.6	1117.4	1118.3	1119.2	1119.6
157.5°	1147.1	1146.8	1146.1	1145.4	1144.8	1144.1	1144.8	1145.4	1146.1	1146.8	1147.1
160°	1172.5	1172.0	1170.9	1169.8	1168.7	1167.6	1168.7	1169.8	1170.9	1172.0	1172.5
162.5°	1197.0	1196.5	1195.4	1194.3	1193.2	1192.1	1193.2	1194.3	1195.4	1196.5	1197.0
165°	1216.6	1216.2	1215.3	1214.4	1213.6	1212.7	1213.6	1214.4	1215.3	1216.2	1216.6
167.5°	1234.3	1233.6	1232.3	1231.0	1229.7	1228.4	1229.7	1231.0	1232.3	1233.6	1234.3
170°	1248.0	1247.2	1245.7	1244.2	1242.6	1241.1	1242.6	1244.2	1245.7	1247.2	1248.0
172.5°	1258.7	1257.9	1256.4	1254.9	1253.4	1251.9	1253.4	1254.9	1256.4	1257.9	1258.7
175°	1265.6	1264.8	1263.3	1261.8	1260.2	1258.7	1260.2	1261.8	1263.3	1264.8	1265.6
177.5°	1270.5	1269.6	1267.9	1266.2	1264.4	1262.7	1264.4	1266.2	1267.9	1269.6	1270.5
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1864.1	1872.1	1868.9	1857.8	1862.5	1872.1	1881.6	1894.3	1902.2	1908.6	1911.7
5°	1754.7	1768.9	1765.8	1765.8	1772.1	1788.0	1803.8	1830.8	1840.3	1851.4	1867.3
7.5°	1657.9	1669.0	1678.5	1681.7	1691.2	1711.8	1732.5	1762.6	1786.4	1799.1	1808.6
10°	1572.2	1580.1	1594.4	1602.4	1611.9	1637.3	1667.4	1699.1	1722.9	1745.1	1757.8
12.5°	1462.7	1494.5	1513.5	1526.2	1538.9	1577.0	1600.8	1635.7	1664.2	1684.9	1703.9
15°	1340.6	1378.7	1389.8	1439.0	1470.7	1500.8	1537.3	1578.6	1605.5	1629.3	1654.7
17.5°	1237.5	1264.4	1277.1	1329.5	1356.5	1404.0	1456.4	1508.8	1550.0	1567.5	1592.8
20°	1172.4	1186.7	1212.1	1229.5	1258.1	1313.6	1370.7	1434.2	1496.1	1513.5	1538.9
22.5°	1105.8	1124.8	1142.3	1166.1	1188.3	1226.4	1283.5	1353.3	1419.9	1451.6	1481.8
25°	1045.5	1064.5	1075.6	1101.0	1121.7	1159.7	1199.4	1270.8	1350.1	1377.1	1424.7
27.5°	997.9	1009.0	1028.0	1039.2	1063.0	1097.9	1134.3	1188.3	1266.0	1312.0	1358.0
30°	950.3	958.2	974.1	990.0	1007.4	1031.2	1072.5	1124.8	1196.2	1235.9	1281.9
32.5°	902.7	915.4	924.9	936.0	955.1	983.6	1012.2	1063.0	1120.1	1164.5	1210.5
35°	863.1	867.8	880.5	893.2	905.9	931.3	961.4	1010.6	1061.4	1096.3	1137.5
37.5°	820.2	828.2	837.7	842.4	863.1	878.9	910.6	948.7	1009.0	1031.2	1072.5
40°	786.9	785.3	794.8	802.8	812.3	837.7	856.7	898.0	945.6	980.5	1005.8
42.5°	745.7	745.7	748.8	758.3	771.0	786.9	809.1	844.0	893.2	918.6	948.7
45°	712.3	707.6	709.2	715.5	723.4	739.3	761.5	791.7	840.8	861.5	893.2
47.5°	672.7	667.9	667.9	674.3	680.6	691.7	709.2	744.1	783.7	810.7	834.5
50°	628.3	629.8	628.3	633.0	636.2	647.3	666.3	694.9	731.4	753.6	780.6
52.5°	587.0	583.8	582.2	585.4	591.8	599.7	620.3	645.7	680.6	702.8	726.6
55°	536.2	539.4	539.4	539.4	548.9	552.1	568.0	593.3	628.3	645.7	667.9
57.5°	490.2	488.6	491.8	490.2	498.2	509.3	522.0	541.0	575.9	593.3	614.0
60°	439.5	441.0	442.6	442.6	449.0	460.1	474.4	491.8	520.4	537.8	556.9
62.5°	377.6	385.5	393.5	396.6	406.1	414.1	423.6	442.6	468.0	480.7	498.2
65°	318.9	330.0	341.1	349.0	355.4	363.3	376.0	393.5	414.1	426.8	444.2
67.5°	268.1	276.1	290.3	298.3	311.0	320.5	328.4	342.7	368.1	372.8	387.1
70°	231.6	234.8	241.1	247.5	261.8	269.7	279.2	293.5	312.5	323.6	331.6
72.5°	195.1	196.7	199.9	206.2	212.6	222.1	233.2	245.9	263.4	268.1	279.2
75°	155.5	165.0	165.0	169.8	174.5	179.3	188.8	201.5	212.6	220.5	226.9
77.5°	115.8	120.6	123.7	131.7	138.0	142.8	149.1	158.6	165.0	171.3	176.1
80°	90.4	92.0	93.6	93.6	96.8	103.1	109.5	115.8	123.7	126.9	131.7
82.5°	66.6	66.6	66.6	69.8	71.4	73.0	73.0	76.2	84.1	87.3	92.0
85°	42.8	42.8	42.8	42.8	44.4	46.0	47.6	49.2	49.2	49.2	52.4
87.5°	17.5	20.6	19.0	20.6	20.6	20.6	20.6	22.2	22.2	23.8	23.8
90°	26.8	25.5	24.2	22.9	21.6	19.8	18.1	16.3	14.6	13.7	12.5
92.5°	45.7	45.0	44.4	43.7	43.1	42.0	40.9	39.8	38.7	38.2	36.8
95°	77.1	76.4	75.7	75.1	74.4	72.9	71.4	69.9	68.4	67.6	66.6
97.5°	113.2	112.3	111.4	110.6	109.7	108.0	106.2	104.5	102.8	101.9	101.0
100°	151.6	151.2	150.7	150.3	149.9	147.9	146.0	144.0	142.1	141.1	140.7
102.5°	193.7	193.0	192.3	191.7	191.0	189.3	187.5	185.8	184.1	183.2	183.1
105°	235.8	235.1	234.4	233.8	233.1	232.2	231.4	230.5	229.6	229.2	229.1
107.5°	281.7	280.8	279.9	279.1	278.2	278.0	277.8	277.5	277.3	277.2	277.1
110°	324.4	324.9	325.3	325.8	326.2	326.4	326.6	326.9	327.1	327.2	327.0

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	374.2	374.2	374.2	374.2	374.2	374.6	375.1	375.5	376.0	376.2	376.2
115°	424.3	424.5	424.7	424.9	425.1	425.5	426.0	426.4	426.9	427.1	427.1
117.5°	471.5	472.2	472.8	473.5	474.1	474.3	474.5	474.8	475.0	475.1	475.1
120°	519.7	520.8	521.9	523.0	524.1	524.7	525.4	526.0	526.7	527.0	526.6
122.5°	570.4	571.1	571.7	572.4	573.0	573.2	573.4	573.7	573.9	574.0	573.9
125°	619.3	619.7	620.2	620.6	621.0	621.2	621.4	621.7	621.9	622.0	622.0
127.5°	665.3	665.8	666.2	666.7	667.1	667.5	667.9	668.4	668.8	669.0	668.7
130°	714.3	714.8	715.2	715.7	716.1	716.1	716.1	716.1	716.1	716.1	715.8
132.5°	760.3	760.8	761.2	761.7	762.1	762.3	762.5	762.8	763.0	763.1	762.9
135°	806.4	806.8	807.3	807.7	808.1	808.1	808.1	808.1	808.1	808.1	807.5
137.5°	850.6	851.3	851.9	852.6	853.2	852.8	852.3	851.9	851.4	851.2	850.9
140°	895.4	895.6	895.9	896.1	896.3	896.3	896.3	896.3	896.3	896.3	896.1
142.5°	937.4	937.4	937.4	937.4	937.4	937.6	937.8	938.1	938.3	938.4	938.2
145°	978.7	978.9	979.2	979.4	979.6	979.4	979.2	978.9	978.7	978.6	978.2
147.5°	1016.9	1017.1	1017.4	1017.6	1017.8	1018.0	1018.2	1018.4	1018.6	1018.7	1018.2
150°	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1053.0	1052.6
152.5°	1088.0	1087.3	1086.7	1086.0	1085.4	1085.2	1085.0	1084.7	1084.5	1084.4	1084.2
155°	1119.2	1118.3	1117.4	1116.6	1115.7	1115.9	1116.1	1116.4	1116.6	1116.7	1116.7
157.5°	1146.8	1146.1	1145.4	1144.8	1144.1	1144.1	1144.1	1144.1	1144.1	1144.1	1144.3
160°	1172.2	1171.5	1170.9	1170.2	1169.6	1169.8	1170.0	1170.3	1170.5	1170.6	1170.7
162.5°	1196.4	1195.1	1193.8	1192.5	1191.2	1191.4	1191.6	1191.8	1192.0	1192.1	1192.4
165°	1215.9	1214.6	1213.3	1212.0	1210.7	1211.1	1211.6	1212.0	1212.5	1212.7	1213.0
167.5°	1233.6	1232.3	1231.0	1229.7	1228.4	1228.4	1228.4	1228.4	1228.4	1228.4	1228.8
170°	1247.3	1246.0	1244.7	1243.4	1242.1	1241.9	1241.7	1241.4	1241.2	1241.1	1241.6
172.5°	1257.9	1256.4	1254.9	1253.4	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1252.3
175°	1264.8	1263.3	1261.8	1260.2	1258.7	1258.9	1259.1	1259.4	1259.6	1259.7	1260.2
177.5°	1269.7	1268.2	1266.7	1265.1	1263.6	1263.6	1263.6	1263.6	1263.6	1263.6	1264.1
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1968.8	1968.8	1968.8	1968.8
2.5°	1924.4	1933.9	1949.8	1972.0
5°	1880.0	1907.0	1932.4	1965.7
7.5°	1840.3	1872.1	1907.0	1954.6
10°	1794.3	1834.0	1878.4	1937.1
12.5°	1740.4	1795.9	1846.7	1910.1
15°	1700.7	1742.0	1807.0	1881.6
17.5°	1645.2	1700.7	1765.8	1849.9
20°	1592.8	1651.5	1724.5	1811.8
22.5°	1537.3	1603.9	1676.9	1770.5
25°	1480.2	1551.6	1624.6	1724.5
27.5°	1427.8	1492.9	1575.4	1676.9
30°	1364.4	1439.0	1518.3	1624.6
32.5°	1302.5	1380.3	1461.2	1567.5
35°	1235.9	1313.6	1402.5	1504.0
37.5°	1170.8	1256.5	1337.4	1435.8
40°	1099.4	1188.3	1272.4	1372.3
42.5°	1029.6	1121.7	1205.7	1291.4
45°	964.6	1055.0	1131.2	1212.1
47.5°	902.7	983.6	1061.4	1134.3
50°	842.4	910.6	982.0	1042.3
52.5°	779.0	844.0	901.1	955.1
55°	721.9	772.6	823.4	872.6
57.5°	653.6	704.4	748.8	786.9
60°	596.5	628.3	671.1	710.8
62.5°	531.5	568.0	601.3	626.7
65°	468.0	499.7	525.1	547.3
67.5°	414.1	433.1	452.2	475.9
70°	349.0	364.9	387.1	404.6
72.5°	293.5	306.2	317.3	337.9
75°	238.0	249.1	255.4	274.5
77.5°	184.0	195.1	199.9	211.0
80°	141.2	142.8	149.1	158.6
82.5°	96.8	99.9	101.5	109.5
85°	55.5	63.5	61.9	65.0
87.5°	23.8	25.4	28.6	31.7
90°	10.1	7.7	5.3	2.9
92.5°	34.0	31.1	28.3	25.5
95°	64.7	62.7	60.8	58.8
97.5°	99.3	97.5	95.8	94.0
100°	139.8	138.9	138.0	137.1
102.5°	182.9	182.6	182.4	182.2
105°	228.9	228.6	228.4	228.2
107.5°	276.9	276.6	276.4	276.2
110°	326.5	326.1	325.6	325.2

TEST NUMBER: P1026080

CATALOG NUMBER: S124RDIP-B1195D1035UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	376.2	376.2	376.2	376.2
115°	427.1	427.1	427.1	427.1
117.5°	475.1	475.1	475.1	475.1
120°	525.7	524.8	524.0	523.1
122.5°	573.7	573.4	573.2	573.0
125°	622.0	622.0	622.0	622.0
127.5°	668.0	667.4	666.7	666.1
130°	715.1	714.4	713.8	713.1
132.5°	762.4	762.0	761.5	761.1
135°	806.2	804.9	803.6	802.3
137.5°	850.2	849.6	848.9	848.3
140°	895.6	895.2	894.7	894.3
142.5°	937.8	937.3	936.9	936.5
145°	977.3	976.4	975.6	974.7
147.5°	1017.1	1016.0	1015.0	1013.9
150°	1051.7	1050.8	1050.0	1049.1
152.5°	1083.7	1083.3	1082.8	1082.4
155°	1116.7	1116.7	1116.7	1116.7
157.5°	1144.8	1145.2	1145.7	1146.1
160°	1170.9	1171.2	1171.4	1171.6
162.5°	1193.1	1193.8	1194.4	1195.1
165°	1213.7	1214.3	1215.0	1215.6
167.5°	1229.7	1230.6	1231.4	1232.3
170°	1242.7	1243.8	1244.9	1246.0
172.5°	1253.2	1254.1	1254.9	1255.8
175°	1261.3	1262.4	1263.5	1264.6
177.5°	1265.2	1266.3	1267.4	1268.5
180°	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)