

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026090

Luminaire Tested: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026090
REPORT IS A COMBINATION OF REPORTS P999040 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8502.3 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026090

CATALOG NUMBER: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026090

CATALOG NUMBER: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	95	92	88	93	89	86	83	77	74	72	66	64	63	56	54	53
2	91	84	78	73	84	78	73	68	68	64	60	58	55	53	49	47	45
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	39	36	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	45	39	60	49	42	37	43	38	33	38	33	30	32	29	26
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	30	26	23
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1026090

CATALOG NUMBER: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	2.3
10°-20°	547.9	6.4
20°-30°	791.1	9.3
30°-40°	896.6	10.5
40°-50°	865.7	10.2
50°-60°	719.7	8.5
60°-70°	496.8	5.8
70°-80°	251.0	3.0
80°-90°	65.7	0.8
90°-100°	373.7	4.4
100°-110°	760.0	8.9
110°-120°	677.5	8.0
120°-130°	569.1	6.7
130°-140°	474.9	5.6
140°-150°	362.7	4.3
150°-160°	254.9	3.0
160°-170°	149.9	1.8
170°-180°	48.8	0.6
0°-30°	1535.6	18.1
0°-40°	2432.1	28.6
0°-60°	4017.5	47.3
0°-90°	4830.9	56.8
90°-120°	1811.2	21.3
90°-150°	3217.8	37.8
90°-180°	3671.0	43.2
0°-180°	8502.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	1	8	18	20	21	7
95°	33	103	806	399	241	36
105°	116	168	648	1396	1391	123
115°	204	255	578	1111	1335	202
125°	284	337	575	945	1066	253
135°	337	401	570	839	953	260
145°	388	445	567	708	778	244
155°	442	477	552	625	651	204
165°	481	496	529	560	568	136
175°	502	503	507	514	512	48
180°	503	503	503	503	503	

TEST NUMBER: P1026090

CATALOG NUMBER: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	1.0	7.9	17.8	19.8	20.8
92.5°	13.8	76.2	387.4	128.0	89.9
95°	32.6	102.8	805.5	398.8	241.2
97.5°	54.4	113.7	861.8	814.4	579.2
100°	75.1	128.5	794.6	1126.8	906.3
102.5°	94.9	146.3	710.6	1322.4	1191.0
105°	115.6	167.6	648.4	1396.0	1390.6
107.5°	138.4	189.2	607.8	1373.8	1485.5
110°	161.1	211.0	589.1	1294.8	1487.5

TEST NUMBER: P1026090

CATALOG NUMBER: S124RDIP-B1195D1035UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.8	232.8	580.2	1197.9	1429.2
115°	203.6	255.4	578.2	1111.0	1335.3
117.5°	225.3	276.8	577.2	1042.7	1243.4
120°	247.1	297.5	577.2	996.8	1168.2
122.5°	266.9	317.8	576.2	966.6	1108.9
125°	283.7	337.0	575.2	945.4	1065.5
127.5°	299.5	354.8	573.2	925.1	1037.8
130°	312.3	372.1	572.3	900.9	1014.1
132.5°	325.2	387.0	571.3	872.2	987.4
135°	337.0	401.2	570.3	839.1	952.8
137.5°	348.9	413.6	570.3	803.6	912.3
140°	361.7	425.0	569.3	769.0	867.8
142.5°	375.6	435.4	569.3	736.8	820.3
145°	388.4	444.8	567.3	707.6	777.8
147.5°	403.3	453.6	564.4	683.4	738.3
150°	417.1	462.0	561.4	661.2	705.7
152.5°	429.9	470.0	556.4	642.4	676.0
155°	441.8	476.9	551.5	624.7	651.3
157.5°	453.7	483.3	546.6	607.8	628.6
160°	464.5	488.8	540.6	591.0	607.8
162.5°	474.4	493.2	534.7	574.8	588.1
165°	481.3	496.2	528.8	559.9	568.3
167.5°	489.2	498.6	522.8	547.0	552.5
170°	494.2	500.6	516.9	534.2	537.7
172.5°	499.1	502.1	511.0	522.8	522.8
175°	502.1	503.1	507.0	513.9	512.0
177.5°	504.1	503.1	504.1	507.5	504.1
180°	503.1	503.1	503.1	503.1	503.1

(END OF REPORT)