

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026647

Luminaire Tested: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026647
REPORT IS A COMBINATION OF REPORTS P999777 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D590UB50-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5076.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026647

CATALOG NUMBER: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026647

CATALOG NUMBER: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41
4	77	66	58	52	72	62	55	50	55	50	45	48	44	40	42	39	36
5	71	59	51	45	66	56	49	43	49	44	39	44	39	35	38	34	32
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	35	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1026647

CATALOG NUMBER: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.5
10°-20°	352.1	6.9
20°-30°	508.3	10.0
30°-40°	576.1	11.3
40°-50°	556.3	11.0
50°-60°	462.5	9.1
60°-70°	319.2	6.3
70°-80°	161.3	3.2
80°-90°	42.5	0.8
90°-100°	46.3	0.9
100°-110°	138.7	2.7
110°-120°	235.6	4.6
120°-130°	310.8	6.1
130°-140°	349.1	6.9
140°-150°	343.1	6.8
150°-160°	288.6	5.7
160°-170°	192.0	3.8
170°-180°	67.2	1.3
0°-30°	986.7	19.4
0°-40°	1562.8	30.8
0°-60°	2581.6	50.9
0°-90°	3104.5	61.2
90°-120°	420.7	8.3
90°-150°	1423.7	28.0
90°-180°	1971.0	38.8
0°-180°	5076.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	2	8	12	15	16	6
95°	33	38	42	43	43	36
105°	128	129	131	132	134	136
115°	240	240	238	238	237	236
125°	349	349	348	347	346	311
135°	450	453	453	452	451	348
145°	547	549	550	549	547	342
155°	626	626	626	628	626	288
165°	682	680	679	682	680	192
175°	709	707	706	710	706	67
180°	710	710	710	710	710	

TEST NUMBER: P1026647

CATALOG NUMBER: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	1.6	7.7	12.1	15.4	16.5
92.5°	14.3	21.4	24.2	25.8	26.4
95°	33.0	37.9	41.8	43.4	43.4
97.5°	52.8	57.2	61.5	63.7	63.7
100°	76.9	79.1	84.1	85.2	85.2
102.5°	102.2	102.8	107.2	108.8	109.4
105°	128.0	128.6	130.8	132.4	134.1
107.5°	155.0	155.5	156.1	158.3	157.7
110°	182.4	183.5	183.0	181.9	183.5



TEST NUMBER: P1026647

CATALOG NUMBER: S124RDIP-B795D590UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.0	211.0	209.9	209.9	209.9
115°	239.6	239.6	238.5	237.9	237.4
117.5°	266.5	266.5	266.0	264.3	262.7
120°	293.4	295.6	294.0	291.2	292.3
122.5°	321.5	322.0	321.5	319.8	317.1
125°	348.9	348.9	348.4	347.3	346.2
127.5°	373.7	375.3	374.2	373.1	372.6
130°	400.1	401.7	401.7	400.6	398.4
132.5°	427.0	428.1	427.5	426.4	425.9
135°	450.1	453.4	453.4	452.3	450.6
137.5°	475.9	477.5	478.6	477.0	477.5
140°	501.7	502.8	502.8	502.3	501.7
142.5°	525.3	526.4	525.9	525.9	525.9
145°	546.8	549.0	549.5	549.0	547.3
147.5°	568.8	571.5	571.0	570.4	569.9
150°	588.5	590.7	590.7	590.7	590.2
152.5°	607.2	608.3	608.9	610.5	608.9
155°	626.5	626.5	625.9	628.1	625.9
157.5°	642.9	641.8	641.8	643.5	641.8
160°	657.2	656.7	656.1	657.8	655.0
162.5°	670.4	668.8	668.2	671.5	668.8
165°	682.0	680.3	679.2	682.5	680.3
167.5°	691.3	689.1	689.1	692.4	689.1
170°	699.0	696.3	696.8	700.1	696.3
172.5°	704.5	702.3	702.3	706.1	702.3
175°	709.4	706.7	706.1	710.0	706.1
177.5°	711.6	708.9	708.9	712.7	708.3
180°	710.5	710.5	710.5	710.5	710.5

(END OF REPORT)