

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026658

Luminaire Tested: S124RDIP-B795D810UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026658
REPORT IS A COMBINATION OF REPORTS P999798 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D810UB30-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6388.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026658

CATALOG NUMBER: S124RDIP-B795D810UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026658

CATALOG NUMBER: S124RDIP-B795D810UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	50	49	48	48	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	41	41	37
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	31	31	27
5	69	58	49	44	63	54	46	41	46	40	36	39	35	31	32	29	27	27	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1026658

CATALOG NUMBER: S124RDIP-B795D810UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.1
10°-20°	366.2	5.7
20°-30°	528.7	8.3
30°-40°	599.1	9.4
40°-50°	578.5	9.1
50°-60°	480.9	7.5
60°-70°	331.9	5.2
70°-80°	167.7	2.6
80°-90°	44.7	0.7
90°-100°	33.9	0.5
100°-110°	223.2	3.5
110°-120°	426.1	6.7
120°-130°	541.0	8.5
130°-140°	578.7	9.1
140°-150°	541.2	8.5
150°-160°	436.4	6.8
160°-170°	281.4	4.4
170°-180°	97.0	1.5
0°-30°	1026.2	16.1
0°-40°	1625.3	25.4
0°-60°	2684.7	42.0
0°-90°	3229.1	50.5
90°-120°	683.2	10.7
90°-150°	2344.0	36.7
90°-180°	3159.0	49.5
0°-180°	6388.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	2	11	17	21	23	6
95°	42	16	17	21	22	52
105°	230	234	238	245	218	241
115°	429	431	431	432	432	422
125°	603	606	605	607	608	539
135°	748	748	751	752	754	577
145°	863	865	865	866	867	539
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1026658

CATALOG NUMBER: S124RDIP-B795D810UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	2.3	10.7	16.8	21.4	22.9
92.5°	11.5	9.9	16.0	20.6	20.6
95°	42.0	16.0	16.8	21.4	22.1
97.5°	80.2	97.0	16.8	20.6	21.4
100°	125.2	139.0	33.6	20.6	21.4
102.5°	175.6	184.8	193.9	22.1	22.1
105°	229.8	234.4	238.2	245.1	217.6
107.5°	279.5	281.7	287.1	290.9	294.0
110°	329.9	332.1	336.7	338.2	340.5

TEST NUMBER: P1026658

CATALOG NUMBER: S124RDIP-B795D810UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	383.3	384.8	384.1	387.1
115°	429.1	431.4	430.6	432.2	432.2
117.5°	474.2	477.2	479.5	478.7	478.7
120°	520.0	523.0	522.3	523.8	522.3
122.5°	562.7	564.3	565.8	566.5	565.0
125°	603.2	606.3	604.7	607.0	607.8
127.5°	642.1	642.9	646.7	646.0	645.2
130°	679.6	680.3	682.6	683.4	683.4
132.5°	713.9	715.4	718.5	719.3	718.5
135°	748.3	747.5	750.6	752.1	753.6
137.5°	778.8	778.8	782.6	784.2	783.4
140°	808.6	810.1	811.6	813.9	814.7
142.5°	835.3	838.4	839.1	840.7	840.7
145°	862.8	865.1	865.1	865.9	867.4
147.5°	884.2	888.8	888.0	888.8	889.5
150°	907.9	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)