

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026101

Luminaire Tested: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026101
REPORT IS A COMBINATION OF REPORTS P999051 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8330.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026101

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026101

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	45	42	39
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	29	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16947	16947	16947
5°	16949	16444	16445
10°	16805	15925	15736
15°	16574	15279	14898
20°	16271	14542	13943
25°	15893	13747	13009
30°	15524	12937	11962
35°	15117	12115	10938
40°	14633	11230	9886
45°	14180	10353	8844
50°	13663	9394	7786
55°	13106	8412	6695
60°	12487	7368	5616
65°	11891	6172	4579
70°	11041	4913	3498
75°	9951	3573	2447
80°	8312	2194	1758
85°	6251	1263	966

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14180 cd/sqm

TEST NUMBER: P1026101

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	2.3
10°-20°	544.9	6.5
20°-30°	786.7	9.4
30°-40°	891.6	10.7
40°-50°	860.8	10.3
50°-60°	715.7	8.6
60°-70°	494.0	5.9
70°-80°	249.6	3.0
80°-90°	66.1	0.8
90°-100°	82.8	1.0
100°-110°	248.1	3.0
110°-120°	421.4	5.1
120°-130°	555.8	6.7
130°-140°	624.2	7.5
140°-150°	613.5	7.4
150°-160°	516.0	6.2
160°-170°	343.3	4.1
170°-180°	120.2	1.4
0°-30°	1527.0	18.3
0°-40°	2418.5	29.0
0°-60°	3995.0	48.0
0°-90°	4804.7	57.7
90°-120°	752.3	9.0
90°-150°	2545.8	30.6
90°-180°	3525.0	42.3
0°-180°	8330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2069	2050	2066	2062	197
15°	1976	1962	1922	1919	1908	557
25°	1787	1758	1693	1666	1650	823
35°	1545	1494	1415	1361	1332	966
45°	1260	1201	1106	1028	999	972
55°	955	891	788	705	675	854
65°	649	581	479	411	392	641
75°	345	286	212	175	166	364
85°	86	54	49	46	46	94
90°	3	14	22	28	30	9
95°	59	68	75	78	78	64
105°	229	230	234	237	240	243
115°	428	428	426	426	424	423
125°	624	624	623	621	619	556
135°	805	811	811	809	806	623
145°	978	982	983	982	979	612
155°	1120	1120	1119	1123	1119	516
165°	1219	1216	1214	1220	1216	344
175°	1269	1264	1263	1270	1263	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1026101

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2078.2	2078.2	2078.2	2078.2	2078.2
2.5°	2084.6	2078.2	2060.7	2078.2	2076.7
5°	2075.1	2068.7	2049.6	2065.5	2062.3
7.5°	2060.7	2054.4	2030.5	2041.6	2036.9
10°	2038.5	2030.5	2001.9	2008.2	2001.9
12.5°	2009.8	2000.3	1965.3	1968.4	1958.9
15°	1976.4	1962.1	1922.3	1919.1	1908.0
17.5°	1938.2	1917.5	1871.4	1863.4	1847.5
20°	1892.1	1871.4	1817.3	1804.5	1783.9
22.5°	1841.1	1817.3	1758.4	1737.7	1721.8
25°	1787.0	1758.4	1693.1	1666.1	1650.2
27.5°	1731.3	1696.3	1627.9	1596.1	1573.8
30°	1672.5	1632.7	1557.9	1518.1	1492.6
32.5°	1610.4	1564.3	1486.3	1438.5	1414.7
35°	1545.2	1494.2	1414.7	1360.6	1331.9
37.5°	1476.7	1424.2	1336.7	1277.8	1249.2
40°	1403.5	1351.0	1260.3	1193.5	1164.8
42.5°	1333.5	1277.8	1182.3	1113.9	1083.7
45°	1260.3	1201.4	1106.0	1028.0	999.3
47.5°	1185.5	1125.1	1026.4	945.2	913.4
50°	1109.1	1047.1	945.2	865.7	835.4
52.5°	1031.2	970.7	865.7	784.5	752.7
55°	954.8	891.1	787.7	704.9	674.7
57.5°	880.0	813.2	711.3	627.0	604.7
60°	798.8	735.2	633.3	550.6	525.1
62.5°	725.6	658.8	553.8	479.0	459.9
65°	649.3	580.8	479.0	410.6	391.5
67.5°	569.7	504.4	409.0	348.5	326.2
70°	494.9	428.1	337.4	284.8	268.9
72.5°	415.3	356.5	272.1	229.1	214.8
75°	345.3	286.4	211.6	175.0	165.5
77.5°	272.1	221.2	157.5	132.1	128.9
80°	202.1	155.9	108.2	103.4	101.8
82.5°	141.6	100.3	78.0	74.8	73.2
85°	85.9	54.1	49.3	46.1	46.1
87.5°	36.6	23.9	22.3	20.7	22.3
90°	2.9	13.8	21.6	27.5	29.5
92.5°	25.5	38.3	43.2	46.2	47.2
95°	59.0	67.8	74.7	77.6	77.6
97.5°	94.3	102.2	110.1	114.0	114.0
100°	137.6	141.5	150.3	152.3	152.3
102.5°	182.8	183.8	191.6	194.6	195.5
105°	229.0	229.9	233.9	236.8	239.8
107.5°	277.1	278.1	279.1	283.0	282.0
110°	326.2	328.2	327.2	325.3	328.2

TEST NUMBER: P1026101

CATALOG NUMBER: S124RDIP-B1195D1035UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.3	377.3	375.4	375.4	375.4
115°	428.4	428.4	426.5	425.5	424.5
117.5°	476.6	476.6	475.6	472.6	469.7
120°	524.7	528.7	525.7	520.8	522.8
122.5°	574.8	575.8	574.8	571.9	567.0
125°	624.0	624.0	623.0	621.0	619.1
127.5°	668.2	671.1	669.2	667.2	666.2
130°	715.4	718.3	718.3	716.3	712.4
132.5°	763.5	765.5	764.5	762.5	761.5
135°	804.8	810.7	810.7	808.7	805.8
137.5°	851.0	853.9	855.9	852.9	853.9
140°	897.1	899.1	899.1	898.1	897.1
142.5°	939.4	941.4	940.4	940.4	940.4
145°	977.7	981.6	982.6	981.6	978.7
147.5°	1017.0	1021.9	1021.0	1020.0	1019.0
150°	1052.4	1056.3	1056.3	1056.3	1055.3
152.5°	1085.8	1087.8	1088.8	1091.7	1088.8
155°	1120.2	1120.2	1119.2	1123.1	1119.2
157.5°	1149.7	1147.7	1147.7	1150.7	1147.7
160°	1175.2	1174.2	1173.3	1176.2	1171.3
162.5°	1198.8	1195.9	1194.9	1200.8	1195.9
165°	1219.4	1216.5	1214.5	1220.4	1216.5
167.5°	1236.1	1232.2	1232.2	1238.1	1232.2
170°	1249.9	1245.0	1246.0	1251.9	1245.0
172.5°	1259.7	1255.8	1255.8	1262.7	1255.8
175°	1268.6	1263.7	1262.7	1269.6	1262.7
177.5°	1272.5	1267.6	1267.6	1274.5	1266.6
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)