

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026666

Luminaire Tested: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026666
REPORT IS A COMBINATION OF REPORTS P999806 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D810UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6091.7 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026666

CATALOG NUMBER: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026666

CATALOG NUMBER: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	63	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1026666

CATALOG NUMBER: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	2.2
10°-20°	367.8	6.0
20°-30°	530.9	8.7
30°-40°	601.7	9.9
40°-50°	581.0	9.5
50°-60°	483.0	7.9
60°-70°	333.4	5.5
70°-80°	168.5	2.8
80°-90°	44.3	0.7
90°-100°	290.0	4.8
100°-110°	589.8	9.7
110°-120°	525.7	8.6
120°-130°	441.6	7.2
130°-140°	368.5	6.0
140°-150°	281.4	4.6
150°-160°	197.8	3.2
160°-170°	116.4	1.9
170°-180°	37.8	0.6
0°-30°	1030.6	16.9
0°-40°	1632.3	26.8
0°-60°	2696.4	44.3
0°-90°	3242.5	53.2
90°-120°	1405.6	23.1
90°-150°	2497.2	41.0
90°-180°	2849.0	46.8
0°-180°	6091.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	1	6	14	15	16	5
95°	25	80	625	310	187	28
105°	90	130	503	1083	1079	96
115°	158	198	449	862	1036	157
125°	220	262	446	734	827	196
135°	262	311	443	651	739	202
145°	301	345	440	549	604	189
155°	343	370	428	485	506	158
165°	374	385	410	434	441	106
175°	390	390	394	399	397	37
180°	390	390	390	390	390	

TEST NUMBER: P1026666

CATALOG NUMBER: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	0.8	6.1	13.8	15.3	16.1
92.5°	10.7	59.0	300.7	99.3	69.8
95°	25.3	79.8	625.1	309.5	187.2
97.5°	42.2	88.2	668.8	632.0	449.5
100°	58.3	99.7	616.7	874.4	703.4
102.5°	73.6	113.5	551.5	1026.2	924.3
105°	89.7	130.0	503.2	1083.4	1079.2
107.5°	107.4	146.9	471.7	1066.2	1152.8
110°	125.0	163.8	457.1	1004.8	1154.4

TEST NUMBER: P1026666

CATALOG NUMBER: S124RDIP-B795D810UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	180.6	450.2	929.6	1109.1
115°	158.0	198.2	448.7	862.1	1036.2
117.5°	174.9	214.8	447.9	809.2	964.9
120°	191.8	230.8	447.9	773.6	906.6
122.5°	207.1	246.6	447.2	750.2	860.6
125°	220.1	261.6	446.4	733.7	826.8
127.5°	232.4	275.4	444.9	718.0	805.4
130°	242.4	288.8	444.1	699.2	787.0
132.5°	252.3	300.2	443.3	676.9	766.2
135°	261.6	311.4	442.6	651.2	739.4
137.5°	270.8	321.0	442.6	623.6	708.0
140°	280.7	329.8	441.8	596.7	673.4
142.5°	291.5	337.8	441.8	571.8	636.6
145°	301.4	345.2	440.3	549.2	603.6
147.5°	312.9	352.0	438.0	530.4	573.0
150°	323.7	358.6	435.7	513.1	547.6
152.5°	333.7	364.7	431.8	498.6	524.6
155°	342.9	370.0	428.0	484.8	505.5
157.5°	352.1	375.1	424.2	471.8	487.8
160°	360.5	379.3	419.6	458.6	471.7
162.5°	368.2	382.8	415.0	446.0	456.4
165°	373.5	385.0	410.4	434.5	441.0
167.5°	379.7	387.0	405.8	424.6	428.8
170°	383.5	388.5	401.1	414.6	417.3
172.5°	387.3	389.6	396.5	405.8	405.8
175°	389.6	390.4	393.5	398.8	397.3
177.5°	391.2	390.4	391.2	393.8	391.2
180°	390.4	390.4	390.4	390.4	390.4

(END OF REPORT)