

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026670

Luminaire Tested: S124RDIP-B795D810UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026670
REPORT IS A COMBINATION OF REPORTS P999810 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D810UB40-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6351.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026670

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026670

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	50	49	48	48	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	41	41	37
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	31	31	27
5	69	58	49	44	63	54	46	41	46	40	36	39	35	31	32	29	27	27	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11322	11322	11322
5°	11323	10985	10986
10°	11227	10639	10512
15°	11072	10207	9952
20°	10870	9715	9314
25°	10617	9184	8691
30°	10371	8643	7991
35°	10099	8094	7307
40°	9776	7503	6605
45°	9473	6916	5908
50°	9128	6276	5202
55°	8755	5619	4472
60°	8343	4923	3752
65°	7942	4123	3058
70°	7376	3282	2338
75°	6648	2388	1635
80°	5552	1466	1175
85°	4177	846	646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9473 cd/sqm

TEST NUMBER: P1026670

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.1
10°-20°	364.0	5.7
20°-30°	525.5	8.3
30°-40°	595.6	9.4
40°-50°	575.1	9.1
50°-60°	478.1	7.5
60°-70°	330.0	5.2
70°-80°	166.8	2.6
80°-90°	44.4	0.7
90°-100°	33.7	0.5
100°-110°	221.9	3.5
110°-120°	423.7	6.7
120°-130°	537.9	8.5
130°-140°	575.4	9.1
140°-150°	538.1	8.5
150°-160°	433.9	6.8
160°-170°	279.8	4.4
170°-180°	96.4	1.5
0°-30°	1020.1	16.1
0°-40°	1615.7	25.4
0°-60°	2668.9	42.0
0°-90°	3210.1	50.5
90°-120°	679.3	10.7
90°-150°	2330.7	36.7
90°-180°	3141.0	49.5
0°-180°	6351.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1369	1380	1378	132
15°	1320	1311	1284	1282	1275	372
25°	1194	1175	1131	1113	1102	550
35°	1032	998	945	909	890	645
45°	842	803	739	687	668	649
55°	638	595	526	471	451	571
65°	434	388	320	274	262	428
75°	231	191	141	117	111	243
85°	57	36	33	31	31	63
90°	2	11	17	21	23	6
95°	42	16	17	21	22	51
105°	228	233	237	244	216	239
115°	427	429	428	430	430	420
125°	600	603	601	604	604	536
135°	744	743	746	748	749	573
145°	858	860	860	861	862	536
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1026670

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1392.6	1388.4	1376.7	1388.4	1387.3
5°	1386.3	1382.0	1369.2	1379.9	1377.7
7.5°	1376.7	1372.4	1356.5	1363.9	1360.7
10°	1361.8	1356.5	1337.4	1341.6	1337.4
12.5°	1342.7	1336.3	1312.9	1315.0	1308.6
15°	1320.3	1310.8	1284.2	1282.1	1274.6
17.5°	1294.8	1281.0	1250.2	1244.9	1234.2
20°	1264.0	1250.2	1214.0	1205.5	1191.7
22.5°	1230.0	1214.0	1174.7	1160.9	1150.3
25°	1193.8	1174.7	1131.1	1113.0	1102.4
27.5°	1156.6	1133.2	1087.5	1066.3	1051.4
30°	1117.3	1090.7	1040.8	1014.2	997.2
32.5°	1075.8	1045.0	992.9	961.0	945.1
35°	1032.2	998.2	945.1	908.9	889.8
37.5°	986.5	951.5	893.0	853.7	834.5
40°	937.6	902.6	842.0	797.3	778.2
42.5°	890.9	853.7	789.9	744.2	724.0
45°	842.0	802.6	738.8	686.7	667.6
47.5°	792.0	751.6	685.7	631.5	610.2
50°	741.0	699.5	631.5	578.3	558.1
52.5°	688.9	648.5	578.3	524.1	502.8
55°	637.8	595.3	526.2	470.9	450.7
57.5°	587.9	543.2	475.2	418.9	404.0
60°	533.7	491.1	423.1	367.8	350.8
62.5°	484.8	440.1	370.0	320.0	307.2
65°	433.7	388.0	320.0	274.3	261.5
67.5°	380.6	337.0	273.2	232.8	217.9
70°	330.6	286.0	225.4	190.3	179.7
72.5°	277.5	238.1	181.8	153.1	143.5
75°	230.7	191.4	141.4	116.9	110.6
77.5°	181.8	147.8	105.2	88.2	86.1
80°	135.0	104.2	72.3	69.1	68.0
82.5°	94.6	67.0	52.1	50.0	48.9
85°	57.4	36.1	33.0	30.8	30.8
87.5°	24.5	15.9	14.9	13.8	14.9
90°	2.3	10.6	16.7	21.3	22.8
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.8	15.9	16.7	21.3	22.0
97.5°	79.7	96.4	16.7	20.5	21.3
100°	124.5	138.2	33.4	20.5	21.3
102.5°	174.6	183.7	192.8	22.0	22.0
105°	228.5	233.1	236.9	243.7	216.4
107.5°	277.9	280.1	285.5	289.3	292.3
110°	328.0	330.2	334.8	336.3	338.6

TEST NUMBER: P1026670

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.6	381.1	382.6	381.9	384.9
115°	426.7	428.9	428.2	429.7	429.7
117.5°	471.5	474.5	476.8	476.0	476.0
120°	517.0	520.0	519.3	520.8	519.3
122.5°	559.5	561.0	562.6	563.3	561.8
125°	599.8	602.8	601.3	603.6	604.3
127.5°	638.5	639.2	643.0	642.3	641.5
130°	675.7	676.4	678.7	679.5	679.5
132.5°	709.8	711.4	714.4	715.2	714.4
135°	744.0	743.3	746.3	747.8	749.3
137.5°	774.4	774.4	778.2	779.7	778.9
140°	804.0	805.5	807.0	809.3	810.1
142.5°	830.6	833.6	834.4	835.9	835.9
145°	857.9	860.2	860.2	860.9	862.4
147.5°	879.1	883.7	882.9	883.7	884.5
150°	902.7	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)