

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026671

Luminaire Tested: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026671
REPORT IS A COMBINATION OF REPORTS P999811 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D810UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5934.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026671

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026671

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11322	11322	11322
5°	11323	10985	10986
10°	11227	10639	10512
15°	11072	10207	9952
20°	10870	9715	9314
25°	10617	9184	8691
30°	10371	8643	7991
35°	10099	8094	7307
40°	9776	7503	6605
45°	9473	6916	5908
50°	9128	6276	5202
55°	8755	5619	4472
60°	8343	4923	3752
65°	7942	4123	3058
70°	7376	3282	2338
75°	6648	2388	1635
80°	5552	1466	1175
85°	4177	846	646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9473 cd/sqm

TEST NUMBER: P1026671

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	2.2
10°-20°	364.0	6.1
20°-30°	525.5	8.9
30°-40°	595.6	10.0
40°-50°	575.1	9.7
50°-60°	478.1	8.1
60°-70°	330.0	5.6
70°-80°	166.8	2.8
80°-90°	44.4	0.7
90°-100°	64.0	1.1
100°-110°	191.7	3.2
110°-120°	325.6	5.5
120°-130°	429.4	7.2
130°-140°	482.3	8.1
140°-150°	474.0	8.0
150°-160°	398.7	6.7
160°-170°	265.3	4.5
170°-180°	92.9	1.6
0°-30°	1020.1	17.2
0°-40°	1615.7	27.2
0°-60°	2668.9	45.0
0°-90°	3210.1	54.1
90°-120°	581.3	9.8
90°-150°	1967.0	33.1
90°-180°	2724.0	45.9
0°-180°	5934.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1369	1380	1378	132
15°	1320	1311	1284	1282	1275	372
25°	1194	1175	1131	1113	1102	550
35°	1032	998	945	909	890	645
45°	842	803	739	687	668	649
55°	638	595	526	471	451	571
65°	434	388	320	274	262	428
75°	231	191	141	117	111	243
85°	57	36	33	31	31	63
90°	2	11	17	21	23	7
95°	46	52	58	60	60	49
105°	177	178	181	183	185	188
115°	331	331	330	329	328	326
125°	482	482	481	480	478	430
135°	622	626	626	625	623	481
145°	756	758	759	758	756	473
155°	866	866	865	868	865	398
165°	942	940	938	943	940	266
175°	980	976	976	981	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1026671

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1392.6	1388.4	1376.7	1388.4	1387.3
5°	1386.3	1382.0	1369.2	1379.9	1377.7
7.5°	1376.7	1372.4	1356.5	1363.9	1360.7
10°	1361.8	1356.5	1337.4	1341.6	1337.4
12.5°	1342.7	1336.3	1312.9	1315.0	1308.6
15°	1320.3	1310.8	1284.2	1282.1	1274.6
17.5°	1294.8	1281.0	1250.2	1244.9	1234.2
20°	1264.0	1250.2	1214.0	1205.5	1191.7
22.5°	1230.0	1214.0	1174.7	1160.9	1150.3
25°	1193.8	1174.7	1131.1	1113.0	1102.4
27.5°	1156.6	1133.2	1087.5	1066.3	1051.4
30°	1117.3	1090.7	1040.8	1014.2	997.2
32.5°	1075.8	1045.0	992.9	961.0	945.1
35°	1032.2	998.2	945.1	908.9	889.8
37.5°	986.5	951.5	893.0	853.7	834.5
40°	937.6	902.6	842.0	797.3	778.2
42.5°	890.9	853.7	789.9	744.2	724.0
45°	842.0	802.6	738.8	686.7	667.6
47.5°	792.0	751.6	685.7	631.5	610.2
50°	741.0	699.5	631.5	578.3	558.1
52.5°	688.9	648.5	578.3	524.1	502.8
55°	637.8	595.3	526.2	470.9	450.7
57.5°	587.9	543.2	475.2	418.9	404.0
60°	533.7	491.1	423.1	367.8	350.8
62.5°	484.8	440.1	370.0	320.0	307.2
65°	433.7	388.0	320.0	274.3	261.5
67.5°	380.6	337.0	273.2	232.8	217.9
70°	330.6	286.0	225.4	190.3	179.7
72.5°	277.5	238.1	181.8	153.1	143.5
75°	230.7	191.4	141.4	116.9	110.6
77.5°	181.8	147.8	105.2	88.2	86.1
80°	135.0	104.2	72.3	69.1	68.0
82.5°	94.6	67.0	52.1	50.0	48.9
85°	57.4	36.1	33.0	30.8	30.8
87.5°	24.5	15.9	14.9	13.8	14.9
90°	2.3	10.6	16.7	21.3	22.8
92.5°	19.7	29.6	33.4	35.7	36.4
95°	45.6	52.4	57.7	60.0	60.0
97.5°	72.9	79.0	85.0	88.1	88.1
100°	106.3	109.3	116.2	117.7	117.7
102.5°	141.2	142.0	148.1	150.3	151.1
105°	176.9	177.7	180.7	183.0	185.3
107.5°	214.1	214.9	215.6	218.7	217.9
110°	252.1	253.6	252.8	251.3	253.6

TEST NUMBER: P1026671

CATALOG NUMBER: S124RDIP-B795D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.6	291.6	290.0	290.0	290.0
115°	331.0	331.0	329.5	328.8	328.0
117.5°	368.2	368.2	367.5	365.2	362.9
120°	405.4	408.5	406.2	402.4	403.9
122.5°	444.2	444.9	444.2	441.9	438.1
125°	482.1	482.1	481.4	479.8	478.3
127.5°	516.3	518.6	517.1	515.5	514.8
130°	552.7	555.0	555.0	553.5	550.5
132.5°	589.9	591.5	590.7	589.2	588.4
135°	621.8	626.4	626.4	624.9	622.6
137.5°	657.5	659.8	661.3	659.0	659.8
140°	693.2	694.7	694.7	694.0	693.2
142.5°	725.8	727.4	726.6	726.6	726.6
145°	755.5	758.5	759.3	758.5	756.2
147.5°	785.8	789.6	788.9	788.1	787.3
150°	813.2	816.2	816.2	816.2	815.4
152.5°	839.0	840.5	841.3	843.5	841.3
155°	865.6	865.6	864.8	867.8	864.8
157.5°	888.3	886.8	886.8	889.1	886.8
160°	908.1	907.3	906.5	908.8	905.0
162.5°	926.3	924.0	923.3	927.8	924.0
165°	942.2	940.0	938.4	943.0	940.0
167.5°	955.1	952.1	952.1	956.7	952.1
170°	965.8	962.0	962.7	967.3	962.0
172.5°	973.4	970.3	970.3	975.6	970.3
175°	980.2	976.4	975.6	981.0	975.6
177.5°	983.2	979.4	979.4	984.8	978.7
180°	981.7	981.7	981.7	981.7	981.7

(END OF REPORT)