

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026676

Luminaire Tested: S124RDIP-B795D810UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026676
REPORT IS A COMBINATION OF REPORTS P999816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D810UB50-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6143.0 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026676

CATALOG NUMBER: S124RDIP-B795D810UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1026676

CATALOG NUMBER: S124RDIP-B795D810UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	50	49	48
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	49	44	63	54	46	41	46	40	36	39	35	31	32	29	27
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1026676

CATALOG NUMBER: S124RDIP-B795D810UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.1
10°-20°	352.1	5.7
20°-30°	508.3	8.3
30°-40°	576.1	9.4
40°-50°	556.3	9.1
50°-60°	462.5	7.5
60°-70°	319.2	5.2
70°-80°	161.3	2.6
80°-90°	43.0	0.7
90°-100°	32.6	0.5
100°-110°	214.6	3.5
110°-120°	409.8	6.7
120°-130°	520.3	8.5
130°-140°	556.6	9.1
140°-150°	520.4	8.5
150°-160°	419.7	6.8
160°-170°	270.7	4.4
170°-180°	93.3	1.5
0°-30°	986.7	16.1
0°-40°	1562.8	25.4
0°-60°	2581.6	42.0
0°-90°	3105.0	50.5
90°-120°	657.0	10.7
90°-150°	2254.3	36.7
90°-180°	3038.0	49.5
0°-180°	6143.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	2	10	16	21	22	5
95°	40	15	16	21	21	50
105°	221	225	229	236	209	231
115°	413	415	414	416	416	406
125°	580	583	582	584	584	518
135°	720	719	722	723	725	554
145°	830	832	832	833	834	518
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1026676

CATALOG NUMBER: S124RDIP-B795D810UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	2.2	10.3	16.2	20.6	22.0
92.5°	11.0	9.5	15.4	19.8	19.8
95°	40.4	15.4	16.2	20.6	21.3
97.5°	77.1	93.3	16.2	19.8	20.6
100°	120.4	133.6	32.3	19.8	20.6
102.5°	168.9	177.7	186.5	21.3	21.3
105°	221.0	225.4	229.1	235.7	209.3
107.5°	268.8	271.0	276.1	279.8	282.7
110°	317.2	319.4	323.8	325.3	327.5

TEST NUMBER: P1026676

CATALOG NUMBER: S124RDIP-B795D810UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	368.6	370.1	369.4	372.3
115°	412.7	414.9	414.2	415.6	415.6
117.5°	456.0	458.9	461.2	460.4	460.4
120°	500.1	503.0	502.3	503.7	502.3
122.5°	541.2	542.7	544.1	544.9	543.4
125°	580.1	583.0	581.6	583.8	584.5
127.5°	617.6	618.3	622.0	621.2	620.5
130°	653.5	654.3	656.5	657.2	657.2
132.5°	686.6	688.1	691.0	691.7	691.0
135°	719.6	718.9	721.8	723.3	724.8
137.5°	749.0	749.0	752.7	754.1	753.4
140°	777.6	779.1	780.6	782.8	783.5
142.5°	803.3	806.3	807.0	808.5	808.5
145°	829.8	832.0	832.0	832.7	834.2
147.5°	850.3	854.7	854.0	854.7	855.5
150°	873.1	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)