

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026150

Luminaire Tested: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026150
REPORT IS A COMBINATION OF REPORTS P999120 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6150.6 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026150

CATALOG NUMBER: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026150

CATALOG NUMBER: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	79			
1	105	100	96	93	100	96	93	89	88	85	83	80	78	76	74	72	70	67			
2	96	88	82	77	91	84	79	74	78	73	69	71	68	64	65	62	60	57			
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52	49			
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45	42			
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	47	43	39	37			
6	68	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32			
7	64	51	43	37	61	49	41	36	46	39	34	42	37	33	39	35	31	29			
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26			
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	25	23			
10	52	39	32	27	50	38	31	26	36	30	25	33	28	24	31	27	23	21			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1026150

CATALOG NUMBER: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	3.2
10°-20°	547.9	8.9
20°-30°	791.1	12.9
30°-40°	896.6	14.6
40°-50°	865.7	14.1
50°-60°	719.7	11.7
60°-70°	496.8	8.1
70°-80°	251.0	4.1
80°-90°	64.4	1.0
90°-100°	134.4	2.2
100°-110°	273.5	4.4
110°-120°	243.7	4.0
120°-130°	204.7	3.3
130°-140°	170.9	2.8
140°-150°	130.5	2.1
150°-160°	91.7	1.5
160°-170°	53.9	0.9
170°-180°	17.5	0.3
0°-30°	1535.6	25.0
0°-40°	2432.1	39.5
0°-60°	4017.5	65.3
0°-90°	4829.7	78.5
90°-120°	651.6	10.6
90°-150°	1157.7	18.8
90°-180°	1321.0	21.5
0°-180°	6150.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	0	3	6	7	8	6
95°	12	37	290	143	87	13
105°	42	60	233	502	500	44
115°	73	92	208	400	480	73
125°	102	121	207	340	383	91
135°	121	144	205	302	343	94
145°	140	160	204	255	280	88
155°	159	172	198	225	234	73
165°	173	178	190	201	204	49
175°	181	181	182	185	184	17
180°	181	181	181	181	181	

TEST NUMBER: P1026150

CATALOG NUMBER: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	0.4	2.8	6.4	7.1	7.5
92.5°	5.0	27.4	139.4	46.0	32.4
95°	11.7	37.0	289.8	143.4	86.8
97.5°	19.6	40.9	310.1	293.0	208.4
100°	27.0	46.2	285.9	405.4	326.1
102.5°	34.1	52.6	255.7	475.8	428.5
105°	41.6	60.2	233.3	502.3	500.3
107.5°	49.8	68.1	218.7	494.3	534.5
110°	58.0	75.9	211.9	465.8	535.2

TEST NUMBER: P1026150

CATALOG NUMBER: S124RDIP-B1195D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.8	83.7	208.7	431.0	514.2
115°	73.3	91.9	208.0	399.7	480.4
117.5°	81.1	99.6	207.7	375.2	447.4
120°	88.9	107.0	207.7	358.6	420.3
122.5°	96.0	114.3	207.3	347.8	399.0
125°	102.1	121.2	207.0	340.2	383.3
127.5°	107.7	127.6	206.3	332.8	373.4
130°	112.4	133.8	205.9	324.2	364.9
132.5°	117.0	139.2	205.5	313.8	355.2
135°	121.3	144.4	205.2	301.9	342.8
137.5°	125.5	148.9	205.2	289.1	328.2
140°	130.2	152.9	204.8	276.6	312.2
142.5°	135.1	156.6	204.8	265.1	295.2
145°	139.8	160.0	204.1	254.6	279.9
147.5°	145.1	163.2	203.1	245.9	265.6
150°	150.1	166.2	202.0	237.9	253.9
152.5°	154.7	169.1	200.2	231.2	243.2
155°	159.0	171.6	198.4	224.8	234.3
157.5°	163.2	173.9	196.6	218.7	226.2
160°	167.1	175.9	194.5	212.6	218.7
162.5°	170.7	177.4	192.4	206.8	211.6
165°	173.2	178.5	190.2	201.4	204.5
167.5°	176.0	179.4	188.1	196.9	198.8
170°	177.8	180.1	186.0	192.2	193.4
172.5°	179.6	180.6	183.8	188.2	188.1
175°	180.6	181.0	182.4	184.9	184.2
177.5°	181.4	181.0	181.4	182.6	181.4
180°	181.0	181.0	181.0	181.0	181.0

(END OF REPORT)