

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007622

Luminaire Tested: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K
Description: Define 4 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3517.0 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007622

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1007622

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 0°

Luminance: 0 cd/sqm

TEST NUMBER: P1007622

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	82.6	2.3
100°-110°	247.3	7.0
110°-120°	420.1	11.9
120°-130°	554.0	15.8
130°-140°	622.3	17.7
140°-150°	611.6	17.4
150°-160°	514.4	14.6
160°-170°	342.3	9.7
170°-180°	119.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	749.9	21.3
90°-150°	2537.8	72.2
90°-180°	3514.0	99.9
0°-180°	3517.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	14	22	27	29	4
95°	59	68	74	77	77	64
105°	228	229	233	236	239	242
115°	427	427	425	424	423	421
125°	622	622	621	619	617	554
135°	802	808	808	806	803	621
145°	975	979	980	979	976	610
155°	1117	1117	1116	1120	1116	514
165°	1216	1213	1211	1217	1213	343
175°	1265	1260	1259	1266	1259	120
180°	1267	1267	1267	1267	1267	

TEST NUMBER: P1007622

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.9	13.7	21.6	27.4	29.4
92.5°	25.5	38.2	43.1	46.0	47.0
95°	58.8	67.6	74.4	77.4	77.4
97.5°	94.0	101.9	109.7	113.6	113.6
100°	137.1	141.1	149.9	151.8	151.8
102.5°	182.2	183.2	191.0	194.0	194.9
105°	228.2	229.2	233.1	236.1	239.0
107.5°	276.2	277.2	278.2	282.1	281.1
110°	325.2	327.2	326.2	324.2	327.2

TEST NUMBER: P1007622

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.2	376.2	374.2	374.2	374.2
115°	427.1	427.1	425.1	424.2	423.2
117.5°	475.1	475.1	474.1	471.2	468.2
120°	523.1	527.0	524.1	519.2	521.1
122.5°	573.0	574.0	573.0	570.1	565.2
125°	622.0	622.0	621.0	619.1	617.1
127.5°	666.1	669.0	667.1	665.1	664.1
130°	713.1	716.1	716.1	714.1	710.2
132.5°	761.1	763.1	762.1	760.1	759.2
135°	802.3	808.1	808.1	806.2	803.2
137.5°	848.3	851.2	853.2	850.3	851.2
140°	894.3	896.3	896.3	895.3	894.3
142.5°	936.5	938.4	937.4	937.4	937.4
145°	974.7	978.6	979.6	978.6	975.6
147.5°	1013.9	1018.7	1017.8	1016.8	1015.8
150°	1049.1	1053.0	1053.0	1053.0	1052.1
152.5°	1082.4	1084.4	1085.4	1088.3	1085.4
155°	1116.7	1116.7	1115.7	1119.6	1115.7
157.5°	1146.1	1144.1	1144.1	1147.1	1144.1
160°	1171.6	1170.6	1169.6	1172.5	1167.6
162.5°	1195.1	1192.1	1191.2	1197.0	1192.1
165°	1215.6	1212.7	1210.7	1216.6	1212.7
167.5°	1232.3	1228.4	1228.4	1234.3	1228.4
170°	1246.0	1241.1	1242.1	1248.0	1241.1
172.5°	1255.8	1251.9	1251.9	1258.7	1251.9
175°	1264.6	1259.7	1258.7	1265.6	1258.7
177.5°	1268.5	1263.6	1263.6	1270.5	1262.7
180°	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)