

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007625

Luminaire Tested: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3528.0 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007625

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007625

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007625

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	82.8	2.3
100°-110°	248.1	7.0
110°-120°	421.4	11.9
120°-130°	555.8	15.8
130°-140°	624.2	17.7
140°-150°	613.5	17.4
150°-160°	516.0	14.6
160°-170°	343.3	9.7
170°-180°	120.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	752.3	21.3
90°-150°	2545.8	72.2
90°-180°	3525.0	99.9
0°-180°	3528.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	14	22	28	30	4
95°	59	68	75	78	78	64
105°	229	230	234	237	240	243
115°	428	428	426	426	424	423
125°	624	624	623	621	619	556
135°	805	811	811	809	806	623
145°	978	982	983	982	979	612
155°	1120	1120	1119	1123	1119	516
165°	1219	1216	1214	1220	1216	344
175°	1269	1264	1263	1270	1263	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1007625

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.9	13.8	21.6	27.5	29.5
92.5°	25.5	38.3	43.2	46.2	47.2
95°	59.0	67.8	74.7	77.6	77.6
97.5°	94.3	102.2	110.1	114.0	114.0
100°	137.6	141.5	150.3	152.3	152.3
102.5°	182.8	183.8	191.6	194.6	195.5
105°	229.0	229.9	233.9	236.8	239.8
107.5°	277.1	278.1	279.1	283.0	282.0
110°	326.2	328.2	327.2	325.3	328.2

TEST NUMBER: P1007625

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.3	377.3	375.4	375.4	375.4
115°	428.4	428.4	426.5	425.5	424.5
117.5°	476.6	476.6	475.6	472.6	469.7
120°	524.7	528.7	525.7	520.8	522.8
122.5°	574.8	575.8	574.8	571.9	567.0
125°	624.0	624.0	623.0	621.0	619.1
127.5°	668.2	671.1	669.2	667.2	666.2
130°	715.4	718.3	718.3	716.3	712.4
132.5°	763.5	765.5	764.5	762.5	761.5
135°	804.8	810.7	810.7	808.7	805.8
137.5°	851.0	853.9	855.9	852.9	853.9
140°	897.1	899.1	899.1	898.1	897.1
142.5°	939.4	941.4	940.4	940.4	940.4
145°	977.7	981.6	982.6	981.6	978.7
147.5°	1017.0	1021.9	1021.0	1020.0	1019.0
150°	1052.4	1056.3	1056.3	1056.3	1055.3
152.5°	1085.8	1087.8	1088.8	1091.7	1088.8
155°	1120.2	1120.2	1119.2	1123.1	1119.2
157.5°	1149.7	1147.7	1147.7	1150.7	1147.7
160°	1175.2	1174.2	1173.3	1176.2	1171.3
162.5°	1198.8	1195.9	1194.9	1200.8	1195.9
165°	1219.4	1216.5	1214.5	1220.4	1216.5
167.5°	1236.1	1232.2	1232.2	1238.1	1232.2
170°	1249.9	1245.0	1246.0	1251.9	1245.0
172.5°	1259.7	1255.8	1255.8	1262.7	1255.8
175°	1268.6	1263.7	1262.7	1269.6	1262.7
177.5°	1272.5	1267.6	1267.6	1274.5	1266.6
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)