

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007634

Luminaire Tested: S124IP-B1035UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB2750-4F0-XX-W2A_3500K
Description: Define 4 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4109.0 lumens
Efficiency: N/A
Efficacy: 144.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007634

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007634

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007634

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	44.0	1.1
100°-110°	290.1	7.1
110°-120°	553.9	13.5
120°-130°	703.2	17.1
130°-140°	752.3	18.3
140°-150°	703.4	17.1
150°-160°	567.3	13.8
160°-170°	365.8	8.9
170°-180°	126.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	888.1	21.6
90°-150°	3047.1	74.2
90°-180°	4106.0	99.9
0°-180°	4109.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	14	22	28	30	3
95°	55	21	22	28	29	67
105°	299	305	310	319	283	313
115°	558	561	560	562	562	549
125°	784	788	786	789	790	700
135°	973	972	976	978	980	750
145°	1122	1124	1124	1126	1128	701
155°	1230	1231	1228	1232	1229	567
165°	1297	1292	1292	1300	1291	367
175°	1327	1321	1322	1331	1319	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1007634

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.0	13.9	21.8	27.8	29.8
92.5°	14.9	12.9	20.8	26.8	26.8
95°	54.6	20.8	21.8	27.8	28.8
97.5°	104.2	126.1	21.8	26.8	27.8
100°	162.8	180.6	43.7	26.8	27.8
102.5°	228.3	240.2	252.1	28.8	28.8
105°	298.8	304.7	309.7	318.6	282.9
107.5°	363.3	366.2	373.2	378.2	382.1
110°	428.8	431.8	437.7	439.7	442.7

TEST NUMBER: P1007634

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.3	498.3	500.2	499.2	503.2
115°	557.8	560.8	559.8	561.8	561.8
117.5°	616.4	620.3	623.3	622.3	622.3
120°	675.9	679.9	678.9	680.9	678.9
122.5°	731.5	733.5	735.5	736.5	734.5
125°	784.1	788.1	786.1	789.1	790.1
127.5°	834.7	835.7	840.7	839.7	838.7
130°	883.4	884.3	887.3	888.3	888.3
132.5°	928.0	930.0	934.0	935.0	934.0
135°	972.7	971.7	975.7	977.6	979.6
137.5°	1012.4	1012.4	1017.3	1019.3	1018.3
140°	1051.1	1053.1	1055.1	1058.0	1059.0
142.5°	1085.8	1089.8	1090.8	1092.8	1092.8
145°	1121.6	1124.5	1124.5	1125.5	1127.5
147.5°	1149.4	1155.3	1154.3	1155.3	1156.3
150°	1180.1	1184.1	1183.1	1183.1	1184.1
152.5°	1205.9	1208.9	1206.9	1208.9	1207.9
155°	1229.7	1230.7	1227.8	1231.7	1228.8
157.5°	1250.6	1250.6	1246.6	1251.6	1246.6
160°	1268.5	1265.5	1264.5	1270.4	1264.5
162.5°	1284.3	1280.4	1279.4	1285.3	1278.4
165°	1297.2	1292.3	1292.3	1300.2	1291.3
167.5°	1308.2	1303.2	1302.2	1311.1	1301.2
170°	1317.1	1311.1	1312.1	1320.1	1310.1
172.5°	1323.0	1317.1	1318.1	1326.0	1315.1
175°	1327.0	1321.1	1322.1	1331.0	1319.1
177.5°	1330.0	1323.0	1325.0	1333.0	1321.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)