

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007663

Luminaire Tested: S124IP-B1205UB2750-4F0-XX-W2A_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1205UB2750-4F0-XX-W2A_3000K
Description: Define 4 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4807.0 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007663

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007663

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007663

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.2	0.1
90°-100°	51.5	1.1
100°-110°	339.4	7.1
110°-120°	648.0	13.5
120°-130°	822.7	17.1
130°-140°	880.1	18.3
140°-150°	823.0	17.1
150°-160°	663.6	13.8
160°-170°	428.0	8.9
170°-180°	147.5	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.2	0.1
90°-120°	1039.0	21.6
90°-150°	3564.7	74.2
90°-180°	4804.0	99.9
0°-180°	4807.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	16	26	32	35	3
95°	64	24	26	32	34	79
105°	350	356	362	373	331	366
115°	653	656	655	657	657	642
125°	917	922	920	923	924	819
135°	1138	1137	1141	1144	1146	877
145°	1312	1316	1316	1317	1319	820
155°	1439	1440	1436	1441	1438	663
165°	1518	1512	1512	1521	1511	429
175°	1552	1546	1547	1557	1543	148
180°	1552	1552	1552	1552	1552	

TEST NUMBER: P1007663

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.5	16.3	25.5	32.5	34.8
92.5°	17.4	15.1	24.4	31.4	31.4
95°	63.9	24.4	25.5	32.5	33.7
97.5°	121.9	147.5	25.5	31.4	32.5
100°	190.4	211.3	51.1	31.4	32.5
102.5°	267.1	281.0	294.9	33.7	33.7
105°	349.5	356.5	362.3	372.7	330.9
107.5°	425.0	428.5	436.6	442.4	447.0
110°	501.6	505.1	512.1	514.4	517.9

TEST NUMBER: P1007663

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.9	582.9	585.2	584.1	588.7
115°	652.6	656.0	654.9	657.2	657.2
117.5°	721.1	725.7	729.2	728.0	728.0
120°	790.7	795.4	794.2	796.5	794.2
122.5°	855.8	858.1	860.4	861.6	859.2
125°	917.3	921.9	919.6	923.1	924.3
127.5°	976.5	977.7	983.5	982.3	981.2
130°	1033.4	1034.6	1038.1	1039.2	1039.2
132.5°	1085.7	1088.0	1092.6	1093.8	1092.6
135°	1137.9	1136.8	1141.4	1143.7	1146.0
137.5°	1184.4	1184.4	1190.2	1192.5	1191.3
140°	1229.6	1232.0	1234.3	1237.8	1238.9
142.5°	1270.3	1274.9	1276.1	1278.4	1278.4
145°	1312.1	1315.6	1315.6	1316.7	1319.1
147.5°	1344.6	1351.6	1350.4	1351.6	1352.7
150°	1380.6	1385.2	1384.1	1384.1	1385.2
152.5°	1410.8	1414.3	1411.9	1414.3	1413.1
155°	1438.6	1439.8	1436.3	1441.0	1437.5
157.5°	1463.0	1463.0	1458.4	1464.2	1458.4
160°	1483.9	1480.4	1479.3	1486.3	1479.3
162.5°	1502.5	1497.9	1496.7	1503.7	1495.5
165°	1517.6	1511.8	1511.8	1521.1	1510.6
167.5°	1530.4	1524.6	1523.4	1533.9	1522.2
170°	1540.8	1533.9	1535.0	1544.3	1532.7
172.5°	1547.8	1540.8	1542.0	1551.3	1538.5
175°	1552.4	1545.5	1546.6	1557.1	1543.1
177.5°	1555.9	1547.8	1550.1	1559.4	1545.5
180°	1552.4	1552.4	1552.4	1552.4	1552.4

(END OF REPORT)