

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026203

Luminaire Tested: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026203
REPORT IS A COMBINATION OF REPORTS P999183 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7506.0 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026203

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026203

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1026203

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.6
10°-20°	543.3	7.2
20°-30°	784.4	10.5
30°-40°	889.0	11.8
40°-50°	858.3	11.4
50°-60°	713.6	9.5
60°-70°	492.5	6.6
70°-80°	248.9	3.3
80°-90°	65.3	0.9
90°-100°	63.8	0.8
100°-110°	191.1	2.5
110°-120°	324.7	4.3
120°-130°	428.2	5.7
130°-140°	480.9	6.4
140°-150°	472.7	6.3
150°-160°	397.5	5.3
160°-170°	264.5	3.5
170°-180°	92.6	1.2
0°-30°	1522.5	20.3
0°-40°	2411.5	32.1
0°-60°	3983.4	53.1
0°-90°	4790.1	63.8
90°-120°	579.5	7.7
90°-150°	1961.2	26.1
90°-180°	2716.0	36.2
0°-180°	7506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	2	11	17	21	23	8
95°	45	52	58	60	60	49
105°	176	177	180	182	185	187
115°	330	330	328	328	327	326
125°	481	481	480	478	477	429
135°	620	624	624	623	621	480
145°	753	756	757	756	754	471
155°	863	863	862	865	862	397
165°	940	937	936	940	937	265
175°	977	974	973	978	973	93
180°	979	979	979	979	979	

TEST NUMBER: P1026203

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	2.3	10.6	16.7	21.2	22.7
92.5°	19.7	29.5	33.3	35.6	36.3
95°	45.4	52.2	57.5	59.8	59.8
97.5°	72.7	78.7	84.8	87.8	87.8
100°	106.0	109.0	115.8	117.3	117.3
102.5°	140.8	141.6	147.6	149.9	150.6
105°	176.4	177.1	180.2	182.4	184.7
107.5°	213.5	214.2	215.0	218.0	217.3
110°	251.3	252.8	252.1	250.6	252.8

TEST NUMBER: P1026203

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.7	290.7	289.2	289.2	289.2
115°	330.1	330.1	328.5	327.8	327.0
117.5°	367.2	367.2	366.4	364.1	361.9
120°	404.3	407.3	405.0	401.2	402.7
122.5°	442.9	443.6	442.9	440.6	436.8
125°	480.7	480.7	480.0	478.4	476.9
127.5°	514.8	517.0	515.5	514.0	513.3
130°	551.1	553.4	553.4	551.9	548.8
132.5°	588.2	589.7	589.0	587.5	586.7
135°	620.0	624.5	624.5	623.0	620.8
137.5°	655.6	657.9	659.4	657.1	657.9
140°	691.2	692.7	692.7	691.9	691.2
142.5°	723.7	725.2	724.5	724.5	724.5
145°	753.2	756.3	757.0	756.3	754.0
147.5°	783.5	787.3	786.6	785.8	785.0
150°	810.8	813.8	813.8	813.8	813.0
152.5°	836.5	838.0	838.8	841.1	838.8
155°	863.0	863.0	862.3	865.3	862.3
157.5°	885.7	884.2	884.2	886.5	884.2
160°	905.4	904.6	903.9	906.2	902.4
162.5°	923.6	921.3	920.5	925.1	921.3
165°	939.5	937.2	935.7	940.2	937.2
167.5°	952.3	949.3	949.3	953.9	949.3
170°	962.9	959.2	959.9	964.5	959.2
172.5°	970.5	967.5	967.5	972.8	967.5
175°	977.3	973.5	972.8	978.1	972.8
177.5°	980.3	976.6	976.6	981.9	975.8
180°	978.8	978.8	978.8	978.8	978.8

(END OF REPORT)