

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007666

Luminaire Tested: S124IP-B1205UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1205UB2750-4F0-XX-W2A_5000K
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4622.0 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007666

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007666

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007666

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	49.5	1.1
100°-110°	326.3	7.1
110°-120°	623.1	13.5
120°-130°	791.0	17.1
130°-140°	846.2	18.3
140°-150°	791.3	17.1
150°-160°	638.1	13.8
160°-170°	411.5	8.9
170°-180°	141.8	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	999.0	21.6
90°-150°	3427.5	74.2
90°-180°	4619.0	99.9
0°-180°	4622.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	16	25	31	34	3
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1007666

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1007666

CATALOG NUMBER: S124IP-B1205UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)