

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007682

Luminaire Tested: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB2750-4F0-XX-W2A-1_2700K
Description: Define 4 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1265.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007682

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007682

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007682

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	29.7	2.3
100°-110°	88.9	7.0
110°-120°	151.1	11.9
120°-130°	199.3	15.8
130°-140°	223.8	17.7
140°-150°	220.0	17.4
150°-160°	185.0	14.6
160°-170°	123.1	9.7
170°-180°	43.1	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	269.7	21.3
90°-150°	912.8	72.2
90°-180°	1264.0	99.9
0°-180°	1265.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	11	2
95°	21	24	27	28	28	23
105°	82	82	84	85	86	87
115°	154	154	153	153	152	152
125°	224	224	223	223	222	199
135°	289	291	291	290	289	223
145°	351	352	352	352	351	219
155°	402	402	401	403	401	185
165°	437	436	436	438	436	123
175°	455	453	453	455	453	43
180°	456	456	456	456	456	

TEST NUMBER: P1007682

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.7	15.5	16.6	16.9
95°	21.1	24.3	26.8	27.8	27.8
97.5°	33.8	36.6	39.5	40.9	40.9
100°	49.3	50.7	53.9	54.6	54.6
102.5°	65.5	65.9	68.7	69.8	70.1
105°	82.1	82.4	83.9	84.9	86.0
107.5°	99.4	99.7	100.1	101.5	101.1
110°	117.0	117.7	117.3	116.6	117.7

TEST NUMBER: P1007682

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.3	135.3	134.6	134.6	134.6
115°	153.6	153.6	152.9	152.6	152.2
117.5°	170.9	170.9	170.5	169.5	168.4
120°	188.1	189.6	188.5	186.7	187.4
122.5°	206.1	206.5	206.1	205.1	203.3
125°	223.7	223.7	223.4	222.7	222.0
127.5°	239.6	240.6	239.9	239.2	238.9
130°	256.5	257.6	257.6	256.9	255.4
132.5°	273.8	274.5	274.1	273.4	273.1
135°	288.6	290.7	290.7	290.0	288.9
137.5°	305.1	306.2	306.9	305.8	306.2
140°	321.7	322.4	322.4	322.0	321.7
142.5°	336.8	337.5	337.2	337.2	337.2
145°	350.6	352.0	352.3	352.0	350.9
147.5°	364.7	366.4	366.1	365.7	365.4
150°	377.3	378.8	378.8	378.8	378.4
152.5°	389.3	390.0	390.4	391.4	390.4
155°	401.7	401.7	401.3	402.7	401.3
157.5°	412.2	411.5	411.5	412.6	411.5
160°	421.4	421.0	420.7	421.7	420.0
162.5°	429.8	428.8	428.4	430.5	428.8
165°	437.2	436.2	435.5	437.6	436.2
167.5°	443.2	441.8	441.8	443.9	441.8
170°	448.2	446.4	446.8	448.9	446.4
172.5°	451.7	450.3	450.3	452.7	450.3
175°	454.9	453.1	452.7	455.2	452.7
177.5°	456.3	454.5	454.5	457.0	454.2
180°	455.6	455.6	455.6	455.6	455.6

(END OF REPORT)