

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026207

Luminaire Tested: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026207
REPORT IS A COMBINATION OF REPORTS P999197 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7853.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	51	57	51	47	50	46	43	44	41	38
5	72	61	52	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16194	16194	16194	16194
5°	16194	18298	16220	13985
10°	16107	21093	16094	12163
15°	15915	23740	15915	10183
20°	15715	25739	15632	8967
25°	15470	25848	15399	8099
30°	15210	21980	15091	7502
35°	14842	16585	14654	7057
40°	14432	12019	14148	6709
45°	13755	9134	13413	6401
50°	12951	7383	12596	5951
55°	12081	6113	11686	5351
60°	11207	5169	10706	4450
65°	10111	4210	9788	3537
70°	9105	3414	8674	2873
75°	7977	2460	7423	2105
80°	6581	1631	5988	1548
85°	4774	838	3959	838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20273 cd/sqm

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.3	2.4
10°-20°	580.7	7.4
20°-30°	909.6	11.6
30°-40°	1010.1	12.9
40°-50°	895.1	11.4
50°-60°	697.6	8.9
60°-70°	456.3	5.8
70°-80°	223.9	2.9
80°-90°	56.0	0.7
90°-100°	281.8	3.6
100°-110°	588.2	7.5
110°-120°	522.9	6.7
120°-130°	440.2	5.6
130°-140°	367.2	4.7
140°-150°	280.4	3.6
150°-160°	197.1	2.5
160°-170°	115.9	1.5
170°-180°	37.7	0.5
0°-30°	1682.6	21.4
0°-40°	2692.7	34.3
0°-60°	4285.3	54.6
0°-90°	5021.5	63.9
90°-120°	1392.9	17.7
90°-150°	2480.7	31.6
90°-180°	2831.0	36.1
0°-180°	7853.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1986	1986	1986	1986	1986	
5°	1983	2295	1986	1754	1983	188
15°	1898	3040	1898	1304	1898	535
25°	1739	3279	1731	1027	1739	802
35°	1517	2020	1498	859	1517	948
45°	1223	1032	1192	723	1223	943
55°	880	616	851	539	880	787
65°	552	360	534	302	552	551
75°	277	166	258	142	277	294
85°	66	40	54	40	66	74
90°	1	16	1	16	1	6
95°	25	186	25	186	25	28
105°	89	1075	89	1075	89	95
115°	157	1032	157	1032	157	156
125°	219	823	219	823	219	195
135°	260	736	260	736	260	201
145°	300	601	300	601	300	188
155°	341	503	341	503	341	157
165°	372	439	372	439	372	105
175°	388	396	388	396	388	37
180°	389	389	389	389	389	

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	1989.1	2006.7	2016.3	2024.3	2040.3	2046.7	2059.5	2062.7	2075.5	2073.9	2069.1
5°	1982.7	2013.1	2035.5	2059.5	2088.3	2104.3	2121.9	2147.5	2160.3	2177.9	2189.1
7.5°	1971.4	2013.1	2049.9	2086.7	2133.1	2158.7	2181.1	2221.1	2254.7	2283.5	2315.5
10°	1953.8	2006.7	2061.1	2110.7	2174.7	2205.1	2238.7	2297.9	2344.3	2384.3	2435.5
12.5°	1926.6	2000.3	2061.1	2128.3	2209.9	2251.5	2296.3	2366.7	2421.1	2486.7	2550.7
15°	1897.8	1979.5	2059.5	2147.5	2240.3	2288.3	2333.1	2427.5	2510.7	2585.9	2656.3
17.5°	1865.8	1955.4	2043.5	2141.1	2253.1	2312.3	2365.1	2478.7	2569.9	2667.5	2737.9
20°	1827.4	1925.0	2025.9	2134.7	2261.1	2326.7	2385.9	2515.5	2616.3	2721.9	2810.0
22.5°	1785.8	1891.4	2001.9	2120.3	2251.5	2323.5	2392.3	2531.5	2648.3	2745.9	2864.4
25°	1739.4	1851.4	1965.0	2089.9	2237.1	2315.5	2385.9	2523.5	2648.3	2776.4	2891.6
27.5°	1691.4	1806.6	1925.0	2056.3	2206.7	2283.5	2363.5	2496.3	2641.9	2781.2	2898.0
30°	1638.6	1750.6	1875.4	2000.3	2160.3	2237.1	2318.7	2462.7	2621.1	2760.3	2886.8
32.5°	1581.0	1696.2	1814.6	1944.2	2101.1	2184.3	2259.5	2422.7	2584.3	2721.9	2840.4
35°	1517.0	1625.8	1737.8	1870.6	2025.9	2101.1	2190.7	2360.3	2523.5	2669.1	2745.9
37.5°	1448.2	1552.2	1656.2	1787.4	1936.2	2027.5	2115.5	2286.7	2459.5	2557.1	2597.1
40°	1384.2	1475.4	1566.6	1693.0	1843.4	1937.8	2027.5	2205.1	2357.1	2432.3	2401.9
42.5°	1302.6	1397.0	1478.6	1595.4	1747.4	1835.4	1926.6	2110.7	2233.9	2264.3	2189.1
45°	1222.6	1301.0	1379.4	1493.0	1653.0	1728.2	1825.8	1997.1	2099.5	2072.3	1961.8
47.5°	1144.1	1208.2	1281.8	1392.2	1536.2	1625.8	1717.0	1865.8	1937.8	1899.4	1745.8
50°	1051.3	1115.3	1192.2	1288.2	1427.4	1513.8	1585.8	1723.4	1777.8	1683.4	1497.8
52.5°	963.3	1019.3	1084.9	1174.5	1307.4	1385.8	1464.2	1582.6	1600.2	1491.4	1296.2
55°	880.1	924.9	993.7	1065.7	1187.4	1270.6	1325.0	1425.8	1421.0	1285.0	1116.9
57.5°	793.7	835.3	881.7	956.9	1072.1	1134.5	1193.8	1281.8	1235.4	1120.1	953.7
60°	716.9	740.9	787.3	859.3	956.9	1011.3	1057.7	1105.7	1065.7	940.9	812.9
62.5°	632.1	659.3	692.9	750.5	836.9	888.1	921.7	942.5	900.9	804.9	688.1
65°	552.1	576.1	611.3	662.5	728.1	766.5	784.1	798.5	776.1	667.3	574.5
67.5°	480.1	496.1	528.1	561.7	632.1	641.7	665.7	672.1	627.3	544.1	470.5
70°	408.1	424.1	438.5	478.5	510.5	528.1	532.9	532.9	488.1	433.7	372.8
72.5°	340.8	350.4	364.8	392.0	409.7	422.5	428.9	420.9	379.2	334.4	289.6
75°	276.8	281.6	294.4	312.0	326.4	321.6	320.0	310.4	280.0	248.0	222.4
77.5°	212.8	216.0	230.4	235.2	235.2	240.0	233.6	224.0	198.4	174.4	163.2
80°	160.0	164.8	166.4	169.6	166.4	166.4	161.6	145.6	132.8	121.6	113.6
82.5°	110.4	113.6	115.2	110.4	113.6	108.8	100.8	89.6	81.6	80.0	76.8
85°	65.6	67.2	65.6	65.6	60.8	59.2	52.8	51.2	48.0	48.0	46.4
87.5°	32.0	30.4	27.2	24.0	24.0	22.4	24.0	20.8	24.0	22.4	20.8
90°	0.8	2.3	4.6	5.3	6.1	6.1	6.1	10.7	10.7	12.2	13.7
92.5°	10.7	15.3	23.7	35.1	48.9	58.8	68.7	116.1	190.2	262.0	299.4
95°	25.2	27.5	35.1	45.1	63.4	79.4	95.5	161.9	287.2	469.7	622.5
97.5°	42.0	42.0	48.9	58.0	74.1	87.8	101.6	154.3	262.0	449.9	666.0
100°	58.0	58.0	63.4	72.6	87.1	99.3	111.5	156.6	242.9	398.7	614.1
102.5°	73.3	74.9	79.4	87.8	101.6	113.0	124.5	164.2	237.5	364.3	549.2
105°	89.4	91.7	95.5	104.6	118.4	129.4	140.5	177.2	240.6	347.5	501.0
107.5°	106.9	108.5	112.3	122.2	135.2	146.2	157.3	190.9	249.8	342.9	469.7
110°	124.5	126.0	129.8	139.0	152.8	163.1	173.4	207.0	260.4	344.5	455.2

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.3	142.8	147.4	155.8	169.6	179.9	190.2	222.3	271.9	349.0	448.3
115°	157.3	159.6	165.0	172.6	187.1	197.4	207.7	238.3	284.1	355.2	446.8
117.5°	174.1	176.4	181.0	189.4	203.2	213.9	224.6	253.6	296.3	361.3	446.0
120°	190.9	192.5	197.8	206.2	219.2	229.9	240.6	269.6	309.3	368.1	446.0
122.5°	206.2	207.7	213.1	220.7	235.2	245.6	255.9	284.9	321.6	375.0	445.3
125°	219.2	222.3	226.8	235.2	249.8	260.5	271.1	298.6	333.8	381.9	444.5
127.5°	231.4	233.7	239.1	248.2	263.5	274.2	284.9	311.6	344.5	387.2	443.0
130°	241.4	244.4	250.5	262.0	276.5	287.6	298.6	324.6	354.4	393.3	442.2
132.5°	251.3	253.6	262.0	272.7	288.7	299.0	309.3	335.3	364.3	398.7	441.5
135°	260.4	263.5	271.1	284.1	300.2	310.1	320.0	345.2	372.7	404.0	440.7
137.5°	269.6	272.7	281.1	293.3	310.1	319.6	329.2	352.9	378.8	407.1	440.7
140°	279.5	281.8	290.2	303.2	319.3	328.5	337.6	360.5	384.9	410.9	439.9
142.5°	290.2	292.5	300.2	312.4	327.7	336.4	345.2	367.4	389.5	414.0	439.9
145°	300.2	302.5	310.1	320.8	335.3	343.7	352.1	372.0	392.6	414.7	438.4
147.5°	311.6	312.4	319.3	330.7	342.9	350.5	358.2	377.3	395.6	415.5	436.1
150°	322.3	323.1	329.2	338.4	349.8	357.0	364.3	381.1	397.9	415.5	433.8
152.5°	332.2	332.2	338.4	346.8	356.7	363.2	369.7	384.2	399.5	414.0	430.0
155°	341.4	342.2	346.8	354.4	362.8	368.6	374.3	387.2	400.2	412.4	426.2
157.5°	350.6	350.6	355.2	361.3	368.9	373.5	378.1	389.5	400.2	410.9	422.4
160°	359.0	359.0	362.0	367.4	373.5	377.7	381.9	391.1	400.2	408.6	417.8
162.5°	366.6	365.9	368.1	372.7	378.1	381.2	384.2	392.6	400.2	406.3	413.2
165°	372.0	372.0	373.5	377.3	381.1	383.4	385.7	392.6	398.7	403.3	408.6
167.5°	378.1	377.3	378.1	381.1	383.4	385.3	387.2	392.6	397.2	400.2	404.0
170°	381.9	381.1	381.9	384.2	385.7	386.8	388.0	391.8	395.6	397.2	399.5
172.5°	385.7	384.9	384.9	386.5	387.2	388.0	388.8	391.1	394.1	394.1	394.9
175°	388.0	387.2	387.2	388.0	388.8	388.8	388.8	390.3	392.6	391.8	391.8
177.5°	389.5	388.8	388.0	388.8	388.8	388.8	388.8	389.5	391.1	389.5	389.5
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	2081.9	2099.5	2101.1	2117.1	2112.3	2104.3	2118.7	2109.1	2128.3	2121.9	2129.9
5°	2203.5	2227.5	2248.3	2261.1	2283.5	2278.7	2302.7	2294.7	2312.3	2294.7	2317.1
7.5°	2345.9	2385.9	2406.7	2440.3	2449.9	2451.5	2480.3	2486.7	2497.9	2486.7	2499.5
10°	2485.1	2533.1	2581.1	2608.3	2625.9	2649.9	2675.5	2686.7	2694.7	2683.5	2691.5
12.5°	2611.5	2686.7	2739.5	2794.0	2806.8	2827.6	2854.8	2851.6	2883.6	2877.2	2891.6
15°	2728.3	2811.6	2875.6	2918.8	2954.0	2971.6	3022.8	3026.0	3024.4	3040.4	3030.8
17.5°	2832.4	2902.8	2994.0	3050.0	3093.2	3093.2	3122.0	3181.2	3176.4	3174.8	3184.4
20°	2917.2	2997.2	3082.0	3176.4	3211.6	3218.0	3258.0	3288.4	3293.2	3293.2	3293.2
22.5°	2981.2	3075.6	3166.8	3234.0	3261.2	3283.6	3318.8	3338.0	3344.4	3341.2	3344.4
25°	3013.2	3102.8	3195.6	3256.4	3272.4	3285.2	3288.4	3299.6	3298.0	3278.8	3290.0
27.5°	3019.6	3106.0	3166.8	3182.8	3174.8	3166.8	3115.6	3120.4	3106.0	3077.2	3088.4
30°	2990.8	3037.2	3035.6	2986.0	2971.6	2938.0	2891.6	2822.8	2766.8	2742.7	2750.7
32.5°	2886.8	2886.8	2829.2	2717.1	2667.5	2606.7	2523.5	2461.1	2387.5	2371.5	2401.9
35°	2742.7	2661.1	2555.5	2408.3	2333.1	2288.3	2144.3	2099.5	2037.1	2019.5	2033.9
37.5°	2518.7	2382.7	2229.1	2091.5	2027.5	1947.4	1821.0	1757.0	1712.2	1681.8	1696.2
40°	2267.5	2102.7	1942.6	1773.0	1702.6	1637.0	1542.6	1485.0	1413.0	1416.2	1421.0
42.5°	2027.5	1833.8	1654.6	1497.8	1430.6	1376.2	1310.6	1240.2	1214.6	1206.6	1198.6
45°	1773.0	1566.6	1398.6	1281.8	1221.0	1169.7	1108.9	1068.9	1038.5	1032.1	1040.1
47.5°	1533.0	1358.6	1198.6	1089.7	1040.1	1014.5	966.5	929.7	910.5	894.5	904.1
50°	1315.4	1152.1	1024.1	932.9	897.7	880.1	835.3	816.1	796.9	792.1	790.5
52.5°	1136.1	996.9	886.5	812.9	785.7	776.1	742.5	715.3	699.3	704.1	707.3
55°	972.9	854.5	768.1	708.9	686.5	675.3	651.3	632.1	620.9	616.1	619.3
57.5°	828.9	726.5	664.1	616.1	598.5	593.7	568.1	561.7	553.7	548.9	548.9
60°	697.7	625.7	568.1	540.9	521.7	516.9	497.7	489.7	488.1	483.3	480.1
62.5°	587.3	528.1	488.1	459.3	451.3	449.7	436.9	427.3	422.5	419.3	419.3
65°	491.3	448.1	414.5	393.6	387.2	384.0	369.6	366.4	363.2	360.0	358.4
67.5°	409.7	371.2	347.2	332.8	324.8	326.4	318.4	312.0	312.0	310.4	308.8
70°	331.2	307.2	286.4	278.4	275.2	272.0	268.8	264.0	262.4	262.4	262.4
72.5°	260.8	244.8	233.6	228.8	225.6	222.4	219.2	219.2	219.2	217.6	217.6
75°	200.0	193.6	185.6	180.8	180.8	184.0	179.2	174.4	169.6	166.4	168.0
77.5°	150.4	147.2	142.4	134.4	136.0	132.8	132.8	129.6	131.2	131.2	128.0
80°	110.4	105.6	104.0	99.2	100.8	99.2	97.6	97.6	94.4	94.4	94.4
82.5°	76.8	72.0	72.0	70.4	68.8	68.8	67.2	67.2	68.8	65.6	65.6
85°	46.4	44.8	44.8	41.6	41.6	41.6	41.6	43.2	41.6	40.0	40.0
87.5°	20.8	22.4	20.8	19.2	19.2	19.2	17.6	17.6	16.0	17.6	17.6
90°	13.0	13.7	14.5	15.3	15.3	15.3	16.0	16.8	16.0	16.0	16.0
92.5°	249.0	184.1	137.5	108.5	99.0	89.4	77.9	72.6	69.5	69.5	69.5
95°	640.0	566.0	447.6	345.2	308.2	271.1	233.7	210.0	196.3	186.4	196.3
97.5°	802.7	815.0	756.1	672.1	629.4	586.6	534.6	488.8	465.9	447.6	465.9
100°	809.6	921.1	936.4	899.0	870.8	842.5	776.0	729.4	706.5	700.4	706.5
102.5°	752.3	915.8	1006.7	1029.6	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9
105°	680.5	855.4	987.6	1063.2	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2
107.5°	621.7	781.3	924.2	1029.6	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2
110°	579.7	715.7	847.8	958.5	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	556.0	667.5	780.6	883.7	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2
115°	543.0	638.5	732.5	821.8	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8
117.5°	536.2	621.7	701.2	773.7	805.8	837.9	891.3	931.0	957.0	960.8	957.0
120°	530.8	611.0	682.1	743.2	770.3	797.4	840.9	874.5	894.4	902.8	894.4
122.5°	524.7	601.9	669.8	724.1	747.0	769.9	805.0	832.5	848.6	857.0	848.6
125°	517.8	591.2	656.9	709.6	730.6	751.6	782.1	804.3	818.8	823.4	818.8
127.5°	508.7	578.9	642.3	695.0	714.9	734.8	765.3	785.2	797.4	802.0	797.4
130°	500.3	563.7	624.0	675.9	696.2	716.4	747.7	766.8	779.1	783.6	779.1
132.5°	492.6	547.6	603.4	653.8	674.0	694.3	724.8	747.0	758.4	763.0	758.4
135°	485.0	533.1	582.8	629.4	648.4	667.5	698.1	719.5	731.7	736.3	731.7
137.5°	478.1	519.4	562.9	603.4	621.0	638.5	667.5	689.7	699.6	705.0	699.6
140°	472.8	507.9	543.8	578.2	594.2	610.3	637.0	653.8	664.5	670.6	664.5
142.5°	468.2	497.2	527.8	556.0	569.4	582.8	605.7	621.0	630.1	633.9	630.1
145°	462.9	487.3	513.3	536.2	546.9	557.6	576.7	589.6	597.3	601.1	597.3
147.5°	458.3	478.9	500.3	519.4	528.2	536.9	551.4	562.9	569.0	570.5	569.0
150°	452.9	471.3	488.8	504.1	511.0	517.8	530.1	540.0	544.6	545.3	544.6
152.5°	446.8	462.9	477.4	491.1	496.4	501.8	511.7	519.4	521.7	522.4	521.7
155°	440.7	454.4	466.7	478.1	482.7	487.3	494.9	501.0	503.3	503.3	503.3
157.5°	434.6	445.3	456.0	465.9	469.7	473.5	479.7	484.2	485.8	485.8	485.8
160°	427.7	436.9	445.3	453.7	456.8	459.8	464.4	469.0	469.7	469.7	469.7
162.5°	421.6	428.5	435.4	441.5	444.2	446.8	449.9	454.4	455.2	454.4	455.2
165°	414.7	420.8	425.4	430.8	432.7	434.6	437.6	440.7	439.9	439.2	439.9
167.5°	408.6	413.2	417.0	421.6	422.8	423.9	425.4	427.7	427.7	427.0	427.7
170°	402.5	406.3	408.6	411.7	412.8	414.0	415.5	416.3	415.5	415.5	415.5
172.5°	397.2	400.2	401.7	403.3	404.0	404.8	405.6	406.3	405.6	404.0	405.6
175°	393.3	394.9	395.6	397.2	397.2	397.2	397.2	398.7	397.2	395.6	397.2
177.5°	390.3	391.1	391.8	391.8	392.2	392.6	391.8	392.6	391.1	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	2134.7	2123.5	2121.9	2121.9	2104.3	2113.9	2094.7	2073.9	2064.3	2064.3	2046.7
5°	2312.3	2301.1	2289.9	2272.3	2272.3	2262.7	2232.3	2201.9	2179.5	2160.3	2139.5
7.5°	2494.7	2483.5	2451.5	2433.9	2443.5	2424.3	2384.3	2333.1	2294.7	2264.3	2221.1
10°	2693.1	2662.7	2646.7	2637.1	2603.5	2582.7	2536.3	2461.1	2413.1	2373.1	2317.1
12.5°	2854.8	2864.4	2803.6	2808.4	2774.8	2745.9	2673.9	2601.9	2529.9	2473.9	2390.7
15°	3029.2	3000.4	2963.6	2934.8	2923.6	2888.4	2827.6	2731.5	2653.1	2565.1	2470.7
17.5°	3166.8	3144.4	3109.2	3082.0	3058.0	2973.2	2922.0	2837.2	2729.9	2643.5	2528.3
20°	3283.6	3262.8	3213.2	3195.6	3152.4	3091.6	3018.0	2886.8	2790.8	2696.3	2584.3
22.5°	3333.2	3312.4	3269.2	3246.8	3219.6	3160.4	3090.0	2965.2	2846.8	2728.3	2609.9
25°	3291.6	3291.6	3270.8	3262.8	3238.8	3186.0	3114.0	3008.4	2882.0	2753.9	2613.1
27.5°	3090.0	3130.0	3144.4	3152.4	3152.4	3154.0	3104.4	3002.0	2878.8	2753.9	2606.7
30°	2798.8	2866.0	2925.2	2942.8	2973.2	3006.8	3027.6	2978.0	2867.6	2736.3	2589.1
32.5°	2432.3	2518.7	2629.1	2656.3	2697.9	2798.8	2854.8	2875.6	2814.8	2699.5	2542.7
35°	2067.5	2176.3	2243.5	2326.7	2365.1	2513.9	2638.7	2713.9	2699.5	2630.7	2488.3
37.5°	1749.0	1811.4	1893.0	1981.1	2057.9	2200.3	2355.5	2501.1	2560.3	2526.7	2419.5
40°	1443.4	1517.0	1614.6	1686.6	1739.4	1881.8	2073.9	2232.3	2361.9	2382.7	2317.1
42.5°	1227.4	1301.0	1360.2	1438.6	1480.2	1617.8	1787.4	1985.9	2139.5	2221.1	2192.3
45°	1060.9	1105.7	1153.7	1198.6	1249.8	1371.4	1528.2	1745.8	1918.6	2033.9	2045.1
47.5°	915.3	955.3	996.9	1038.5	1067.3	1161.7	1305.8	1483.4	1672.2	1830.6	1893.0
50°	812.9	832.1	862.5	886.5	920.1	1001.7	1116.9	1270.6	1470.6	1641.8	1723.4
52.5°	712.1	736.1	760.1	780.9	803.3	860.9	966.5	1099.3	1272.2	1448.2	1549.0
55°	627.3	646.5	668.9	683.3	696.1	747.3	827.3	929.7	1078.5	1245.0	1369.8
57.5°	558.5	566.5	585.7	593.7	608.1	649.7	707.3	798.5	918.5	1080.1	1182.5
60°	483.3	499.3	513.7	520.1	531.3	560.1	600.1	684.9	788.9	907.3	1024.1
62.5°	422.5	428.9	440.1	448.1	456.1	486.5	520.1	584.1	662.5	761.7	868.9
65°	366.4	369.6	376.0	387.2	392.0	414.5	433.7	480.1	553.7	628.9	736.1
67.5°	308.8	312.0	320.0	326.4	331.2	345.6	366.4	400.1	440.1	523.3	582.5
70°	264.0	264.0	268.8	272.0	276.8	283.2	294.4	320.0	356.8	409.7	464.1
72.5°	220.8	220.8	220.8	225.6	225.6	230.4	236.8	254.4	280.0	321.6	356.8
75°	171.2	172.8	176.0	176.0	177.6	184.0	188.8	193.6	206.4	233.6	265.6
77.5°	129.6	132.8	134.4	131.2	134.4	134.4	140.8	147.2	153.6	161.6	185.6
80°	96.0	97.6	94.4	96.0	96.0	99.2	102.4	100.8	104.0	113.6	120.0
82.5°	64.0	65.6	65.6	65.6	65.6	70.4	70.4	68.8	70.4	72.0	73.6
85°	40.0	38.4	38.4	40.0	38.4	38.4	40.0	41.6	40.0	41.6	43.2
87.5°	17.6	17.6	17.6	17.6	16.0	16.0	17.6	16.0	17.6	16.0	14.4
90°	16.8	16.0	15.3	15.3	15.3	14.5	13.7	13.0	13.7	12.2	10.7
92.5°	72.6	77.9	89.4	99.0	108.5	137.5	184.1	249.0	299.4	262.0	190.2
95°	210.0	233.7	271.1	308.2	345.2	447.6	566.0	640.0	622.5	469.7	287.2
97.5°	488.8	534.6	586.6	629.4	672.1	756.1	815.0	802.7	666.0	449.9	262.0
100°	729.4	776.0	842.5	870.8	899.0	936.4	921.1	809.6	614.1	398.7	242.9
102.5°	949.4	979.9	1014.3	1022.0	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5
105°	1089.9	1096.0	1094.5	1078.8	1063.2	987.6	855.4	680.5	501.0	347.5	240.6
107.5°	1141.1	1127.3	1093.7	1061.6	1029.6	924.2	781.3	621.7	469.7	342.9	249.8
110°	1128.9	1096.8	1042.6	1000.6	958.5	847.8	715.7	579.7	455.2	344.5	260.4

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1071.6	1031.1	967.7	925.7	883.7	780.6	667.5	556.0	448.3	349.0	271.9
115°	1001.3	955.5	895.2	858.5	821.8	732.5	638.5	543.0	446.8	355.2	284.1
117.5°	931.0	891.3	837.9	805.8	773.7	701.2	621.7	536.2	446.0	361.3	296.3
120°	874.5	840.9	797.4	770.3	743.2	682.1	611.0	530.8	446.0	368.1	309.3
122.5°	832.5	805.0	769.9	747.0	724.1	669.8	601.9	524.7	445.3	375.0	321.6
125°	804.3	782.1	751.6	730.6	709.6	656.9	591.2	517.8	444.5	381.9	333.8
127.5°	785.2	765.3	734.8	714.9	695.0	642.3	578.9	508.7	443.0	387.2	344.5
130°	766.8	747.7	716.4	696.2	675.9	624.0	563.7	500.3	442.2	393.3	354.4
132.5°	747.0	724.8	694.3	674.0	653.8	603.4	547.6	492.6	441.5	398.7	364.3
135°	719.5	698.1	667.5	648.4	629.4	582.8	533.1	485.0	440.7	404.0	372.7
137.5°	689.7	667.5	638.5	621.0	603.4	562.9	519.4	478.1	440.7	407.1	378.8
140°	653.8	637.0	610.3	594.2	578.2	543.8	507.9	472.8	439.9	410.9	384.9
142.5°	621.0	605.7	582.8	569.4	556.0	527.8	497.2	468.2	439.9	414.0	389.5
145°	589.6	576.7	557.6	546.9	536.2	513.3	487.3	462.9	438.4	414.7	392.6
147.5°	562.9	551.4	536.9	528.2	519.4	500.3	478.9	458.3	436.1	415.5	395.6
150°	540.0	530.1	517.8	511.0	504.1	488.8	471.3	452.9	433.8	415.5	397.9
152.5°	519.4	511.7	501.8	496.4	491.1	477.4	462.9	446.8	430.0	414.0	399.5
155°	501.0	494.9	487.3	482.7	478.1	466.7	454.4	440.7	426.2	412.4	400.2
157.5°	484.2	479.7	473.5	469.7	465.9	456.0	445.3	434.6	422.4	410.9	400.2
160°	469.0	464.4	459.8	456.8	453.7	445.3	436.9	427.7	417.8	408.6	400.2
162.5°	454.4	449.9	446.8	444.2	441.5	435.4	428.5	421.6	413.2	406.3	400.2
165°	440.7	437.6	434.6	432.7	430.8	425.4	420.8	414.7	408.6	403.3	398.7
167.5°	427.7	425.4	423.9	422.8	421.6	417.0	413.2	408.6	404.0	400.2	397.2
170°	416.3	415.5	414.0	412.8	411.7	408.6	406.3	402.5	399.5	397.2	395.6
172.5°	406.3	405.6	404.8	404.0	403.3	401.7	400.2	397.2	394.9	394.1	394.1
175°	398.7	397.2	397.2	397.2	397.2	395.6	394.9	393.3	391.8	391.8	392.6
177.5°	392.6	391.8	392.6	392.2	391.8	391.8	391.1	390.3	389.5	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	2037.1	2029.1	2024.3	2022.7	2008.3	2000.3	1995.5	1992.3	1987.5	1974.7	1963.4
5°	2113.9	2091.5	2080.3	2067.5	2045.1	2019.5	1998.7	1985.9	1969.8	1944.2	1920.2
7.5°	2185.9	2152.3	2129.9	2112.3	2073.9	2032.3	1998.7	1971.4	1941.0	1905.8	1872.2
10°	2261.1	2206.7	2177.9	2150.7	2094.7	2040.3	1992.3	1952.2	1909.0	1862.6	1825.8
12.5°	2320.3	2248.3	2216.3	2177.9	2109.1	2045.1	1984.3	1929.8	1873.8	1824.2	1771.4
15°	2389.1	2299.5	2262.7	2213.1	2118.7	2035.5	1957.0	1897.8	1840.2	1766.6	1710.6
17.5°	2429.1	2325.1	2272.3	2229.1	2126.7	2025.9	1934.6	1861.0	1793.8	1720.2	1661.0
20°	2469.1	2350.7	2291.5	2230.7	2109.1	2001.9	1905.8	1817.8	1747.4	1667.4	1606.6
22.5°	2481.9	2344.3	2281.9	2225.9	2097.9	1977.9	1867.4	1777.8	1696.2	1616.2	1547.4
25°	2481.9	2342.7	2269.1	2197.1	2062.7	1939.4	1829.0	1731.4	1640.2	1560.2	1491.4
27.5°	2456.3	2310.7	2233.9	2168.3	2029.1	1896.2	1782.6	1675.4	1587.4	1507.4	1429.0
30°	2424.3	2264.3	2187.5	2109.1	1974.7	1848.2	1725.0	1625.8	1533.0	1441.8	1371.4
32.5°	2384.3	2214.7	2129.9	2049.9	1907.4	1776.2	1662.6	1565.0	1477.0	1382.6	1304.2
35°	2326.7	2141.1	2046.7	1976.3	1838.6	1702.6	1593.8	1497.8	1413.0	1315.4	1230.6
37.5°	2253.1	2073.9	1977.9	1891.4	1749.0	1624.2	1521.8	1429.0	1345.8	1256.2	1161.7
40°	2166.7	1979.5	1896.2	1805.0	1654.6	1536.2	1440.2	1357.0	1273.8	1189.0	1097.7
42.5°	2069.1	1883.4	1790.6	1702.6	1558.6	1441.8	1352.2	1277.0	1200.2	1121.7	1024.1
45°	1952.2	1777.8	1688.2	1605.0	1465.8	1345.8	1264.2	1192.2	1126.5	1046.5	960.1
47.5°	1821.0	1669.0	1577.8	1488.2	1352.2	1248.2	1168.1	1107.3	1051.3	971.3	892.9
50°	1693.0	1542.6	1469.0	1377.8	1253.0	1155.3	1073.7	1022.5	979.3	900.9	830.5
52.5°	1531.4	1417.8	1347.4	1269.0	1148.9	1049.7	985.7	940.9	889.7	828.9	766.5
55°	1389.0	1283.4	1227.4	1153.7	1035.3	947.3	892.9	851.3	811.3	756.9	707.3
57.5°	1227.4	1161.7	1105.7	1041.7	924.9	849.7	801.7	766.5	729.7	684.9	644.9
60°	1057.7	1027.3	972.9	921.7	822.5	756.9	716.9	684.9	649.7	612.9	579.3
62.5°	907.3	889.7	857.7	817.7	724.9	668.9	628.9	604.9	579.3	545.7	513.7
65°	764.9	756.9	726.5	697.7	633.7	584.1	548.9	534.5	505.7	480.1	451.3
67.5°	638.5	628.9	611.3	598.5	544.1	497.7	480.1	460.9	436.9	417.7	393.6
70°	510.5	508.9	497.7	481.7	452.9	419.3	401.7	388.8	364.8	350.4	332.8
72.5°	396.9	404.9	395.3	388.8	369.6	345.6	329.6	321.6	302.4	291.2	278.4
75°	296.0	302.4	307.2	296.0	291.2	280.0	265.6	257.6	248.0	232.0	227.2
77.5°	201.6	216.0	216.0	219.2	220.8	214.4	203.2	196.8	185.6	182.4	176.0
80°	132.8	145.6	147.2	150.4	155.2	155.2	147.2	145.6	134.4	132.8	128.0
82.5°	76.8	88.0	94.4	99.2	97.6	104.0	97.6	96.0	89.6	89.6	86.4
85°	41.6	43.2	46.4	49.6	52.8	56.0	56.0	54.4	52.8	51.2	48.0
87.5°	16.0	16.0	17.6	16.0	17.6	20.8	22.4	22.4	20.8	19.2	16.0
90°	10.7	6.1	6.1	6.1	5.3	4.6	2.3	0.8	2.3	4.6	5.3
92.5°	116.1	68.7	58.8	48.9	35.1	23.7	15.3	10.7	15.3	23.7	35.1
95°	161.9	95.5	79.4	63.4	45.1	35.1	27.5	25.2	27.5	35.1	45.1
97.5°	154.3	101.6	87.8	74.1	58.0	48.9	42.0	42.0	42.0	48.9	58.0
100°	156.6	111.5	99.3	87.1	72.6	63.4	58.0	58.0	58.0	63.4	72.6
102.5°	164.2	124.5	113.0	101.6	87.8	79.4	74.9	73.3	74.9	79.4	87.8
105°	177.2	140.5	129.4	118.4	104.6	95.5	91.7	89.4	91.7	95.5	104.6
107.5°	190.9	157.3	146.2	135.2	122.2	112.3	108.5	106.9	108.5	112.3	122.2
110°	207.0	173.4	163.1	152.8	139.0	129.8	126.0	124.5	126.0	129.8	139.0

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	222.3	190.2	179.9	169.6	155.8	147.4	142.8	141.3	142.8	147.4	155.8
115°	238.3	207.7	197.4	187.1	172.6	165.0	159.6	157.3	159.6	165.0	172.6
117.5°	253.6	224.6	213.9	203.2	189.4	181.0	176.4	174.1	176.4	181.0	189.4
120°	269.6	240.6	229.9	219.2	206.2	197.8	192.5	190.9	192.5	197.8	206.2
122.5°	284.9	255.9	245.6	235.2	220.7	213.1	207.7	206.2	207.7	213.1	220.7
125°	298.6	271.1	260.5	249.8	235.2	226.8	222.3	219.2	222.3	226.8	235.2
127.5°	311.6	284.9	274.2	263.5	248.2	239.1	233.7	231.4	233.7	239.1	248.2
130°	324.6	298.6	287.6	276.5	262.0	250.5	244.4	241.4	244.4	250.5	262.0
132.5°	335.3	309.3	299.0	288.7	272.7	262.0	253.6	251.3	253.6	262.0	272.7
135°	345.2	320.0	310.1	300.2	284.1	271.1	263.5	260.4	263.5	271.1	284.1
137.5°	352.9	329.2	319.6	310.1	293.3	281.1	272.7	269.6	272.7	281.1	293.3
140°	360.5	337.6	328.5	319.3	303.2	290.2	281.8	279.5	281.8	290.2	303.2
142.5°	367.4	345.2	336.4	327.7	312.4	300.2	292.5	290.2	292.5	300.2	312.4
145°	372.0	352.1	343.7	335.3	320.8	310.1	302.5	300.2	302.5	310.1	320.8
147.5°	377.3	358.2	350.5	342.9	330.7	319.3	312.4	311.6	312.4	319.3	330.7
150°	381.1	364.3	357.0	349.8	338.4	329.2	323.1	322.3	323.1	329.2	338.4
152.5°	384.2	369.7	363.2	356.7	346.8	338.4	332.2	332.2	332.2	338.4	346.8
155°	387.2	374.3	368.6	362.8	354.4	346.8	342.2	341.4	342.2	346.8	354.4
157.5°	389.5	378.1	373.5	368.9	361.3	355.2	350.6	350.6	350.6	355.2	361.3
160°	391.1	381.9	377.7	373.5	367.4	362.0	359.0	359.0	359.0	362.0	367.4
162.5°	392.6	384.2	381.2	378.1	372.7	368.1	365.9	366.6	365.9	368.1	372.7
165°	392.6	385.7	383.4	381.1	377.3	373.5	372.0	372.0	372.0	373.5	377.3
167.5°	392.6	387.2	385.3	383.4	381.1	378.1	377.3	378.1	377.3	378.1	381.1
170°	391.8	388.0	386.8	385.7	384.2	381.9	381.1	381.9	381.1	381.9	384.2
172.5°	391.1	388.8	388.0	387.2	386.5	384.9	384.9	385.7	384.9	384.9	386.5
175°	390.3	388.8	388.8	388.8	388.0	387.2	387.2	388.0	387.2	387.2	388.0
177.5°	389.5	388.8	388.8	388.8	388.8	388.0	388.8	389.5	388.8	388.0	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	1953.8	1950.6	1947.4	1934.6	1923.4	1904.2	1888.2	1881.8	1880.2	1881.8	1877.0
5°	1897.8	1896.2	1885.0	1862.6	1841.8	1819.4	1803.4	1787.4	1777.8	1777.8	1766.6
7.5°	1845.0	1833.8	1824.2	1795.4	1771.4	1741.0	1717.0	1702.6	1694.6	1677.0	1677.0
10°	1789.0	1773.0	1760.2	1733.0	1697.8	1667.4	1637.0	1619.4	1605.0	1592.2	1587.4
12.5°	1733.0	1720.2	1696.2	1667.4	1632.2	1593.8	1561.8	1549.0	1515.4	1488.2	1489.8
15°	1680.2	1651.4	1640.2	1598.6	1557.0	1520.2	1473.8	1437.0	1409.8	1392.2	1369.8
17.5°	1621.0	1592.2	1571.4	1536.2	1481.8	1424.2	1379.4	1329.8	1302.6	1272.2	1257.8
20°	1555.4	1531.4	1515.4	1459.4	1393.8	1325.0	1275.4	1245.0	1214.6	1192.2	1179.3
22.5°	1499.4	1469.0	1449.8	1374.6	1302.6	1233.8	1195.4	1169.7	1144.1	1124.9	1118.5
25°	1427.4	1409.8	1363.4	1297.8	1209.8	1163.3	1129.7	1096.1	1081.7	1068.9	1054.5
27.5°	1368.2	1325.0	1293.0	1206.6	1152.1	1099.3	1065.7	1040.1	1022.5	1009.7	998.5
30°	1294.6	1254.6	1209.8	1137.7	1088.1	1038.5	1008.1	987.3	968.1	960.1	950.5
32.5°	1217.8	1180.9	1137.7	1080.1	1019.3	980.9	956.9	934.5	921.7	913.7	902.5
35°	1148.9	1102.5	1073.7	1019.3	969.7	926.5	904.1	884.9	870.5	867.3	865.7
37.5°	1075.3	1040.1	1012.9	956.9	915.3	878.5	857.7	836.9	828.9	827.3	820.9
40°	1011.3	980.9	955.3	902.5	857.7	824.1	808.1	795.3	787.3	787.3	785.7
42.5°	955.3	923.3	897.7	849.7	809.7	779.3	761.7	748.9	745.7	747.3	745.7
45°	892.9	865.7	840.1	790.5	756.9	734.5	715.3	708.9	704.1	705.7	707.3
47.5°	833.7	811.3	785.7	745.7	707.3	683.3	672.1	665.7	665.7	665.7	668.9
50°	780.9	755.3	732.9	691.3	656.1	636.9	627.3	619.3	620.9	622.5	624.1
52.5°	718.5	696.1	680.1	638.5	612.9	588.9	577.7	579.3	577.7	577.7	580.9
55°	664.1	641.7	625.7	587.3	561.7	545.7	536.1	531.3	532.9	529.7	536.1
57.5°	603.3	584.1	572.9	536.1	513.7	499.3	491.3	483.3	486.5	484.9	483.3
60°	550.5	528.1	510.5	484.9	465.7	448.1	443.3	435.3	438.5	435.3	433.7
62.5°	489.7	472.1	459.3	433.7	417.7	403.3	392.0	387.2	385.6	380.8	376.0
65°	428.9	419.3	406.5	380.8	364.8	353.6	347.2	342.4	340.8	328.0	313.6
67.5°	372.8	366.4	353.6	334.4	320.0	308.8	299.2	291.2	281.6	272.0	264.0
70°	320.0	310.4	302.4	284.8	272.0	260.8	251.2	241.6	236.8	227.2	224.0
72.5°	268.8	259.2	251.2	235.2	224.0	212.8	209.6	198.4	193.6	192.0	192.0
75°	216.0	208.0	203.2	188.8	179.2	171.2	166.4	163.2	160.0	156.8	152.0
77.5°	164.8	160.0	156.8	147.2	139.2	134.4	132.8	121.6	118.4	115.2	112.0
80°	120.0	118.4	115.2	107.2	104.0	92.8	92.8	89.6	88.0	88.0	88.0
82.5°	81.6	78.4	76.8	68.8	67.2	65.6	64.0	62.4	64.0	62.4	64.0
85°	43.2	41.6	40.0	40.0	40.0	40.0	40.0	40.0	40.0	38.4	40.0
87.5°	16.0	16.0	16.0	16.0	14.4	16.0	16.0	14.4	16.0	16.0	16.0
90°	6.1	6.1	6.1	10.7	10.7	12.2	13.7	13.0	13.7	14.5	15.3
92.5°	48.9	58.8	68.7	116.1	190.2	262.0	299.4	249.0	184.1	137.5	108.5
95°	63.4	79.4	95.5	161.9	287.2	469.7	622.5	640.0	566.0	447.6	345.2
97.5°	74.1	87.8	101.6	154.3	262.0	449.9	666.0	802.7	815.0	756.1	672.1
100°	87.1	99.3	111.5	156.6	242.9	398.7	614.1	809.6	921.1	936.4	899.0
102.5°	101.6	113.0	124.5	164.2	237.5	364.3	549.2	752.3	915.8	1006.7	1029.6
105°	118.4	129.4	140.5	177.2	240.6	347.5	501.0	680.5	855.4	987.6	1063.2
107.5°	135.2	146.2	157.3	190.9	249.8	342.9	469.7	621.7	781.3	924.2	1029.6
110°	152.8	163.1	173.4	207.0	260.4	344.5	455.2	579.7	715.7	847.8	958.5

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	169.6	179.9	190.2	222.3	271.9	349.0	448.3	556.0	667.5	780.6	883.7
115°	187.1	197.4	207.7	238.3	284.1	355.2	446.8	543.0	638.5	732.5	821.8
117.5°	203.2	213.9	224.6	253.6	296.3	361.3	446.0	536.2	621.7	701.2	773.7
120°	219.2	229.9	240.6	269.6	309.3	368.1	446.0	530.8	611.0	682.1	743.2
122.5°	235.2	245.6	255.9	284.9	321.6	375.0	445.3	524.7	601.9	669.8	724.1
125°	249.8	260.5	271.1	298.6	333.8	381.9	444.5	517.8	591.2	656.9	709.6
127.5°	263.5	274.2	284.9	311.6	344.5	387.2	443.0	508.7	578.9	642.3	695.0
130°	276.5	287.6	298.6	324.6	354.4	393.3	442.2	500.3	563.7	624.0	675.9
132.5°	288.7	299.0	309.3	335.3	364.3	398.7	441.5	492.6	547.6	603.4	653.8
135°	300.2	310.1	320.0	345.2	372.7	404.0	440.7	485.0	533.1	582.8	629.4
137.5°	310.1	319.6	329.2	352.9	378.8	407.1	440.7	478.1	519.4	562.9	603.4
140°	319.3	328.5	337.6	360.5	384.9	410.9	439.9	472.8	507.9	543.8	578.2
142.5°	327.7	336.4	345.2	367.4	389.5	414.0	439.9	468.2	497.2	527.8	556.0
145°	335.3	343.7	352.1	372.0	392.6	414.7	438.4	462.9	487.3	513.3	536.2
147.5°	342.9	350.5	358.2	377.3	395.6	415.5	436.1	458.3	478.9	500.3	519.4
150°	349.8	357.0	364.3	381.1	397.9	415.5	433.8	452.9	471.3	488.8	504.1
152.5°	356.7	363.2	369.7	384.2	399.5	414.0	430.0	446.8	462.9	477.4	491.1
155°	362.8	368.6	374.3	387.2	400.2	412.4	426.2	440.7	454.4	466.7	478.1
157.5°	368.9	373.5	378.1	389.5	400.2	410.9	422.4	434.6	445.3	456.0	465.9
160°	373.5	377.7	381.9	391.1	400.2	408.6	417.8	427.7	436.9	445.3	453.7
162.5°	378.1	381.2	384.2	392.6	400.2	406.3	413.2	421.6	428.5	435.4	441.5
165°	381.1	383.4	385.7	392.6	398.7	403.3	408.6	414.7	420.8	425.4	430.8
167.5°	383.4	385.3	387.2	392.6	397.2	400.2	404.0	408.6	413.2	417.0	421.6
170°	385.7	386.8	388.0	391.8	395.6	397.2	399.5	402.5	406.3	408.6	411.7
172.5°	387.2	388.0	388.8	391.1	394.1	394.1	394.9	397.2	400.2	401.7	403.3
175°	388.8	388.8	388.8	390.3	392.6	391.8	391.8	393.3	394.9	395.6	397.2
177.5°	388.8	388.8	388.8	389.5	391.1	389.5	389.5	390.3	391.1	391.8	391.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	1877.0	1883.4	1875.4	1880.2	1869.0	1867.4	1869.0	1869.0	1870.6	1872.2	1873.8
5°	1771.4	1769.8	1760.2	1753.8	1749.0	1753.8	1757.0	1760.2	1757.0	1760.2	1761.8
7.5°	1672.2	1667.4	1662.6	1651.4	1654.6	1651.4	1661.0	1656.2	1656.2	1664.2	1670.6
10°	1584.2	1574.6	1571.4	1558.6	1549.0	1547.4	1558.6	1563.4	1568.2	1571.4	1584.2
12.5°	1470.6	1456.2	1445.0	1449.8	1422.6	1433.8	1437.0	1430.6	1449.8	1472.2	1459.4
15°	1349.0	1350.6	1328.2	1320.2	1297.8	1304.2	1305.8	1321.8	1337.8	1336.2	1355.4
17.5°	1259.4	1249.8	1230.6	1229.0	1219.4	1224.2	1222.6	1235.4	1230.6	1238.6	1254.6
20°	1176.1	1169.7	1153.7	1147.3	1150.5	1147.3	1148.9	1150.5	1155.3	1172.9	1169.7
22.5°	1110.5	1102.5	1102.5	1094.5	1084.9	1081.7	1089.7	1094.5	1100.9	1104.1	1112.1
25°	1052.9	1046.5	1038.5	1033.7	1025.7	1027.3	1032.1	1038.5	1043.3	1049.7	1056.1
27.5°	993.7	993.7	985.7	984.1	980.9	979.3	985.7	988.9	988.9	993.7	1000.1
30°	947.3	947.3	939.3	937.7	936.1	936.1	940.9	942.5	944.1	948.9	952.1
32.5°	902.5	900.9	897.7	899.3	897.7	899.3	899.3	900.9	904.1	905.7	912.1
35°	860.9	862.5	859.3	859.3	857.7	859.3	862.5	864.1	865.7	868.9	868.9
37.5°	820.9	824.1	822.5	827.3	827.3	827.3	827.3	830.5	830.5	830.5	828.9
40°	785.7	785.7	784.1	787.3	790.5	790.5	792.1	792.1	793.7	793.7	792.1
42.5°	745.7	748.9	753.7	755.3	758.5	756.9	761.7	760.1	761.7	758.5	755.3
45°	708.9	708.9	715.3	721.7	723.3	723.3	723.3	726.5	723.3	718.5	716.9
47.5°	668.9	672.1	675.3	683.3	684.9	684.9	684.9	684.9	681.7	681.7	681.7
50°	628.9	630.5	632.1	635.3	640.1	638.5	638.5	638.5	644.9	638.5	640.1
52.5°	580.9	582.5	584.1	590.5	588.9	588.9	590.5	590.5	595.3	593.7	590.5
55°	532.9	532.9	536.1	536.1	536.1	539.3	540.9	544.1	542.5	544.1	545.7
57.5°	484.9	481.7	480.1	480.1	484.9	483.3	484.9	484.9	491.3	494.5	496.1
60°	428.9	428.9	427.3	417.7	417.7	416.1	420.9	424.1	427.3	441.7	440.1
62.5°	371.2	364.8	358.4	360.0	350.4	355.2	352.0	355.2	364.8	376.0	377.6
65°	313.6	308.8	302.4	300.8	297.6	302.4	300.8	302.4	307.2	313.6	321.6
67.5°	262.4	260.8	257.6	256.0	256.0	256.0	259.2	259.2	260.8	265.6	270.4
70°	224.0	222.4	224.0	220.8	222.4	220.8	222.4	224.0	225.6	227.2	232.0
72.5°	188.8	188.8	188.8	185.6	188.8	187.2	187.2	188.8	190.4	192.0	195.2
75°	150.4	147.2	144.0	140.8	139.2	142.4	144.0	142.4	147.2	153.6	153.6
77.5°	113.6	112.0	112.0	112.0	113.6	112.0	115.2	113.6	115.2	115.2	118.4
80°	88.0	86.4	88.0	88.0	86.4	89.6	88.0	88.0	89.6	91.2	89.6
82.5°	64.0	65.6	64.0	64.0	64.0	67.2	64.0	64.0	64.0	65.6	65.6
85°	40.0	40.0	40.0	40.0	41.6	40.0	41.6	40.0	43.2	41.6	41.6
87.5°	14.4	16.0	17.6	17.6	17.6	17.6	16.0	17.6	19.2	17.6	19.2
90°	15.3	15.3	16.0	16.8	16.0	16.0	16.0	16.8	16.0	15.3	15.3
92.5°	99.0	89.4	77.9	72.6	69.5	69.5	69.5	72.6	77.9	89.4	99.0
95°	308.2	271.1	233.7	210.0	196.3	186.4	196.3	210.0	233.7	271.1	308.2
97.5°	629.4	586.6	534.6	488.8	465.9	447.6	465.9	488.8	534.6	586.6	629.4
100°	870.8	842.5	776.0	729.4	706.5	700.4	706.5	729.4	776.0	842.5	870.8
102.5°	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9	949.4	979.9	1014.3	1022.0
105°	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2	1089.9	1096.0	1094.5	1078.8
107.5°	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2	1141.1	1127.3	1093.7	1061.6
110°	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6	1128.9	1096.8	1042.6	1000.6

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2	1071.6	1031.1	967.7	925.7
115°	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8	1001.3	955.5	895.2	858.5
117.5°	805.8	837.9	891.3	931.0	957.0	960.8	957.0	931.0	891.3	837.9	805.8
120°	770.3	797.4	840.9	874.5	894.4	902.8	894.4	874.5	840.9	797.4	770.3
122.5°	747.0	769.9	805.0	832.5	848.6	857.0	848.6	832.5	805.0	769.9	747.0
125°	730.6	751.6	782.1	804.3	818.8	823.4	818.8	804.3	782.1	751.6	730.6
127.5°	714.9	734.8	765.3	785.2	797.4	802.0	797.4	785.2	765.3	734.8	714.9
130°	696.2	716.4	747.7	766.8	779.1	783.6	779.1	766.8	747.7	716.4	696.2
132.5°	674.0	694.3	724.8	747.0	758.4	763.0	758.4	747.0	724.8	694.3	674.0
135°	648.4	667.5	698.1	719.5	731.7	736.3	731.7	719.5	698.1	667.5	648.4
137.5°	621.0	638.5	667.5	689.7	699.6	705.0	699.6	689.7	667.5	638.5	621.0
140°	594.2	610.3	637.0	653.8	664.5	670.6	664.5	653.8	637.0	610.3	594.2
142.5°	569.4	582.8	605.7	621.0	630.1	633.9	630.1	621.0	605.7	582.8	569.4
145°	546.9	557.6	576.7	589.6	597.3	601.1	597.3	589.6	576.7	557.6	546.9
147.5°	528.2	536.9	551.4	562.9	569.0	570.5	569.0	562.9	551.4	536.9	528.2
150°	511.0	517.8	530.1	540.0	544.6	545.3	544.6	540.0	530.1	517.8	511.0
152.5°	496.4	501.8	511.7	519.4	521.7	522.4	521.7	519.4	511.7	501.8	496.4
155°	482.7	487.3	494.9	501.0	503.3	503.3	503.3	501.0	494.9	487.3	482.7
157.5°	469.7	473.5	479.7	484.2	485.8	485.8	485.8	484.2	479.7	473.5	469.7
160°	456.8	459.8	464.4	469.0	469.7	469.7	469.7	469.0	464.4	459.8	456.8
162.5°	444.2	446.8	449.9	454.4	455.2	454.4	455.2	454.4	449.9	446.8	444.2
165°	432.7	434.6	437.6	440.7	439.9	439.2	439.9	440.7	437.6	434.6	432.7
167.5°	422.8	423.9	425.4	427.7	427.7	427.0	427.7	427.7	425.4	423.9	422.8
170°	412.8	414.0	415.5	416.3	415.5	415.5	415.5	416.3	415.5	414.0	412.8
172.5°	404.0	404.8	405.6	406.3	405.6	404.0	405.6	406.3	405.6	404.8	404.0
175°	397.2	397.2	397.2	398.7	397.2	395.6	397.2	398.7	397.2	397.2	397.2
177.5°	392.2	392.6	391.8	392.6	391.1	389.5	391.1	392.6	391.8	392.6	392.2
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9	1985.9
2.5°	1880.2	1888.2	1885.0	1873.8	1878.6	1888.2	1897.8	1910.6	1918.6	1925.0	1928.2
5°	1769.8	1784.2	1781.0	1781.0	1787.4	1803.4	1819.4	1846.6	1856.2	1867.4	1883.4
7.5°	1672.2	1683.4	1693.0	1696.2	1705.8	1726.6	1747.4	1777.8	1801.8	1814.6	1824.2
10°	1585.8	1593.8	1608.2	1616.2	1625.8	1651.4	1681.8	1713.8	1737.8	1760.2	1773.0
12.5°	1475.4	1507.4	1526.6	1539.4	1552.2	1590.6	1614.6	1649.8	1678.6	1699.4	1718.6
15°	1352.2	1390.6	1401.8	1451.4	1483.4	1513.8	1550.6	1592.2	1619.4	1643.4	1669.0
17.5°	1248.2	1275.4	1288.2	1341.0	1368.2	1416.2	1469.0	1521.8	1563.4	1581.0	1606.6
20°	1182.5	1197.0	1222.6	1240.2	1269.0	1325.0	1382.6	1446.6	1509.0	1526.6	1552.2
22.5°	1115.3	1134.5	1152.1	1176.1	1198.6	1237.0	1294.6	1365.0	1432.2	1464.2	1494.6
25°	1054.5	1073.7	1084.9	1110.5	1131.3	1169.7	1209.8	1281.8	1361.8	1389.0	1437.0
27.5°	1006.5	1017.7	1036.9	1048.1	1072.1	1107.3	1144.1	1198.6	1277.0	1323.4	1369.8
30°	958.5	966.5	982.5	998.5	1016.1	1040.1	1081.7	1134.5	1206.6	1246.6	1293.0
32.5°	910.5	923.3	932.9	944.1	963.3	992.1	1020.9	1072.1	1129.7	1174.5	1221.0
35°	870.5	875.3	888.1	900.9	913.7	939.3	969.7	1019.3	1070.5	1105.7	1147.3
37.5°	827.3	835.3	844.9	849.7	870.5	886.5	918.5	956.9	1017.7	1040.1	1081.7
40°	793.7	792.1	801.7	809.7	819.3	844.9	864.1	905.7	953.7	988.9	1014.5
42.5°	752.1	752.1	755.3	764.9	777.7	793.7	816.1	851.3	900.9	926.5	956.9
45°	718.5	713.7	715.3	721.7	729.7	745.7	768.1	798.5	848.1	868.9	900.9
47.5°	678.5	673.7	673.7	680.1	686.5	697.7	715.3	750.5	790.5	817.7	841.7
50°	633.7	635.3	633.7	638.5	641.7	652.9	672.1	700.9	737.7	760.1	787.3
52.5°	592.1	588.9	587.3	590.5	596.9	604.9	625.7	651.3	686.5	708.9	732.9
55°	540.9	544.1	544.1	544.1	553.7	556.9	572.9	598.5	633.7	651.3	673.7
57.5°	494.5	492.9	496.1	494.5	502.5	513.7	526.5	545.7	580.9	598.5	619.3
60°	443.3	444.9	446.5	446.5	452.9	464.1	478.5	496.1	524.9	542.5	561.7
62.5°	380.8	388.8	396.9	400.1	409.7	417.7	427.3	446.5	472.1	484.9	502.5
65°	321.6	332.8	344.0	352.0	358.4	366.4	379.2	396.9	417.7	430.5	448.1
67.5°	270.4	278.4	292.8	300.8	313.6	323.2	331.2	345.6	371.2	376.0	390.4
70°	233.6	236.8	243.2	249.6	264.0	272.0	281.6	296.0	315.2	326.4	334.4
72.5°	196.8	198.4	201.6	208.0	214.4	224.0	235.2	248.0	265.6	270.4	281.6
75°	156.8	166.4	166.4	171.2	176.0	180.8	190.4	203.2	214.4	222.4	228.8
77.5°	116.8	121.6	124.8	132.8	139.2	144.0	150.4	160.0	166.4	172.8	177.6
80°	91.2	92.8	94.4	94.4	97.6	104.0	110.4	116.8	124.8	128.0	132.8
82.5°	67.2	67.2	67.2	70.4	72.0	73.6	73.6	76.8	84.8	88.0	92.8
85°	43.2	43.2	43.2	43.2	44.8	46.4	48.0	49.6	49.6	49.6	52.8
87.5°	17.6	20.8	19.2	20.8	20.8	20.8	20.8	22.4	22.4	24.0	24.0
90°	15.3	14.5	13.7	13.0	13.7	12.2	10.7	10.7	6.1	6.1	6.1
92.5°	108.5	137.5	184.1	249.0	299.4	262.0	190.2	116.1	68.7	58.8	48.9
95°	345.2	447.6	566.0	640.0	622.5	469.7	287.2	161.9	95.5	79.4	63.4
97.5°	672.1	756.1	815.0	802.7	666.0	449.9	262.0	154.3	101.6	87.8	74.1
100°	899.0	936.4	921.1	809.6	614.1	398.7	242.9	156.6	111.5	99.3	87.1
102.5°	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5	164.2	124.5	113.0	101.6
105°	1063.2	987.6	855.4	680.5	501.0	347.5	240.6	177.2	140.5	129.4	118.4
107.5°	1029.6	924.2	781.3	621.7	469.7	342.9	249.8	190.9	157.3	146.2	135.2
110°	958.5	847.8	715.7	579.7	455.2	344.5	260.4	207.0	173.4	163.1	152.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	883.7	780.6	667.5	556.0	448.3	349.0	271.9	222.3	190.2	179.9	169.6
115°	821.8	732.5	638.5	543.0	446.8	355.2	284.1	238.3	207.7	197.4	187.1
117.5°	773.7	701.2	621.7	536.2	446.0	361.3	296.3	253.6	224.6	213.9	203.2
120°	743.2	682.1	611.0	530.8	446.0	368.1	309.3	269.6	240.6	229.9	219.2
122.5°	724.1	669.8	601.9	524.7	445.3	375.0	321.6	284.9	255.9	245.6	235.2
125°	709.6	656.9	591.2	517.8	444.5	381.9	333.8	298.6	271.1	260.5	249.8
127.5°	695.0	642.3	578.9	508.7	443.0	387.2	344.5	311.6	284.9	274.2	263.5
130°	675.9	624.0	563.7	500.3	442.2	393.3	354.4	324.6	298.6	287.6	276.5
132.5°	653.8	603.4	547.6	492.6	441.5	398.7	364.3	335.3	309.3	299.0	288.7
135°	629.4	582.8	533.1	485.0	440.7	404.0	372.7	345.2	320.0	310.1	300.2
137.5°	603.4	562.9	519.4	478.1	440.7	407.1	378.8	352.9	329.2	319.6	310.1
140°	578.2	543.8	507.9	472.8	439.9	410.9	384.9	360.5	337.6	328.5	319.3
142.5°	556.0	527.8	497.2	468.2	439.9	414.0	389.5	367.4	345.2	336.4	327.7
145°	536.2	513.3	487.3	462.9	438.4	414.7	392.6	372.0	352.1	343.7	335.3
147.5°	519.4	500.3	478.9	458.3	436.1	415.5	395.6	377.3	358.2	350.5	342.9
150°	504.1	488.8	471.3	452.9	433.8	415.5	397.9	381.1	364.3	357.0	349.8
152.5°	491.1	477.4	462.9	446.8	430.0	414.0	399.5	384.2	369.7	363.2	356.7
155°	478.1	466.7	454.4	440.7	426.2	412.4	400.2	387.2	374.3	368.6	362.8
157.5°	465.9	456.0	445.3	434.6	422.4	410.9	400.2	389.5	378.1	373.5	368.9
160°	453.7	445.3	436.9	427.7	417.8	408.6	400.2	391.1	381.9	377.7	373.5
162.5°	441.5	435.4	428.5	421.6	413.2	406.3	400.2	392.6	384.2	381.2	378.1
165°	430.8	425.4	420.8	414.7	408.6	403.3	398.7	392.6	385.7	383.4	381.1
167.5°	421.6	417.0	413.2	408.6	404.0	400.2	397.2	392.6	387.2	385.3	383.4
170°	411.7	408.6	406.3	402.5	399.5	397.2	395.6	391.8	388.0	386.8	385.7
172.5°	403.3	401.7	400.2	397.2	394.9	394.1	394.1	391.1	388.8	388.0	387.2
175°	397.2	395.6	394.9	393.3	391.8	391.8	392.6	390.3	388.8	388.8	388.8
177.5°	391.8	391.8	391.1	390.3	389.5	389.5	391.1	389.5	388.8	388.8	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1985.9	1985.9	1985.9	1985.9
2.5°	1941.0	1950.6	1966.6	1989.1
5°	1896.2	1923.4	1949.0	1982.7
7.5°	1856.2	1888.2	1923.4	1971.4
10°	1809.8	1849.8	1894.6	1953.8
12.5°	1755.4	1811.4	1862.6	1926.6
15°	1715.4	1757.0	1822.6	1897.8
17.5°	1659.4	1715.4	1781.0	1865.8
20°	1606.6	1665.8	1739.4	1827.4
22.5°	1550.6	1617.8	1691.4	1785.8
25°	1493.0	1565.0	1638.6	1739.4
27.5°	1440.2	1505.8	1589.0	1691.4
30°	1376.2	1451.4	1531.4	1638.6
32.5°	1313.8	1392.2	1473.8	1581.0
35°	1246.6	1325.0	1414.6	1517.0
37.5°	1180.9	1267.4	1349.0	1448.2
40°	1108.9	1198.6	1283.4	1384.2
42.5°	1038.5	1131.3	1216.2	1302.6
45°	972.9	1064.1	1140.9	1222.6
47.5°	910.5	992.1	1070.5	1144.1
50°	849.7	918.5	990.5	1051.3
52.5°	785.7	851.3	908.9	963.3
55°	728.1	779.3	830.5	880.1
57.5°	659.3	710.5	755.3	793.7
60°	601.7	633.7	676.9	716.9
62.5°	536.1	572.9	606.5	632.1
65°	472.1	504.1	529.7	552.1
67.5°	417.7	436.9	456.1	480.1
70°	352.0	368.0	390.4	408.1
72.5°	296.0	308.8	320.0	340.8
75°	240.0	251.2	257.6	276.8
77.5°	185.6	196.8	201.6	212.8
80°	142.4	144.0	150.4	160.0
82.5°	97.6	100.8	102.4	110.4
85°	56.0	64.0	62.4	65.6
87.5°	24.0	25.6	28.8	32.0
90°	5.3	4.6	2.3	0.8
92.5°	35.1	23.7	15.3	10.7
95°	45.1	35.1	27.5	25.2
97.5°	58.0	48.9	42.0	42.0
100°	72.6	63.4	58.0	58.0
102.5°	87.8	79.4	74.9	73.3
105°	104.6	95.5	91.7	89.4
107.5°	122.2	112.3	108.5	106.9
110°	139.0	129.8	126.0	124.5

TEST NUMBER: P1026207

CATALOG NUMBER: S124RDIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.8	147.4	142.8	141.3
115°	172.6	165.0	159.6	157.3
117.5°	189.4	181.0	176.4	174.1
120°	206.2	197.8	192.5	190.9
122.5°	220.7	213.1	207.7	206.2
125°	235.2	226.8	222.3	219.2
127.5°	248.2	239.1	233.7	231.4
130°	262.0	250.5	244.4	241.4
132.5°	272.7	262.0	253.6	251.3
135°	284.1	271.1	263.5	260.4
137.5°	293.3	281.1	272.7	269.6
140°	303.2	290.2	281.8	279.5
142.5°	312.4	300.2	292.5	290.2
145°	320.8	310.1	302.5	300.2
147.5°	330.7	319.3	312.4	311.6
150°	338.4	329.2	323.1	322.3
152.5°	346.8	338.4	332.2	332.2
155°	354.4	346.8	342.2	341.4
157.5°	361.3	355.2	350.6	350.6
160°	367.4	362.0	359.0	359.0
162.5°	372.7	368.1	365.9	366.6
165°	377.3	373.5	372.0	372.0
167.5°	381.1	378.1	377.3	378.1
170°	384.2	381.9	381.1	381.9
172.5°	386.5	384.9	384.9	385.7
175°	388.0	387.2	387.2	388.0
177.5°	388.8	388.0	388.8	389.5
180°	388.8	388.8	388.8	388.8

(END OF REPORT)