

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026219

Luminaire Tested: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026219
REPORT IS A COMBINATION OF REPORTS P999209 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7808.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59	55		
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51	47		
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44	41		
4	78	68	60	54	73	64	57	51	57	51	47	50	46	43	44	41	38	35		
5	72	61	52	47	68	57	50	45	51	45	41	46	41	37	40	37	34	31		
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30	27		
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24		
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22		
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16103	16103	16103	16103
5°	16104	18196	16130	13907
10°	16017	20976	16005	12095
15°	15827	23607	15827	10126
20°	15627	25595	15545	8917
25°	15384	25704	15313	8054
30°	15125	21857	15006	7460
35°	14758	16492	14572	7017
40°	14352	11952	14069	6672
45°	13678	9084	13338	6366
50°	12880	7342	12526	5917
55°	12014	6079	11621	5322
60°	11144	5140	10647	4425
65°	10054	4187	9734	3518
70°	9053	3396	8627	2857
75°	7934	2447	7383	2094
80°	6544	1622	5955	1539
85°	4745	834	3937	834

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20160 cd/sqm

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	2.4
10°-20°	577.5	7.4
20°-30°	904.5	11.6
30°-40°	1004.5	12.9
40°-50°	890.1	11.4
50°-60°	693.7	8.9
60°-70°	453.7	5.8
70°-80°	222.6	2.9
80°-90°	55.7	0.7
90°-100°	280.1	3.6
100°-110°	584.7	7.5
110°-120°	519.8	6.7
120°-130°	437.5	5.6
130°-140°	365.0	4.7
140°-150°	278.7	3.6
150°-160°	195.9	2.5
160°-170°	115.2	1.5
170°-180°	37.5	0.5
0°-30°	1673.2	21.4
0°-40°	2677.7	34.3
0°-60°	4261.4	54.6
0°-90°	4993.5	64.0
90°-120°	1384.6	17.7
90°-150°	2465.8	31.6
90°-180°	2814.0	36.0
0°-180°	7808.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	2282	1975	1744	1972	187
15°	1887	3023	1887	1297	1887	532
25°	1730	3260	1722	1022	1730	797
35°	1508	2008	1489	854	1508	943
45°	1216	1026	1186	719	1216	937
55°	875	613	847	536	875	783
65°	549	358	532	301	549	548
75°	275	166	256	142	275	292
85°	65	40	54	40	65	74
90°	1	16	1	16	1	6
95°	25	185	25	185	25	27
105°	89	1068	89	1068	89	95
115°	156	1026	156	1026	156	155
125°	218	818	218	818	218	194
135°	259	732	259	732	259	200
145°	298	598	298	598	298	187
155°	339	500	339	500	339	157
165°	370	436	370	436	370	104
175°	386	393	386	393	386	37
180°	386	386	386	386	386	

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	1978.0	1995.5	2005.0	2013.0	2028.9	2035.2	2048.0	2051.2	2063.9	2062.3	2057.5
5°	1971.6	2001.8	2024.1	2048.0	2076.6	2092.5	2110.0	2135.5	2148.2	2165.7	2176.9
7.5°	1960.5	2001.8	2038.4	2075.0	2121.2	2146.6	2168.9	2208.7	2242.1	2270.8	2302.6
10°	1942.9	1995.5	2049.6	2098.9	2162.5	2192.8	2226.2	2285.1	2331.2	2371.0	2421.9
12.5°	1915.9	1989.1	2049.6	2116.4	2197.6	2238.9	2283.5	2353.5	2407.6	2472.8	2536.5
15°	1887.3	1968.4	2048.0	2135.5	2227.8	2275.5	2320.1	2414.0	2496.7	2571.5	2641.5
17.5°	1855.4	1944.5	2032.1	2129.1	2240.5	2299.4	2351.9	2464.9	2555.6	2652.7	2722.7
20°	1817.2	1914.3	2014.6	2122.8	2248.5	2313.7	2372.6	2501.5	2601.7	2706.8	2794.3
22.5°	1775.9	1880.9	1990.7	2108.4	2238.9	2310.5	2379.0	2517.4	2633.6	2730.6	2848.4
25°	1729.7	1841.1	1954.1	2078.2	2224.6	2302.6	2372.6	2509.4	2633.6	2760.9	2875.4
27.5°	1682.0	1796.6	1914.3	2044.8	2194.4	2270.8	2350.3	2482.4	2627.2	2765.6	2881.8
30°	1629.5	1740.9	1865.0	1989.1	2148.2	2224.6	2305.8	2449.0	2606.5	2745.0	2870.7
32.5°	1572.2	1686.8	1804.5	1933.4	2089.3	2172.1	2246.9	2409.2	2569.9	2706.8	2824.5
35°	1508.5	1616.7	1728.1	1860.2	2014.6	2089.3	2178.5	2347.1	2509.4	2654.3	2730.6
37.5°	1440.1	1543.5	1647.0	1777.5	1925.4	2016.1	2103.7	2273.9	2445.8	2542.9	2582.6
40°	1376.5	1467.2	1557.9	1683.6	1833.2	1927.0	2016.1	2192.8	2344.0	2418.7	2388.5
42.5°	1295.3	1389.2	1470.3	1586.5	1737.7	1825.2	1915.9	2098.9	2221.4	2251.7	2176.9
45°	1215.7	1293.7	1371.7	1484.7	1643.8	1718.6	1815.6	1985.9	2087.8	2060.7	1950.9
47.5°	1137.8	1201.4	1274.6	1384.4	1527.6	1616.7	1707.4	1855.4	1927.0	1888.8	1736.1
50°	1045.5	1109.1	1185.5	1281.0	1419.4	1505.3	1577.0	1713.8	1767.9	1674.0	1489.4
52.5°	957.9	1013.6	1078.9	1168.0	1300.1	1378.0	1456.0	1573.8	1591.3	1483.1	1288.9
55°	875.2	919.8	988.2	1059.8	1180.7	1263.5	1317.6	1417.8	1413.1	1277.8	1110.7
57.5°	789.3	830.6	876.8	951.6	1066.2	1128.2	1187.1	1274.6	1228.5	1113.9	948.4
60°	712.9	736.8	782.9	854.5	951.6	1005.7	1051.8	1099.6	1059.8	935.7	808.4
62.5°	628.6	655.6	689.0	746.3	832.2	883.2	916.6	937.3	895.9	800.4	684.2
65°	549.0	572.9	607.9	658.8	724.0	762.2	779.7	794.0	771.8	663.6	571.3
67.5°	477.4	493.3	525.1	558.5	628.6	638.1	662.0	668.3	623.8	541.0	467.8
70°	405.8	421.7	436.0	475.8	507.6	525.1	529.9	529.9	485.3	431.2	370.8
72.5°	338.9	348.5	362.8	389.9	407.4	420.1	426.5	418.5	377.1	332.6	288.0
75°	275.3	280.1	292.8	310.3	324.6	319.8	318.3	308.7	278.5	246.6	221.2
77.5°	211.6	214.8	229.1	233.9	233.9	238.7	232.3	222.8	197.3	173.4	162.3
80°	159.1	163.9	165.5	168.7	165.5	165.5	160.7	144.8	132.1	120.9	113.0
82.5°	109.8	113.0	114.6	109.8	113.0	108.2	100.3	89.1	81.2	79.6	76.4
85°	65.2	66.8	65.2	65.2	60.5	58.9	52.5	50.9	47.7	47.7	46.1
87.5°	31.8	30.2	27.1	23.9	23.9	22.3	23.9	20.7	23.9	22.3	20.7
90°	0.8	2.3	4.6	5.3	6.1	6.1	6.1	10.6	10.6	12.1	13.7
92.5°	10.6	15.2	23.5	34.9	48.6	58.4	68.3	115.4	189.0	260.4	297.6
95°	25.1	27.3	34.9	44.8	63.0	79.0	94.9	160.9	285.5	466.9	618.7
97.5°	41.8	41.8	48.6	57.7	73.6	87.3	101.0	153.4	260.4	447.2	662.0
100°	57.7	57.7	63.0	72.1	86.5	98.6	110.8	155.6	241.4	396.3	610.4
102.5°	72.9	74.4	79.0	87.3	101.0	112.4	123.7	163.2	236.1	362.1	545.9
105°	88.8	91.1	94.9	104.0	117.7	128.7	139.7	176.1	239.1	345.4	498.0
107.5°	106.3	107.8	111.6	121.5	134.4	145.4	156.4	189.8	248.3	340.9	466.9
110°	123.7	125.3	129.1	138.2	151.8	162.0	172.3	205.7	258.9	342.4	452.5

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	140.5	142.0	146.5	154.9	168.5	178.8	189.0	220.9	270.3	347.0	445.6
115°	156.4	158.7	164.0	171.6	186.0	196.2	206.5	236.9	282.4	353.0	444.1
117.5°	173.1	175.4	179.9	188.3	201.9	212.6	223.2	252.1	294.6	359.1	443.4
120°	189.8	191.3	196.6	205.0	217.9	228.5	239.1	268.0	307.5	365.9	443.4
122.5°	205.0	206.5	211.8	219.4	233.8	244.0	254.3	283.2	319.6	372.8	442.6
125°	217.9	220.9	225.5	233.8	248.3	258.9	269.5	296.8	331.8	379.6	441.9
127.5°	230.0	232.3	237.6	246.7	261.9	272.5	283.2	309.8	342.4	384.9	440.3
130°	239.9	242.9	249.0	260.4	274.8	285.8	296.8	322.7	352.3	391.0	439.6
132.5°	249.8	252.1	260.4	271.0	287.0	297.2	307.5	333.3	362.1	396.3	438.8
135°	258.9	261.9	269.5	282.4	298.4	308.2	318.1	343.2	370.5	401.6	438.1
137.5°	268.0	271.0	279.4	291.5	308.2	317.7	327.2	350.7	376.6	404.7	438.1
140°	277.9	280.1	288.5	301.4	317.3	326.5	335.6	358.3	382.6	408.4	437.3
142.5°	288.5	290.8	298.4	310.5	325.7	334.4	343.2	365.2	387.2	411.5	437.3
145°	298.4	300.6	308.2	318.9	333.3	341.6	350.0	369.7	390.2	412.2	435.8
147.5°	309.8	310.5	317.3	328.7	340.9	348.5	356.1	375.0	393.3	413.0	433.5
150°	320.4	321.1	327.2	336.3	347.7	354.9	362.1	378.8	395.5	413.0	431.2
152.5°	330.3	330.3	336.3	344.7	354.5	361.0	367.5	381.9	397.1	411.5	427.4
155°	339.4	340.1	344.7	352.3	360.6	366.3	372.0	384.9	397.8	410.0	423.6
157.5°	348.5	348.5	353.0	359.1	366.7	371.2	375.8	387.2	397.8	408.4	419.8
160°	356.8	356.8	359.9	365.2	371.2	375.4	379.6	388.7	397.8	406.2	415.3
162.5°	364.4	363.7	365.9	370.5	375.8	378.8	381.9	390.2	397.8	403.9	410.7
165°	369.7	369.7	371.2	375.0	378.8	381.1	383.4	390.2	396.3	400.9	406.2
167.5°	375.8	375.0	375.8	378.8	381.1	383.0	384.9	390.2	394.8	397.8	401.6
170°	379.6	378.8	379.6	381.9	383.4	384.5	385.7	389.5	393.3	394.8	397.1
172.5°	383.4	382.6	382.6	384.2	384.9	385.6	386.4	388.7	391.7	391.7	392.5
175°	385.7	384.9	384.9	385.7	386.4	386.4	386.4	388.0	390.2	389.5	389.5
177.5°	387.2	386.4	385.7	386.4	386.4	386.4	386.4	387.2	388.7	387.2	387.2
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	2070.3	2087.8	2089.3	2105.3	2100.5	2092.5	2106.9	2097.3	2116.4	2110.0	2118.0
5°	2191.2	2215.1	2235.7	2248.5	2270.8	2266.0	2289.8	2281.9	2299.4	2281.9	2304.2
7.5°	2332.8	2372.6	2393.3	2426.7	2436.2	2437.8	2466.5	2472.8	2484.0	2472.8	2485.6
10°	2471.3	2519.0	2566.7	2593.8	2611.3	2635.2	2660.6	2671.8	2679.7	2668.6	2676.5
12.5°	2597.0	2671.8	2724.3	2778.4	2791.1	2811.8	2838.8	2835.7	2867.5	2861.1	2875.4
15°	2713.1	2795.9	2859.5	2902.5	2937.5	2955.0	3005.9	3009.1	3007.5	3023.4	3013.9
17.5°	2816.6	2886.6	2977.3	3033.0	3075.9	3075.9	3104.6	3163.5	3158.7	3157.1	3166.6
20°	2900.9	2980.5	3064.8	3158.7	3193.7	3200.1	3239.8	3270.1	3274.8	3274.8	3274.8
22.5°	2964.5	3058.4	3149.1	3216.0	3243.0	3265.3	3300.3	3319.4	3325.8	3322.6	3325.8
25°	2996.4	3085.5	3177.8	3238.2	3254.2	3266.9	3270.1	3281.2	3279.6	3260.5	3271.7
27.5°	3002.7	3088.7	3149.1	3165.1	3157.1	3149.1	3098.2	3103.0	3088.7	3060.0	3071.2
30°	2974.1	3020.2	3018.7	2969.3	2955.0	2921.6	2875.4	2807.0	2751.3	2727.4	2735.4
32.5°	2870.7	2870.7	2813.4	2702.0	2652.7	2592.2	2509.4	2447.4	2374.2	2358.3	2388.5
35°	2727.4	2646.3	2541.3	2394.9	2320.1	2275.5	2132.3	2087.8	2025.7	2008.2	2022.5
37.5°	2504.7	2369.4	2216.6	2079.8	2016.1	1936.6	1810.9	1747.2	1702.7	1672.4	1686.8
40°	2254.8	2090.9	1931.8	1763.1	1693.1	1627.9	1534.0	1476.7	1405.1	1408.3	1413.1
42.5°	2016.1	1823.6	1645.4	1489.4	1422.6	1368.5	1303.3	1233.2	1207.8	1199.8	1191.9
45°	1763.1	1557.9	1390.8	1274.6	1214.1	1163.2	1102.8	1063.0	1032.7	1026.4	1034.3
47.5°	1524.4	1351.0	1191.9	1083.7	1034.3	1008.9	961.1	924.5	905.4	889.5	899.1
50°	1308.0	1145.7	1018.4	927.7	892.7	875.2	830.6	811.6	792.5	787.7	786.1
52.5°	1129.8	991.4	881.6	808.4	781.3	771.8	738.4	711.3	695.4	700.2	703.3
55°	967.5	849.7	763.8	704.9	682.7	671.5	647.6	628.6	617.4	612.6	615.8
57.5°	824.3	722.4	660.4	612.6	595.1	590.4	564.9	558.5	550.6	545.8	545.8
60°	693.8	622.2	564.9	537.9	518.8	514.0	494.9	486.9	485.3	480.6	477.4
62.5°	584.0	525.1	485.3	456.7	448.7	447.1	434.4	424.9	420.1	416.9	416.9
65°	488.5	445.6	412.1	391.5	385.1	381.9	367.6	364.4	361.2	358.0	356.4
67.5°	407.4	369.2	345.3	331.0	323.0	324.6	316.7	310.3	310.3	308.7	307.1
70°	329.4	305.5	284.8	276.9	273.7	270.5	267.3	262.6	261.0	261.0	261.0
72.5°	259.4	243.5	232.3	227.6	224.4	221.2	218.0	218.0	218.0	216.4	216.4
75°	198.9	192.5	184.6	179.8	179.8	183.0	178.2	173.4	168.7	165.5	167.1
77.5°	149.6	146.4	141.6	133.7	135.3	132.1	132.1	128.9	130.5	130.5	127.3
80°	109.8	105.0	103.4	98.7	100.3	98.7	97.1	97.1	93.9	93.9	93.9
82.5°	76.4	71.6	71.6	70.0	68.4	68.4	66.8	66.8	68.4	65.2	65.2
85°	46.1	44.6	44.6	41.4	41.4	41.4	41.4	43.0	41.4	39.8	39.8
87.5°	20.7	22.3	20.7	19.1	19.1	19.1	17.5	17.5	15.9	17.5	17.5
90°	12.9	13.7	14.4	15.2	15.2	15.2	15.9	16.7	15.9	15.9	15.9
92.5°	247.5	183.0	136.7	107.8	98.3	88.8	77.4	72.1	69.1	69.1	69.1
95°	636.2	562.6	444.9	343.2	306.4	269.5	232.3	208.8	195.1	185.2	195.1
97.5°	797.9	810.1	751.6	668.1	625.6	583.1	531.4	485.9	463.1	444.9	463.1
100°	804.7	915.6	930.8	893.6	865.5	837.4	771.3	725.0	702.3	696.2	702.3
102.5°	747.8	910.3	1000.6	1023.4	1015.8	1008.2	974.1	943.7	919.4	914.8	919.4
105°	676.4	850.3	981.6	1056.8	1072.4	1087.9	1089.4	1083.4	1072.7	1068.2	1072.7
107.5°	618.0	776.7	918.6	1023.4	1055.3	1087.2	1120.6	1134.2	1140.3	1141.1	1140.3
110°	576.2	711.4	842.7	952.8	994.6	1036.3	1090.2	1122.1	1135.8	1142.6	1135.8

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	552.7	663.5	775.9	878.4	920.2	961.9	1024.9	1065.2	1085.7	1097.8	1085.7
115°	539.8	634.7	728.1	816.9	853.4	889.8	949.8	995.3	1019.6	1025.7	1019.6
117.5°	533.0	618.0	696.9	769.1	801.0	832.8	886.0	925.5	951.3	955.1	951.3
120°	527.6	607.4	678.0	738.7	765.7	792.6	835.9	869.3	889.0	897.4	889.0
122.5°	521.6	598.2	665.8	719.7	742.5	765.3	800.2	827.5	843.5	851.8	843.5
125°	514.7	587.6	652.9	705.3	726.2	747.1	777.4	799.4	813.9	818.4	813.9
127.5°	505.6	575.5	638.5	690.9	710.6	730.3	760.7	780.5	792.6	797.2	792.6
130°	497.3	560.3	620.3	671.9	692.0	712.1	743.3	762.2	774.4	778.9	774.4
132.5°	489.7	544.3	599.8	649.9	670.0	690.1	720.5	742.5	753.9	758.4	753.9
135°	482.1	529.9	579.3	625.6	644.6	663.5	693.9	715.2	727.3	731.9	727.3
137.5°	475.3	516.3	559.5	599.8	617.2	634.7	663.5	685.6	695.4	700.7	695.4
140°	469.9	504.9	540.5	574.7	590.7	606.6	633.2	649.9	660.5	666.6	660.5
142.5°	465.4	494.2	524.6	552.7	566.0	579.3	602.0	617.2	626.3	630.1	626.3
145°	460.1	484.4	510.2	533.0	543.6	554.2	573.2	586.1	593.7	597.5	593.7
147.5°	455.5	476.0	497.3	516.3	525.0	533.7	548.1	559.5	565.6	567.1	565.6
150°	450.2	468.4	485.9	501.1	507.9	514.7	526.9	536.8	541.3	542.1	541.3
152.5°	444.1	460.1	474.5	488.2	493.5	498.8	508.7	516.3	518.5	519.3	518.5
155°	438.1	451.7	463.9	475.3	479.8	484.4	492.0	498.0	500.3	500.3	500.3
157.5°	432.0	442.6	453.2	463.1	466.9	470.7	476.8	481.3	482.8	482.8	482.8
160°	425.2	434.3	442.6	451.0	454.0	457.0	461.6	466.1	466.9	466.9	466.9
162.5°	419.1	425.9	432.7	438.8	441.4	444.1	447.2	451.7	452.5	451.7	452.5
165°	412.2	418.3	422.9	428.2	430.1	432.0	435.0	438.1	437.3	436.5	437.3
167.5°	406.2	410.7	414.5	419.1	420.2	421.4	422.9	425.2	425.2	424.4	425.2
170°	400.1	403.9	406.2	409.2	410.4	411.5	413.0	413.8	413.0	413.0	413.0
172.5°	394.8	397.8	399.3	400.9	401.6	402.4	403.1	403.9	403.1	401.6	403.1
175°	391.0	392.5	393.3	394.8	394.8	394.8	394.8	396.3	394.8	393.3	394.8
177.5°	388.0	388.7	389.5	389.5	389.8	390.2	389.5	390.2	388.7	387.2	388.7
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	2122.8	2111.6	2110.0	2110.0	2092.5	2102.1	2083.0	2062.3	2052.7	2052.7	2035.2
5°	2299.4	2288.3	2277.1	2259.6	2259.6	2250.1	2219.8	2189.6	2167.3	2148.2	2127.5
7.5°	2480.8	2469.7	2437.8	2420.3	2429.9	2410.8	2371.0	2320.1	2281.9	2251.7	2208.7
10°	2678.1	2647.9	2632.0	2622.4	2589.0	2568.3	2522.2	2447.4	2399.6	2359.9	2304.2
12.5°	2838.8	2848.4	2787.9	2792.7	2759.3	2730.6	2659.0	2587.4	2515.8	2460.1	2377.4
15°	3012.3	2983.6	2947.0	2918.4	2907.3	2872.3	2811.8	2716.3	2638.3	2550.8	2456.9
17.5°	3149.1	3126.9	3091.9	3064.8	3040.9	2956.6	2905.7	2821.3	2714.7	2628.8	2514.2
20°	3265.3	3244.6	3195.3	3177.8	3134.8	3074.3	3001.1	2870.7	2775.2	2681.3	2569.9
22.5°	3314.6	3293.9	3251.0	3228.7	3201.7	3142.8	3072.8	2948.6	2830.9	2713.1	2595.4
25°	3273.3	3273.3	3252.6	3244.6	3220.7	3168.2	3096.6	2991.6	2865.9	2738.6	2598.6
27.5°	3072.8	3112.5	3126.9	3134.8	3134.8	3136.4	3087.1	2985.2	2862.7	2738.6	2592.2
30°	2783.1	2850.0	2908.9	2926.4	2956.6	2990.0	3010.7	2961.4	2851.6	2721.1	2574.7
32.5°	2418.7	2504.7	2614.5	2641.5	2682.9	2783.1	2838.8	2859.5	2799.1	2684.5	2528.5
35°	2055.9	2164.1	2231.0	2313.7	2351.9	2499.9	2624.0	2698.8	2684.5	2616.1	2474.4
37.5°	1739.3	1801.3	1882.5	1970.0	2046.4	2188.0	2342.4	2487.2	2546.0	2512.6	2406.0
40°	1435.3	1508.5	1605.6	1677.2	1729.7	1871.3	2062.3	2219.8	2348.7	2369.4	2304.2
42.5°	1220.5	1293.7	1352.6	1430.6	1471.9	1608.8	1777.5	1974.8	2127.5	2208.7	2180.0
45°	1055.0	1099.6	1147.3	1191.9	1242.8	1363.7	1519.7	1736.1	1907.9	2022.5	2033.7
47.5°	910.2	950.0	991.4	1032.7	1061.4	1155.3	1298.5	1475.1	1662.9	1820.4	1882.5
50°	808.4	827.5	857.7	881.6	915.0	996.1	1110.7	1263.5	1462.4	1632.7	1713.8
52.5°	708.1	732.0	755.9	776.5	798.8	856.1	961.1	1093.2	1265.1	1440.1	1540.4
55°	623.8	642.9	665.2	679.5	692.2	743.1	822.7	924.5	1072.5	1238.0	1362.1
57.5°	555.4	563.3	582.4	590.4	604.7	646.1	703.3	794.0	913.4	1074.1	1176.0
60°	480.6	496.5	510.8	517.2	528.3	556.9	596.7	681.1	784.5	902.3	1018.4
62.5°	420.1	426.5	437.6	445.6	453.5	483.7	517.2	580.8	658.8	757.4	864.1
65°	364.4	367.6	374.0	385.1	389.9	412.1	431.2	477.4	550.6	625.4	732.0
67.5°	307.1	310.3	318.3	324.6	329.4	343.7	364.4	397.8	437.6	520.3	579.2
70°	262.6	262.6	267.3	270.5	275.3	281.7	292.8	318.3	354.9	407.4	461.5
72.5°	219.6	219.6	219.6	224.4	224.4	229.1	235.5	253.0	278.5	319.8	354.9
75°	170.3	171.9	175.0	175.0	176.6	183.0	187.8	192.5	205.3	232.3	264.2
77.5°	128.9	132.1	133.7	130.5	133.7	133.7	140.0	146.4	152.8	160.7	184.6
80°	95.5	97.1	93.9	95.5	95.5	98.7	101.8	100.3	103.4	113.0	119.3
82.5°	63.7	65.2	65.2	65.2	65.2	70.0	70.0	68.4	70.0	71.6	73.2
85°	39.8	38.2	38.2	39.8	38.2	38.2	39.8	41.4	39.8	41.4	43.0
87.5°	17.5	17.5	17.5	17.5	15.9	15.9	17.5	15.9	17.5	15.9	14.3
90°	16.7	15.9	15.2	15.2	15.2	14.4	13.7	12.9	13.7	12.1	10.6
92.5°	72.1	77.4	88.8	98.3	107.8	136.7	183.0	247.5	297.6	260.4	189.0
95°	208.8	232.3	269.5	306.4	343.2	444.9	562.6	636.2	618.7	466.9	285.5
97.5°	485.9	531.4	583.1	625.6	668.1	751.6	810.1	797.9	662.0	447.2	260.4
100°	725.0	771.3	837.4	865.5	893.6	930.8	915.6	804.7	610.4	396.3	241.4
102.5°	943.7	974.1	1008.2	1015.8	1023.4	1000.6	910.3	747.8	545.9	362.1	236.1
105°	1083.4	1089.4	1087.9	1072.4	1056.8	981.6	850.3	676.4	498.0	345.4	239.1
107.5°	1134.2	1120.6	1087.2	1055.3	1023.4	918.6	776.7	618.0	466.9	340.9	248.3
110°	1122.1	1090.2	1036.3	994.6	952.8	842.7	711.4	576.2	452.5	342.4	258.9

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1065.2	1024.9	961.9	920.2	878.4	775.9	663.5	552.7	445.6	347.0	270.3
115°	995.3	949.8	889.8	853.4	816.9	728.1	634.7	539.8	444.1	353.0	282.4
117.5°	925.5	886.0	832.8	801.0	769.1	696.9	618.0	533.0	443.4	359.1	294.6
120°	869.3	835.9	792.6	765.7	738.7	678.0	607.4	527.6	443.4	365.9	307.5
122.5°	827.5	800.2	765.3	742.5	719.7	665.8	598.2	521.6	442.6	372.8	319.6
125°	799.4	777.4	747.1	726.2	705.3	652.9	587.6	514.7	441.9	379.6	331.8
127.5°	780.5	760.7	730.3	710.6	690.9	638.5	575.5	505.6	440.3	384.9	342.4
130°	762.2	743.3	712.1	692.0	671.9	620.3	560.3	497.3	439.6	391.0	352.3
132.5°	742.5	720.5	690.1	670.0	649.9	599.8	544.3	489.7	438.8	396.3	362.1
135°	715.2	693.9	663.5	644.6	625.6	579.3	529.9	482.1	438.1	401.6	370.5
137.5°	685.6	663.5	634.7	617.2	599.8	559.5	516.3	475.3	438.1	404.7	376.6
140°	649.9	633.2	606.6	590.7	574.7	540.5	504.9	469.9	437.3	408.4	382.6
142.5°	617.2	602.0	579.3	566.0	552.7	524.6	494.2	465.4	437.3	411.5	387.2
145°	586.1	573.2	554.2	543.6	533.0	510.2	484.4	460.1	435.8	412.2	390.2
147.5°	559.5	548.1	533.7	525.0	516.3	497.3	476.0	455.5	433.5	413.0	393.3
150°	536.8	526.9	514.7	507.9	501.1	485.9	468.4	450.2	431.2	413.0	395.5
152.5°	516.3	508.7	498.8	493.5	488.2	474.5	460.1	444.1	427.4	411.5	397.1
155°	498.0	492.0	484.4	479.8	475.3	463.9	451.7	438.1	423.6	410.0	397.8
157.5°	481.3	476.8	470.7	466.9	463.1	453.2	442.6	432.0	419.8	408.4	397.8
160°	466.1	461.6	457.0	454.0	451.0	442.6	434.3	425.2	415.3	406.2	397.8
162.5°	451.7	447.2	444.1	441.4	438.8	432.7	425.9	419.1	410.7	403.9	397.8
165°	438.1	435.0	432.0	430.1	428.2	422.9	418.3	412.2	406.2	400.9	396.3
167.5°	425.2	422.9	421.4	420.2	419.1	414.5	410.7	406.2	401.6	397.8	394.8
170°	413.8	413.0	411.5	410.4	409.2	406.2	403.9	400.1	397.1	394.8	393.3
172.5°	403.9	403.1	402.4	401.6	400.9	399.3	397.8	394.8	392.5	391.7	391.7
175°	396.3	394.8	394.8	394.8	394.8	393.3	392.5	391.0	389.5	389.5	390.2
177.5°	390.2	389.5	390.2	389.8	389.5	389.5	388.7	388.0	387.2	387.2	388.7
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	2025.7	2017.7	2013.0	2011.4	1997.1	1989.1	1984.3	1981.1	1976.4	1963.6	1952.5
5°	2102.1	2079.8	2068.7	2055.9	2033.7	2008.2	1987.5	1974.8	1958.9	1933.4	1909.5
7.5°	2173.7	2140.3	2118.0	2100.5	2062.3	2020.9	1987.5	1960.5	1930.2	1895.2	1861.8
10°	2248.5	2194.4	2165.7	2138.7	2083.0	2028.9	1981.1	1941.4	1898.4	1852.2	1815.6
12.5°	2307.4	2235.7	2203.9	2165.7	2097.3	2033.7	1973.2	1919.1	1863.4	1814.1	1761.5
15°	2375.8	2286.7	2250.1	2200.7	2106.9	2024.1	1946.1	1887.3	1830.0	1756.8	1701.1
17.5°	2415.6	2312.1	2259.6	2216.6	2114.8	2014.6	1923.9	1850.7	1783.8	1710.6	1651.7
20°	2455.3	2337.6	2278.7	2218.2	2097.3	1990.7	1895.2	1807.7	1737.7	1658.1	1597.6
22.5°	2468.1	2331.2	2269.2	2213.5	2086.2	1966.8	1857.0	1767.9	1686.8	1607.2	1538.8
25°	2468.1	2329.6	2256.4	2184.8	2051.2	1928.6	1818.8	1721.8	1631.1	1551.5	1483.1
27.5°	2442.6	2297.8	2221.4	2156.2	2017.7	1885.7	1772.7	1666.1	1578.5	1499.0	1421.0
30°	2410.8	2251.7	2175.3	2097.3	1963.6	1837.9	1715.4	1616.7	1524.4	1433.7	1363.7
32.5°	2371.0	2202.3	2118.0	2038.4	1896.8	1766.3	1653.3	1556.3	1468.7	1374.9	1296.9
35°	2313.7	2129.1	2035.2	1965.2	1828.4	1693.1	1584.9	1489.4	1405.1	1308.0	1223.7
37.5°	2240.5	2062.3	1966.8	1880.9	1739.3	1615.1	1513.3	1421.0	1338.3	1249.2	1155.3
40°	2154.6	1968.4	1885.7	1795.0	1645.4	1527.6	1432.1	1349.4	1266.7	1182.3	1091.6
42.5°	2057.5	1872.9	1780.6	1693.1	1549.9	1433.7	1344.6	1269.8	1193.5	1115.5	1018.4
45°	1941.4	1767.9	1678.8	1596.1	1457.6	1338.3	1257.1	1185.5	1120.3	1040.7	954.8
47.5°	1810.9	1659.7	1569.0	1479.9	1344.6	1241.2	1161.6	1101.2	1045.5	965.9	887.9
50°	1683.6	1534.0	1460.8	1370.1	1246.0	1148.9	1067.7	1016.8	973.9	895.9	825.9
52.5°	1522.9	1409.9	1339.9	1261.9	1142.5	1043.9	980.2	935.7	884.8	824.3	762.2
55°	1381.2	1276.2	1220.5	1147.3	1029.6	942.0	887.9	846.6	806.8	752.7	703.3
57.5°	1220.5	1155.3	1099.6	1035.9	919.8	845.0	797.2	762.2	725.6	681.1	641.3
60°	1051.8	1021.6	967.5	916.6	817.9	752.7	712.9	681.1	646.1	609.5	576.0
62.5°	902.3	884.8	852.9	813.1	720.8	665.2	625.4	601.5	576.0	542.6	510.8
65°	760.6	752.7	722.4	693.8	630.1	580.8	545.8	531.5	502.8	477.4	448.7
67.5°	634.9	625.4	607.9	595.1	541.0	494.9	477.4	458.3	434.4	415.3	391.5
70°	507.6	506.0	494.9	479.0	450.3	416.9	399.4	386.7	362.8	348.5	331.0
72.5°	394.6	402.6	393.0	386.7	367.6	343.7	327.8	319.8	300.8	289.6	276.9
75°	294.4	300.8	305.5	294.4	289.6	278.5	264.2	256.2	246.6	230.7	226.0
77.5°	200.5	214.8	214.8	218.0	219.6	213.2	202.1	195.7	184.6	181.4	175.0
80°	132.1	144.8	146.4	149.6	154.4	154.4	146.4	144.8	133.7	132.1	127.3
82.5°	76.4	87.5	93.9	98.7	97.1	103.4	97.1	95.5	89.1	89.1	85.9
85°	41.4	43.0	46.1	49.3	52.5	55.7	55.7	54.1	52.5	50.9	47.7
87.5°	15.9	15.9	17.5	15.9	17.5	20.7	22.3	22.3	20.7	19.1	15.9
90°	10.6	6.1	6.1	6.1	5.3	4.6	2.3	0.8	2.3	4.6	5.3
92.5°	115.4	68.3	58.4	48.6	34.9	23.5	15.2	10.6	15.2	23.5	34.9
95°	160.9	94.9	79.0	63.0	44.8	34.9	27.3	25.1	27.3	34.9	44.8
97.5°	153.4	101.0	87.3	73.6	57.7	48.6	41.8	41.8	41.8	48.6	57.7
100°	155.6	110.8	98.6	86.5	72.1	63.0	57.7	57.7	57.7	63.0	72.1
102.5°	163.2	123.7	112.4	101.0	87.3	79.0	74.4	72.9	74.4	79.0	87.3
105°	176.1	139.7	128.7	117.7	104.0	94.9	91.1	88.8	91.1	94.9	104.0
107.5°	189.8	156.4	145.4	134.4	121.5	111.6	107.8	106.3	107.8	111.6	121.5
110°	205.7	172.3	162.0	151.8	138.2	129.1	125.3	123.7	125.3	129.1	138.2

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	220.9	189.0	178.8	168.5	154.9	146.5	142.0	140.5	142.0	146.5	154.9
115°	236.9	206.5	196.2	186.0	171.6	164.0	158.7	156.4	158.7	164.0	171.6
117.5°	252.1	223.2	212.6	201.9	188.3	179.9	175.4	173.1	175.4	179.9	188.3
120°	268.0	239.1	228.5	217.9	205.0	196.6	191.3	189.8	191.3	196.6	205.0
122.5°	283.2	254.3	244.0	233.8	219.4	211.8	206.5	205.0	206.5	211.8	219.4
125°	296.8	269.5	258.9	248.3	233.8	225.5	220.9	217.9	220.9	225.5	233.8
127.5°	309.8	283.2	272.5	261.9	246.7	237.6	232.3	230.0	232.3	237.6	246.7
130°	322.7	296.8	285.8	274.8	260.4	249.0	242.9	239.9	242.9	249.0	260.4
132.5°	333.3	307.5	297.2	287.0	271.0	260.4	252.1	249.8	252.1	260.4	271.0
135°	343.2	318.1	308.2	298.4	282.4	269.5	261.9	258.9	261.9	269.5	282.4
137.5°	350.7	327.2	317.7	308.2	291.5	279.4	271.0	268.0	271.0	279.4	291.5
140°	358.3	335.6	326.5	317.3	301.4	288.5	280.1	277.9	280.1	288.5	301.4
142.5°	365.2	343.2	334.4	325.7	310.5	298.4	290.8	288.5	290.8	298.4	310.5
145°	369.7	350.0	341.6	333.3	318.9	308.2	300.6	298.4	300.6	308.2	318.9
147.5°	375.0	356.1	348.5	340.9	328.7	317.3	310.5	309.8	310.5	317.3	328.7
150°	378.8	362.1	354.9	347.7	336.3	327.2	321.1	320.4	321.1	327.2	336.3
152.5°	381.9	367.5	361.0	354.5	344.7	336.3	330.3	330.3	330.3	336.3	344.7
155°	384.9	372.0	366.3	360.6	352.3	344.7	340.1	339.4	340.1	344.7	352.3
157.5°	387.2	375.8	371.2	366.7	359.1	353.0	348.5	348.5	348.5	353.0	359.1
160°	388.7	379.6	375.4	371.2	365.2	359.9	356.8	356.8	356.8	359.9	365.2
162.5°	390.2	381.9	378.8	375.8	370.5	365.9	363.7	364.4	363.7	365.9	370.5
165°	390.2	383.4	381.1	378.8	375.0	371.2	369.7	369.7	369.7	371.2	375.0
167.5°	390.2	384.9	383.0	381.1	378.8	375.8	375.0	375.8	375.0	375.8	378.8
170°	389.5	385.7	384.5	383.4	381.9	379.6	378.8	379.6	378.8	379.6	381.9
172.5°	388.7	386.4	385.6	384.9	384.2	382.6	382.6	383.4	382.6	382.6	384.2
175°	388.0	386.4	386.4	386.4	385.7	384.9	384.9	385.7	384.9	384.9	385.7
177.5°	387.2	386.4	386.4	386.4	386.4	385.7	386.4	387.2	386.4	385.7	386.4
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	1942.9	1939.8	1936.6	1923.9	1912.7	1893.6	1877.7	1871.3	1869.8	1871.3	1866.6
5°	1887.3	1885.7	1874.5	1852.2	1831.6	1809.3	1793.4	1777.5	1767.9	1767.9	1756.8
7.5°	1834.7	1823.6	1814.1	1785.4	1761.5	1731.3	1707.4	1693.1	1685.2	1667.7	1667.7
10°	1779.0	1763.1	1750.4	1723.4	1688.3	1658.1	1627.9	1610.4	1596.1	1583.3	1578.5
12.5°	1723.4	1710.6	1686.8	1658.1	1623.1	1584.9	1553.1	1540.4	1506.9	1479.9	1481.5
15°	1670.8	1642.2	1631.1	1589.7	1548.3	1511.7	1465.6	1429.0	1401.9	1384.4	1362.1
17.5°	1612.0	1583.3	1562.6	1527.6	1473.5	1416.2	1371.7	1322.4	1295.3	1265.1	1250.7
20°	1546.7	1522.9	1506.9	1451.2	1386.0	1317.6	1268.2	1238.0	1207.8	1185.5	1172.8
22.5°	1491.0	1460.8	1441.7	1366.9	1295.3	1226.9	1188.7	1163.2	1137.8	1118.7	1112.3
25°	1419.4	1401.9	1355.8	1290.5	1203.0	1156.9	1123.4	1090.0	1075.7	1063.0	1048.7
27.5°	1360.5	1317.6	1285.8	1199.8	1145.7	1093.2	1059.8	1034.3	1016.8	1004.1	993.0
30°	1287.3	1247.6	1203.0	1131.4	1082.1	1032.7	1002.5	981.8	962.7	954.8	945.2
32.5°	1211.0	1174.4	1131.4	1074.1	1013.6	975.5	951.6	929.3	916.6	908.6	897.5
35°	1142.5	1096.4	1067.7	1013.6	964.3	921.3	899.1	880.0	865.7	862.5	860.9
37.5°	1069.3	1034.3	1007.3	951.6	910.2	873.6	852.9	832.2	824.3	822.7	816.3
40°	1005.7	975.5	950.0	897.5	852.9	819.5	803.6	790.9	782.9	782.9	781.3
42.5°	950.0	918.2	892.7	845.0	805.2	775.0	757.4	744.7	741.5	743.1	741.5
45°	887.9	860.9	835.4	786.1	752.7	730.4	711.3	704.9	700.2	701.8	703.3
47.5°	829.1	806.8	781.3	741.5	703.3	679.5	668.3	662.0	662.0	662.0	665.2
50°	776.5	751.1	728.8	687.4	652.4	633.3	623.8	615.8	617.4	619.0	620.6
52.5°	714.5	692.2	676.3	634.9	609.5	585.6	574.5	576.0	574.5	574.5	577.6
55°	660.4	638.1	622.2	584.0	558.5	542.6	533.1	528.3	529.9	526.7	533.1
57.5°	599.9	580.8	569.7	533.1	510.8	496.5	488.5	480.6	483.7	482.2	480.6
60°	547.4	525.1	507.6	482.2	463.1	445.6	440.8	432.8	436.0	432.8	431.2
62.5°	486.9	469.4	456.7	431.2	415.3	401.0	389.9	385.1	383.5	378.7	374.0
65°	426.5	416.9	404.2	378.7	362.8	351.7	345.3	340.5	338.9	326.2	311.9
67.5°	370.8	364.4	351.7	332.6	318.3	307.1	297.6	289.6	280.1	270.5	262.6
70°	318.3	308.7	300.8	283.2	270.5	259.4	249.8	240.3	235.5	226.0	222.8
72.5°	267.3	257.8	249.8	233.9	222.8	211.6	208.5	197.3	192.5	191.0	191.0
75°	214.8	206.9	202.1	187.8	178.2	170.3	165.5	162.3	159.1	155.9	151.2
77.5°	163.9	159.1	155.9	146.4	138.4	133.7	132.1	120.9	117.8	114.6	111.4
80°	119.3	117.8	114.6	106.6	103.4	92.3	92.3	89.1	87.5	87.5	87.5
82.5°	81.2	78.0	76.4	68.4	66.8	65.2	63.7	62.1	63.7	62.1	63.7
85°	43.0	41.4	39.8	39.8	39.8	39.8	39.8	39.8	39.8	38.2	39.8
87.5°	15.9	15.9	15.9	15.9	14.3	15.9	15.9	14.3	15.9	15.9	15.9
90°	6.1	6.1	6.1	10.6	10.6	12.1	13.7	12.9	13.7	14.4	15.2
92.5°	48.6	58.4	68.3	115.4	189.0	260.4	297.6	247.5	183.0	136.7	107.8
95°	63.0	79.0	94.9	160.9	285.5	466.9	618.7	636.2	562.6	444.9	343.2
97.5°	73.6	87.3	101.0	153.4	260.4	447.2	662.0	797.9	810.1	751.6	668.1
100°	86.5	98.6	110.8	155.6	241.4	396.3	610.4	804.7	915.6	930.8	893.6
102.5°	101.0	112.4	123.7	163.2	236.1	362.1	545.9	747.8	910.3	1000.6	1023.4
105°	117.7	128.7	139.7	176.1	239.1	345.4	498.0	676.4	850.3	981.6	1056.8
107.5°	134.4	145.4	156.4	189.8	248.3	340.9	466.9	618.0	776.7	918.6	1023.4
110°	151.8	162.0	172.3	205.7	258.9	342.4	452.5	576.2	711.4	842.7	952.8

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.5	178.8	189.0	220.9	270.3	347.0	445.6	552.7	663.5	775.9	878.4
115°	186.0	196.2	206.5	236.9	282.4	353.0	444.1	539.8	634.7	728.1	816.9
117.5°	201.9	212.6	223.2	252.1	294.6	359.1	443.4	533.0	618.0	696.9	769.1
120°	217.9	228.5	239.1	268.0	307.5	365.9	443.4	527.6	607.4	678.0	738.7
122.5°	233.8	244.0	254.3	283.2	319.6	372.8	442.6	521.6	598.2	665.8	719.7
125°	248.3	258.9	269.5	296.8	331.8	379.6	441.9	514.7	587.6	652.9	705.3
127.5°	261.9	272.5	283.2	309.8	342.4	384.9	440.3	505.6	575.5	638.5	690.9
130°	274.8	285.8	296.8	322.7	352.3	391.0	439.6	497.3	560.3	620.3	671.9
132.5°	287.0	297.2	307.5	333.3	362.1	396.3	438.8	489.7	544.3	599.8	649.9
135°	298.4	308.2	318.1	343.2	370.5	401.6	438.1	482.1	529.9	579.3	625.6
137.5°	308.2	317.7	327.2	350.7	376.6	404.7	438.1	475.3	516.3	559.5	599.8
140°	317.3	326.5	335.6	358.3	382.6	408.4	437.3	469.9	504.9	540.5	574.7
142.5°	325.7	334.4	343.2	365.2	387.2	411.5	437.3	465.4	494.2	524.6	552.7
145°	333.3	341.6	350.0	369.7	390.2	412.2	435.8	460.1	484.4	510.2	533.0
147.5°	340.9	348.5	356.1	375.0	393.3	413.0	433.5	455.5	476.0	497.3	516.3
150°	347.7	354.9	362.1	378.8	395.5	413.0	431.2	450.2	468.4	485.9	501.1
152.5°	354.5	361.0	367.5	381.9	397.1	411.5	427.4	444.1	460.1	474.5	488.2
155°	360.6	366.3	372.0	384.9	397.8	410.0	423.6	438.1	451.7	463.9	475.3
157.5°	366.7	371.2	375.8	387.2	397.8	408.4	419.8	432.0	442.6	453.2	463.1
160°	371.2	375.4	379.6	388.7	397.8	406.2	415.3	425.2	434.3	442.6	451.0
162.5°	375.8	378.8	381.9	390.2	397.8	403.9	410.7	419.1	425.9	432.7	438.8
165°	378.8	381.1	383.4	390.2	396.3	400.9	406.2	412.2	418.3	422.9	428.2
167.5°	381.1	383.0	384.9	390.2	394.8	397.8	401.6	406.2	410.7	414.5	419.1
170°	383.4	384.5	385.7	389.5	393.3	394.8	397.1	400.1	403.9	406.2	409.2
172.5°	384.9	385.6	386.4	388.7	391.7	391.7	392.5	394.8	397.8	399.3	400.9
175°	386.4	386.4	386.4	388.0	390.2	389.5	389.5	391.0	392.5	393.3	394.8
177.5°	386.4	386.4	386.4	387.2	388.7	387.2	387.2	388.0	388.7	389.5	389.5
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	1866.6	1872.9	1865.0	1869.8	1858.6	1857.0	1858.6	1858.6	1860.2	1861.8	1863.4
5°	1761.5	1760.0	1750.4	1744.0	1739.3	1744.0	1747.2	1750.4	1747.2	1750.4	1752.0
7.5°	1662.9	1658.1	1653.3	1642.2	1645.4	1642.2	1651.7	1647.0	1647.0	1654.9	1661.3
10°	1575.4	1565.8	1562.6	1549.9	1540.4	1538.8	1549.9	1554.7	1559.5	1562.6	1575.4
12.5°	1462.4	1448.1	1436.9	1441.7	1414.6	1425.8	1429.0	1422.6	1441.7	1464.0	1451.2
15°	1341.4	1343.0	1320.8	1312.8	1290.5	1296.9	1298.5	1314.4	1330.3	1328.7	1347.8
17.5°	1252.3	1242.8	1223.7	1222.1	1212.6	1217.3	1215.7	1228.5	1223.7	1231.6	1247.6
20°	1169.6	1163.2	1147.3	1140.9	1144.1	1140.9	1142.5	1144.1	1148.9	1166.4	1163.2
22.5°	1104.3	1096.4	1096.4	1088.4	1078.9	1075.7	1083.7	1088.4	1094.8	1098.0	1105.9
25°	1047.1	1040.7	1032.7	1028.0	1020.0	1021.6	1026.4	1032.7	1037.5	1043.9	1050.2
27.5°	988.2	988.2	980.2	978.6	975.5	973.9	980.2	983.4	983.4	988.2	994.5
30°	942.0	942.0	934.1	932.5	930.9	930.9	935.7	937.3	938.9	943.6	946.8
32.5°	897.5	895.9	892.7	894.3	892.7	894.3	894.3	895.9	899.1	900.7	907.0
35°	856.1	857.7	854.5	854.5	852.9	854.5	857.7	859.3	860.9	864.1	864.1
37.5°	816.3	819.5	817.9	822.7	822.7	822.7	822.7	825.9	825.9	825.9	824.3
40°	781.3	781.3	779.7	782.9	786.1	786.1	787.7	787.7	789.3	789.3	787.7
42.5°	741.5	744.7	749.5	751.1	754.3	752.7	757.4	755.9	757.4	754.3	751.1
45°	704.9	704.9	711.3	717.7	719.3	719.3	719.3	722.4	719.3	714.5	712.9
47.5°	665.2	668.3	671.5	679.5	681.1	681.1	681.1	681.1	677.9	677.9	677.9
50°	625.4	627.0	628.6	631.7	636.5	634.9	634.9	634.9	641.3	634.9	636.5
52.5°	577.6	579.2	580.8	587.2	585.6	585.6	587.2	587.2	592.0	590.4	587.2
55°	529.9	529.9	533.1	533.1	533.1	536.3	537.9	541.0	539.4	541.0	542.6
57.5°	482.2	479.0	477.4	477.4	482.2	480.6	482.2	482.2	488.5	491.7	493.3
60°	426.5	426.5	424.9	415.3	415.3	413.7	418.5	421.7	424.9	439.2	437.6
62.5°	369.2	362.8	356.4	358.0	348.5	353.3	350.1	353.3	362.8	374.0	375.5
65°	311.9	307.1	300.8	299.2	296.0	300.8	299.2	300.8	305.5	311.9	319.8
67.5°	261.0	259.4	256.2	254.6	254.6	254.6	257.8	257.8	259.4	264.2	268.9
70°	222.8	221.2	222.8	219.6	221.2	219.6	221.2	222.8	224.4	226.0	230.7
72.5°	187.8	187.8	187.8	184.6	187.8	186.2	186.2	187.8	189.4	191.0	194.1
75°	149.6	146.4	143.2	140.0	138.4	141.6	143.2	141.6	146.4	152.8	152.8
77.5°	113.0	111.4	111.4	111.4	113.0	111.4	114.6	113.0	114.6	114.6	117.8
80°	87.5	85.9	87.5	87.5	85.9	89.1	87.5	87.5	89.1	90.7	89.1
82.5°	63.7	65.2	63.7	63.7	63.7	66.8	63.7	63.7	63.7	65.2	65.2
85°	39.8	39.8	39.8	39.8	41.4	39.8	41.4	39.8	43.0	41.4	41.4
87.5°	14.3	15.9	17.5	17.5	17.5	17.5	15.9	17.5	19.1	17.5	19.1
90°	15.2	15.2	15.9	16.7	15.9	15.9	15.9	16.7	15.9	15.2	15.2
92.5°	98.3	88.8	77.4	72.1	69.1	69.1	69.1	72.1	77.4	88.8	98.3
95°	306.4	269.5	232.3	208.8	195.1	185.2	195.1	208.8	232.3	269.5	306.4
97.5°	625.6	583.1	531.4	485.9	463.1	444.9	463.1	485.9	531.4	583.1	625.6
100°	865.5	837.4	771.3	725.0	702.3	696.2	702.3	725.0	771.3	837.4	865.5
102.5°	1015.8	1008.2	974.1	943.7	919.4	914.8	919.4	943.7	974.1	1008.2	1015.8
105°	1072.4	1087.9	1089.4	1083.4	1072.7	1068.2	1072.7	1083.4	1089.4	1087.9	1072.4
107.5°	1055.3	1087.2	1120.6	1134.2	1140.3	1141.1	1140.3	1134.2	1120.6	1087.2	1055.3
110°	994.6	1036.3	1090.2	1122.1	1135.8	1142.6	1135.8	1122.1	1090.2	1036.3	994.6

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	920.2	961.9	1024.9	1065.2	1085.7	1097.8	1085.7	1065.2	1024.9	961.9	920.2
115°	853.4	889.8	949.8	995.3	1019.6	1025.7	1019.6	995.3	949.8	889.8	853.4
117.5°	801.0	832.8	886.0	925.5	951.3	955.1	951.3	925.5	886.0	832.8	801.0
120°	765.7	792.6	835.9	869.3	889.0	897.4	889.0	869.3	835.9	792.6	765.7
122.5°	742.5	765.3	800.2	827.5	843.5	851.8	843.5	827.5	800.2	765.3	742.5
125°	726.2	747.1	777.4	799.4	813.9	818.4	813.9	799.4	777.4	747.1	726.2
127.5°	710.6	730.3	760.7	780.5	792.6	797.2	792.6	780.5	760.7	730.3	710.6
130°	692.0	712.1	743.3	762.2	774.4	778.9	774.4	762.2	743.3	712.1	692.0
132.5°	670.0	690.1	720.5	742.5	753.9	758.4	753.9	742.5	720.5	690.1	670.0
135°	644.6	663.5	693.9	715.2	727.3	731.9	727.3	715.2	693.9	663.5	644.6
137.5°	617.2	634.7	663.5	685.6	695.4	700.7	695.4	685.6	663.5	634.7	617.2
140°	590.7	606.6	633.2	649.9	660.5	666.6	660.5	649.9	633.2	606.6	590.7
142.5°	566.0	579.3	602.0	617.2	626.3	630.1	626.3	617.2	602.0	579.3	566.0
145°	543.6	554.2	573.2	586.1	593.7	597.5	593.7	586.1	573.2	554.2	543.6
147.5°	525.0	533.7	548.1	559.5	565.6	567.1	565.6	559.5	548.1	533.7	525.0
150°	507.9	514.7	526.9	536.8	541.3	542.1	541.3	536.8	526.9	514.7	507.9
152.5°	493.5	498.8	508.7	516.3	518.5	519.3	518.5	516.3	508.7	498.8	493.5
155°	479.8	484.4	492.0	498.0	500.3	500.3	500.3	498.0	492.0	484.4	479.8
157.5°	466.9	470.7	476.8	481.3	482.8	482.8	482.8	481.3	476.8	470.7	466.9
160°	454.0	457.0	461.6	466.1	466.9	466.9	466.9	466.1	461.6	457.0	454.0
162.5°	441.4	444.1	447.2	451.7	452.5	451.7	452.5	451.7	447.2	444.1	441.4
165°	430.1	432.0	435.0	438.1	437.3	436.5	437.3	438.1	435.0	432.0	430.1
167.5°	420.2	421.4	422.9	425.2	425.2	424.4	425.2	425.2	422.9	421.4	420.2
170°	410.4	411.5	413.0	413.8	413.0	413.0	413.0	413.8	413.0	411.5	410.4
172.5°	401.6	402.4	403.1	403.9	403.1	401.6	403.1	403.9	403.1	402.4	401.6
175°	394.8	394.8	394.8	396.3	394.8	393.3	394.8	396.3	394.8	394.8	394.8
177.5°	389.8	390.2	389.5	390.2	388.7	387.2	388.7	390.2	389.5	390.2	389.8
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8	1974.8
2.5°	1869.8	1877.7	1874.5	1863.4	1868.2	1877.7	1887.3	1900.0	1907.9	1914.3	1917.5
5°	1760.0	1774.3	1771.1	1771.1	1777.5	1793.4	1809.3	1836.3	1845.9	1857.0	1872.9
7.5°	1662.9	1674.0	1683.6	1686.8	1696.3	1717.0	1737.7	1767.9	1791.8	1804.5	1814.1
10°	1577.0	1584.9	1599.2	1607.2	1616.7	1642.2	1672.4	1704.3	1728.1	1750.4	1763.1
12.5°	1467.2	1499.0	1518.1	1530.8	1543.5	1581.7	1605.6	1640.6	1669.2	1689.9	1709.0
15°	1344.6	1382.8	1394.0	1443.3	1475.1	1505.3	1541.9	1583.3	1610.4	1634.2	1659.7
17.5°	1241.2	1268.2	1281.0	1333.5	1360.5	1408.3	1460.8	1513.3	1554.7	1572.2	1597.6
20°	1176.0	1190.3	1215.7	1233.2	1261.9	1317.6	1374.9	1438.5	1500.6	1518.1	1543.5
22.5°	1109.1	1128.2	1145.7	1169.6	1191.9	1230.1	1287.3	1357.4	1424.2	1456.0	1486.3
25°	1048.7	1067.7	1078.9	1104.3	1125.0	1163.2	1203.0	1274.6	1354.2	1381.2	1429.0
27.5°	1000.9	1012.1	1031.1	1042.3	1066.2	1101.2	1137.8	1191.9	1269.8	1316.0	1362.1
30°	953.2	961.1	977.0	993.0	1010.5	1034.3	1075.7	1128.2	1199.8	1239.6	1285.8
32.5°	905.4	918.2	927.7	938.9	957.9	986.6	1015.2	1066.2	1123.4	1168.0	1214.1
35°	865.7	870.4	883.2	895.9	908.6	934.1	964.3	1013.6	1064.6	1099.6	1140.9
37.5°	822.7	830.6	840.2	845.0	865.7	881.6	913.4	951.6	1012.1	1034.3	1075.7
40°	789.3	787.7	797.2	805.2	814.7	840.2	859.3	900.7	948.4	983.4	1008.9
42.5°	747.9	747.9	751.1	760.6	773.4	789.3	811.6	846.6	895.9	921.3	951.6
45°	714.5	709.7	711.3	717.7	725.6	741.5	763.8	794.0	843.4	864.1	895.9
47.5°	674.7	669.9	669.9	676.3	682.7	693.8	711.3	746.3	786.1	813.1	837.0
50°	630.1	631.7	630.1	634.9	638.1	649.2	668.3	697.0	733.6	755.9	782.9
52.5°	588.8	585.6	584.0	587.2	593.5	601.5	622.2	647.6	682.7	704.9	728.8
55°	537.9	541.0	541.0	541.0	550.6	553.8	569.7	595.1	630.1	647.6	669.9
57.5°	491.7	490.1	493.3	491.7	499.7	510.8	523.5	542.6	577.6	595.1	615.8
60°	440.8	442.4	444.0	444.0	450.3	461.5	475.8	493.3	521.9	539.4	558.5
62.5°	378.7	386.7	394.6	397.8	407.4	415.3	424.9	444.0	469.4	482.2	499.7
65°	319.8	331.0	342.1	350.1	356.4	364.4	377.1	394.6	415.3	428.1	445.6
67.5°	268.9	276.9	291.2	299.2	311.9	321.4	329.4	343.7	369.2	374.0	388.3
70°	232.3	235.5	241.9	248.2	262.6	270.5	280.1	294.4	313.5	324.6	332.6
72.5°	195.7	197.3	200.5	206.9	213.2	222.8	233.9	246.6	264.2	268.9	280.1
75°	155.9	165.5	165.5	170.3	175.0	179.8	189.4	202.1	213.2	221.2	227.6
77.5°	116.2	120.9	124.1	132.1	138.4	143.2	149.6	159.1	165.5	171.9	176.6
80°	90.7	92.3	93.9	93.9	97.1	103.4	109.8	116.2	124.1	127.3	132.1
82.5°	66.8	66.8	66.8	70.0	71.6	73.2	73.2	76.4	84.3	87.5	92.3
85°	43.0	43.0	43.0	43.0	44.6	46.1	47.7	49.3	49.3	49.3	52.5
87.5°	17.5	20.7	19.1	20.7	20.7	20.7	20.7	22.3	22.3	23.9	23.9
90°	15.2	14.4	13.7	12.9	13.7	12.1	10.6	10.6	6.1	6.1	6.1
92.5°	107.8	136.7	183.0	247.5	297.6	260.4	189.0	115.4	68.3	58.4	48.6
95°	343.2	444.9	562.6	636.2	618.7	466.9	285.5	160.9	94.9	79.0	63.0
97.5°	668.1	751.6	810.1	797.9	662.0	447.2	260.4	153.4	101.0	87.3	73.6
100°	893.6	930.8	915.6	804.7	610.4	396.3	241.4	155.6	110.8	98.6	86.5
102.5°	1023.4	1000.6	910.3	747.8	545.9	362.1	236.1	163.2	123.7	112.4	101.0
105°	1056.8	981.6	850.3	676.4	498.0	345.4	239.1	176.1	139.7	128.7	117.7
107.5°	1023.4	918.6	776.7	618.0	466.9	340.9	248.3	189.8	156.4	145.4	134.4
110°	952.8	842.7	711.4	576.2	452.5	342.4	258.9	205.7	172.3	162.0	151.8

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	878.4	775.9	663.5	552.7	445.6	347.0	270.3	220.9	189.0	178.8	168.5
115°	816.9	728.1	634.7	539.8	444.1	353.0	282.4	236.9	206.5	196.2	186.0
117.5°	769.1	696.9	618.0	533.0	443.4	359.1	294.6	252.1	223.2	212.6	201.9
120°	738.7	678.0	607.4	527.6	443.4	365.9	307.5	268.0	239.1	228.5	217.9
122.5°	719.7	665.8	598.2	521.6	442.6	372.8	319.6	283.2	254.3	244.0	233.8
125°	705.3	652.9	587.6	514.7	441.9	379.6	331.8	296.8	269.5	258.9	248.3
127.5°	690.9	638.5	575.5	505.6	440.3	384.9	342.4	309.8	283.2	272.5	261.9
130°	671.9	620.3	560.3	497.3	439.6	391.0	352.3	322.7	296.8	285.8	274.8
132.5°	649.9	599.8	544.3	489.7	438.8	396.3	362.1	333.3	307.5	297.2	287.0
135°	625.6	579.3	529.9	482.1	438.1	401.6	370.5	343.2	318.1	308.2	298.4
137.5°	599.8	559.5	516.3	475.3	438.1	404.7	376.6	350.7	327.2	317.7	308.2
140°	574.7	540.5	504.9	469.9	437.3	408.4	382.6	358.3	335.6	326.5	317.3
142.5°	552.7	524.6	494.2	465.4	437.3	411.5	387.2	365.2	343.2	334.4	325.7
145°	533.0	510.2	484.4	460.1	435.8	412.2	390.2	369.7	350.0	341.6	333.3
147.5°	516.3	497.3	476.0	455.5	433.5	413.0	393.3	375.0	356.1	348.5	340.9
150°	501.1	485.9	468.4	450.2	431.2	413.0	395.5	378.8	362.1	354.9	347.7
152.5°	488.2	474.5	460.1	444.1	427.4	411.5	397.1	381.9	367.5	361.0	354.5
155°	475.3	463.9	451.7	438.1	423.6	410.0	397.8	384.9	372.0	366.3	360.6
157.5°	463.1	453.2	442.6	432.0	419.8	408.4	397.8	387.2	375.8	371.2	366.7
160°	451.0	442.6	434.3	425.2	415.3	406.2	397.8	388.7	379.6	375.4	371.2
162.5°	438.8	432.7	425.9	419.1	410.7	403.9	397.8	390.2	381.9	378.8	375.8
165°	428.2	422.9	418.3	412.2	406.2	400.9	396.3	390.2	383.4	381.1	378.8
167.5°	419.1	414.5	410.7	406.2	401.6	397.8	394.8	390.2	384.9	383.0	381.1
170°	409.2	406.2	403.9	400.1	397.1	394.8	393.3	389.5	385.7	384.5	383.4
172.5°	400.9	399.3	397.8	394.8	392.5	391.7	391.7	388.7	386.4	385.6	384.9
175°	394.8	393.3	392.5	391.0	389.5	389.5	390.2	388.0	386.4	386.4	386.4
177.5°	389.5	389.5	388.7	388.0	387.2	387.2	388.7	387.2	386.4	386.4	386.4
180°	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4	386.4

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1974.8	1974.8	1974.8	1974.8
2.5°	1930.2	1939.8	1955.7	1978.0
5°	1885.7	1912.7	1938.2	1971.6
7.5°	1845.9	1877.7	1912.7	1960.5
10°	1799.7	1839.5	1884.1	1942.9
12.5°	1745.6	1801.3	1852.2	1915.9
15°	1705.8	1747.2	1812.5	1887.3
17.5°	1650.2	1705.8	1771.1	1855.4
20°	1597.6	1656.5	1729.7	1817.2
22.5°	1541.9	1608.8	1682.0	1775.9
25°	1484.7	1556.3	1629.5	1729.7
27.5°	1432.1	1497.4	1580.1	1682.0
30°	1368.5	1443.3	1522.9	1629.5
32.5°	1306.4	1384.4	1465.6	1572.2
35°	1239.6	1317.6	1406.7	1508.5
37.5°	1174.4	1260.3	1341.4	1440.1
40°	1102.8	1191.9	1276.2	1376.5
42.5°	1032.7	1125.0	1209.4	1295.3
45°	967.5	1058.2	1134.6	1215.7
47.5°	905.4	986.6	1064.6	1137.8
50°	845.0	913.4	985.0	1045.5
52.5°	781.3	846.6	903.8	957.9
55°	724.0	775.0	825.9	875.2
57.5°	655.6	706.5	751.1	789.3
60°	598.3	630.1	673.1	712.9
62.5°	533.1	569.7	603.1	628.6
65°	469.4	501.3	526.7	549.0
67.5°	415.3	434.4	453.5	477.4
70°	350.1	366.0	388.3	405.8
72.5°	294.4	307.1	318.3	338.9
75°	238.7	249.8	256.2	275.3
77.5°	184.6	195.7	200.5	211.6
80°	141.6	143.2	149.6	159.1
82.5°	97.1	100.3	101.8	109.8
85°	55.7	63.7	62.1	65.2
87.5°	23.9	25.5	28.6	31.8
90°	5.3	4.6	2.3	0.8
92.5°	34.9	23.5	15.2	10.6
95°	44.8	34.9	27.3	25.1
97.5°	57.7	48.6	41.8	41.8
100°	72.1	63.0	57.7	57.7
102.5°	87.3	79.0	74.4	72.9
105°	104.0	94.9	91.1	88.8
107.5°	121.5	111.6	107.8	106.3
110°	138.2	129.1	125.3	123.7

TEST NUMBER: P1026219

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	154.9	146.5	142.0	140.5
115°	171.6	164.0	158.7	156.4
117.5°	188.3	179.9	175.4	173.1
120°	205.0	196.6	191.3	189.8
122.5°	219.4	211.8	206.5	205.0
125°	233.8	225.5	220.9	217.9
127.5°	246.7	237.6	232.3	230.0
130°	260.4	249.0	242.9	239.9
132.5°	271.0	260.4	252.1	249.8
135°	282.4	269.5	261.9	258.9
137.5°	291.5	279.4	271.0	268.0
140°	301.4	288.5	280.1	277.9
142.5°	310.5	298.4	290.8	288.5
145°	318.9	308.2	300.6	298.4
147.5°	328.7	317.3	310.5	309.8
150°	336.3	327.2	321.1	320.4
152.5°	344.7	336.3	330.3	330.3
155°	352.3	344.7	340.1	339.4
157.5°	359.1	353.0	348.5	348.5
160°	365.2	359.9	356.8	356.8
162.5°	370.5	365.9	363.7	364.4
165°	375.0	371.2	369.7	369.7
167.5°	378.8	375.8	375.0	375.8
170°	381.9	379.6	378.8	379.6
172.5°	384.2	382.6	382.6	383.4
175°	385.7	384.9	384.9	385.7
177.5°	386.4	385.7	386.4	387.2
180°	386.4	386.4	386.4	386.4

(END OF REPORT)