

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026221

Luminaire Tested: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026221
REPORT IS A COMBINATION OF REPORTS P999211 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7528.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026221

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026221

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37
5	71	60	52	45	67	56	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16947	16947	16947
5°	16949	16444	16445
10°	16805	15925	15736
15°	16574	15279	14898
20°	16271	14542	13943
25°	15893	13747	13009
30°	15524	12937	11962
35°	15117	12115	10938
40°	14633	11230	9886
45°	14180	10353	8844
50°	13663	9394	7786
55°	13106	8412	6695
60°	12487	7368	5616
65°	11891	6172	4579
70°	11041	4913	3498
75°	9951	3573	2447
80°	8312	2194	1758
85°	6251	1263	966

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14180 cd/sqm

TEST NUMBER: P1026221

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	2.6
10°-20°	544.9	7.2
20°-30°	786.7	10.4
30°-40°	891.6	11.8
40°-50°	860.8	11.4
50°-60°	715.7	9.5
60°-70°	494.0	6.6
70°-80°	249.6	3.3
80°-90°	65.5	0.9
90°-100°	64.0	0.9
100°-110°	191.7	2.5
110°-120°	325.6	4.3
120°-130°	429.4	5.7
130°-140°	482.3	6.4
140°-150°	474.0	6.3
150°-160°	398.7	5.3
160°-170°	265.3	3.5
170°-180°	92.9	1.2
0°-30°	1527.0	20.3
0°-40°	2418.5	32.1
0°-60°	3995.0	53.1
0°-90°	4804.1	63.8
90°-120°	581.3	7.7
90°-150°	1967.0	26.1
90°-180°	2724.0	36.2
0°-180°	7528.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2069	2050	2066	2062	197
15°	1976	1962	1922	1919	1908	557
25°	1787	1758	1693	1666	1650	823
35°	1545	1494	1415	1361	1332	966
45°	1260	1201	1106	1028	999	972
55°	955	891	788	705	675	854
65°	649	581	479	411	392	641
75°	345	286	212	175	166	364
85°	86	54	49	46	46	94
90°	2	11	17	21	23	8
95°	46	52	58	60	60	49
105°	177	178	181	183	185	188
115°	331	331	330	329	328	326
125°	482	482	481	480	478	430
135°	622	626	626	625	623	481
145°	756	758	759	758	756	473
155°	866	866	865	868	865	398
165°	942	940	938	943	940	266
175°	980	976	976	981	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1026221

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2078.2	2078.2	2078.2	2078.2	2078.2
2.5°	2084.6	2078.2	2060.7	2078.2	2076.7
5°	2075.1	2068.7	2049.6	2065.5	2062.3
7.5°	2060.7	2054.4	2030.5	2041.6	2036.9
10°	2038.5	2030.5	2001.9	2008.2	2001.9
12.5°	2009.8	2000.3	1965.3	1968.4	1958.9
15°	1976.4	1962.1	1922.3	1919.1	1908.0
17.5°	1938.2	1917.5	1871.4	1863.4	1847.5
20°	1892.1	1871.4	1817.3	1804.5	1783.9
22.5°	1841.1	1817.3	1758.4	1737.7	1721.8
25°	1787.0	1758.4	1693.1	1666.1	1650.2
27.5°	1731.3	1696.3	1627.9	1596.1	1573.8
30°	1672.5	1632.7	1557.9	1518.1	1492.6
32.5°	1610.4	1564.3	1486.3	1438.5	1414.7
35°	1545.2	1494.2	1414.7	1360.6	1331.9
37.5°	1476.7	1424.2	1336.7	1277.8	1249.2
40°	1403.5	1351.0	1260.3	1193.5	1164.8
42.5°	1333.5	1277.8	1182.3	1113.9	1083.7
45°	1260.3	1201.4	1106.0	1028.0	999.3
47.5°	1185.5	1125.1	1026.4	945.2	913.4
50°	1109.1	1047.1	945.2	865.7	835.4
52.5°	1031.2	970.7	865.7	784.5	752.7
55°	954.8	891.1	787.7	704.9	674.7
57.5°	880.0	813.2	711.3	627.0	604.7
60°	798.8	735.2	633.3	550.6	525.1
62.5°	725.6	658.8	553.8	479.0	459.9
65°	649.3	580.8	479.0	410.6	391.5
67.5°	569.7	504.4	409.0	348.5	326.2
70°	494.9	428.1	337.4	284.8	268.9
72.5°	415.3	356.5	272.1	229.1	214.8
75°	345.3	286.4	211.6	175.0	165.5
77.5°	272.1	221.2	157.5	132.1	128.9
80°	202.1	155.9	108.2	103.4	101.8
82.5°	141.6	100.3	78.0	74.8	73.2
85°	85.9	54.1	49.3	46.1	46.1
87.5°	36.6	23.9	22.3	20.7	22.3
90°	2.3	10.6	16.7	21.3	22.8
92.5°	19.7	29.6	33.4	35.7	36.4
95°	45.6	52.4	57.7	60.0	60.0
97.5°	72.9	79.0	85.0	88.1	88.1
100°	106.3	109.3	116.2	117.7	117.7
102.5°	141.2	142.0	148.1	150.3	151.1
105°	176.9	177.7	180.7	183.0	185.3
107.5°	214.1	214.9	215.6	218.7	217.9
110°	252.1	253.6	252.8	251.3	253.6



TEST NUMBER: P1026221

CATALOG NUMBER: S124RDIP-B1195D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.6	291.6	290.0	290.0	290.0
115°	331.0	331.0	329.5	328.8	328.0
117.5°	368.2	368.2	367.5	365.2	362.9
120°	405.4	408.5	406.2	402.4	403.9
122.5°	444.2	444.9	444.2	441.9	438.1
125°	482.1	482.1	481.4	479.8	478.3
127.5°	516.3	518.6	517.1	515.5	514.8
130°	552.7	555.0	555.0	553.5	550.5
132.5°	589.9	591.5	590.7	589.2	588.4
135°	621.8	626.4	626.4	624.9	622.6
137.5°	657.5	659.8	661.3	659.0	659.8
140°	693.2	694.7	694.7	694.0	693.2
142.5°	725.8	727.4	726.6	726.6	726.6
145°	755.5	758.5	759.3	758.5	756.2
147.5°	785.8	789.6	788.9	788.1	787.3
150°	813.2	816.2	816.2	816.2	815.4
152.5°	839.0	840.5	841.3	843.5	841.3
155°	865.6	865.6	864.8	867.8	864.8
157.5°	888.3	886.8	886.8	889.1	886.8
160°	908.1	907.3	906.5	908.8	905.0
162.5°	926.3	924.0	923.3	927.8	924.0
165°	942.2	940.0	938.4	943.0	940.0
167.5°	955.1	952.1	952.1	956.7	952.1
170°	965.8	962.0	962.7	967.3	962.0
172.5°	973.4	970.3	970.3	975.6	970.3
175°	980.2	976.4	975.6	981.0	975.6
177.5°	983.2	979.4	979.4	984.8	978.7
180°	981.7	981.7	981.7	981.7	981.7

(END OF REPORT)