

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007692

Luminaire Tested: S124IP-B365UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB2750-4F0-XX-W2A_2700K
Description: Define 4 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1459.0 lumens
Efficiency: N/A
Efficacy: 156.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007692

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007692

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007692

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	15.7	1.1
100°-110°	103.0	7.1
110°-120°	196.7	13.5
120°-130°	249.7	17.1
130°-140°	267.1	18.3
140°-150°	249.8	17.1
150°-160°	201.4	13.8
160°-170°	129.9	8.9
170°-180°	44.8	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	315.4	21.6
90°-150°	1081.9	74.2
90°-180°	1458.0	99.9
0°-180°	1459.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	11	1
95°	19	7	8	10	10	24
105°	106	108	110	113	100	111
115°	198	199	199	200	200	195
125°	278	280	279	280	280	249
135°	345	345	346	347	348	266
145°	398	399	399	400	400	249
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1007692

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	4.9	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.2
97.5°	37.0	44.8	7.8	9.5	9.9
100°	57.8	64.1	15.5	9.5	9.9
102.5°	81.1	85.3	89.5	10.2	10.2
105°	106.1	108.2	110.0	113.1	100.4
107.5°	129.0	130.0	132.5	134.3	135.7
110°	152.2	153.3	155.4	156.1	157.2

TEST NUMBER: P1007692

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	176.9	177.6	177.3	178.7
115°	198.1	199.1	198.8	199.5	199.5
117.5°	218.9	220.3	221.3	221.0	221.0
120°	240.0	241.4	241.1	241.8	241.1
122.5°	259.7	260.4	261.1	261.5	260.8
125°	278.4	279.8	279.1	280.2	280.5
127.5°	296.4	296.7	298.5	298.1	297.8
130°	313.7	314.0	315.1	315.4	315.4
132.5°	329.5	330.2	331.6	332.0	331.6
135°	345.4	345.0	346.4	347.1	347.8
137.5°	359.5	359.5	361.2	361.9	361.6
140°	373.2	373.9	374.6	375.7	376.0
142.5°	385.6	387.0	387.3	388.0	388.0
145°	398.2	399.3	399.3	399.6	400.4
147.5°	408.1	410.2	409.9	410.2	410.6
150°	419.0	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)