

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007712

Luminaire Tested: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B590UB2750-4F0-XX-W2A-1_2700K
Description: Define 4 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2034.0 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007712

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007712

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007712

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.6	0.1
90°-100°	47.7	2.3
100°-110°	143.0	7.0
110°-120°	242.9	11.9
120°-130°	320.4	15.8
130°-140°	359.9	17.7
140°-150°	353.7	17.4
150°-160°	297.5	14.6
160°-170°	197.9	9.7
170°-180°	69.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.6	0.1
90°-120°	433.7	21.3
90°-150°	1467.7	72.2
90°-180°	2032.0	99.9
0°-180°	2034.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	8	12	16	17	2
95°	34	39	43	45	45	37
105°	132	133	135	136	138	140
115°	247	247	246	245	245	244
125°	360	360	359	358	357	321
135°	464	467	467	466	464	359
145°	564	566	566	566	564	353
155°	646	646	645	648	645	297
165°	703	701	700	704	701	198
175°	731	728	728	732	728	69
180°	732	732	732	732	732	

TEST NUMBER: P1007712

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.7	7.9	12.5	15.9	17.0
92.5°	14.7	22.1	24.9	26.6	27.2
95°	34.0	39.1	43.1	44.8	44.8
97.5°	54.4	58.9	63.4	65.7	65.7
100°	79.3	81.6	86.7	87.8	87.8
102.5°	105.4	105.9	110.5	112.2	112.7
105°	132.0	132.6	134.8	136.5	138.2
107.5°	159.8	160.3	160.9	163.2	162.6
110°	188.1	189.2	188.6	187.5	189.2

TEST NUMBER: P1007712

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	217.5	217.5	216.4	216.4	216.4
115°	247.0	247.0	245.9	245.3	244.7
117.5°	274.8	274.8	274.2	272.5	270.8
120°	302.5	304.8	303.1	300.3	301.4
122.5°	331.4	332.0	331.4	329.7	326.9
125°	359.7	359.7	359.2	358.0	356.9
127.5°	385.2	386.9	385.8	384.7	384.1
130°	412.4	414.1	414.1	413.0	410.7
132.5°	440.2	441.3	440.7	439.6	439.1
135°	464.0	467.4	467.4	466.2	464.5
137.5°	490.6	492.3	493.4	491.7	492.3
140°	517.2	518.4	518.4	517.8	517.2
142.5°	541.6	542.7	542.2	542.2	542.2
145°	563.7	565.9	566.5	565.9	564.3
147.5°	586.3	589.2	588.6	588.0	587.5
150°	606.7	609.0	609.0	609.0	608.4
152.5°	626.0	627.1	627.7	629.4	627.7
155°	645.8	645.8	645.3	647.5	645.3
157.5°	662.8	661.7	661.7	663.4	661.7
160°	677.6	677.0	676.4	678.1	675.3
162.5°	691.2	689.5	688.9	692.3	689.5
165°	703.0	701.3	700.2	703.6	701.3
167.5°	712.7	710.4	710.4	713.8	710.4
170°	720.6	717.8	718.3	721.7	717.8
172.5°	726.3	724.0	724.0	728.0	724.0
175°	731.4	728.5	728.0	731.9	728.0
177.5°	733.6	730.8	730.8	734.8	730.2
180°	732.5	732.5	732.5	732.5	732.5

(END OF REPORT)