

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007715

Luminaire Tested: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B590UB2750-4F0-XX-W2A-1_4000K
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2040.0 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007715

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007715

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007715

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.6	0.1
90°-100°	47.9	2.3
100°-110°	143.4	7.0
110°-120°	243.7	11.9
120°-130°	321.4	15.8
130°-140°	360.9	17.7
140°-150°	354.8	17.4
150°-160°	298.4	14.6
160°-170°	198.5	9.7
170°-180°	69.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.6	0.1
90°-120°	435.0	21.3
90°-150°	1472.0	72.2
90°-180°	2038.0	99.9
0°-180°	2040.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	8	12	16	17	2
95°	34	39	43	45	45	37
105°	132	133	135	137	139	140
115°	248	248	247	246	246	244
125°	361	361	360	359	358	322
135°	465	469	469	468	466	360
145°	565	568	568	568	566	354
155°	648	648	647	649	647	298
165°	705	703	702	706	703	199
175°	734	731	730	734	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1007715

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.7	8.0	12.5	15.9	17.0
92.5°	14.8	22.2	25.0	26.7	27.3
95°	34.1	39.2	43.2	44.9	44.9
97.5°	54.5	59.1	63.6	65.9	65.9
100°	79.5	81.8	86.9	88.1	88.1
102.5°	105.7	106.3	110.8	112.5	113.1
105°	132.4	133.0	135.2	136.9	138.6
107.5°	160.2	160.8	161.4	163.6	163.1
110°	188.6	189.8	189.2	188.1	189.8

TEST NUMBER: P1007715

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.2	218.2	217.0	217.0	217.0
115°	247.7	247.7	246.6	246.0	245.5
117.5°	275.6	275.6	275.0	273.3	271.6
120°	303.4	305.7	304.0	301.1	302.3
122.5°	332.4	333.0	332.4	330.7	327.8
125°	360.8	360.8	360.2	359.1	358.0
127.5°	386.4	388.1	386.9	385.8	385.2
130°	413.6	415.3	415.3	414.2	411.9
132.5°	441.5	442.6	442.0	440.9	440.3
135°	465.3	468.8	468.8	467.6	465.9
137.5°	492.1	493.8	494.9	493.2	493.8
140°	518.8	519.9	519.9	519.3	518.8
142.5°	543.2	544.3	543.8	543.8	543.8
145°	565.3	567.6	568.2	567.6	565.9
147.5°	588.1	590.9	590.3	589.8	589.2
150°	608.5	610.8	610.8	610.8	610.2
152.5°	627.8	629.0	629.6	631.3	629.6
155°	647.7	647.7	647.2	649.4	647.2
157.5°	664.8	663.6	663.6	665.3	663.6
160°	679.6	679.0	678.4	680.1	677.3
162.5°	693.2	691.5	690.9	694.3	691.5
165°	705.1	703.4	702.3	705.7	703.4
167.5°	714.8	712.5	712.5	715.9	712.5
170°	722.7	719.9	720.5	723.9	719.9
172.5°	728.4	726.1	726.1	730.1	726.1
175°	733.5	730.7	730.1	734.1	730.1
177.5°	735.8	733.0	733.0	736.9	732.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)