

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007744

Luminaire Tested: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B810UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2753.0 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007744

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007744

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007744

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	64.6	2.3
100°-110°	193.6	7.0
110°-120°	328.8	11.9
120°-130°	433.7	15.8
130°-140°	487.1	17.7
140°-150°	478.7	17.4
150°-160°	402.7	14.6
160°-170°	267.9	9.7
170°-180°	93.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	587.0	21.3
90°-150°	1986.5	72.2
90°-180°	2751.0	99.9
0°-180°	2753.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	11	17	22	23	3
95°	46	53	58	61	61	50
105°	179	179	182	185	187	189
115°	334	334	333	332	331	330
125°	487	487	486	485	483	434
135°	628	633	633	631	629	486
145°	763	766	767	766	764	478
155°	874	874	873	876	873	402
165°	952	949	948	952	949	268
175°	990	986	985	991	985	94
180°	991	991	991	991	991	

TEST NUMBER: P1007744

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.7	16.9	21.5	23.0
92.5°	19.9	29.9	33.7	36.0	36.8
95°	46.0	52.9	58.3	60.6	60.6
97.5°	73.6	79.7	85.9	88.9	88.9
100°	107.3	110.4	117.3	118.9	118.9
102.5°	142.6	143.4	149.5	151.8	152.6
105°	178.7	179.4	182.5	184.8	187.1
107.5°	216.2	217.0	217.8	220.8	220.1
110°	254.6	256.1	255.3	253.8	256.1

TEST NUMBER: P1007744

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.4	294.4	292.9	292.9	292.9
115°	334.3	334.3	332.8	332.0	331.2
117.5°	371.9	371.9	371.1	368.8	366.5
120°	409.5	412.5	410.2	406.4	407.9
122.5°	448.6	449.3	448.6	446.3	442.4
125°	486.9	486.9	486.1	484.6	483.1
127.5°	521.4	523.7	522.2	520.6	519.9
130°	558.2	560.5	560.5	559.0	555.9
132.5°	595.8	597.3	596.6	595.0	594.3
135°	628.0	632.6	632.6	631.1	628.8
137.5°	664.0	666.3	667.9	665.6	666.3
140°	700.1	701.6	701.6	700.8	700.1
142.5°	733.0	734.6	733.8	733.8	733.8
145°	762.9	766.0	766.8	766.0	763.7
147.5°	793.6	797.4	796.7	795.9	795.1
150°	821.2	824.3	824.3	824.3	823.5
152.5°	847.3	848.8	849.6	851.9	849.6
155°	874.1	874.1	873.4	876.4	873.4
157.5°	897.1	895.6	895.6	897.9	895.6
160°	917.1	916.3	915.5	917.8	914.0
162.5°	935.5	933.2	932.4	937.0	933.2
165°	951.6	949.3	947.7	952.3	949.3
167.5°	964.6	961.5	961.5	966.1	961.5
170°	975.3	971.5	972.3	976.9	971.5
172.5°	983.0	979.9	979.9	985.3	979.9
175°	989.9	986.1	985.3	990.7	985.3
177.5°	993.0	989.1	989.1	994.5	988.4
180°	991.4	991.4	991.4	991.4	991.4

(END OF REPORT)