

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026269

Luminaire Tested: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026269
REPORT IS A COMBINATION OF REPORTS P999279 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5559.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026269

CATALOG NUMBER: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026269

CATALOG NUMBER: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		90	90	90	90		69	69	69		51	51	51		33	33	33
1	92	88	85	81		82	79	76	73		61	59	57		45	43	42		30	29	28
2	84	77	71	66		75	69	64	60		53	50	47		39	37	35		26	25	24
3	77	68	61	55		68	61	55	50		47	43	40		35	32	30		23	22	21
4	70	60	52	47		62	54	47	42		42	37	34		31	28	26		21	19	18
5	64	53	46	40		57	48	41	36		37	33	29		28	25	22		19	17	15
6	59	48	40	34		53	43	36	31		34	29	25		25	22	19		17	15	14
7	55	43	35	30		49	39	32	27		30	26	22		23	20	17		16	14	12
8	51	39	31	26		45	35	29	24		28	23	20		21	18	15		14	12	11
9	47	35	28	23		42	32	26	21		25	21	17		19	16	14		13	11	10
10	44	32	25	21		39	29	23	19		23	19	16		18	14	12		12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4906	4906	4906
5°	4906	4760	4761
10°	4865	4610	4555
15°	4798	4422	4312
20°	4710	4209	4036
25°	4601	3979	3766
30°	4493	3744	3463
35°	4376	3507	3166
40°	4236	3251	2862
45°	4104	2996	2560
50°	3956	2719	2254
55°	3794	2435	1938
60°	3614	2133	1626
65°	3441	1786	1325
70°	3197	1423	1012
75°	2882	1035	708
80°	2406	635	510
85°	1812	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4104 cd/sqm

TEST NUMBER: P1026269

CATALOG NUMBER: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	1.0
10°-20°	157.7	2.8
20°-30°	227.7	4.1
30°-40°	258.1	4.6
40°-50°	249.2	4.5
50°-60°	207.2	3.7
60°-70°	143.0	2.6
70°-80°	72.3	1.3
80°-90°	21.5	0.4
90°-100°	97.9	1.8
100°-110°	293.1	5.3
110°-120°	498.0	9.0
120°-130°	656.7	11.8
130°-140°	737.6	13.3
140°-150°	725.0	13.0
150°-160°	609.8	11.0
160°-170°	405.7	7.3
170°-180°	142.1	2.6
0°-30°	442.0	8.0
0°-40°	700.1	12.6
0°-60°	1156.4	20.8
0°-90°	1393.2	25.1
90°-120°	889.0	16.0
90°-150°	3008.3	54.1
90°-180°	4166.0	74.9
0°-180°	5559.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	602	602	602	602	602	
5°	601	599	593	598	597	57
15°	572	568	556	556	552	161
25°	517	509	490	482	478	238
35°	447	432	410	394	386	280
45°	365	348	320	298	289	281
55°	276	258	228	204	195	247
65°	188	168	139	119	113	186
75°	100	83	61	51	48	105
85°	25	16	14	13	13	27
90°	4	16	26	32	35	7
95°	70	80	88	92	92	75
105°	271	272	276	280	283	287
115°	506	506	504	503	502	499
125°	737	737	736	734	732	657
135°	951	958	958	956	952	736
145°	1155	1160	1161	1160	1156	723
155°	1324	1324	1323	1327	1323	609
165°	1441	1438	1435	1442	1438	406
175°	1499	1493	1492	1500	1492	142
180°	1501	1501	1501	1501	1501	

TEST NUMBER: P1026269

CATALOG NUMBER: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.6	601.6	601.6	601.6	601.6
2.5°	603.4	601.6	596.5	601.6	601.1
5°	600.7	598.8	593.3	597.9	597.0
7.5°	596.5	594.7	587.8	591.0	589.6
10°	590.1	587.8	579.5	581.3	579.5
12.5°	581.8	579.0	568.9	569.8	567.0
15°	572.1	567.9	556.4	555.5	552.3
17.5°	561.0	555.1	541.7	539.4	534.8
20°	547.7	541.7	526.0	522.3	516.4
22.5°	532.9	526.0	509.0	503.0	498.4
25°	517.3	509.0	490.1	482.3	477.7
27.5°	501.2	491.0	471.2	462.0	455.6
30°	484.1	472.6	450.9	439.4	432.1
32.5°	466.2	452.8	430.2	416.4	409.5
35°	447.3	432.5	409.5	393.8	385.5
37.5°	427.5	412.3	386.9	369.9	361.6
40°	406.3	391.1	364.8	345.5	337.2
42.5°	386.0	369.9	342.2	322.4	313.7
45°	364.8	347.8	320.1	297.6	289.3
47.5°	343.2	325.7	297.1	273.6	264.4
50°	321.1	303.1	273.6	250.6	241.8
52.5°	298.5	281.0	250.6	227.1	217.9
55°	276.4	257.9	228.0	204.1	195.3
57.5°	254.7	235.4	205.9	181.5	175.0
60°	231.2	212.8	183.3	159.4	152.0
62.5°	210.0	190.7	160.3	138.6	133.1
65°	187.9	168.1	138.6	118.8	113.3
67.5°	164.9	146.0	118.4	100.9	94.4
70°	143.3	123.9	97.7	82.5	77.8
72.5°	120.2	103.2	78.8	66.3	62.2
75°	100.0	82.9	61.3	50.7	47.9
77.5°	78.8	64.0	45.6	38.2	37.3
80°	58.5	45.1	31.3	29.9	29.5
82.5°	41.0	29.0	22.6	21.6	21.2
85°	24.9	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.4	6.0	6.4
90°	3.5	16.3	25.5	32.5	34.8
92.5°	30.2	45.3	51.1	54.6	55.7
95°	69.7	80.1	88.2	91.7	91.7
97.5°	111.5	120.8	130.1	134.7	134.7
100°	162.6	167.2	177.7	180.0	180.0
102.5°	216.0	217.1	226.4	229.9	231.1
105°	270.6	271.7	276.4	279.8	283.3
107.5°	327.4	328.6	329.8	334.4	333.3
110°	385.5	387.8	386.7	384.3	387.8

TEST NUMBER: P1026269

CATALOG NUMBER: S124RDIP-B350D1205UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	445.9	445.9	443.6	443.6	443.6
115°	506.3	506.3	503.9	502.8	501.6
117.5°	563.2	563.2	562.0	558.5	555.0
120°	620.1	624.7	621.2	615.4	617.7
122.5°	679.3	680.4	679.3	675.8	670.0
125°	737.3	737.3	736.2	733.9	731.5
127.5°	789.6	793.1	790.8	788.4	787.3
130°	845.3	848.8	848.8	846.5	841.8
132.5°	902.2	904.5	903.4	901.1	899.9
135°	951.0	958.0	958.0	955.6	952.2
137.5°	1005.6	1009.1	1011.4	1007.9	1009.1
140°	1060.1	1062.5	1062.5	1061.3	1060.1
142.5°	1110.1	1112.4	1111.2	1111.2	1111.2
145°	1155.4	1160.0	1161.2	1160.0	1156.5
147.5°	1201.8	1207.6	1206.4	1205.3	1204.1
150°	1243.6	1248.3	1248.3	1248.3	1247.1
152.5°	1283.1	1285.4	1286.6	1290.1	1286.6
155°	1323.7	1323.7	1322.6	1327.2	1322.6
157.5°	1358.6	1356.2	1356.2	1359.7	1356.2
160°	1388.8	1387.6	1386.4	1389.9	1384.1
162.5°	1416.6	1413.1	1412.0	1418.9	1413.1
165°	1441.0	1437.5	1435.2	1442.2	1437.5
167.5°	1460.7	1456.1	1456.1	1463.1	1456.1
170°	1477.0	1471.2	1472.4	1479.3	1471.2
172.5°	1488.6	1484.0	1484.0	1492.1	1484.0
175°	1499.1	1493.3	1492.1	1500.2	1492.1
177.5°	1503.7	1497.9	1497.9	1506.0	1496.7
180°	1501.4	1501.4	1501.4	1501.4	1501.4

(END OF REPORT)