

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007673

Luminaire Tested: S124IP-B1205UB40-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007673
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1205UB40-4F0-XX-W2A-1
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4145.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007673

CATALOG NUMBER: S124IP-B1205UB40-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007673

CATALOG NUMBER: S124IP-B1205UB40-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007673

CATALOG NUMBER: S124IP-B1205UB40-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.2	0.1
90°-100°	97.3	2.3
100°-110°	291.4	7.0
110°-120°	495.1	11.9
120°-130°	652.9	15.8
130°-140°	733.4	17.7
140°-150°	720.8	17.4
150°-160°	606.2	14.6
160°-170°	403.4	9.7
170°-180°	141.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.2	0.1
90°-120°	883.8	21.3
90°-150°	2990.9	72.2
90°-180°	4142.0	99.9
0°-180°	4145.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	16	25	32	35	5
95°	69	80	88	91	91	75
105°	269	270	275	278	282	285
115°	503	503	501	500	499	496
125°	733	733	732	730	727	653
135°	946	952	952	950	947	731
145°	1149	1153	1154	1153	1150	719
155°	1316	1316	1315	1320	1315	606
165°	1433	1429	1427	1434	1429	404
175°	1490	1485	1484	1492	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1007673

CATALOG NUMBER: S124IP-B1205UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.5	16.2	25.4	32.3	34.6
92.5°	30.0	45.0	50.8	54.3	55.4
95°	69.3	79.7	87.7	91.2	91.2
97.5°	110.8	120.1	129.3	133.9	133.9
100°	161.6	166.2	176.6	178.9	178.9
102.5°	214.7	215.9	225.1	228.6	229.7
105°	269.0	270.1	274.8	278.2	281.7
107.5°	325.6	326.7	327.9	332.5	331.3
110°	383.3	385.6	384.4	382.1	385.6

TEST NUMBER: P1007673

CATALOG NUMBER: S124IP-B1205UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.3	443.3	441.0	441.0	441.0
115°	503.4	503.4	501.0	499.9	498.7
117.5°	559.9	559.9	558.8	555.3	551.8
120°	616.5	621.1	617.6	611.9	614.2
122.5°	675.4	676.5	675.4	671.9	666.1
125°	733.1	733.1	731.9	729.6	727.3
127.5°	785.0	788.5	786.2	783.9	782.7
130°	840.5	843.9	843.9	841.6	837.0
132.5°	897.0	899.3	898.2	895.9	894.7
135°	945.5	952.4	952.4	950.1	946.7
137.5°	999.8	1003.2	1005.6	1002.1	1003.2
140°	1054.0	1056.3	1056.3	1055.2	1054.0
142.5°	1103.7	1106.0	1104.8	1104.8	1104.8
145°	1148.7	1153.3	1154.5	1153.3	1149.9
147.5°	1194.9	1200.7	1199.5	1198.3	1197.2
150°	1236.4	1241.1	1241.1	1241.1	1239.9
152.5°	1275.7	1278.0	1279.2	1282.6	1279.2
155°	1316.1	1316.1	1315.0	1319.6	1315.0
157.5°	1350.7	1348.4	1348.4	1351.9	1348.4
160°	1380.8	1379.6	1378.4	1381.9	1376.1
162.5°	1408.5	1405.0	1403.8	1410.8	1405.0
165°	1432.7	1429.2	1426.9	1433.9	1429.2
167.5°	1452.3	1447.7	1447.7	1454.6	1447.7
170°	1468.5	1462.7	1463.9	1470.8	1462.7
172.5°	1480.0	1475.4	1475.4	1483.5	1475.4
175°	1490.4	1484.7	1483.5	1491.6	1483.5
177.5°	1495.1	1489.3	1489.3	1497.4	1488.1
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)