

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007705

Luminaire Tested: S124IP-B365UB40-4F0-XX-W2A

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB40-4F0-XX-W2A
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1464.0 lumens
Efficiency: N/A
Efficacy: 157.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007705

CATALOG NUMBER: S124IP-B365UB40-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P1007705

CATALOG NUMBER: S124IP-B365UB40-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007705

CATALOG NUMBER: S124IP-B365UB40-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	15.7	1.1
100°-110°	103.4	7.1
110°-120°	197.4	13.5
120°-130°	250.5	17.1
130°-140°	268.0	18.3
140°-150°	250.6	17.1
150°-160°	202.1	13.8
160°-170°	130.3	8.9
170°-180°	44.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	316.4	21.6
90°-150°	1085.6	74.2
90°-180°	1463.0	99.9
0°-180°	1464.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	11	1
95°	19	7	8	10	10	24
105°	106	109	110	114	101	111
115°	199	200	199	200	200	196
125°	279	281	280	281	282	249
135°	347	346	348	348	349	267
145°	400	401	401	401	402	250
155°	438	438	437	439	438	202
165°	462	460	460	463	460	131
175°	473	471	471	474	470	45
180°	473	473	473	473	473	

TEST NUMBER: P1007705

CATALOG NUMBER: S124IP-B365UB40-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	5.0	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.3
97.5°	37.1	44.9	7.8	9.5	9.9
100°	58.0	64.4	15.6	9.5	9.9
102.5°	81.3	85.6	89.8	10.3	10.3
105°	106.4	108.6	110.3	113.5	100.8
107.5°	129.4	130.5	133.0	134.7	136.1
110°	152.8	153.8	156.0	156.7	157.7

TEST NUMBER: P1007705

CATALOG NUMBER: S124IP-B365UB40-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.4	177.5	178.2	177.9	179.3
115°	198.7	199.8	199.4	200.2	200.2
117.5°	219.6	221.0	222.1	221.7	221.7
120°	240.8	242.2	241.9	242.6	241.9
122.5°	260.6	261.3	262.0	262.4	261.7
125°	279.4	280.8	280.1	281.1	281.5
127.5°	297.4	297.8	299.5	299.2	298.8
130°	314.7	315.1	316.1	316.5	316.5
132.5°	330.6	331.4	332.8	333.1	332.8
135°	346.6	346.2	347.6	348.3	349.0
137.5°	360.7	360.7	362.5	363.2	362.8
140°	374.5	375.2	375.9	377.0	377.3
142.5°	386.9	388.3	388.6	389.3	389.3
145°	399.6	400.7	400.7	401.0	401.7
147.5°	409.5	411.6	411.3	411.6	412.0
150°	420.5	421.9	421.5	421.5	421.9
152.5°	429.7	430.7	430.0	430.7	430.4
155°	438.1	438.5	437.4	438.9	437.8
157.5°	445.6	445.6	444.2	445.9	444.2
160°	451.9	450.9	450.5	452.6	450.5
162.5°	457.6	456.2	455.8	458.0	455.5
165°	462.2	460.4	460.4	463.3	460.1
167.5°	466.1	464.3	464.0	467.1	463.6
170°	469.3	467.1	467.5	470.3	466.8
172.5°	471.4	469.3	469.6	472.5	468.6
175°	472.8	470.7	471.0	474.2	470.0
177.5°	473.9	471.4	472.1	474.9	470.7
180°	472.8	472.8	472.8	472.8	472.8

(END OF REPORT)