

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026360

Luminaire Tested: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026360
REPORT IS A COMBINATION OF REPORTS P999400 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D810UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4228.7 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026360

CATALOG NUMBER: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026360

CATALOG NUMBER: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13
9	48	36	29	24	43	33	27	23	27	22	19	22	18	16	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4906	4906	4906
5°	4906	4760	4761
10°	4865	4610	4555
15°	4798	4422	4312
20°	4710	4209	4036
25°	4601	3979	3766
30°	4493	3744	3463
35°	4376	3507	3166
40°	4236	3251	2862
45°	4104	2996	2560
50°	3956	2719	2254
55°	3794	2435	1938
60°	3614	2133	1626
65°	3441	1786	1325
70°	3197	1423	1012
75°	2882	1035	708
80°	2406	635	510
85°	1812	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4104 cd/sqm

TEST NUMBER: P1026360

CATALOG NUMBER: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	1.3
10°-20°	157.7	3.7
20°-30°	227.7	5.4
30°-40°	258.1	6.1
40°-50°	249.2	5.9
50°-60°	207.2	4.9
60°-70°	143.0	3.4
70°-80°	72.3	1.7
80°-90°	19.8	0.5
90°-100°	288.8	6.8
100°-110°	587.3	13.9
110°-120°	523.5	12.4
120°-130°	439.8	10.4
130°-140°	367.0	8.7
140°-150°	280.3	6.6
150°-160°	197.0	4.7
160°-170°	115.9	2.7
170°-180°	37.7	0.9
0°-30°	442.0	10.5
0°-40°	700.1	16.6
0°-60°	1156.4	27.3
0°-90°	1391.5	32.9
90°-120°	1399.6	33.1
90°-150°	2486.6	58.8
90°-180°	2837.0	67.1
0°-180°	4228.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	602	602	602	602	602	
5°	601	599	593	598	597	57
15°	572	568	556	556	552	161
25°	517	509	490	482	478	238
35°	447	432	410	394	386	280
45°	365	348	320	298	289	281
55°	276	258	228	204	195	247
65°	188	168	139	119	113	186
75°	100	83	61	51	48	105
85°	25	16	14	13	13	27
90°	1	6	14	15	16	3
95°	25	79	622	308	186	28
105°	89	129	501	1079	1075	95
115°	157	197	447	858	1032	156
125°	219	260	444	731	823	195
135°	260	310	441	648	736	201
145°	300	344	438	547	601	188
155°	341	369	426	483	503	157
165°	372	383	409	433	439	105
175°	388	389	392	397	396	37
180°	389	389	389	389	389	

TEST NUMBER: P1026360

CATALOG NUMBER: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.6	601.6	601.6	601.6	601.6
2.5°	603.4	601.6	596.5	601.6	601.1
5°	600.7	598.8	593.3	597.9	597.0
7.5°	596.5	594.7	587.8	591.0	589.6
10°	590.1	587.8	579.5	581.3	579.5
12.5°	581.8	579.0	568.9	569.8	567.0
15°	572.1	567.9	556.4	555.5	552.3
17.5°	561.0	555.1	541.7	539.4	534.8
20°	547.7	541.7	526.0	522.3	516.4
22.5°	532.9	526.0	509.0	503.0	498.4
25°	517.3	509.0	490.1	482.3	477.7
27.5°	501.2	491.0	471.2	462.0	455.6
30°	484.1	472.6	450.9	439.4	432.1
32.5°	466.2	452.8	430.2	416.4	409.5
35°	447.3	432.5	409.5	393.8	385.5
37.5°	427.5	412.3	386.9	369.9	361.6
40°	406.3	391.1	364.8	345.5	337.2
42.5°	386.0	369.9	342.2	322.4	313.7
45°	364.8	347.8	320.1	297.6	289.3
47.5°	343.2	325.7	297.1	273.6	264.4
50°	321.1	303.1	273.6	250.6	241.8
52.5°	298.5	281.0	250.6	227.1	217.9
55°	276.4	257.9	228.0	204.1	195.3
57.5°	254.7	235.4	205.9	181.5	175.0
60°	231.2	212.8	183.3	159.4	152.0
62.5°	210.0	190.7	160.3	138.6	133.1
65°	187.9	168.1	138.6	118.8	113.3
67.5°	164.9	146.0	118.4	100.9	94.4
70°	143.3	123.9	97.7	82.5	77.8
72.5°	120.2	103.2	78.8	66.3	62.2
75°	100.0	82.9	61.3	50.7	47.9
77.5°	78.8	64.0	45.6	38.2	37.3
80°	58.5	45.1	31.3	29.9	29.5
82.5°	41.0	29.0	22.6	21.6	21.2
85°	24.9	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.4	6.0	6.4
90°	0.8	6.1	13.7	15.3	16.0
92.5°	10.7	58.8	299.4	99.0	69.5
95°	25.2	79.4	622.5	308.2	186.4
97.5°	42.0	87.8	666.0	629.4	447.6
100°	58.0	99.3	614.1	870.8	700.4
102.5°	73.3	113.0	549.2	1022.0	920.4
105°	89.4	129.4	501.0	1078.8	1074.6
107.5°	106.9	146.2	469.7	1061.6	1148.0
110°	124.5	163.1	455.2	1000.6	1149.5

TEST NUMBER: P1026360

CATALOG NUMBER: S124RDIP-B350D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.3	179.9	448.3	925.7	1104.4
115°	157.3	197.4	446.8	858.5	1031.9
117.5°	174.1	213.9	446.0	805.8	960.8
120°	190.9	229.9	446.0	770.3	902.8
122.5°	206.2	245.6	445.3	747.0	857.0
125°	219.2	260.5	444.5	730.6	823.4
127.5°	231.4	274.2	443.0	714.9	802.0
130°	241.4	287.6	442.2	696.2	783.6
132.5°	251.3	299.0	441.5	674.0	763.0
135°	260.4	310.1	440.7	648.4	736.3
137.5°	269.6	319.6	440.7	621.0	705.0
140°	279.5	328.5	439.9	594.2	670.6
142.5°	290.2	336.4	439.9	569.4	633.9
145°	300.2	343.7	438.4	546.9	601.1
147.5°	311.6	350.5	436.1	528.2	570.5
150°	322.3	357.0	433.8	511.0	545.3
152.5°	332.2	363.2	430.0	496.4	522.4
155°	341.4	368.6	426.2	482.7	503.3
157.5°	350.6	373.5	422.4	469.7	485.8
160°	359.0	377.7	417.8	456.8	469.7
162.5°	366.6	381.2	413.2	444.2	454.4
165°	372.0	383.4	408.6	432.7	439.2
167.5°	378.1	385.3	404.0	422.8	427.0
170°	381.9	386.8	399.5	412.8	415.5
172.5°	385.7	388.0	394.9	404.0	404.0
175°	388.0	388.8	391.8	397.2	395.6
177.5°	389.5	388.8	389.5	392.2	389.5
180°	388.8	388.8	388.8	388.8	388.8

(END OF REPORT)