

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026365

Luminaire Tested: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026365
REPORT IS A COMBINATION OF REPORTS P999405 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D810UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4149.0 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026365

CATALOG NUMBER: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026365

CATALOG NUMBER: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30
3	79	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	26
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4927	4927	4927
5°	4927	4780	4781
10°	4885	4630	4575
15°	4819	4441	4331
20°	4730	4228	4053
25°	4620	3996	3782
30°	4513	3761	3477
35°	4395	3522	3180
40°	4254	3265	2874
45°	4122	3010	2571
50°	3972	2731	2264
55°	3811	2446	1946
60°	3630	2142	1633
65°	3456	1794	1331
70°	3210	1429	1017
75°	2893	1039	711
80°	2418	639	511
85°	1819	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4122 cd/sqm

TEST NUMBER: P1026365

CATALOG NUMBER: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.4
10°-20°	158.4	3.8
20°-30°	228.7	5.5
30°-40°	259.2	6.2
40°-50°	250.3	6.0
50°-60°	208.1	5.0
60°-70°	143.6	3.5
70°-80°	72.6	1.7
80°-90°	20.5	0.5
90°-100°	64.6	1.6
100°-110°	193.6	4.7
110°-120°	328.8	7.9
120°-130°	433.7	10.5
130°-140°	487.1	11.7
140°-150°	478.7	11.5
150°-160°	402.7	9.7
160°-170°	267.9	6.5
170°-180°	93.8	2.3
0°-30°	443.9	10.7
0°-40°	703.1	16.9
0°-60°	1161.4	28.0
0°-90°	1398.1	33.7
90°-120°	587.0	14.1
90°-150°	1986.5	47.9
90°-180°	2751.0	66.3
0°-180°	4149.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	604	604	604	604	604	
5°	603	601	596	600	600	57
15°	575	570	559	558	555	162
25°	520	511	492	484	480	239
35°	449	434	411	396	387	281
45°	366	349	322	299	290	283
55°	278	259	229	205	196	248
65°	189	169	139	119	114	186
75°	100	83	62	51	48	106
85°	25	16	14	13	13	27
90°	2	11	17	22	23	5
95°	46	53	58	61	61	50
105°	179	179	182	185	187	189
115°	334	334	333	332	331	330
125°	487	487	486	485	483	434
135°	628	633	633	631	629	486
145°	763	766	767	766	764	478
155°	874	874	873	876	873	402
165°	952	949	948	952	949	268
175°	990	986	985	991	985	94
180°	991	991	991	991	991	

TEST NUMBER: P1026365

CATALOG NUMBER: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	604.2	604.2	604.2	604.2	604.2
2.5°	606.0	604.2	599.1	604.2	603.7
5°	603.2	601.4	595.8	600.5	599.5
7.5°	599.1	597.2	590.3	593.5	592.1
10°	592.6	590.3	582.0	583.8	582.0
12.5°	584.3	581.5	571.3	572.3	569.5
15°	574.6	570.4	558.8	557.9	554.7
17.5°	563.5	557.4	544.0	541.7	537.1
20°	550.0	544.0	528.3	524.6	518.6
22.5°	535.2	528.3	511.2	505.2	500.5
25°	519.5	511.2	492.2	484.4	479.7
27.5°	503.3	493.1	473.3	464.0	457.5
30°	486.2	474.6	452.9	441.3	433.9
32.5°	468.2	454.7	432.1	418.2	411.3
35°	449.2	434.4	411.3	395.5	387.2
37.5°	429.3	414.0	388.6	371.5	363.1
40°	408.0	392.8	366.4	347.0	338.6
42.5°	387.7	371.5	343.7	323.8	315.0
45°	366.4	349.3	321.5	298.8	290.5
47.5°	344.6	327.1	298.4	274.8	265.5
50°	322.4	304.4	274.8	251.7	242.9
52.5°	299.8	282.2	251.7	228.1	218.8
55°	277.6	259.1	229.0	204.9	196.1
57.5°	255.8	236.4	206.8	182.3	175.8
60°	232.2	213.7	184.1	160.1	152.7
62.5°	211.0	191.5	161.0	139.2	133.7
65°	188.7	168.9	139.2	119.4	113.8
67.5°	165.6	146.6	118.9	101.3	94.8
70°	143.9	124.4	98.1	82.8	78.2
72.5°	120.7	103.6	79.1	66.6	62.5
75°	100.4	83.3	61.5	50.9	48.1
77.5°	79.1	64.3	45.8	38.4	37.5
80°	58.8	45.3	31.5	30.1	29.6
82.5°	41.2	29.1	22.7	21.7	21.3
85°	25.0	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.5	6.0	6.5
90°	2.3	10.7	16.9	21.5	23.0
92.5°	19.9	29.9	33.7	36.0	36.8
95°	46.0	52.9	58.3	60.6	60.6
97.5°	73.6	79.7	85.9	88.9	88.9
100°	107.3	110.4	117.3	118.9	118.9
102.5°	142.6	143.4	149.5	151.8	152.6
105°	178.7	179.4	182.5	184.8	187.1
107.5°	216.2	217.0	217.8	220.8	220.1
110°	254.6	256.1	255.3	253.8	256.1

TEST NUMBER: P1026365

CATALOG NUMBER: S124RDIP-B350D810UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.4	294.4	292.9	292.9	292.9
115°	334.3	334.3	332.8	332.0	331.2
117.5°	371.9	371.9	371.1	368.8	366.5
120°	409.5	412.5	410.2	406.4	407.9
122.5°	448.6	449.3	448.6	446.3	442.4
125°	486.9	486.9	486.1	484.6	483.1
127.5°	521.4	523.7	522.2	520.6	519.9
130°	558.2	560.5	560.5	559.0	555.9
132.5°	595.8	597.3	596.6	595.0	594.3
135°	628.0	632.6	632.6	631.1	628.8
137.5°	664.0	666.3	667.9	665.6	666.3
140°	700.1	701.6	701.6	700.8	700.1
142.5°	733.0	734.6	733.8	733.8	733.8
145°	762.9	766.0	766.8	766.0	763.7
147.5°	793.6	797.4	796.7	795.9	795.1
150°	821.2	824.3	824.3	824.3	823.5
152.5°	847.3	848.8	849.6	851.9	849.6
155°	874.1	874.1	873.4	876.4	873.4
157.5°	897.1	895.6	895.6	897.9	895.6
160°	917.1	916.3	915.5	917.8	914.0
162.5°	935.5	933.2	932.4	937.0	933.2
165°	951.6	949.3	947.7	952.3	949.3
167.5°	964.6	961.5	961.5	966.1	961.5
170°	975.3	971.5	972.3	976.9	971.5
172.5°	983.0	979.9	979.9	985.3	979.9
175°	989.9	986.1	985.3	990.7	985.3
177.5°	993.0	989.1	989.1	994.5	988.4
180°	991.4	991.4	991.4	991.4	991.4

(END OF REPORT)