

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026686

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026686
REPORT IS A COMBINATION OF REPORTS P1001235 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8374.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026686

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026686

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	92	88	84	89	85	81	78	71	68	66	58	56	55	47	45	44
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	65	58	53	54	49	45	45	41	38	36	33	31
4	73	62	54	47	67	57	50	44	48	43	38	40	36	32	32	29	26
5	67	55	47	40	61	51	43	38	43	37	33	35	31	28	29	25	23
6	61	49	41	35	56	45	38	33	39	33	28	32	28	24	26	23	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	24	20	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8807	8807	8807
5°	8821	8622	8643
10°	8755	8446	8422
15°	8648	8241	8150
20°	8504	7994	7880
25°	8334	7731	7554
30°	8127	7445	7257
35°	7935	7180	6984
40°	7738	6902	6708
45°	7517	6661	6460
50°	7304	6399	6236
55°	7049	6149	5976
60°	6770	5864	5709
65°	6477	5564	5409
70°	6142	5162	5097
75°	5615	4765	4716
80°	4922	4282	4295
85°	4237	3899	4073

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7517 cd/sqm

TEST NUMBER: P1026686

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	1.6
10°-20°	369.2	4.4
20°-30°	549.1	6.6
30°-40°	650.3	7.8
40°-50°	672.3	8.0
50°-60°	619.3	7.4
60°-70°	500.6	6.0
70°-80°	335.0	4.0
80°-90°	175.1	2.1
90°-100°	143.0	1.7
100°-110°	374.2	4.5
110°-120°	592.4	7.1
120°-130°	725.9	8.7
130°-140°	763.4	9.1
140°-150°	707.6	8.5
150°-160°	570.5	6.8
160°-170°	368.9	4.4
170°-180°	127.2	1.5
0°-30°	1048.4	12.5
0°-40°	1698.6	20.3
0°-60°	2990.2	35.7
0°-90°	4000.9	47.8
90°-120°	1109.6	13.3
90°-150°	3306.4	39.5
90°-180°	4373.0	52.2
0°-180°	8374.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1374	1372	1362	1373	1372	130
15°	1312	1314	1304	1312	1307	370
25°	1193	1197	1188	1194	1187	549
35°	1032	1042	1038	1042	1042	646
45°	850	865	872	881	883	656
55°	654	675	697	712	717	584
65°	450	481	513	534	539	447
75°	248	283	326	353	360	263
85°	74	119	166	195	206	77
90°	23	74	126	162	175	18
95°	74	106	114	149	158	83
105°	304	330	370	397	405	322
115°	556	570	607	627	629	551
125°	785	790	817	835	839	701
135°	975	979	987	1002	1003	751
145°	1128	1129	1129	1136	1136	705
155°	1241	1235	1237	1240	1232	572
165°	1310	1304	1304	1310	1303	370
175°	1339	1333	1334	1342	1333	128
180°	1339	1339	1339	1339	1339	

TEST NUMBER: P1026686

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.5	1374.5	1374.5	1374.5	1374.5
2.5°	1378.6	1375.9	1366.4	1375.9	1374.5
5°	1374.5	1371.8	1362.4	1373.2	1371.8
7.5°	1365.1	1363.7	1354.3	1363.7	1362.4
10°	1351.6	1351.6	1340.8	1350.3	1348.9
12.5°	1332.7	1334.1	1326.0	1332.7	1328.7
15°	1312.5	1313.9	1304.4	1312.5	1307.1
17.5°	1286.9	1289.6	1280.2	1286.9	1282.9
20°	1258.6	1261.3	1251.9	1255.9	1255.9
22.5°	1226.3	1231.7	1220.9	1226.3	1222.2
25°	1192.6	1196.6	1188.5	1193.9	1187.2
27.5°	1156.2	1161.6	1152.2	1156.2	1153.5
30°	1114.4	1122.5	1114.4	1117.1	1115.8
32.5°	1076.7	1083.4	1078.0	1080.7	1079.4
35°	1032.2	1041.7	1037.6	1041.7	1041.7
37.5°	989.1	997.2	995.8	1001.2	999.9
40°	944.6	955.4	954.1	959.5	962.2
42.5°	896.1	911.0	915.0	921.7	921.7
45°	850.3	865.1	871.9	881.3	882.7
47.5°	803.1	816.6	827.4	840.9	843.6
50°	754.6	769.5	784.3	799.1	803.1
52.5°	703.4	722.3	741.2	757.3	760.0
55°	653.6	675.1	696.7	711.5	716.9
57.5°	602.4	628.0	652.2	668.4	672.4
60°	551.2	578.1	605.1	625.3	629.3
62.5°	501.3	528.2	557.9	580.8	586.2
65°	450.1	481.1	513.4	533.6	539.0
67.5°	402.9	432.6	464.9	489.2	495.9
70°	350.4	381.4	416.4	442.0	450.1
72.5°	299.2	331.5	370.6	398.9	404.3
75°	248.0	283.0	326.1	353.1	359.8
77.5°	198.1	238.5	278.9	308.6	314.0
80°	152.3	192.7	238.5	268.2	273.6
82.5°	110.5	153.6	200.8	229.1	239.9
85°	74.1	118.6	165.8	195.4	206.2
87.5°	47.2	90.3	136.1	167.1	176.5
90°	22.6	73.6	126.4	162.3	174.7
92.5°	37.8	67.8	121.0	155.6	166.0
95°	74.1	106.2	114.3	148.8	158.3
97.5°	122.4	160.7	110.9	141.2	151.5
100°	180.6	211.9	258.9	139.3	143.4
102.5°	239.9	269.4	313.2	342.1	266.8
105°	304.0	329.6	370.0	397.0	405.4
107.5°	370.2	389.0	430.1	458.1	462.2
110°	434.3	450.5	490.2	512.8	523.3

TEST NUMBER: P1026686

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.9	511.1	548.3	568.7	576.1
115°	556.1	570.5	606.6	626.8	629.0
117.5°	619.3	626.1	663.7	680.7	688.1
120°	678.8	681.9	715.9	736.8	740.0
122.5°	730.1	736.4	767.1	786.6	788.8
125°	784.7	790.3	817.3	834.9	838.6
127.5°	836.0	839.6	861.5	879.8	879.9
130°	883.6	887.3	907.2	923.0	924.8
132.5°	930.0	935.9	946.5	965.3	965.7
135°	974.7	979.2	986.7	1002.2	1003.0
137.5°	1016.4	1020.9	1024.3	1040.5	1041.0
140°	1055.7	1057.6	1058.0	1074.8	1074.3
142.5°	1092.4	1092.1	1094.1	1106.2	1105.6
145°	1128.1	1128.8	1128.8	1136.5	1136.0
147.5°	1158.6	1158.6	1159.6	1163.3	1159.0
150°	1188.4	1186.4	1188.4	1190.4	1183.7
152.5°	1217.2	1212.2	1214.2	1216.2	1209.2
155°	1241.0	1235.0	1237.0	1240.0	1232.1
157.5°	1259.9	1256.9	1256.9	1259.9	1251.9
160°	1279.7	1273.8	1274.8	1278.7	1270.8
162.5°	1295.6	1289.6	1290.6	1296.6	1287.7
165°	1309.5	1303.5	1304.5	1310.5	1302.6
167.5°	1320.4	1314.5	1315.5	1322.4	1313.5
170°	1329.4	1322.4	1323.4	1331.3	1322.4
172.5°	1335.3	1328.4	1330.4	1337.3	1328.4
175°	1339.3	1333.3	1334.3	1342.3	1333.3
177.5°	1342.3	1336.3	1337.3	1344.3	1336.3
180°	1339.3	1339.3	1339.3	1339.3	1339.3

(END OF REPORT)