

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026687

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026687
REPORT IS A COMBINATION OF REPORTS P1001236 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8291.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026687

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026687

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	92	88	84	89	85	81	78	71	68	66	58	56	55	47	45	44
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	65	58	53	54	49	45	45	41	38	36	33	31
4	73	62	54	47	67	57	50	44	48	43	38	40	36	32	32	29	26
5	67	55	47	40	61	51	43	38	43	37	33	35	31	28	29	25	23
6	61	49	41	35	56	45	38	33	39	33	28	32	28	24	26	23	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	24	20	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8720	8720	8720
5°	8734	8537	8558
10°	8669	8363	8339
15°	8563	8161	8070
20°	8420	7915	7802
25°	8251	7655	7480
30°	8047	7371	7186
35°	7857	7110	6914
40°	7662	6834	6641
45°	7442	6595	6396
50°	7232	6335	6174
55°	6979	6088	5917
60°	6702	5806	5653
65°	6412	5510	5356
70°	6081	5111	5046
75°	5559	4718	4669
80°	4873	4241	4253
85°	4197	3859	4032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7442 cd/sqm

TEST NUMBER: P1026687

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	1.6
10°-20°	365.6	4.4
20°-30°	543.6	6.6
30°-40°	643.8	7.8
40°-50°	665.6	8.0
50°-60°	613.2	7.4
60°-70°	495.7	6.0
70°-80°	331.7	4.0
80°-90°	173.4	2.1
90°-100°	141.6	1.7
100°-110°	370.4	4.5
110°-120°	586.5	7.1
120°-130°	718.7	8.7
130°-140°	755.8	9.1
140°-150°	700.6	8.4
150°-160°	564.8	6.8
160°-170°	365.3	4.4
170°-180°	126.0	1.5
0°-30°	1038.0	12.5
0°-40°	1681.9	20.3
0°-60°	2960.7	35.7
0°-90°	3961.4	47.8
90°-120°	1098.5	13.2
90°-150°	3273.6	39.5
90°-180°	4330.0	52.2
0°-180°	8291.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1361	1361	1361	1361	1361	
5°	1361	1358	1349	1360	1358	129
15°	1300	1301	1292	1300	1294	366
25°	1181	1185	1177	1182	1176	544
35°	1022	1031	1027	1031	1031	640
45°	842	857	863	873	874	650
55°	647	668	690	704	710	578
65°	446	476	508	528	534	442
75°	246	280	323	350	356	260
85°	73	117	164	194	204	77
90°	22	73	125	161	173	18
95°	73	105	113	147	157	82
105°	301	326	366	393	401	319
115°	551	565	600	621	623	546
125°	777	782	809	826	830	694
135°	965	970	977	992	993	744
145°	1117	1118	1118	1125	1125	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026687

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.0	1361.0	1361.0	1361.0	1361.0
2.5°	1365.0	1362.3	1352.9	1362.3	1361.0
5°	1361.0	1358.3	1348.9	1359.6	1358.3
7.5°	1351.6	1350.3	1340.9	1350.3	1348.9
10°	1338.3	1338.3	1327.6	1336.9	1335.6
12.5°	1319.6	1320.9	1312.9	1319.6	1315.6
15°	1299.6	1300.9	1291.6	1299.6	1294.2
17.5°	1274.2	1276.9	1267.6	1274.2	1270.2
20°	1246.2	1248.9	1239.5	1243.5	1243.5
22.5°	1214.2	1219.5	1208.8	1214.2	1210.2
25°	1180.8	1184.8	1176.8	1182.2	1175.5
27.5°	1144.8	1150.1	1140.8	1144.8	1142.1
30°	1103.4	1111.4	1103.4	1106.1	1104.8
32.5°	1066.1	1072.8	1067.4	1070.1	1068.7
35°	1022.1	1031.4	1027.4	1031.4	1031.4
37.5°	979.4	987.4	986.0	991.4	990.0
40°	935.3	946.0	944.7	950.0	952.7
42.5°	887.3	902.0	906.0	912.6	912.6
45°	841.9	856.6	863.3	872.6	873.9
47.5°	795.2	808.6	819.2	832.6	835.3
50°	747.2	761.9	776.5	791.2	795.2
52.5°	696.5	715.2	733.8	749.9	752.5
55°	647.1	668.5	689.8	704.5	709.8
57.5°	596.4	621.8	645.8	661.8	665.8
60°	545.7	572.4	599.1	619.1	623.1
62.5°	496.3	523.0	552.4	575.1	580.4
65°	445.6	476.3	508.4	528.4	533.7
67.5°	398.9	428.3	460.3	484.3	491.0
70°	346.9	377.6	412.3	437.6	445.6
72.5°	296.2	328.2	366.9	394.9	400.3
75°	245.5	280.2	322.9	349.6	356.2
77.5°	196.1	236.2	276.2	305.5	310.9
80°	150.8	190.8	236.2	265.5	270.9
82.5°	109.4	152.1	198.8	226.8	237.5
85°	73.4	117.4	164.1	193.5	204.1
87.5°	46.7	89.4	134.8	165.4	174.8
90°	22.3	72.8	125.1	160.7	173.0
92.5°	37.4	67.2	119.8	154.0	164.4
95°	73.3	105.1	113.1	147.4	156.7
97.5°	121.2	159.1	109.8	139.8	150.0
100°	178.8	209.8	256.4	138.0	142.0
102.5°	237.4	266.7	310.1	338.7	264.1
105°	301.0	326.3	366.3	393.0	401.3
107.5°	366.5	385.2	425.8	453.5	457.5
110°	430.0	446.1	485.4	507.8	518.1



TEST NUMBER: P1026687

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.9	505.9	543.0	563.0	570.4
115°	550.6	564.8	600.5	620.6	622.7
117.5°	613.2	619.8	657.1	673.9	681.2
120°	672.1	675.1	708.8	729.4	732.6
122.5°	722.8	729.1	759.4	778.9	781.0
125°	776.9	782.5	809.2	826.5	830.3
127.5°	827.7	831.3	853.0	871.0	871.2
130°	874.9	878.5	898.1	913.8	915.6
132.5°	920.7	926.6	937.0	955.7	956.1
135°	965.0	969.5	976.9	992.2	993.0
137.5°	1006.3	1010.8	1014.2	1030.2	1030.6
140°	1045.2	1047.1	1047.5	1064.1	1063.6
142.5°	1081.5	1081.2	1083.2	1095.2	1094.6
145°	1116.9	1117.6	1117.6	1125.3	1124.7
147.5°	1147.1	1147.1	1148.0	1151.7	1147.4
150°	1176.5	1174.6	1176.5	1178.5	1171.9
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)