

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026690

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026690
REPORT IS A COMBINATION OF REPORTS P1001239 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8513.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026690

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026690

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	71	71	71	58	58	58	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	49	49	44
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41	41	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	35	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	30	30	26
5	68	57	49	42	63	53	46	40	45	40	35	38	34	31	32	29	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	20	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17	17	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1026690

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	1.9
10°-20°	452.1	5.3
20°-30°	667.5	7.8
30°-40°	778.8	9.1
40°-50°	782.2	9.2
50°-60°	686.6	8.1
60°-70°	511.4	6.0
70°-80°	292.1	3.4
80°-90°	86.3	1.0
90°-100°	45.3	0.5
100°-110°	300.9	3.5
110°-120°	541.9	6.4
120°-130°	695.6	8.2
130°-140°	748.1	8.8
140°-150°	702.2	8.2
150°-160°	568.0	6.7
160°-170°	367.3	4.3
170°-180°	126.7	1.5
0°-30°	1279.7	15.0
0°-40°	2058.4	24.2
0°-60°	3527.2	41.4
0°-90°	4417.0	51.9
90°-120°	888.1	10.4
90°-150°	3034.1	35.6
90°-180°	4096.0	48.1
0°-180°	8513.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	9	16	21	24	8
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1026690

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1026690

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)