

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026691

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026691
REPORT IS A COMBINATION OF REPORTS P1001240 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8550.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026691

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026691

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	71	71	71	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30
5	68	57	49	42	63	53	46	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10915	10915	10915
5°	10916	10662	10682
10°	10825	10417	10384
15°	10683	10125	10034
20°	10491	9786	9632
25°	10285	9416	9202
30°	10036	9031	8749
35°	9769	8627	8241
40°	9495	8200	7789
45°	9198	7784	7309
50°	8871	7313	6750
55°	8547	6792	6235
60°	8162	6243	5637
65°	7700	5608	5018
70°	7229	4878	4305
75°	6440	4017	3480
80°	5487	3000	2560
85°	4237	1775	1410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9198 cd/sqm

TEST NUMBER: P1026691

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	1.9
10°-20°	454.1	5.3
20°-30°	670.4	7.8
30°-40°	782.1	9.1
40°-50°	785.5	9.2
50°-60°	689.5	8.1
60°-70°	513.6	6.0
70°-80°	293.3	3.4
80°-90°	86.7	1.0
90°-100°	45.4	0.5
100°-110°	302.3	3.5
110°-120°	544.3	6.4
120°-130°	698.7	8.2
130°-140°	751.4	8.8
140°-150°	705.3	8.2
150°-160°	570.5	6.7
160°-170°	368.9	4.3
170°-180°	127.2	1.5
0°-30°	1285.2	15.0
0°-40°	2067.3	24.2
0°-60°	3542.4	41.4
0°-90°	4436.0	51.9
90°-120°	892.0	10.4
90°-150°	3047.4	35.6
90°-180°	4114.0	48.1
0°-180°	8550.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1701	1698	1685	1697	1696	161
15°	1621	1617	1602	1609	1609	457
25°	1472	1465	1448	1450	1446	677
35°	1271	1266	1247	1240	1229	795
45°	1040	1035	1019	1003	999	802
55°	792	788	770	757	748	707
65°	535	532	518	505	500	531
75°	284	282	275	271	266	303
85°	74	76	76	74	71	81
90°	1	9	16	21	24	8
95°	57	54	16	21	21	69
105°	292	296	296	296	295	309
115°	548	553	554	550	544	543
125°	779	786	786	782	779	696
135°	972	978	976	974	968	749
145°	1127	1129	1129	1130	1124	705
155°	1241	1235	1237	1240	1232	572
165°	1310	1304	1304	1310	1303	370
175°	1339	1333	1334	1342	1333	128
180°	1339	1339	1339	1339	1339	

TEST NUMBER: P1026691

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1703.6	1703.6	1703.6	1703.6	1703.6
2.5°	1709.0	1704.9	1691.5	1704.9	1703.6
5°	1700.9	1698.2	1684.7	1696.8	1695.5
7.5°	1688.8	1686.1	1671.2	1683.4	1682.0
10°	1671.2	1668.5	1653.7	1664.5	1663.1
12.5°	1649.7	1644.3	1630.8	1638.9	1638.9
15°	1621.4	1617.3	1602.5	1609.2	1609.2
17.5°	1591.7	1585.0	1570.2	1578.2	1571.5
20°	1552.6	1549.9	1532.4	1541.8	1535.1
22.5°	1513.5	1508.2	1492.0	1497.4	1493.3
25°	1471.8	1465.0	1447.5	1450.2	1446.2
27.5°	1423.2	1419.2	1401.7	1403.0	1399.0
30°	1376.1	1372.0	1351.8	1349.1	1345.1
32.5°	1324.9	1318.1	1300.6	1295.2	1287.1
35°	1270.9	1265.6	1246.7	1239.9	1229.2
37.5°	1215.7	1208.9	1191.4	1182.0	1175.3
40°	1159.1	1152.3	1133.5	1121.3	1117.3
42.5°	1098.4	1093.0	1074.2	1063.4	1056.7
45°	1040.5	1035.1	1018.9	1002.7	998.7
47.5°	977.1	978.5	958.3	942.1	932.7
50°	916.5	912.4	896.3	878.7	869.3
52.5°	854.5	851.8	834.3	819.4	808.7
55°	792.5	788.4	769.6	757.4	748.0
57.5°	726.4	725.1	708.9	692.8	688.7
60°	664.5	659.1	644.2	630.8	621.3
62.5°	599.8	595.7	583.6	568.8	562.0
65°	535.1	532.4	517.5	505.4	500.0
67.5°	471.7	466.3	455.5	444.8	442.1
70°	412.4	405.7	393.5	385.5	380.1
72.5°	347.7	343.7	336.9	327.5	322.1
75°	284.4	281.7	274.9	270.9	265.5
77.5°	225.1	223.7	219.7	217.0	212.9
80°	169.8	169.8	167.1	165.8	163.1
82.5°	121.3	118.6	118.6	115.9	115.9
85°	74.1	75.5	75.5	74.1	71.4
87.5°	36.4	36.4	35.0	35.0	32.3
90°	1.0	8.9	15.9	20.8	23.8
92.5°	18.9	9.9	15.9	20.8	21.8
95°	56.6	53.6	15.9	20.8	20.8
97.5°	106.2	112.2	17.9	19.9	20.8
100°	165.8	168.8	172.7	24.8	20.8
102.5°	226.4	230.3	232.3	234.3	150.9
105°	291.9	295.9	295.9	295.9	294.9
107.5°	359.4	359.4	361.4	362.4	358.4
110°	424.9	424.9	426.9	423.9	424.9



TEST NUMBER: P1026691

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.5	489.5	490.4	486.5	484.5
115°	548.0	553.0	554.0	550.0	544.1
117.5°	612.6	612.6	616.5	610.6	608.6
120°	672.1	671.1	674.1	672.1	667.2
122.5°	724.7	729.7	730.7	728.7	722.8
125°	779.3	786.3	786.3	782.3	779.3
127.5°	832.0	836.9	835.9	834.0	826.0
130°	879.6	884.6	885.6	882.6	877.6
132.5°	927.3	933.2	930.3	930.3	925.3
135°	972.0	977.9	975.9	973.9	968.0
137.5°	1013.7	1019.6	1017.6	1017.6	1012.7
140°	1054.4	1056.3	1055.3	1057.3	1051.4
142.5°	1091.1	1092.1	1094.1	1094.1	1088.1
145°	1126.8	1128.8	1128.8	1129.8	1123.9
147.5°	1158.6	1158.6	1159.6	1160.6	1153.6
150°	1188.4	1186.4	1188.4	1190.4	1182.4
152.5°	1217.2	1212.2	1214.2	1216.2	1209.2
155°	1241.0	1235.0	1237.0	1240.0	1232.1
157.5°	1259.9	1256.9	1256.9	1259.9	1251.9
160°	1279.7	1273.8	1274.8	1278.7	1270.8
162.5°	1295.6	1289.6	1290.6	1296.6	1287.7
165°	1309.5	1303.5	1304.5	1310.5	1302.6
167.5°	1320.4	1314.5	1315.5	1322.4	1313.5
170°	1329.4	1322.4	1323.4	1331.3	1322.4
172.5°	1335.3	1328.4	1330.4	1337.3	1328.4
175°	1339.3	1333.3	1334.3	1342.3	1333.3
177.5°	1342.3	1336.3	1337.3	1344.3	1336.3
180°	1339.3	1339.3	1339.3	1339.3	1339.3

(END OF REPORT)