

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026692

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026692
REPORT IS A COMBINATION OF REPORTS P1001241 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8465.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026692

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026692

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	71	71	71	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30
5	68	57	49	42	63	53	46	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10807	10807	10807
5°	10807	10556	10576
10°	10717	10314	10281
15°	10577	10024	9935
20°	10387	9689	9537
25°	10183	9322	9111
30°	9936	8941	8662
35°	9673	8542	8159
40°	9401	8119	7711
45°	9107	7707	7237
50°	8783	7240	6683
55°	8462	6724	6174
60°	8081	6181	5582
65°	7623	5553	4969
70°	7157	4830	4262
75°	6376	3977	3446
80°	5432	2971	2535
85°	4197	1756	1397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9107 cd/sqm

TEST NUMBER: P1026692

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	1.9
10°-20°	449.6	5.3
20°-30°	663.7	7.8
30°-40°	774.4	9.1
40°-50°	777.7	9.2
50°-60°	682.7	8.1
60°-70°	508.5	6.0
70°-80°	290.4	3.4
80°-90°	85.8	1.0
90°-100°	45.0	0.5
100°-110°	299.2	3.5
110°-120°	538.9	6.4
120°-130°	691.7	8.2
130°-140°	744.0	8.8
140°-150°	698.2	8.2
150°-160°	564.8	6.7
160°-170°	365.3	4.3
170°-180°	126.0	1.5
0°-30°	1272.4	15.0
0°-40°	2046.8	24.2
0°-60°	3507.2	41.4
0°-90°	4391.9	51.9
90°-120°	883.1	10.4
90°-150°	3017.0	35.6
90°-180°	4073.0	48.1
0°-180°	8465.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1687	1687	1687	1687	1687	
5°	1684	1681	1668	1680	1679	160
15°	1605	1601	1587	1593	1593	453
25°	1457	1450	1433	1436	1432	670
35°	1258	1253	1234	1228	1217	787
45°	1030	1025	1009	993	989	794
55°	785	781	762	750	741	700
65°	530	527	512	500	495	525
75°	282	279	272	268	263	300
85°	73	75	75	73	71	80
90°	1	9	16	21	24	8
95°	56	53	16	21	21	69
105°	289	293	293	293	292	306
115°	543	548	548	544	539	538
125°	772	778	778	774	772	689
135°	962	968	966	964	958	742
145°	1116	1118	1118	1119	1113	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026692

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1686.7	1686.7	1686.7	1686.7	1686.7
2.5°	1692.0	1688.0	1674.7	1688.0	1686.7
5°	1684.0	1681.3	1668.0	1680.0	1678.7
7.5°	1672.0	1669.3	1654.6	1666.7	1665.3
10°	1654.6	1652.0	1637.3	1648.0	1646.6
12.5°	1633.3	1628.0	1614.6	1622.6	1622.6
15°	1605.3	1601.3	1586.6	1593.3	1593.3
17.5°	1575.9	1569.2	1554.6	1562.6	1555.9
20°	1537.2	1534.6	1517.2	1526.5	1519.9
22.5°	1498.5	1493.2	1477.2	1482.5	1478.5
25°	1457.2	1450.5	1433.1	1435.8	1431.8
27.5°	1409.1	1405.1	1387.8	1389.1	1385.1
30°	1362.4	1358.4	1338.4	1335.7	1331.7
32.5°	1311.7	1305.0	1287.7	1282.4	1274.3
35°	1258.3	1253.0	1234.3	1227.6	1217.0
37.5°	1203.6	1197.0	1179.6	1170.3	1163.6
40°	1147.6	1140.9	1122.2	1110.2	1106.2
42.5°	1087.5	1082.2	1063.5	1052.8	1046.2
45°	1030.2	1024.8	1008.8	992.8	988.8
47.5°	967.4	968.8	948.8	932.7	923.4
50°	907.4	903.4	887.4	870.0	860.7
52.5°	846.0	843.3	826.0	811.3	800.6
55°	784.6	780.6	761.9	749.9	740.6
57.5°	719.2	717.9	701.9	685.9	681.9
60°	657.9	652.5	637.8	624.5	615.2
62.5°	593.8	589.8	577.8	563.1	556.4
65°	529.8	527.1	512.4	500.4	495.1
67.5°	467.0	461.7	451.0	440.4	437.7
70°	408.3	401.7	389.6	381.6	376.3
72.5°	344.3	340.3	333.6	324.3	318.9
75°	281.6	278.9	272.2	268.2	262.9
77.5°	222.8	221.5	217.5	214.8	210.8
80°	168.1	168.1	165.5	164.1	161.5
82.5°	120.1	117.4	117.4	114.8	114.8
85°	73.4	74.7	74.7	73.4	70.7
87.5°	36.0	36.0	34.7	34.7	32.0
90°	1.0	8.8	15.7	20.6	23.6
92.5°	18.7	9.8	15.7	20.6	21.6
95°	56.0	53.1	15.7	20.6	20.6
97.5°	105.2	111.1	17.7	19.7	20.6
100°	164.1	167.1	171.0	24.6	20.6
102.5°	224.1	228.0	230.0	232.0	149.4
105°	289.0	292.9	292.9	292.9	291.9
107.5°	355.8	355.8	357.8	358.8	354.8
110°	420.7	420.7	422.7	419.7	420.7

TEST NUMBER: P1026692

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	481.6	484.6	485.6	481.6	479.7
115°	542.6	547.5	548.5	544.5	538.6
117.5°	606.5	606.5	610.4	604.5	602.5
120°	665.4	664.4	667.4	665.4	660.5
122.5°	717.5	722.4	723.4	721.5	715.6
125°	771.6	778.5	778.5	774.5	771.6
127.5°	823.7	828.6	827.6	825.6	817.8
130°	870.9	875.8	876.8	873.8	868.9
132.5°	918.0	923.9	921.0	921.0	916.1
135°	962.3	968.2	966.2	964.2	958.3
137.5°	1003.6	1009.5	1007.5	1007.5	1002.6
140°	1043.9	1045.8	1044.8	1046.8	1040.9
142.5°	1080.2	1081.2	1083.2	1083.2	1077.3
145°	1115.6	1117.6	1117.6	1118.6	1112.7
147.5°	1147.1	1147.1	1148.0	1149.0	1142.1
150°	1176.5	1174.6	1176.5	1178.5	1170.6
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)