

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026420

Luminaire Tested: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026420
REPORT IS A COMBINATION OF REPORTS P999480 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6654.6 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026420

CATALOG NUMBER: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026420

CATALOG NUMBER: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18
7	56	44	37	31	51	41	34	29	33	28	25	26	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1026420

CATALOG NUMBER: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.4
10°-20°	265.4	4.0
20°-30°	383.2	5.8
30°-40°	434.3	6.5
40°-50°	419.3	6.3
50°-60°	348.6	5.2
60°-70°	240.6	3.6
70°-80°	121.6	1.8
80°-90°	33.2	0.5
90°-100°	439.0	6.6
100°-110°	893.0	13.4
110°-120°	795.9	12.0
120°-130°	668.6	10.0
130°-140°	557.9	8.4
140°-150°	426.1	6.4
150°-160°	299.5	4.5
160°-170°	176.2	2.6
170°-180°	57.3	0.9
0°-30°	743.8	11.2
0°-40°	1178.0	17.7
0°-60°	1945.9	29.2
0°-90°	2341.3	35.2
90°-120°	2127.9	32.0
90°-150°	3780.4	56.8
90°-180°	4313.0	64.8
0°-180°	6654.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	1	9	21	23	24	5
95°	38	121	946	469	283	42
105°	136	197	762	1640	1634	145
115°	239	300	679	1305	1569	237
125°	333	396	676	1111	1252	297
135°	396	471	670	986	1119	306
145°	456	523	666	831	914	286
155°	519	560	648	734	765	239
165°	566	583	621	658	668	160
175°	590	591	596	604	602	56
180°	591	591	591	591	591	

TEST NUMBER: P1026420

CATALOG NUMBER: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	1.2	9.3	20.9	23.2	24.4
92.5°	16.3	89.4	455.2	150.4	105.7
95°	38.3	120.8	946.4	468.6	283.3
97.5°	63.9	133.5	1012.5	956.8	680.4
100°	88.2	151.0	933.6	1323.8	1064.8
102.5°	111.5	171.9	834.9	1553.6	1399.2
105°	135.9	196.8	761.7	1640.2	1633.8
107.5°	162.6	222.4	714.1	1614.0	1745.2
110°	189.3	247.9	692.1	1521.2	1747.6

TEST NUMBER: P1026420

CATALOG NUMBER: S124RDIP-B575D1205UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.8	273.5	681.6	1407.4	1679.1
115°	239.2	300.2	679.3	1305.2	1568.7
117.5°	264.7	325.2	678.1	1225.0	1460.8
120°	290.3	349.6	678.1	1171.0	1372.5
122.5°	313.5	373.3	677.0	1135.6	1302.8
125°	333.3	396.0	675.8	1110.6	1251.7
127.5°	351.8	416.8	673.5	1086.8	1219.2
130°	366.9	437.2	672.3	1058.4	1191.4
132.5°	382.0	454.6	671.2	1024.8	1160.0
135°	396.0	471.4	670.0	985.8	1119.4
137.5°	409.9	486.0	670.0	944.0	1071.8
140°	425.0	499.3	668.8	903.4	1019.5
142.5°	441.2	511.5	668.8	865.6	963.8
145°	456.3	522.6	666.5	831.4	913.8
147.5°	473.8	533.0	663.0	803.0	867.4
150°	490.0	542.8	659.5	776.8	829.1
152.5°	505.1	552.2	653.7	754.8	794.2
155°	519.0	560.3	647.9	733.8	765.2
157.5°	533.0	567.8	642.1	714.1	738.5
160°	545.8	574.2	635.2	694.4	714.1
162.5°	557.4	579.4	628.2	675.2	690.9
165°	565.5	582.9	621.2	657.8	667.7
167.5°	574.8	585.8	614.3	642.8	649.1
170°	580.6	588.2	607.3	627.6	631.7
172.5°	586.4	589.8	600.3	614.2	614.3
175°	589.9	591.0	595.7	603.8	601.5
177.5°	592.2	591.0	592.2	596.2	592.2
180°	591.0	591.0	591.0	591.0	591.0

(END OF REPORT)