

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026697

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026697
REPORT IS A COMBINATION OF REPORTS P1001291 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9223.1 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	38	34	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	26	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10077	11423	10086	8666
10°	10016	13020	9998	7439
15°	9943	14117	9881	6722
20°	9817	15470	9727	6136
25°	9706	17726	9528	5790
30°	9545	18701	9380	5476
35°	9292	14991	9097	5224
40°	8897	10361	8765	4957
45°	8397	7714	8303	4736
50°	7826	6351	7697	4558
55°	7209	5416	7152	4404
60°	6604	4636	6489	4285
65°	5951	4003	5855	4111
70°	5262	3324	5192	3807
75°	4531	2570	4472	3306
80°	3577	1738	3448	2430
85°	2287	869	2213	1239

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15381 cd/sqm

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	1.6
10°-20°	450.6	4.9
20°-30°	731.9	7.9
30°-40°	894.4	9.7
40°-50°	811.3	8.8
50°-60°	646.2	7.0
60°-70°	450.1	4.9
70°-80°	239.8	2.6
80°-90°	61.8	0.7
90°-100°	52.9	0.6
100°-110°	351.6	3.8
110°-120°	633.2	6.9
120°-130°	812.7	8.8
130°-140°	874.1	9.5
140°-150°	820.4	8.9
150°-160°	663.6	7.2
160°-170°	429.2	4.7
170°-180°	148.0	1.6
0°-30°	1333.7	14.5
0°-40°	2228.1	24.2
0°-60°	3685.7	40.0
0°-90°	4437.3	48.1
90°-120°	1037.7	11.3
90°-150°	3545.0	38.4
90°-180°	4786.0	51.9
0°-180°	9223.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1570	1813	1572	1376	1570	149
15°	1509	2264	1500	1078	1509	426
25°	1389	2786	1364	910	1389	640
35°	1209	2236	1183	779	1209	755
45°	950	1054	939	647	950	732
55°	668	650	663	528	668	598
65°	414	399	407	410	414	410
75°	200	196	198	252	200	213
85°	40	44	39	63	40	48
90°	1	28	1	28	1	6
95°	66	24	66	24	66	81
105°	340	343	340	343	340	360
115°	638	633	638	633	638	632
125°	907	907	907	907	907	810
135°	1131	1126	1131	1126	1131	872
145°	1311	1307	1311	1307	1311	820
155°	1444	1433	1444	1433	1444	665
165°	1523	1515	1523	1515	1523	430
175°	1558	1551	1558	1551	1558	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1574.3	1583.7	1594.3	1602.3	1615.7	1619.7	1626.4	1630.4	1634.4	1638.4	1641.0
5°	1570.3	1593.0	1613.0	1627.7	1653.0	1662.4	1674.4	1689.1	1706.4	1721.1	1730.4
7.5°	1559.7	1595.7	1622.4	1651.7	1686.4	1709.1	1721.1	1751.8	1779.8	1801.1	1829.2
10°	1546.3	1589.0	1630.4	1674.4	1723.8	1749.1	1773.1	1815.8	1854.5	1889.2	1917.2
12.5°	1531.6	1583.7	1633.0	1690.4	1757.1	1787.8	1803.8	1877.2	1925.2	1943.9	1998.6
15°	1509.0	1570.3	1641.0	1711.7	1767.8	1803.8	1847.8	1906.5	1954.6	1995.9	2040.0
17.5°	1487.6	1554.3	1626.4	1705.1	1786.5	1833.2	1866.5	1918.5	1970.6	2023.9	2065.3
20°	1452.9	1539.6	1613.0	1697.1	1793.1	1826.5	1861.2	1922.5	1978.6	2036.0	2088.0
22.5°	1424.9	1507.6	1607.7	1687.7	1769.1	1802.5	1845.2	1909.2	1975.9	2041.3	2117.3
25°	1388.9	1480.9	1567.7	1653.0	1737.1	1773.1	1811.8	1894.5	1963.9	2048.0	2132.0
27.5°	1350.2	1444.9	1531.6	1609.0	1687.7	1737.1	1778.5	1865.2	1957.2	2049.3	2158.7
30°	1308.8	1398.2	1480.9	1557.0	1643.7	1694.4	1735.8	1837.2	1939.9	2057.3	2188.1
32.5°	1264.8	1348.9	1419.6	1496.9	1589.0	1635.7	1691.7	1802.5	1923.9	2064.0	2228.1
35°	1208.8	1288.8	1351.5	1430.2	1522.3	1582.3	1641.0	1765.1	1906.5	2062.6	2250.8
37.5°	1152.7	1215.4	1275.5	1359.5	1466.3	1521.0	1582.3	1718.4	1879.9	2058.6	2260.1
40°	1086.0	1147.4	1199.4	1284.8	1396.9	1459.6	1523.6	1666.4	1849.2	2044.0	2226.7
42.5°	1019.3	1071.3	1128.7	1218.1	1326.2	1392.9	1460.9	1619.7	1809.1	2001.3	2134.7
45°	949.9	990.0	1052.7	1134.1	1248.8	1312.8	1390.2	1562.3	1753.1	1923.9	1990.6
47.5°	877.9	917.9	976.6	1055.3	1168.7	1244.8	1318.2	1490.3	1682.4	1814.5	1814.5
50°	808.5	840.5	897.9	976.6	1091.4	1160.7	1235.4	1418.2	1573.0	1670.4	1583.7
52.5°	733.8	769.8	817.9	900.6	1014.0	1076.7	1158.1	1314.2	1460.9	1500.9	1367.5
55°	668.4	697.8	743.1	821.9	927.3	992.6	1062.0	1211.4	1335.5	1332.8	1190.1
57.5°	600.4	624.4	672.4	744.5	841.9	900.6	969.9	1099.4	1200.8	1164.7	1030.0
60°	537.7	555.0	601.7	660.4	753.8	808.5	875.2	980.6	1058.0	1007.3	871.2
62.5°	472.3	492.3	529.7	587.0	669.8	713.8	763.1	869.9	919.2	873.9	735.1
65°	413.6	429.6	463.0	511.0	585.7	625.7	668.4	756.5	803.2	737.8	623.1
67.5°	354.9	373.6	397.6	440.3	499.0	536.3	573.7	649.7	671.1	612.4	516.3
70°	300.2	316.2	338.9	369.6	418.9	452.3	480.3	543.0	557.7	503.0	426.9
72.5°	246.8	257.5	276.2	301.5	346.9	365.6	394.9	437.6	456.3	406.9	352.2
75°	200.1	208.1	220.1	238.8	269.5	289.5	313.5	353.6	352.2	317.5	278.8
77.5°	154.8	156.1	169.4	186.8	205.5	222.8	234.8	262.8	265.5	244.2	212.1
80°	110.7	114.7	120.1	133.4	149.4	156.1	170.8	188.1	190.8	174.8	153.4
82.5°	70.7	73.4	77.4	85.4	96.1	104.1	112.1	118.7	125.4	116.1	98.7
85°	40.0	41.4	45.4	48.0	53.4	57.4	64.0	70.7	69.4	62.7	57.4
87.5°	20.0	20.0	20.0	22.7	25.3	25.3	28.0	29.4	30.7	28.0	25.3
90°	1.2	3.2	5.3	7.3	9.4	10.4	11.3	13.1	14.9	16.7	18.5
92.5°	21.9	19.6	17.3	15.0	12.7	11.5	12.3	13.8	15.4	16.9	18.5
95°	65.8	65.0	64.3	63.5	62.8	62.4	57.5	47.8	38.0	28.3	18.5
97.5°	123.6	125.1	126.7	128.2	129.7	130.5	118.3	93.9	69.6	45.2	20.8
100°	192.9	193.7	194.4	195.2	195.9	196.3	196.8	197.9	198.9	200.0	201.0
102.5°	263.3	264.3	265.3	266.4	267.4	267.9	268.2	268.7	269.2	269.7	270.2
105°	339.5	340.5	341.6	342.6	343.7	344.2	344.2	344.2	344.2	344.2	344.2
107.5°	418.1	418.1	418.1	418.1	418.1	418.1	418.4	418.9	419.4	419.9	420.4
110°	494.3	494.3	494.3	494.3	494.3	494.3	494.6	495.1	495.6	496.1	496.6

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	565.9	566.7	567.5	568.2	569.0	569.4	569.5	569.8	570.0	570.3	570.5
115°	637.5	638.8	640.1	641.4	642.7	643.3	643.4	643.7	643.9	644.2	644.4
117.5°	712.6	712.6	712.6	712.6	712.6	712.6	713.1	714.1	715.2	716.2	717.2
120°	781.9	781.6	781.4	781.1	780.8	780.7	781.1	781.9	782.6	783.4	784.2
122.5°	843.1	844.4	845.6	846.9	848.2	848.8	848.9	849.2	849.5	849.7	850.0
125°	906.6	908.4	910.2	912.0	913.8	914.7	914.7	914.7	914.7	914.7	914.7
127.5°	967.8	969.1	970.4	971.7	973.0	973.6	973.5	973.2	972.9	972.7	972.4
130°	1023.2	1024.5	1025.8	1027.1	1028.4	1029.0	1029.1	1029.4	1029.7	1029.9	1030.2
132.5°	1078.7	1080.2	1081.8	1083.3	1084.8	1085.6	1085.2	1084.4	1083.7	1082.9	1082.1
135°	1130.6	1132.2	1133.7	1135.3	1136.8	1137.6	1137.3	1136.8	1136.3	1135.8	1135.3
137.5°	1179.1	1180.7	1182.2	1183.8	1185.3	1186.1	1185.8	1185.3	1184.8	1184.3	1183.8
140°	1226.5	1227.0	1227.5	1228.0	1228.5	1228.8	1228.7	1228.4	1228.1	1227.9	1227.6
142.5°	1269.2	1269.5	1269.7	1270.0	1270.3	1270.4	1270.7	1271.2	1271.7	1272.2	1272.7
145°	1310.8	1311.3	1311.8	1312.3	1312.8	1313.1	1313.1	1313.1	1313.1	1313.1	1313.1
147.5°	1347.8	1347.8	1347.8	1347.8	1347.8	1347.8	1347.9	1348.2	1348.4	1348.7	1348.9
150°	1382.4	1381.9	1381.4	1380.9	1380.4	1380.1	1380.4	1380.9	1381.4	1381.9	1382.4
152.5°	1415.9	1414.6	1413.3	1412.0	1410.7	1410.1	1410.4	1410.9	1411.4	1411.9	1412.4
155°	1443.6	1442.1	1440.5	1439.0	1437.5	1436.7	1437.0	1437.5	1438.0	1438.5	1439.0
157.5°	1465.6	1464.8	1464.0	1463.3	1462.5	1462.1	1462.1	1462.1	1462.1	1462.1	1462.1
160°	1488.7	1487.1	1485.6	1484.0	1482.5	1481.7	1481.8	1482.1	1482.4	1482.6	1482.9
162.5°	1507.1	1505.6	1504.0	1502.5	1501.0	1500.2	1500.3	1500.6	1500.9	1501.1	1501.4
165°	1523.3	1521.8	1520.2	1518.7	1517.2	1516.4	1516.5	1516.8	1517.0	1517.3	1517.5
167.5°	1536.0	1534.5	1532.9	1531.4	1529.9	1529.1	1529.2	1529.5	1529.7	1530.0	1530.2
170°	1546.4	1544.6	1542.8	1541.0	1539.2	1538.3	1538.4	1538.7	1539.0	1539.2	1539.5
172.5°	1553.3	1551.5	1549.7	1547.9	1546.1	1545.2	1545.5	1546.0	1546.5	1547.1	1547.6
175°	1557.9	1556.4	1554.8	1553.3	1551.8	1551.0	1551.1	1551.4	1551.7	1551.9	1552.2
177.5°	1561.4	1559.9	1558.3	1556.8	1555.3	1554.5	1554.6	1554.9	1555.1	1555.4	1555.6
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1643.7	1653.0	1661.1	1667.7	1673.1	1681.1	1675.7	1677.1	1679.7	1685.1	1685.1
5°	1750.4	1765.1	1773.1	1799.8	1806.5	1805.1	1801.1	1822.5	1821.2	1813.1	1811.8
7.5°	1854.5	1879.9	1902.5	1923.9	1930.6	1947.9	1951.9	1961.2	1958.6	1971.9	1965.2
10°	1949.2	1989.3	2010.6	2042.6	2050.6	2058.6	2069.3	2074.6	2086.7	2085.3	2085.3
12.5°	2022.6	2070.6	2098.7	2106.7	2137.4	2146.7	2156.0	2173.4	2169.4	2170.7	2178.7
15°	2080.0	2126.7	2150.7	2188.1	2209.4	2220.1	2236.1	2254.8	2252.1	2264.1	2261.4
17.5°	2122.7	2166.7	2210.7	2266.8	2268.1	2296.1	2333.5	2341.5	2358.8	2346.8	2346.8
20°	2157.4	2216.1	2278.8	2350.8	2358.8	2376.2	2421.5	2452.2	2472.2	2465.6	2469.6
22.5°	2194.7	2278.8	2352.2	2424.2	2462.9	2493.6	2537.6	2585.6	2603.0	2613.7	2611.0
25°	2242.8	2330.8	2438.9	2538.9	2579.0	2637.7	2696.4	2743.1	2756.4	2785.8	2759.1
27.5°	2292.1	2416.2	2550.9	2668.4	2719.1	2767.1	2837.8	2872.5	2889.8	2903.2	2893.8
30°	2333.5	2504.3	2651.0	2759.1	2795.1	2823.1	2863.1	2871.1	2864.5	2875.2	2888.5
32.5°	2397.5	2564.3	2688.4	2740.4	2736.4	2735.1	2704.4	2661.7	2652.3	2627.0	2661.7
35°	2432.2	2565.6	2613.7	2544.3	2516.3	2465.6	2368.2	2304.1	2248.1	2236.1	2238.7
37.5°	2412.2	2464.2	2406.9	2224.1	2178.7	2101.3	1971.9	1881.2	1839.8	1807.8	1849.2
40°	2304.1	2246.8	2089.3	1866.5	1801.1	1727.8	1606.3	1557.0	1498.3	1486.3	1541.0
42.5°	2125.3	1950.6	1727.8	1555.7	1487.6	1446.2	1344.9	1298.2	1256.8	1238.1	1268.8
45°	1882.5	1670.4	1446.2	1304.8	1247.5	1198.1	1138.1	1088.7	1062.0	1054.0	1079.3
47.5°	1631.7	1407.6	1228.8	1123.4	1063.3	1026.0	969.9	941.9	920.6	923.3	927.3
50°	1391.5	1187.4	1050.0	944.6	915.2	885.9	848.5	824.5	813.8	817.9	815.2
52.5°	1184.7	1019.3	903.2	821.9	808.5	780.5	749.8	729.8	725.8	727.1	731.1
55°	1003.3	873.9	781.8	723.1	708.4	688.4	669.8	656.4	645.7	649.7	648.4
57.5°	865.9	752.5	681.8	633.7	623.1	611.1	593.7	587.0	583.0	575.0	581.7
60°	744.5	652.4	591.0	561.7	552.3	544.3	525.7	517.7	515.0	511.0	521.7
62.5°	629.7	564.4	517.7	491.0	481.6	473.6	464.3	457.6	459.0	453.6	459.0
65°	539.0	485.6	452.3	428.3	416.3	410.9	409.6	398.9	397.6	398.9	400.3
67.5°	455.0	409.6	384.2	369.6	360.2	354.9	350.9	344.2	349.6	345.6	348.2
70°	378.9	348.2	321.5	306.9	302.9	304.2	297.5	294.9	296.2	293.5	296.2
72.5°	305.5	280.2	269.5	258.8	253.5	252.2	248.2	244.2	248.2	246.8	246.8
75°	244.2	225.5	213.5	206.8	206.8	204.1	197.5	197.5	197.5	196.1	197.5
77.5°	188.1	172.1	166.8	160.1	160.1	156.1	154.8	154.8	152.1	156.1	153.4
80°	140.1	128.1	120.1	116.1	116.1	114.7	112.1	110.7	112.1	110.7	110.7
82.5°	90.7	85.4	81.4	77.4	76.0	77.4	76.0	73.4	74.7	73.4	76.0
85°	52.0	46.7	46.7	44.0	45.4	42.7	44.0	41.4	40.0	44.0	41.4
87.5°	22.7	21.3	21.3	18.7	18.7	18.7	17.3	18.7	17.3	16.0	17.3
90°	19.8	21.1	22.4	23.7	24.3	24.7	25.4	26.2	26.9	27.7	26.9
92.5°	19.8	21.1	22.4	23.7	24.3	24.4	24.7	24.9	25.2	25.4	25.2
95°	19.8	21.1	22.4	23.7	24.3	24.3	24.3	24.3	24.3	24.3	24.3
97.5°	21.3	21.8	22.3	22.8	23.1	23.2	23.5	23.8	24.0	24.3	24.0
100°	162.8	124.5	86.3	48.0	28.9	28.4	27.4	26.3	25.3	24.3	25.3
102.5°	270.7	271.3	271.8	272.3	272.6	261.8	240.2	218.7	197.1	175.5	197.1
105°	344.2	344.2	344.2	344.2	344.2	344.1	343.8	343.5	343.3	343.0	343.3
107.5°	420.6	420.9	421.1	421.4	421.5	421.0	420.0	418.9	417.9	416.9	417.9
110°	495.8	495.0	494.3	493.5	493.1	493.2	493.5	493.8	494.0	494.3	494.0

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	569.5	568.5	567.4	566.4	565.9	565.6	565.1	564.6	564.1	563.6	564.1
115°	643.4	642.4	641.3	640.3	639.8	639.0	637.5	636.0	634.4	632.9	634.4
117.5°	715.7	714.1	712.6	711.1	710.3	710.0	709.5	709.0	708.4	707.9	708.4
120°	783.7	783.2	782.7	782.2	781.9	781.3	780.0	778.7	777.4	776.1	777.4
122.5°	849.5	849.0	848.5	848.0	847.7	846.9	845.4	843.9	842.3	840.8	842.3
125°	913.7	912.7	911.6	910.6	910.1	909.7	908.9	908.2	907.4	906.6	907.4
127.5°	971.9	971.4	970.9	970.4	970.1	969.1	967.0	965.0	962.9	960.9	962.9
130°	1029.4	1028.6	1027.9	1027.1	1026.7	1026.1	1024.8	1023.5	1022.2	1020.9	1022.2
132.5°	1082.1	1082.1	1082.1	1082.1	1082.1	1081.5	1080.2	1078.9	1077.7	1076.4	1077.7
135°	1134.8	1134.2	1133.7	1133.2	1132.9	1132.1	1130.6	1129.1	1127.5	1126.0	1127.5
137.5°	1183.8	1183.8	1183.8	1183.8	1183.8	1183.2	1181.9	1180.6	1179.3	1178.0	1179.3
140°	1228.1	1228.7	1229.2	1229.7	1230.0	1229.2	1227.7	1226.1	1224.6	1223.0	1224.6
142.5°	1272.7	1272.7	1272.7	1272.7	1272.7	1271.9	1270.4	1268.9	1267.3	1265.8	1267.3
145°	1313.4	1313.6	1313.9	1314.2	1314.3	1313.5	1312.0	1310.4	1308.9	1307.3	1308.9
147.5°	1349.2	1349.4	1349.7	1350.0	1350.1	1349.2	1347.4	1345.6	1343.8	1342.0	1343.8
150°	1382.9	1383.4	1383.9	1384.4	1384.7	1383.7	1381.6	1379.6	1377.5	1375.5	1377.5
152.5°	1412.9	1413.4	1413.9	1414.4	1414.7	1413.8	1412.0	1410.3	1408.5	1406.7	1408.5
155°	1439.8	1440.6	1441.3	1442.1	1442.5	1441.5	1439.4	1437.3	1435.3	1433.2	1435.3
157.5°	1462.9	1463.7	1464.4	1465.2	1465.6	1464.6	1462.5	1460.4	1458.4	1456.3	1458.4
160°	1483.9	1484.9	1486.0	1487.0	1487.5	1486.5	1484.4	1482.4	1480.3	1478.3	1480.3
162.5°	1502.9	1504.5	1506.0	1507.5	1508.3	1507.1	1504.8	1502.5	1500.2	1497.9	1500.2
165°	1519.1	1520.6	1522.2	1523.7	1524.5	1523.5	1521.4	1519.3	1517.3	1515.2	1517.3
167.5°	1532.0	1533.8	1535.6	1537.4	1538.3	1537.1	1534.8	1532.5	1530.2	1527.9	1530.2
170°	1541.5	1543.6	1545.6	1547.7	1548.7	1547.5	1545.2	1542.9	1540.6	1538.3	1540.6
172.5°	1549.4	1551.2	1552.9	1554.7	1555.6	1554.4	1552.1	1549.8	1547.5	1545.2	1547.5
175°	1554.2	1556.3	1558.3	1560.4	1561.4	1560.2	1557.9	1555.6	1553.3	1551.0	1553.3
177.5°	1557.4	1559.2	1561.0	1562.8	1563.7	1562.7	1560.6	1558.6	1556.5	1554.5	1556.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1682.4	1673.1	1675.7	1673.1	1666.4	1662.4	1651.7	1638.4	1633.0	1626.4	1622.4
5°	1817.1	1810.5	1809.1	1798.5	1795.8	1779.8	1753.1	1739.8	1723.8	1707.7	1691.7
7.5°	1963.9	1955.9	1929.2	1925.2	1927.9	1907.9	1873.2	1846.5	1813.1	1790.5	1759.8
10°	2085.3	2069.3	2046.6	2048.0	2038.6	2011.9	1977.3	1949.2	1901.2	1871.9	1827.8
12.5°	2158.7	2145.4	2142.7	2129.3	2121.3	2086.7	2045.3	2009.3	1973.2	1933.2	1899.9
15°	2248.1	2230.7	2218.7	2200.1	2194.7	2158.7	2113.3	2072.0	2030.6	1993.3	1922.5
17.5°	2346.8	2328.1	2282.8	2278.8	2246.8	2212.1	2168.0	2106.7	2062.6	2009.3	1957.2
20°	2458.9	2432.2	2373.5	2358.8	2333.5	2276.1	2216.1	2148.0	2077.3	2022.6	1961.2
22.5°	2584.3	2537.6	2494.9	2448.2	2429.5	2358.8	2276.1	2193.4	2108.0	2033.3	1959.9
25°	2747.1	2685.7	2625.7	2579.0	2546.9	2454.9	2344.1	2234.7	2136.0	2038.6	1942.6
27.5°	2875.2	2821.8	2756.4	2695.0	2653.7	2544.3	2417.5	2276.1	2153.4	2034.6	1931.9
30°	2884.5	2868.5	2828.5	2795.1	2749.7	2632.3	2492.2	2332.1	2180.0	2036.0	1910.5
32.5°	2709.7	2741.7	2759.1	2764.4	2755.1	2687.0	2559.0	2382.8	2204.1	2023.9	1891.9
35°	2333.5	2418.9	2524.3	2564.3	2603.0	2639.0	2572.3	2418.9	2212.1	2021.3	1862.5
37.5°	1921.2	1998.6	2173.4	2253.4	2298.8	2441.5	2496.2	2413.5	2228.1	2023.9	1834.5
40°	1550.3	1673.1	1798.5	1906.5	1977.3	2137.4	2306.8	2325.5	2205.4	1998.6	1798.5
42.5°	1304.8	1376.9	1471.6	1571.7	1634.4	1823.8	2053.3	2188.1	2134.7	1957.2	1754.4
45°	1111.4	1164.7	1254.1	1287.5	1367.5	1549.0	1791.8	1986.6	2013.3	1891.9	1703.7
47.5°	953.9	999.3	1056.7	1098.0	1162.1	1298.2	1503.6	1718.4	1846.5	1802.5	1633.0
50°	840.5	877.9	925.9	949.9	991.3	1114.0	1268.8	1482.3	1654.4	1669.1	1541.0
52.5°	745.8	767.2	804.5	831.2	864.5	939.3	1079.3	1255.5	1448.9	1529.0	1427.6
55°	663.1	680.4	713.8	731.1	748.5	812.5	921.9	1082.0	1263.5	1368.9	1311.5
57.5°	588.4	603.0	631.1	647.1	656.4	717.8	801.8	927.3	1090.0	1218.1	1186.1
60°	527.0	540.3	556.4	568.4	579.0	629.7	688.4	789.8	935.3	1059.3	1051.3
62.5°	461.6	473.6	491.0	503.0	512.3	544.3	593.7	671.1	795.2	909.9	932.6
65°	404.3	413.6	425.6	430.9	442.9	467.0	507.0	576.4	677.8	780.5	796.5
67.5°	352.2	354.9	362.9	374.9	377.6	398.9	434.9	487.0	565.7	649.7	675.1
70°	296.2	300.2	306.9	316.2	321.5	334.9	365.6	400.3	468.3	541.7	560.4
72.5°	246.8	252.2	254.8	260.2	262.8	284.2	297.5	332.2	378.9	440.3	460.3
75°	200.1	205.5	206.8	209.5	212.1	221.5	240.2	261.5	300.2	340.2	366.9
77.5°	158.8	157.4	160.1	164.1	162.8	170.8	182.8	201.5	226.8	260.2	277.5
80°	112.1	112.1	116.1	120.1	118.7	126.7	130.7	144.1	165.4	186.8	193.5
82.5°	74.7	74.7	78.7	78.7	81.4	82.7	88.1	94.7	112.1	122.7	126.7
85°	42.7	42.7	44.0	44.0	44.0	46.7	50.7	53.4	58.7	65.4	68.0
87.5°	17.3	18.7	18.7	18.7	18.7	21.3	21.3	24.0	25.3	28.0	28.0
90°	26.2	25.4	24.7	24.3	23.7	22.4	21.1	19.8	18.5	16.7	14.9
92.5°	24.9	24.7	24.4	24.3	23.7	22.4	21.1	19.8	18.5	16.9	15.4
95°	24.3	24.3	24.3	24.3	23.7	22.4	21.1	19.8	18.5	28.3	38.0
97.5°	23.8	23.5	23.2	23.1	22.8	22.3	21.8	21.3	20.8	45.2	69.6
100°	26.3	27.4	28.4	28.9	48.0	86.3	124.5	162.8	201.0	200.0	198.9
102.5°	218.7	240.2	261.8	272.6	272.3	271.8	271.3	270.7	270.2	269.7	269.2
105°	343.5	343.8	344.1	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2
107.5°	418.9	420.0	421.0	421.5	421.4	421.1	420.9	420.6	420.4	419.9	419.4
110°	493.8	493.5	493.2	493.1	493.5	494.3	495.0	495.8	496.6	496.1	495.6

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	564.6	565.1	565.6	565.9	566.4	567.4	568.5	569.5	570.5	570.3	570.0
115°	636.0	637.5	639.0	639.8	640.3	641.3	642.4	643.4	644.4	644.2	643.9
117.5°	709.0	709.5	710.0	710.3	711.1	712.6	714.1	715.7	717.2	716.2	715.2
120°	778.7	780.0	781.3	781.9	782.2	782.7	783.2	783.7	784.2	783.4	782.6
122.5°	843.9	845.4	846.9	847.7	848.0	848.5	849.0	849.5	850.0	849.7	849.5
125°	908.2	908.9	909.7	910.1	910.6	911.6	912.7	913.7	914.7	914.7	914.7
127.5°	965.0	967.0	969.1	970.1	970.4	970.9	971.4	971.9	972.4	972.7	972.9
130°	1023.5	1024.8	1026.1	1026.7	1027.1	1027.9	1028.6	1029.4	1030.2	1029.9	1029.7
132.5°	1078.9	1080.2	1081.5	1082.1	1082.1	1082.1	1082.1	1082.1	1082.1	1082.9	1083.7
135°	1129.1	1130.6	1132.1	1132.9	1133.2	1133.7	1134.2	1134.8	1135.3	1135.8	1136.3
137.5°	1180.6	1181.9	1183.2	1183.8	1183.8	1183.8	1183.8	1183.8	1183.8	1184.3	1184.8
140°	1226.1	1227.7	1229.2	1230.0	1229.7	1229.2	1228.7	1228.1	1227.6	1227.9	1228.1
142.5°	1268.9	1270.4	1271.9	1272.7	1272.7	1272.7	1272.7	1272.7	1272.7	1272.2	1271.7
145°	1310.4	1312.0	1313.5	1314.3	1314.2	1313.9	1313.6	1313.4	1313.1	1313.1	1313.1
147.5°	1345.6	1347.4	1349.2	1350.1	1350.0	1349.7	1349.4	1349.2	1348.9	1348.7	1348.4
150°	1379.6	1381.6	1383.7	1384.7	1384.4	1383.9	1383.4	1382.9	1382.4	1381.9	1381.4
152.5°	1410.3	1412.0	1413.8	1414.7	1414.4	1413.9	1413.4	1412.9	1412.4	1411.9	1411.4
155°	1437.3	1439.4	1441.5	1442.5	1442.1	1441.3	1440.6	1439.8	1439.0	1438.5	1438.0
157.5°	1460.4	1462.5	1464.6	1465.6	1465.2	1464.4	1463.7	1462.9	1462.1	1462.1	1462.1
160°	1482.4	1484.4	1486.5	1487.5	1487.0	1486.0	1484.9	1483.9	1482.9	1482.6	1482.4
162.5°	1502.5	1504.8	1507.1	1508.3	1507.5	1506.0	1504.5	1502.9	1501.4	1501.1	1500.9
165°	1519.3	1521.4	1523.5	1524.5	1523.7	1522.2	1520.6	1519.1	1517.5	1517.3	1517.0
167.5°	1532.5	1534.8	1537.1	1538.3	1537.4	1535.6	1533.8	1532.0	1530.2	1530.0	1529.7
170°	1542.9	1545.2	1547.5	1548.7	1547.7	1545.6	1543.6	1541.5	1539.5	1539.2	1539.0
172.5°	1549.8	1552.1	1554.4	1555.6	1554.7	1552.9	1551.2	1549.4	1547.6	1547.1	1546.5
175°	1555.6	1557.9	1560.2	1561.4	1560.4	1558.3	1556.3	1554.2	1552.2	1551.9	1551.7
177.5°	1558.6	1560.6	1562.7	1563.7	1562.8	1561.0	1559.2	1557.4	1555.6	1555.4	1555.1
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1617.0	1610.4	1602.3	1602.3	1593.0	1589.0	1581.0	1578.3	1571.7	1561.0	1553.0
5°	1674.4	1657.0	1646.4	1637.0	1617.0	1602.3	1587.7	1571.7	1555.7	1537.0	1515.6
7.5°	1730.4	1698.4	1683.7	1667.7	1638.4	1607.7	1578.3	1557.0	1535.6	1506.3	1479.6
10°	1789.1	1749.1	1722.4	1701.1	1655.7	1617.0	1574.3	1543.6	1510.3	1472.9	1438.2
12.5°	1838.5	1786.5	1763.8	1723.8	1671.7	1625.0	1571.7	1525.0	1480.9	1436.9	1394.2
15°	1879.9	1830.5	1774.5	1758.4	1686.4	1619.7	1559.7	1499.6	1444.9	1400.9	1351.5
17.5°	1893.2	1830.5	1802.5	1763.8	1678.4	1609.0	1533.0	1467.6	1415.6	1350.2	1311.5
20°	1897.2	1837.2	1798.5	1762.4	1686.4	1594.3	1519.6	1439.6	1376.9	1311.5	1250.1
22.5°	1886.5	1815.8	1778.5	1743.8	1658.4	1579.7	1492.9	1404.9	1331.5	1271.5	1210.1
25°	1866.5	1783.8	1747.8	1710.4	1629.0	1542.3	1447.6	1363.5	1295.5	1223.4	1163.4
27.5°	1839.8	1745.1	1703.7	1665.1	1585.0	1503.6	1414.2	1327.5	1251.5	1175.4	1119.4
30°	1806.5	1697.1	1659.7	1609.0	1531.6	1454.3	1372.9	1286.1	1200.8	1128.7	1067.3
32.5°	1763.8	1649.0	1599.7	1551.6	1467.6	1396.9	1319.5	1238.1	1155.4	1084.7	1020.6
35°	1725.1	1594.3	1539.6	1491.6	1398.2	1323.5	1259.5	1183.4	1110.0	1036.7	979.3
37.5°	1673.1	1539.6	1474.3	1424.9	1330.2	1254.1	1194.1	1135.4	1058.0	987.3	933.9
40°	1618.4	1471.6	1410.2	1360.9	1262.1	1179.4	1122.0	1070.0	1007.3	941.9	885.9
42.5°	1569.0	1406.2	1340.8	1280.8	1180.7	1107.4	1048.7	1008.6	951.3	892.6	841.9
45°	1506.3	1336.8	1266.1	1203.4	1107.4	1027.3	971.3	939.3	896.6	839.2	795.2
47.5°	1442.2	1262.1	1188.8	1127.4	1023.3	952.6	897.9	867.2	837.9	792.5	748.5
50°	1358.2	1183.4	1116.7	1046.0	943.3	871.2	825.9	795.2	772.5	740.5	703.1
52.5°	1266.1	1102.0	1030.0	968.6	867.2	801.8	749.8	732.5	709.8	685.8	653.7
55°	1168.7	1014.0	944.6	884.6	791.2	724.5	681.8	663.1	645.7	627.1	605.7
57.5°	1071.3	921.9	856.5	803.2	716.5	652.4	617.7	592.4	580.4	569.7	552.3
60°	949.9	823.2	772.5	724.5	639.1	580.4	547.0	528.3	517.7	512.3	504.3
62.5°	843.2	739.1	683.1	636.4	568.4	516.3	484.3	469.6	460.3	457.6	448.3
65°	729.8	640.4	596.4	556.4	497.6	451.0	424.3	406.9	400.3	398.9	398.9
67.5°	623.1	551.0	507.0	479.0	428.3	386.9	361.6	354.9	350.9	345.6	344.2
70°	523.0	465.6	426.9	402.9	357.6	326.9	306.9	296.2	296.2	292.2	289.5
72.5°	434.9	377.6	352.2	332.2	294.9	268.2	253.5	250.8	241.5	240.2	240.2
75°	340.2	297.5	280.2	262.8	234.8	216.1	204.1	197.5	192.1	192.1	193.5
77.5°	256.2	226.8	210.8	197.5	177.4	165.4	156.1	153.4	148.1	148.1	148.1
80°	181.4	165.4	153.4	142.8	128.1	117.4	112.1	106.7	106.7	105.4	106.7
82.5°	117.4	104.1	97.4	96.1	82.7	78.7	72.0	73.4	69.4	68.0	70.7
85°	68.0	61.4	53.4	50.7	45.4	40.0	37.4	38.7	37.4	36.0	37.4
87.5°	26.7	22.7	21.3	21.3	17.3	16.0	14.7	16.0	13.3	13.3	14.7
90°	13.1	11.3	10.4	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	13.8	12.3	11.5	12.7	15.0	17.3	19.6	21.9	19.6	17.3	15.0
95°	47.8	57.5	62.4	62.8	63.5	64.3	65.0	65.8	65.0	64.3	63.5
97.5°	93.9	118.3	130.5	129.7	128.2	126.7	125.1	123.6	125.1	126.7	128.2
100°	197.9	196.8	196.3	195.9	195.2	194.4	193.7	192.9	193.7	194.4	195.2
102.5°	268.7	268.2	267.9	267.4	266.4	265.3	264.3	263.3	264.3	265.3	266.4
105°	344.2	344.2	344.2	343.7	342.6	341.6	340.5	339.5	340.5	341.6	342.6
107.5°	418.9	418.4	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1
110°	495.1	494.6	494.3	494.3	494.3	494.3	494.3	494.3	494.3	494.3	494.3

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	569.8	569.5	569.4	569.0	568.2	567.5	566.7	565.9	566.7	567.5	568.2
115°	643.7	643.4	643.3	642.7	641.4	640.1	638.8	637.5	638.8	640.1	641.4
117.5°	714.1	713.1	712.6	712.6	712.6	712.6	712.6	712.6	712.6	712.6	712.6
120°	781.9	781.1	780.7	780.8	781.1	781.4	781.6	781.9	781.6	781.4	781.1
122.5°	849.2	848.9	848.8	848.2	846.9	845.6	844.4	843.1	844.4	845.6	846.9
125°	914.7	914.7	914.7	913.8	912.0	910.2	908.4	906.6	908.4	910.2	912.0
127.5°	973.2	973.5	973.6	973.0	971.7	970.4	969.1	967.8	969.1	970.4	971.7
130°	1029.4	1029.1	1029.0	1028.4	1027.1	1025.8	1024.5	1023.2	1024.5	1025.8	1027.1
132.5°	1084.4	1085.2	1085.6	1084.8	1083.3	1081.8	1080.2	1078.7	1080.2	1081.8	1083.3
135°	1136.8	1137.3	1137.6	1136.8	1135.3	1133.7	1132.2	1130.6	1132.2	1133.7	1135.3
137.5°	1185.3	1185.8	1186.1	1185.3	1183.8	1182.2	1180.7	1179.1	1180.7	1182.2	1183.8
140°	1228.4	1228.7	1228.8	1228.5	1228.0	1227.5	1227.0	1226.5	1227.0	1227.5	1228.0
142.5°	1271.2	1270.7	1270.4	1270.3	1270.0	1269.7	1269.5	1269.2	1269.5	1269.7	1270.0
145°	1313.1	1313.1	1313.1	1312.8	1312.3	1311.8	1311.3	1310.8	1311.3	1311.8	1312.3
147.5°	1348.2	1347.9	1347.8	1347.8	1347.8	1347.8	1347.8	1347.8	1347.8	1347.8	1347.8
150°	1380.9	1380.4	1380.1	1380.4	1380.9	1381.4	1381.9	1382.4	1381.9	1381.4	1380.9
152.5°	1410.9	1410.4	1410.1	1410.7	1412.0	1413.3	1414.6	1415.9	1414.6	1413.3	1412.0
155°	1437.5	1437.0	1436.7	1437.5	1439.0	1440.5	1442.1	1443.6	1442.1	1440.5	1439.0
157.5°	1462.1	1462.1	1462.1	1462.5	1463.3	1464.0	1464.8	1465.6	1464.8	1464.0	1463.3
160°	1482.1	1481.8	1481.7	1482.5	1484.0	1485.6	1487.1	1488.7	1487.1	1485.6	1484.0
162.5°	1500.6	1500.3	1500.2	1501.0	1502.5	1504.0	1505.6	1507.1	1505.6	1504.0	1502.5
165°	1516.8	1516.5	1516.4	1517.2	1518.7	1520.2	1521.8	1523.3	1521.8	1520.2	1518.7
167.5°	1529.5	1529.2	1529.1	1529.9	1531.4	1532.9	1534.5	1536.0	1534.5	1532.9	1531.4
170°	1538.7	1538.4	1538.3	1539.2	1541.0	1542.8	1544.6	1546.4	1544.6	1542.8	1541.0
172.5°	1546.0	1545.5	1545.2	1546.1	1547.9	1549.7	1551.5	1553.3	1551.5	1549.7	1547.9
175°	1551.4	1551.1	1551.0	1551.8	1553.3	1554.8	1556.4	1557.9	1556.4	1554.8	1553.3
177.5°	1554.9	1554.6	1554.5	1555.3	1556.8	1558.3	1559.9	1561.4	1559.9	1558.3	1556.8
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1550.3	1547.6	1541.0	1537.0	1523.6	1507.6	1502.3	1488.9	1494.3	1484.9	1484.9
5°	1509.0	1496.9	1488.9	1476.9	1451.6	1434.2	1415.6	1406.2	1400.9	1394.2	1388.9
7.5°	1455.6	1446.2	1438.2	1415.6	1387.5	1363.5	1340.8	1331.5	1314.2	1302.2	1296.8
10°	1408.9	1395.5	1376.9	1350.2	1320.8	1290.1	1270.1	1250.1	1236.8	1230.1	1215.4
12.5°	1360.9	1344.9	1324.8	1286.1	1254.1	1235.4	1199.4	1180.7	1174.1	1168.7	1151.4
15°	1311.5	1294.2	1270.1	1234.1	1206.1	1162.1	1140.7	1126.0	1110.0	1108.7	1095.4
17.5°	1267.5	1246.1	1226.1	1182.1	1147.4	1108.7	1096.7	1080.7	1066.0	1050.0	1043.3
20°	1211.4	1191.4	1176.7	1128.7	1090.0	1066.0	1046.0	1032.7	1023.3	1007.3	1004.6
22.5°	1160.7	1139.4	1119.4	1083.4	1050.0	1019.3	995.3	980.6	976.6	969.9	957.9
25°	1111.4	1090.0	1066.0	1032.7	998.0	976.6	955.3	945.9	937.9	927.3	917.9
27.5°	1070.0	1050.0	1027.3	986.0	956.6	940.6	917.9	907.2	896.6	891.2	887.2
30°	1020.6	998.0	980.6	948.6	916.6	895.2	879.2	869.9	860.5	855.2	852.5
32.5°	972.6	951.3	939.3	904.6	879.2	853.9	841.9	835.2	829.9	824.5	819.2
35°	933.9	912.6	893.9	861.9	836.5	819.2	809.8	799.2	795.2	789.8	789.8
37.5°	885.9	869.9	851.2	820.5	797.8	784.5	776.5	763.1	761.8	759.1	755.1
40°	844.5	828.5	811.2	784.5	764.5	748.5	737.8	731.1	727.1	724.5	721.8
42.5°	800.5	783.2	775.2	744.5	727.1	711.1	705.8	699.1	697.8	692.4	685.8
45°	757.8	743.1	727.1	704.4	689.8	676.4	668.4	663.1	656.4	655.1	651.1
47.5°	720.5	703.1	688.4	667.1	651.1	640.4	633.7	627.1	621.7	617.7	613.7
50°	672.4	659.1	647.1	624.4	611.1	600.4	591.0	585.7	580.4	580.4	580.4
52.5°	625.7	613.7	603.0	587.0	571.0	561.7	551.0	547.0	544.3	540.3	544.3
55°	580.4	568.4	557.7	545.7	527.0	519.0	508.3	504.3	505.7	505.7	509.7
57.5°	532.3	523.0	516.3	501.7	484.3	476.3	469.6	465.6	465.6	471.0	472.3
60°	485.6	476.3	464.3	451.0	440.3	430.9	426.9	428.3	428.3	430.9	437.6
62.5°	433.6	428.3	421.6	402.9	396.3	389.6	384.2	388.2	386.9	393.6	402.9
65°	385.6	380.2	370.9	361.6	353.6	346.9	345.6	346.9	349.6	356.2	366.9
67.5°	332.2	332.2	324.2	316.2	309.5	302.9	304.2	305.5	308.2	316.2	332.2
70°	288.2	282.8	274.8	269.5	264.2	261.5	258.8	264.2	272.2	277.5	289.5
72.5°	240.2	236.1	229.5	224.1	222.8	220.1	218.8	221.5	229.5	238.8	252.2
75°	189.5	190.8	186.8	182.8	182.8	178.8	181.4	181.4	189.5	198.8	209.5
77.5°	146.8	145.4	144.1	141.4	140.1	140.1	140.1	142.8	150.8	156.1	166.8
80°	104.1	105.4	101.4	102.7	101.4	102.7	102.7	108.1	112.1	118.7	126.7
82.5°	69.4	69.4	66.7	68.0	68.0	68.0	69.4	72.0	77.4	82.7	88.1
85°	38.7	40.0	37.4	40.0	40.0	40.0	41.4	42.7	46.7	48.0	53.4
87.5°	14.7	17.3	17.3	14.7	16.0	17.3	18.7	17.3	20.0	22.7	24.0
90°	9.4	10.4	11.3	13.1	14.9	16.7	18.5	19.8	21.1	22.4	23.7
92.5°	12.7	11.5	12.3	13.8	15.4	16.9	18.5	19.8	21.1	22.4	23.7
95°	62.8	62.4	57.5	47.8	38.0	28.3	18.5	19.8	21.1	22.4	23.7
97.5°	129.7	130.5	118.3	93.9	69.6	45.2	20.8	21.3	21.8	22.3	22.8
100°	195.9	196.3	196.8	197.9	198.9	200.0	201.0	162.8	124.5	86.3	48.0
102.5°	267.4	267.9	268.2	268.7	269.2	269.7	270.2	270.7	271.3	271.8	272.3
105°	343.7	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2
107.5°	418.1	418.1	418.4	418.9	419.4	419.9	420.4	420.6	420.9	421.1	421.4
110°	494.3	494.3	494.6	495.1	495.6	496.1	496.6	495.8	495.0	494.3	493.5

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	569.0	569.4	569.5	569.8	570.0	570.3	570.5	569.5	568.5	567.4	566.4
115°	642.7	643.3	643.4	643.7	643.9	644.2	644.4	643.4	642.4	641.3	640.3
117.5°	712.6	712.6	713.1	714.1	715.2	716.2	717.2	715.7	714.1	712.6	711.1
120°	780.8	780.7	781.1	781.9	782.6	783.4	784.2	783.7	783.2	782.7	782.2
122.5°	848.2	848.8	848.9	849.2	849.5	849.7	850.0	849.5	849.0	848.5	848.0
125°	913.8	914.7	914.7	914.7	914.7	914.7	914.7	913.7	912.7	911.6	910.6
127.5°	973.0	973.6	973.5	973.2	972.9	972.7	972.4	971.9	971.4	970.9	970.4
130°	1028.4	1029.0	1029.1	1029.4	1029.7	1029.9	1030.2	1029.4	1028.6	1027.9	1027.1
132.5°	1084.8	1085.6	1085.2	1084.4	1083.7	1082.9	1082.1	1082.1	1082.1	1082.1	1082.1
135°	1136.8	1137.6	1137.3	1136.8	1136.3	1135.8	1135.3	1134.8	1134.2	1133.7	1133.2
137.5°	1185.3	1186.1	1185.8	1185.3	1184.8	1184.3	1183.8	1183.8	1183.8	1183.8	1183.8
140°	1228.5	1228.8	1228.7	1228.4	1228.1	1227.9	1227.6	1228.1	1228.7	1229.2	1229.7
142.5°	1270.3	1270.4	1270.7	1271.2	1271.7	1272.2	1272.7	1272.7	1272.7	1272.7	1272.7
145°	1312.8	1313.1	1313.1	1313.1	1313.1	1313.1	1313.1	1313.4	1313.6	1313.9	1314.2
147.5°	1347.8	1347.8	1347.9	1348.2	1348.4	1348.7	1348.9	1349.2	1349.4	1349.7	1350.0
150°	1380.4	1380.1	1380.4	1380.9	1381.4	1381.9	1382.4	1382.9	1383.4	1383.9	1384.4
152.5°	1410.7	1410.1	1410.4	1410.9	1411.4	1411.9	1412.4	1412.9	1413.4	1413.9	1414.4
155°	1437.5	1436.7	1437.0	1437.5	1438.0	1438.5	1439.0	1439.8	1440.6	1441.3	1442.1
157.5°	1462.5	1462.1	1462.1	1462.1	1462.1	1462.1	1462.1	1462.9	1463.7	1464.4	1465.2
160°	1482.5	1481.7	1481.8	1482.1	1482.4	1482.6	1482.9	1483.9	1484.9	1486.0	1487.0
162.5°	1501.0	1500.2	1500.3	1500.6	1500.9	1501.1	1501.4	1502.9	1504.5	1506.0	1507.5
165°	1517.2	1516.4	1516.5	1516.8	1517.0	1517.3	1517.5	1519.1	1520.6	1522.2	1523.7
167.5°	1529.9	1529.1	1529.2	1529.5	1529.7	1530.0	1530.2	1532.0	1533.8	1535.6	1537.4
170°	1539.2	1538.3	1538.4	1538.7	1539.0	1539.2	1539.5	1541.5	1543.6	1545.6	1547.7
172.5°	1546.1	1545.2	1545.5	1546.0	1546.5	1547.1	1547.6	1549.4	1551.2	1552.9	1554.7
175°	1551.8	1551.0	1551.1	1551.4	1551.7	1551.9	1552.2	1554.2	1556.3	1558.3	1560.4
177.5°	1555.3	1554.5	1554.6	1554.9	1555.1	1555.4	1555.6	1557.4	1559.2	1561.0	1562.8
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1490.3	1480.9	1479.6	1482.3	1476.9	1484.9	1482.3	1484.9	1478.3	1484.9	1480.9
5°	1387.5	1384.9	1379.5	1372.9	1374.2	1375.5	1382.2	1375.5	1380.9	1382.2	1388.9
7.5°	1291.5	1286.1	1290.1	1287.5	1275.5	1272.8	1275.5	1279.5	1287.5	1292.8	1296.8
10°	1214.1	1211.4	1206.1	1202.1	1195.4	1191.4	1196.8	1191.4	1202.1	1211.4	1211.4
12.5°	1155.4	1144.7	1138.1	1136.7	1122.0	1124.7	1130.0	1134.1	1146.1	1151.4	1151.4
15°	1094.0	1086.0	1083.4	1078.0	1072.7	1078.0	1075.3	1079.3	1084.7	1090.0	1092.7
17.5°	1040.7	1039.3	1040.7	1027.3	1031.3	1024.6	1026.0	1032.7	1028.7	1032.7	1040.7
20°	992.6	995.3	991.3	986.0	986.0	978.0	987.3	984.6	986.0	994.0	1006.0
22.5°	956.6	955.3	951.3	947.3	941.9	943.3	944.6	941.9	952.6	959.3	960.6
25°	917.9	915.2	913.9	909.9	904.6	909.9	908.6	909.9	912.6	923.3	915.2
27.5°	881.9	876.6	879.2	875.2	873.9	875.2	875.2	876.6	879.2	880.6	881.9
30°	851.2	845.9	844.5	841.9	840.5	841.9	844.5	841.9	852.5	851.2	851.2
32.5°	817.9	813.8	811.2	811.2	809.8	808.5	809.8	811.2	819.2	813.8	819.2
35°	785.8	783.2	783.2	780.5	779.2	779.2	779.2	784.5	781.8	785.8	785.8
37.5°	755.1	755.1	753.8	751.1	749.8	751.1	749.8	752.5	751.1	752.5	753.8
40°	723.1	720.5	719.1	719.1	715.1	711.1	715.1	715.1	716.5	720.5	721.8
42.5°	684.4	685.8	685.8	680.4	680.4	680.4	681.8	683.1	683.1	685.8	685.8
45°	651.1	648.4	648.4	648.4	645.7	647.1	649.7	649.7	649.7	649.7	647.1
47.5°	613.7	613.7	615.1	615.1	619.1	617.7	617.7	616.4	613.7	613.7	615.1
50°	579.0	583.0	584.4	584.4	585.7	587.0	587.0	584.4	583.0	579.0	579.0
52.5°	545.7	548.3	551.0	555.0	557.7	556.4	556.4	553.7	548.3	547.0	545.7
55°	509.7	513.7	519.0	523.0	527.0	528.3	528.3	523.0	517.7	511.0	511.0
57.5°	476.3	480.3	489.6	493.6	499.0	499.0	496.3	492.3	484.3	479.0	475.0
60°	442.9	449.6	456.3	464.3	471.0	472.3	468.3	463.0	453.6	446.9	441.6
62.5°	406.9	413.6	426.9	434.9	440.3	440.3	440.3	433.6	421.6	412.3	404.3
65°	372.2	378.9	390.9	401.6	405.6	409.6	405.6	398.9	389.6	378.9	370.9
67.5°	336.2	344.2	356.2	364.2	369.6	373.6	370.9	365.6	353.6	338.9	333.5
70°	296.2	300.2	317.5	325.5	333.5	336.2	333.5	325.5	313.5	297.5	292.2
72.5°	258.8	262.8	278.8	285.5	292.2	294.9	290.9	285.5	274.8	260.2	253.5
75°	216.1	222.8	230.8	241.5	249.5	252.2	248.2	244.2	230.8	221.5	216.1
77.5°	170.8	177.4	188.1	197.5	205.5	204.1	198.8	200.1	185.5	174.8	170.8
80°	129.4	134.8	142.8	150.8	154.8	154.8	153.4	148.1	142.8	134.8	128.1
82.5°	89.4	96.1	102.7	108.1	108.1	109.4	106.7	105.4	100.1	93.4	92.1
85°	53.4	54.7	60.0	60.0	65.4	62.7	61.4	65.4	60.0	56.0	54.7
87.5°	24.0	22.7	24.0	24.0	22.7	25.3	25.3	24.0	25.3	24.0	24.0
90°	24.3	24.7	25.4	26.2	26.9	27.7	26.9	26.2	25.4	24.7	24.3
92.5°	24.3	24.4	24.7	24.9	25.2	25.4	25.2	24.9	24.7	24.4	24.3
95°	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3
97.5°	23.1	23.2	23.5	23.8	24.0	24.3	24.0	23.8	23.5	23.2	23.1
100°	28.9	28.4	27.4	26.3	25.3	24.3	25.3	26.3	27.4	28.4	28.9
102.5°	272.6	261.8	240.2	218.7	197.1	175.5	197.1	218.7	240.2	261.8	272.6
105°	344.2	344.1	343.8	343.5	343.3	343.0	343.3	343.5	343.8	344.1	344.2
107.5°	421.5	421.0	420.0	418.9	417.9	416.9	417.9	418.9	420.0	421.0	421.5
110°	493.1	493.2	493.5	493.8	494.0	494.3	494.0	493.8	493.5	493.2	493.1

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	565.9	565.6	565.1	564.6	564.1	563.6	564.1	564.6	565.1	565.6	565.9
115°	639.8	639.0	637.5	636.0	634.4	632.9	634.4	636.0	637.5	639.0	639.8
117.5°	710.3	710.0	709.5	709.0	708.4	707.9	708.4	709.0	709.5	710.0	710.3
120°	781.9	781.3	780.0	778.7	777.4	776.1	777.4	778.7	780.0	781.3	781.9
122.5°	847.7	846.9	845.4	843.9	842.3	840.8	842.3	843.9	845.4	846.9	847.7
125°	910.1	909.7	908.9	908.2	907.4	906.6	907.4	908.2	908.9	909.7	910.1
127.5°	970.1	969.1	967.0	965.0	962.9	960.9	962.9	965.0	967.0	969.1	970.1
130°	1026.7	1026.1	1024.8	1023.5	1022.2	1020.9	1022.2	1023.5	1024.8	1026.1	1026.7
132.5°	1082.1	1081.5	1080.2	1078.9	1077.7	1076.4	1077.7	1078.9	1080.2	1081.5	1082.1
135°	1132.9	1132.1	1130.6	1129.1	1127.5	1126.0	1127.5	1129.1	1130.6	1132.1	1132.9
137.5°	1183.8	1183.2	1181.9	1180.6	1179.3	1178.0	1179.3	1180.6	1181.9	1183.2	1183.8
140°	1230.0	1229.2	1227.7	1226.1	1224.6	1223.0	1224.6	1226.1	1227.7	1229.2	1230.0
142.5°	1272.7	1271.9	1270.4	1268.9	1267.3	1265.8	1267.3	1268.9	1270.4	1271.9	1272.7
145°	1314.3	1313.5	1312.0	1310.4	1308.9	1307.3	1308.9	1310.4	1312.0	1313.5	1314.3
147.5°	1350.1	1349.2	1347.4	1345.6	1343.8	1342.0	1343.8	1345.6	1347.4	1349.2	1350.1
150°	1384.7	1383.7	1381.6	1379.6	1377.5	1375.5	1377.5	1379.6	1381.6	1383.7	1384.7
152.5°	1414.7	1413.8	1412.0	1410.3	1408.5	1406.7	1408.5	1410.3	1412.0	1413.8	1414.7
155°	1442.5	1441.5	1439.4	1437.3	1435.3	1433.2	1435.3	1437.3	1439.4	1441.5	1442.5
157.5°	1465.6	1464.6	1462.5	1460.4	1458.4	1456.3	1458.4	1460.4	1462.5	1464.6	1465.6
160°	1487.5	1486.5	1484.4	1482.4	1480.3	1478.3	1480.3	1482.4	1484.4	1486.5	1487.5
162.5°	1508.3	1507.1	1504.8	1502.5	1500.2	1497.9	1500.2	1502.5	1504.8	1507.1	1508.3
165°	1524.5	1523.5	1521.4	1519.3	1517.3	1515.2	1517.3	1519.3	1521.4	1523.5	1524.5
167.5°	1538.3	1537.1	1534.8	1532.5	1530.2	1527.9	1530.2	1532.5	1534.8	1537.1	1538.3
170°	1548.7	1547.5	1545.2	1542.9	1540.6	1538.3	1540.6	1542.9	1545.2	1547.5	1548.7
172.5°	1555.6	1554.4	1552.1	1549.8	1547.5	1545.2	1547.5	1549.8	1552.1	1554.4	1555.6
175°	1561.4	1560.2	1557.9	1555.6	1553.3	1551.0	1553.3	1555.6	1557.9	1560.2	1561.4
177.5°	1563.7	1562.7	1560.6	1558.6	1556.5	1554.5	1556.5	1558.6	1560.6	1562.7	1563.7
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1492.9	1484.9	1494.3	1482.3	1484.9	1499.6	1498.3	1511.6	1519.6	1518.3	1525.0
5°	1394.2	1394.2	1398.2	1396.9	1410.2	1422.2	1438.2	1451.6	1466.3	1474.3	1483.6
7.5°	1296.8	1310.2	1312.8	1319.5	1335.5	1355.5	1371.5	1391.5	1412.9	1427.6	1438.2
10°	1216.8	1227.4	1238.1	1243.5	1260.8	1287.5	1310.2	1342.2	1368.9	1384.9	1399.6
12.5°	1146.1	1158.1	1163.4	1187.4	1199.4	1216.8	1248.8	1283.5	1312.8	1330.2	1342.2
15°	1095.4	1102.0	1114.0	1128.7	1140.7	1162.1	1188.8	1227.4	1255.5	1270.1	1311.5
17.5°	1052.7	1060.7	1067.3	1074.0	1092.7	1115.4	1140.7	1174.1	1210.1	1235.4	1256.8
20°	1008.6	1012.6	1020.6	1031.3	1044.7	1066.0	1088.7	1123.4	1155.4	1175.4	1203.4
22.5°	956.6	968.6	976.6	984.6	999.3	1023.3	1044.7	1070.0	1110.0	1132.7	1162.1
25°	925.9	931.3	936.6	945.9	956.6	978.0	1002.0	1028.7	1060.7	1084.7	1110.0
27.5°	885.9	893.9	900.6	912.6	919.2	936.6	959.3	986.0	1024.6	1044.7	1066.0
30°	852.5	860.5	865.9	871.2	880.6	899.2	920.6	941.9	978.0	1003.3	1024.6
32.5°	819.2	827.2	833.9	837.9	847.2	859.2	876.6	903.2	933.9	951.3	979.3
35°	789.8	789.8	797.8	803.2	811.2	821.9	837.9	857.9	889.9	912.6	937.9
37.5°	756.5	757.8	764.5	768.5	776.5	787.2	803.2	821.9	848.5	865.9	891.2
40°	721.8	725.8	728.5	735.1	744.5	748.5	764.5	785.8	812.5	828.5	849.9
42.5°	687.1	689.8	696.4	701.8	709.8	716.5	727.1	747.1	767.2	791.2	808.5
45°	648.4	655.1	659.1	668.4	672.4	679.1	689.8	705.8	729.8	744.5	764.5
47.5°	615.1	617.7	620.4	632.4	640.4	644.4	655.1	664.4	689.8	703.1	721.8
50°	579.0	579.0	583.0	588.4	597.7	605.7	615.1	625.7	645.7	659.1	677.8
52.5°	545.7	541.7	544.3	547.0	556.4	564.4	573.7	588.4	607.1	615.1	631.1
55°	509.7	503.0	507.0	511.0	513.7	524.3	535.0	544.3	559.0	571.0	585.7
57.5°	471.0	469.6	467.0	468.3	475.0	481.6	489.6	501.7	519.0	528.3	536.3
60°	436.3	428.3	425.6	428.3	432.3	436.3	446.9	457.6	472.3	481.6	491.0
62.5°	400.3	392.2	386.9	382.9	386.9	396.3	402.9	410.9	422.9	433.6	441.6
65°	365.6	353.6	348.2	345.6	344.2	350.9	356.2	366.9	377.6	381.6	390.9
67.5°	326.9	316.2	309.5	305.5	305.5	305.5	310.9	321.5	332.2	333.5	342.9
70°	288.2	276.2	269.5	264.2	261.5	264.2	270.8	272.2	281.5	284.2	289.5
72.5°	246.8	236.1	228.1	221.5	222.8	225.5	225.5	228.1	233.5	240.2	240.2
75°	208.1	193.5	189.5	184.1	181.4	181.4	181.4	186.8	190.8	196.1	194.8
77.5°	164.1	156.1	148.1	145.4	141.4	140.1	142.8	142.8	145.4	149.4	150.8
80°	126.7	117.4	112.1	109.4	104.1	102.7	104.1	104.1	108.1	106.7	108.1
82.5°	88.1	81.4	77.4	73.4	70.7	72.0	70.7	70.7	72.0	70.7	70.7
85°	50.7	49.4	46.7	45.4	44.0	41.4	44.0	42.7	41.4	40.0	42.7
87.5°	24.0	22.7	22.7	20.0	20.0	18.7	20.0	20.0	18.7	18.7	18.7
90°	23.7	22.4	21.1	19.8	18.5	16.7	14.9	13.1	11.3	10.4	9.4
92.5°	23.7	22.4	21.1	19.8	18.5	16.9	15.4	13.8	12.3	11.5	12.7
95°	23.7	22.4	21.1	19.8	18.5	28.3	38.0	47.8	57.5	62.4	62.8
97.5°	22.8	22.3	21.8	21.3	20.8	45.2	69.6	93.9	118.3	130.5	129.7
100°	48.0	86.3	124.5	162.8	201.0	200.0	198.9	197.9	196.8	196.3	195.9
102.5°	272.3	271.8	271.3	270.7	270.2	269.7	269.2	268.7	268.2	267.9	267.4
105°	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2	344.2	343.7
107.5°	421.4	421.1	420.9	420.6	420.4	419.9	419.4	418.9	418.4	418.1	418.1
110°	493.5	494.3	495.0	495.8	496.6	496.1	495.6	495.1	494.6	494.3	494.3

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	566.4	567.4	568.5	569.5	570.5	570.3	570.0	569.8	569.5	569.4	569.0
115°	640.3	641.3	642.4	643.4	644.4	644.2	643.9	643.7	643.4	643.3	642.7
117.5°	711.1	712.6	714.1	715.7	717.2	716.2	715.2	714.1	713.1	712.6	712.6
120°	782.2	782.7	783.2	783.7	784.2	783.4	782.6	781.9	781.1	780.7	780.8
122.5°	848.0	848.5	849.0	849.5	850.0	849.7	849.5	849.2	848.9	848.8	848.2
125°	910.6	911.6	912.7	913.7	914.7	914.7	914.7	914.7	914.7	914.7	913.8
127.5°	970.4	970.9	971.4	971.9	972.4	972.7	972.9	973.2	973.5	973.6	973.0
130°	1027.1	1027.9	1028.6	1029.4	1030.2	1029.9	1029.7	1029.4	1029.1	1029.0	1028.4
132.5°	1082.1	1082.1	1082.1	1082.1	1082.1	1082.9	1083.7	1084.4	1085.2	1085.6	1084.8
135°	1133.2	1133.7	1134.2	1134.8	1135.3	1135.8	1136.3	1136.8	1137.3	1137.6	1136.8
137.5°	1183.8	1183.8	1183.8	1183.8	1183.8	1184.3	1184.8	1185.3	1185.8	1186.1	1185.3
140°	1229.7	1229.2	1228.7	1228.1	1227.6	1227.9	1228.1	1228.4	1228.7	1228.8	1228.5
142.5°	1272.7	1272.7	1272.7	1272.7	1272.7	1272.2	1271.7	1271.2	1270.7	1270.4	1270.3
145°	1314.2	1313.9	1313.6	1313.4	1313.1	1313.1	1313.1	1313.1	1313.1	1313.1	1312.8
147.5°	1350.0	1349.7	1349.4	1349.2	1348.9	1348.7	1348.4	1348.2	1347.9	1347.8	1347.8
150°	1384.4	1383.9	1383.4	1382.9	1382.4	1381.9	1381.4	1380.9	1380.4	1380.1	1380.4
152.5°	1414.4	1413.9	1413.4	1412.9	1412.4	1411.9	1411.4	1410.9	1410.4	1410.1	1410.7
155°	1442.1	1441.3	1440.6	1439.8	1439.0	1438.5	1438.0	1437.5	1437.0	1436.7	1437.5
157.5°	1465.2	1464.4	1463.7	1462.9	1462.1	1462.1	1462.1	1462.1	1462.1	1462.1	1462.5
160°	1487.0	1486.0	1484.9	1483.9	1482.9	1482.6	1482.4	1482.1	1481.8	1481.7	1482.5
162.5°	1507.5	1506.0	1504.5	1502.9	1501.4	1501.1	1500.9	1500.6	1500.3	1500.2	1501.0
165°	1523.7	1522.2	1520.6	1519.1	1517.5	1517.3	1517.0	1516.8	1516.5	1516.4	1517.2
167.5°	1537.4	1535.6	1533.8	1532.0	1530.2	1530.0	1529.7	1529.5	1529.2	1529.1	1529.9
170°	1547.7	1545.6	1543.6	1541.5	1539.5	1539.2	1539.0	1538.7	1538.4	1538.3	1539.2
172.5°	1554.7	1552.9	1551.2	1549.4	1547.6	1547.1	1546.5	1546.0	1545.5	1545.2	1546.1
175°	1560.4	1558.3	1556.3	1554.2	1552.2	1551.9	1551.7	1551.4	1551.1	1551.0	1551.8
177.5°	1562.8	1561.0	1559.2	1557.4	1555.6	1555.4	1555.1	1554.9	1554.6	1554.5	1555.3
180°	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9	1557.9

TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1534.3	1547.6	1557.0	1574.3
5°	1499.6	1523.6	1546.3	1570.3
7.5°	1464.9	1492.9	1529.0	1559.7
10°	1426.2	1462.3	1505.0	1546.3
12.5°	1387.5	1430.2	1476.9	1531.6
15°	1340.8	1395.5	1450.3	1509.0
17.5°	1299.5	1355.5	1414.2	1487.6
20°	1252.8	1314.2	1378.2	1452.9
22.5°	1211.4	1279.5	1346.2	1424.9
25°	1164.7	1231.4	1304.8	1388.9
27.5°	1126.0	1187.4	1259.5	1350.2
30°	1079.3	1146.1	1218.1	1308.8
32.5°	1035.3	1099.4	1175.4	1264.8
35°	990.0	1055.3	1123.4	1208.8
37.5°	947.3	1003.3	1071.3	1152.7
40°	899.2	960.6	1022.0	1086.0
42.5°	855.2	911.2	968.6	1019.3
45°	805.8	853.9	908.6	949.9
47.5°	760.5	803.2	845.9	877.9
50°	715.1	748.5	780.5	808.5
52.5°	661.8	699.1	716.5	733.8
55°	613.7	635.1	651.1	668.4
57.5°	567.0	576.4	584.4	600.4
60°	505.7	516.3	525.7	537.7
62.5°	452.3	457.6	460.3	472.3
65°	401.6	400.3	406.9	413.6
67.5°	346.9	345.6	352.2	354.9
70°	293.5	292.2	293.5	300.2
72.5°	242.8	242.8	244.2	246.8
75°	196.1	196.1	197.5	200.1
77.5°	148.1	150.8	149.4	154.8
80°	108.1	105.4	108.1	110.7
82.5°	70.7	73.4	73.4	70.7
85°	40.0	40.0	40.0	40.0
87.5°	17.3	17.3	18.7	20.0
90°	7.3	5.3	3.2	1.2
92.5°	15.0	17.3	19.6	21.9
95°	63.5	64.3	65.0	65.8
97.5°	128.2	126.7	125.1	123.6
100°	195.2	194.4	193.7	192.9
102.5°	266.4	265.3	264.3	263.3
105°	342.6	341.6	340.5	339.5
107.5°	418.1	418.1	418.1	418.1
110°	494.3	494.3	494.3	494.3



TEST NUMBER: P1026697

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	568.2	567.5	566.7	565.9
115°	641.4	640.1	638.8	637.5
117.5°	712.6	712.6	712.6	712.6
120°	781.1	781.4	781.6	781.9
122.5°	846.9	845.6	844.4	843.1
125°	912.0	910.2	908.4	906.6
127.5°	971.7	970.4	969.1	967.8
130°	1027.1	1025.8	1024.5	1023.2
132.5°	1083.3	1081.8	1080.2	1078.7
135°	1135.3	1133.7	1132.2	1130.6
137.5°	1183.8	1182.2	1180.7	1179.1
140°	1228.0	1227.5	1227.0	1226.5
142.5°	1270.0	1269.7	1269.5	1269.2
145°	1312.3	1311.8	1311.3	1310.8
147.5°	1347.8	1347.8	1347.8	1347.8
150°	1380.9	1381.4	1381.9	1382.4
152.5°	1412.0	1413.3	1414.6	1415.9
155°	1439.0	1440.5	1442.1	1443.6
157.5°	1463.3	1464.0	1464.8	1465.6
160°	1484.0	1485.6	1487.1	1488.7
162.5°	1502.5	1504.0	1505.6	1507.1
165°	1518.7	1520.2	1521.8	1523.3
167.5°	1531.4	1532.9	1534.5	1536.0
170°	1541.0	1542.8	1544.6	1546.4
172.5°	1547.9	1549.7	1551.5	1553.3
175°	1553.3	1554.8	1556.4	1557.9
177.5°	1556.8	1558.3	1559.9	1561.4
180°	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)