

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026425

Luminaire Tested: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026425
REPORT IS A COMBINATION OF REPORTS P999485 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6536.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026425

CATALOG NUMBER: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026425

CATALOG NUMBER: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37
2	86	79	73	69	78	72	67	63	58	55	52	46	43	41	34	33	31
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6936 cd/sqm

TEST NUMBER: P1026425

CATALOG NUMBER: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.5
10°-20°	266.5	4.1
20°-30°	384.8	5.9
30°-40°	436.1	6.7
40°-50°	421.1	6.4
50°-60°	350.1	5.4
60°-70°	241.6	3.7
70°-80°	122.1	1.9
80°-90°	34.2	0.5
90°-100°	98.3	1.5
100°-110°	294.4	4.5
110°-120°	500.1	7.7
120°-130°	659.6	10.1
130°-140°	740.8	11.3
140°-150°	728.1	11.1
150°-160°	612.4	9.4
160°-170°	407.5	6.2
170°-180°	142.7	2.2
0°-30°	747.0	11.4
0°-40°	1183.1	18.1
0°-60°	1954.3	29.9
0°-90°	2352.2	36.0
90°-120°	892.8	13.7
90°-150°	3021.3	46.2
90°-180°	4184.0	64.0
0°-180°	6536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	4	16	26	33	35	8
95°	70	80	89	92	92	76
105°	272	273	278	281	284	288
115°	508	508	506	505	504	501
125°	740	740	739	737	735	660
135°	955	962	962	960	956	739
145°	1160	1165	1166	1165	1162	726
155°	1329	1329	1328	1333	1328	612
165°	1447	1444	1441	1448	1444	408
175°	1506	1500	1498	1507	1498	143
180°	1508	1508	1508	1508	1508	

TEST NUMBER: P1026425

CATALOG NUMBER: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	3.5	16.3	25.7	32.7	35.0
92.5°	30.3	45.5	51.3	54.8	56.0
95°	70.0	80.5	88.6	92.1	92.1
97.5°	112.0	121.3	130.6	135.3	135.3
100°	163.3	167.9	178.4	180.8	180.8
102.5°	216.9	218.1	227.4	230.9	232.1
105°	271.7	272.9	277.6	281.0	284.5
107.5°	328.9	330.0	331.2	335.9	334.7
110°	387.2	389.5	388.3	386.0	389.5

TEST NUMBER: P1026425

CATALOG NUMBER: S124RDIP-B575D1205UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	447.8	447.8	445.5	445.5	445.5
115°	508.5	508.5	506.1	505.0	503.8
117.5°	565.6	565.6	564.4	560.9	557.4
120°	622.7	627.4	623.9	618.1	620.4
122.5°	682.2	683.4	682.2	678.7	672.9
125°	740.5	740.5	739.4	737.0	734.7
127.5°	793.0	796.5	794.2	791.8	790.7
130°	849.0	852.5	852.5	850.1	845.5
132.5°	906.1	908.5	907.3	905.0	903.8
135°	955.1	962.1	962.1	959.8	956.3
137.5°	1009.9	1013.4	1015.7	1012.2	1013.4
140°	1064.7	1067.1	1067.1	1065.9	1064.7
142.5°	1114.9	1117.2	1116.0	1116.0	1116.0
145°	1160.3	1165.0	1166.2	1165.0	1161.5
147.5°	1207.0	1212.8	1211.7	1210.5	1209.3
150°	1249.0	1253.6	1253.6	1253.6	1252.5
152.5°	1288.6	1291.0	1292.1	1295.6	1292.1
155°	1329.4	1329.4	1328.3	1332.9	1328.3
157.5°	1364.4	1362.1	1362.1	1365.6	1362.1
160°	1394.7	1393.6	1392.4	1395.9	1390.1
162.5°	1422.7	1419.2	1418.1	1425.1	1419.2
165°	1447.2	1443.7	1441.4	1448.4	1443.7
167.5°	1467.1	1462.4	1462.4	1469.4	1462.4
170°	1483.4	1477.5	1478.7	1485.7	1477.5
172.5°	1495.0	1490.4	1490.4	1498.5	1490.4
175°	1505.5	1499.7	1498.5	1506.7	1498.5
177.5°	1510.2	1504.4	1504.4	1512.5	1503.2
180°	1507.9	1507.9	1507.9	1507.9	1507.9

(END OF REPORT)