

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026699

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026699
REPORT IS A COMBINATION OF REPORTS P1001293 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8978.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026699

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026699

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	84	80	77	69	67	64	56	54	52	44	43	41
2	87	79	73	68	79	73	67	62	60	56	53	49	46	43	38	36	34
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	21
6	61	49	41	35	55	45	38	32	38	32	28	31	26	23	24	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17
8	52	40	32	27	48	37	30	25	31	25	22	25	21	18	20	17	15
9	49	36	29	24	44	34	27	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8695	8695	8695
5°	8709	8513	8533
10°	8644	8339	8315
15°	8539	8137	8047
20°	8397	7893	7780
25°	8228	7634	7458
30°	8024	7351	7165
35°	7834	7090	6895
40°	7641	6815	6623
45°	7421	6576	6378
50°	7212	6317	6157
55°	6960	6071	5900
60°	6684	5790	5637
65°	6394	5493	5341
70°	6063	5096	5033
75°	5543	4705	4656
80°	4857	4228	4240
85°	4185	3847	4022

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7421 cd/sqm

TEST NUMBER: P1026699

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.4
10°-20°	364.6	4.1
20°-30°	542.1	6.0
30°-40°	642.0	7.2
40°-50°	663.7	7.4
50°-60°	611.4	6.8
60°-70°	494.3	5.5
70°-80°	330.7	3.7
80°-90°	173.3	1.9
90°-100°	149.0	1.7
100°-110°	421.6	4.7
110°-120°	678.8	7.6
120°-130°	837.3	9.3
130°-140°	883.3	9.8
140°-150°	820.3	9.1
150°-160°	661.7	7.4
160°-170°	427.9	4.8
170°-180°	147.6	1.6
0°-30°	1035.1	11.5
0°-40°	1677.1	18.7
0°-60°	2952.3	32.9
0°-90°	3950.5	44.0
90°-120°	1249.4	13.9
90°-150°	3790.4	42.2
90°-180°	5028.0	56.0
0°-180°	8978.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1357	1357	1357	1357	1357	
5°	1357	1354	1345	1356	1354	129
15°	1296	1297	1288	1296	1291	365
25°	1178	1182	1174	1179	1172	542
35°	1019	1028	1024	1028	1028	638
45°	840	854	861	870	872	648
55°	645	667	688	702	708	577
65°	444	475	507	527	532	441
75°	245	279	322	349	355	259
85°	73	117	164	193	204	76
90°	22	74	128	164	177	18
95°	83	114	116	151	160	94
105°	350	376	416	443	451	371
115°	644	659	694	714	715	638
125°	909	916	943	959	962	812
135°	1130	1136	1142	1158	1157	871
145°	1308	1309	1309	1317	1316	818
155°	1439	1432	1435	1438	1429	663
165°	1519	1512	1513	1520	1511	429
175°	1553	1546	1548	1557	1546	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1026699

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1357.1	1357.1	1357.1	1357.1	1357.1
2.5°	1361.1	1358.4	1349.1	1358.4	1357.1
5°	1357.1	1354.4	1345.1	1355.8	1354.4
7.5°	1347.8	1346.4	1337.1	1346.4	1345.1
10°	1334.5	1334.5	1323.8	1333.1	1331.8
12.5°	1315.8	1317.2	1309.2	1315.8	1311.8
15°	1295.9	1297.2	1287.9	1295.9	1290.6
17.5°	1270.6	1273.3	1263.9	1270.6	1266.6
20°	1242.7	1245.3	1236.0	1240.0	1240.0
22.5°	1210.7	1216.1	1205.4	1210.7	1206.7
25°	1177.5	1181.5	1173.5	1178.8	1172.1
27.5°	1141.5	1146.9	1137.6	1141.5	1138.9
30°	1100.3	1108.3	1100.3	1103.0	1101.6
32.5°	1063.0	1069.7	1064.4	1067.0	1065.7
35°	1019.1	1028.5	1024.5	1028.5	1028.5
37.5°	976.6	984.5	983.2	988.5	987.2
40°	932.7	943.3	942.0	947.3	950.0
42.5°	884.8	899.4	903.4	910.0	910.0
45°	839.5	854.2	860.8	870.1	871.5
47.5°	793.0	806.3	816.9	830.2	832.9
50°	745.1	759.7	774.3	789.0	793.0
52.5°	694.5	713.1	731.8	747.7	750.4
55°	645.3	666.6	687.9	702.5	707.8
57.5°	594.7	620.0	643.9	659.9	663.9
60°	544.2	570.8	597.4	617.3	621.3
62.5°	494.9	521.5	550.8	573.4	578.8
65°	444.4	475.0	506.9	526.9	532.2
67.5°	397.8	427.1	459.0	483.0	489.6
70°	345.9	376.5	411.1	436.4	444.4
72.5°	295.4	327.3	365.9	393.8	399.1
75°	244.8	279.4	322.0	348.6	355.2
77.5°	195.6	235.5	275.4	304.7	310.0
80°	150.3	190.3	235.5	264.8	270.1
82.5°	109.1	151.7	198.2	226.2	236.8
85°	73.2	117.1	163.6	192.9	203.6
87.5°	46.6	89.1	134.4	165.0	174.3
90°	22.5	74.3	127.5	163.9	176.6
92.5°	40.5	68.7	122.2	157.2	167.7
95°	82.9	114.1	115.5	150.6	159.9
97.5°	139.2	178.0	112.5	142.7	153.3
100°	206.9	238.4	285.6	141.9	145.3
102.5°	275.8	305.8	349.3	378.2	289.4
105°	350.5	376.5	416.4	443.0	451.1
107.5°	427.4	446.1	487.1	514.8	518.1
110°	502.1	518.1	557.7	579.5	589.9

TEST NUMBER: P1026699

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	573.5	589.0	626.0	645.4	652.4
115°	643.6	658.7	694.4	713.7	714.8
117.5°	717.2	723.8	761.7	777.4	784.4
120°	786.3	789.0	823.1	843.5	845.6
122.5°	845.9	853.1	883.4	902.4	903.5
125°	909.2	916.0	942.6	959.3	962.4
127.5°	969.0	973.4	994.9	1012.5	1011.3
130°	1024.2	1028.7	1048.5	1063.6	1064.5
132.5°	1078.2	1085.1	1095.0	1113.6	1113.1
135°	1130.0	1135.5	1142.5	1157.5	1157.3
137.5°	1178.4	1183.9	1187.0	1202.9	1202.4
140°	1224.2	1226.5	1226.8	1243.7	1242.1
142.5°	1266.8	1266.7	1269.0	1281.0	1279.4
145°	1308.3	1309.3	1309.3	1317.1	1315.5
147.5°	1343.8	1343.8	1345.0	1348.8	1343.4
150°	1378.4	1376.1	1378.4	1380.7	1372.8
152.5°	1411.8	1406.0	1408.3	1410.6	1402.5
155°	1439.4	1432.5	1434.8	1438.2	1429.0
157.5°	1461.3	1457.8	1457.8	1461.3	1452.1
160°	1484.3	1477.4	1478.5	1483.2	1473.9
162.5°	1502.7	1495.8	1497.0	1503.9	1493.5
165°	1518.8	1511.9	1513.1	1520.0	1510.8
167.5°	1531.5	1524.6	1525.8	1533.8	1523.5
170°	1541.9	1533.8	1535.0	1544.2	1533.8
172.5°	1548.8	1540.7	1543.0	1551.1	1540.7
175°	1553.4	1546.5	1547.6	1556.8	1546.5
177.5°	1556.8	1549.9	1551.1	1559.2	1549.9
180°	1553.4	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)