

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026700

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026700
REPORT IS A COMBINATION OF REPORTS P1001294 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9055.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026700

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026700

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	97	97	97	97		80	80	80		65	65	65		51	51	51
1	96	91	87	83	87	84	80	77		69	67	64		56	54	52		44	43	41
2	87	79	73	68	79	73	67	62		60	56	53		49	46	43		38	36	34
3	79	69	62	56	72	64	57	52		53	48	44		43	39	36		34	31	29
4	72	61	53	47	66	56	49	44		47	41	37		38	34	31		30	27	25
5	66	54	46	40	60	50	43	37		42	36	32		34	30	27		27	24	21
6	61	49	41	35	55	45	38	32		38	32	28		31	26	23		24	21	19
7	56	44	36	30	51	40	33	28		34	28	24		28	24	20		22	19	17
8	52	40	32	27	48	37	30	25		31	25	22		25	21	18		20	17	15
9	49	36	29	24	44	34	27	22		28	23	19		23	19	16		19	16	13
10	45	33	26	21	41	31	24	20		26	21	17		22	18	15		17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8769	8769	8769
5°	8784	8585	8606
10°	8718	8411	8387
15°	8612	8207	8116
20°	8468	7961	7847
25°	8299	7699	7522
30°	8093	7414	7227
35°	7902	7150	6954
40°	7705	6873	6679
45°	7485	6633	6432
50°	7273	6372	6210
55°	7019	6122	5951
60°	6741	5839	5686
65°	6449	5541	5386
70°	6116	5140	5076
75°	5590	4744	4697
80°	4899	4264	4276
85°	4220	3880	4055

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7485 cd/sqm

TEST NUMBER: P1026700

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	1.4
10°-20°	367.7	4.1
20°-30°	546.7	6.0
30°-40°	647.5	7.2
40°-50°	669.4	7.4
50°-60°	616.7	6.8
60°-70°	498.5	5.5
70°-80°	333.6	3.7
80°-90°	174.7	1.9
90°-100°	150.3	1.7
100°-110°	425.2	4.7
110°-120°	684.7	7.6
120°-130°	844.4	9.3
130°-140°	890.9	9.8
140°-150°	827.4	9.1
150°-160°	667.4	7.4
160°-170°	431.6	4.8
170°-180°	148.8	1.6
0°-30°	1043.9	11.5
0°-40°	1691.5	18.7
0°-60°	2977.5	32.9
0°-90°	3984.3	44.0
90°-120°	1260.2	13.9
90°-150°	3822.9	42.2
90°-180°	5071.0	56.0
0°-180°	9055.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1369	1369	1369	1369	1369	
5°	1369	1366	1357	1367	1366	130
15°	1307	1308	1299	1307	1302	368
25°	1188	1192	1184	1189	1182	547
35°	1028	1037	1033	1037	1037	643
45°	847	862	868	878	879	653
55°	651	672	694	708	714	582
65°	448	479	511	531	537	445
75°	247	282	325	352	358	262
85°	74	118	165	195	205	77
90°	23	75	129	165	178	18
95°	84	115	117	152	161	95
105°	354	380	420	447	455	375
115°	649	664	700	720	721	644
125°	917	924	951	968	971	819
135°	1140	1145	1152	1168	1167	879
145°	1320	1320	1320	1328	1327	825
155°	1452	1445	1447	1451	1441	669
165°	1532	1525	1526	1533	1524	433
175°	1567	1560	1561	1570	1560	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1026700

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1372.7	1370.0	1360.7	1370.0	1368.7
5°	1368.7	1366.0	1356.6	1367.4	1366.0
7.5°	1359.3	1358.0	1348.6	1358.0	1356.6
10°	1345.9	1345.9	1335.2	1344.5	1343.2
12.5°	1327.1	1328.4	1320.4	1327.1	1323.1
15°	1307.0	1308.3	1298.9	1307.0	1301.6
17.5°	1281.5	1284.2	1274.8	1281.5	1277.5
20°	1253.3	1256.0	1246.6	1250.6	1250.6
22.5°	1221.1	1226.5	1215.7	1221.1	1217.1
25°	1187.6	1191.6	1183.5	1188.9	1182.2
27.5°	1151.3	1156.7	1147.3	1151.3	1148.6
30°	1109.7	1117.8	1109.7	1112.4	1111.1
32.5°	1072.2	1078.9	1073.5	1076.2	1074.8
35°	1027.9	1037.3	1033.2	1037.3	1037.3
37.5°	984.9	993.0	991.6	997.0	995.7
40°	940.6	951.4	950.0	955.4	958.1
42.5°	892.3	907.1	911.1	917.8	917.8
45°	846.7	861.5	868.2	877.6	878.9
47.5°	799.8	813.2	823.9	837.3	840.0
50°	751.4	766.2	781.0	795.7	799.8
52.5°	700.5	719.2	738.0	754.1	756.8
55°	650.8	672.3	693.7	708.5	713.9
57.5°	599.8	625.3	649.5	665.6	669.6
60°	548.8	575.7	602.5	622.6	626.7
62.5°	499.2	526.0	555.5	578.3	583.7
65°	448.2	479.0	511.3	531.4	536.7
67.5°	401.2	430.7	462.9	487.1	493.8
70°	348.9	379.7	414.6	440.1	448.2
72.5°	297.9	330.1	369.0	397.2	402.6
75°	246.9	281.8	324.7	351.6	358.3
77.5°	197.3	237.5	277.8	307.3	312.7
80°	151.6	191.9	237.5	267.0	272.4
82.5°	110.0	153.0	199.9	228.1	238.9
85°	73.8	118.1	165.0	194.6	205.3
87.5°	47.0	89.9	135.5	166.4	175.8
90°	22.7	74.9	128.6	165.3	178.2
92.5°	40.9	69.3	123.3	158.6	169.2
95°	83.6	115.0	116.6	151.9	161.3
97.5°	140.4	179.5	113.5	144.0	154.6
100°	208.8	240.3	288.0	143.1	146.5
102.5°	278.2	308.3	352.3	381.4	291.9
105°	353.6	379.6	419.9	446.7	454.9
107.5°	431.1	449.9	491.2	519.2	522.6
110°	506.5	522.6	562.5	584.5	595.1

TEST NUMBER: P1026700

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.5	594.1	631.4	651.0	658.0
115°	649.2	664.3	700.4	719.9	720.9
117.5°	723.3	730.0	768.2	784.1	791.1
120°	793.0	795.8	830.2	850.7	853.0
122.5°	853.2	860.3	891.0	910.2	911.3
125°	917.1	923.8	950.7	967.5	970.7
127.5°	977.3	981.8	1003.4	1021.2	1020.0
130°	1033.0	1037.5	1057.5	1072.8	1073.7
132.5°	1087.5	1094.4	1104.3	1123.1	1122.7
135°	1139.7	1145.3	1152.4	1167.5	1167.3
137.5°	1188.5	1194.1	1197.1	1213.2	1212.8
140°	1234.7	1237.0	1237.3	1254.3	1252.7
142.5°	1277.7	1277.5	1279.9	1292.0	1290.3
145°	1319.5	1320.5	1320.5	1328.4	1326.8
147.5°	1355.4	1355.4	1356.5	1360.4	1355.0
150°	1390.2	1387.9	1390.2	1392.5	1384.5
152.5°	1423.9	1418.1	1420.4	1422.7	1414.6
155°	1451.8	1444.8	1447.1	1450.6	1441.3
157.5°	1473.8	1470.3	1470.3	1473.8	1464.5
160°	1497.0	1490.1	1491.2	1495.9	1486.6
162.5°	1515.6	1508.7	1509.8	1516.8	1506.3
165°	1531.9	1524.9	1526.1	1533.1	1523.8
167.5°	1544.7	1537.7	1538.9	1547.0	1536.5
170°	1555.1	1547.0	1548.2	1557.4	1547.0
172.5°	1562.1	1554.0	1556.3	1564.4	1554.0
175°	1566.7	1559.8	1560.9	1570.2	1559.8
177.5°	1570.2	1563.2	1564.4	1572.5	1563.2
180°	1566.7	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)