

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026702

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026702
REPORT IS A COMBINATION OF REPORTS P1001296 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9004.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026702

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026702

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	84	80	77	69	67	64	56	54	52	44	43	41
2	87	79	73	68	79	73	67	62	60	56	53	49	46	43	38	36	34
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	21
6	61	49	41	35	55	45	38	32	38	32	28	31	26	23	24	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17
8	52	40	32	27	48	37	30	25	31	25	22	25	21	18	20	17	15
9	49	36	29	24	44	34	27	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8720	8720	8720
5°	8734	8537	8558
10°	8669	8363	8339
15°	8563	8161	8070
20°	8420	7915	7802
25°	8251	7655	7480
30°	8047	7371	7186
35°	7857	7110	6914
40°	7662	6834	6641
45°	7442	6595	6396
50°	7232	6335	6174
55°	6979	6088	5917
60°	6702	5806	5653
65°	6412	5510	5356
70°	6081	5111	5046
75°	5559	4718	4669
80°	4873	4241	4253
85°	4197	3859	4032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7442 cd/sqm

TEST NUMBER: P1026702

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	1.4
10°-20°	365.6	4.1
20°-30°	543.6	6.0
30°-40°	643.8	7.2
40°-50°	665.6	7.4
50°-60°	613.2	6.8
60°-70°	495.7	5.5
70°-80°	331.7	3.7
80°-90°	173.7	1.9
90°-100°	149.5	1.7
100°-110°	422.8	4.7
110°-120°	680.8	7.6
120°-130°	839.7	9.3
130°-140°	885.9	9.8
140°-150°	822.7	9.1
150°-160°	663.6	7.4
160°-170°	429.2	4.8
170°-180°	148.0	1.6
0°-30°	1038.0	11.5
0°-40°	1681.9	18.7
0°-60°	2960.7	32.9
0°-90°	3961.8	44.0
90°-120°	1253.1	13.9
90°-150°	3801.5	42.2
90°-180°	5042.0	56.0
0°-180°	9004.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1361	1361	1361	1361	1361	
5°	1361	1358	1349	1360	1358	129
15°	1300	1301	1292	1300	1294	366
25°	1181	1185	1177	1182	1176	544
35°	1022	1031	1027	1031	1031	640
45°	842	857	863	873	874	650
55°	647	668	690	704	710	578
65°	446	476	508	528	534	442
75°	246	280	323	350	356	260
85°	73	117	164	194	204	77
90°	22	74	128	164	177	18
95°	83	114	116	151	160	94
105°	352	378	418	444	452	372
115°	646	661	696	716	717	640
125°	912	919	945	962	965	814
135°	1133	1139	1146	1161	1161	874
145°	1312	1313	1313	1321	1319	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1026702

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.0	1361.0	1361.0	1361.0	1361.0
2.5°	1365.0	1362.3	1352.9	1362.3	1361.0
5°	1361.0	1358.3	1348.9	1359.6	1358.3
7.5°	1351.6	1350.3	1340.9	1350.3	1348.9
10°	1338.3	1338.3	1327.6	1336.9	1335.6
12.5°	1319.6	1320.9	1312.9	1319.6	1315.6
15°	1299.6	1300.9	1291.6	1299.6	1294.2
17.5°	1274.2	1276.9	1267.6	1274.2	1270.2
20°	1246.2	1248.9	1239.5	1243.5	1243.5
22.5°	1214.2	1219.5	1208.8	1214.2	1210.2
25°	1180.8	1184.8	1176.8	1182.2	1175.5
27.5°	1144.8	1150.1	1140.8	1144.8	1142.1
30°	1103.4	1111.4	1103.4	1106.1	1104.8
32.5°	1066.1	1072.8	1067.4	1070.1	1068.7
35°	1022.1	1031.4	1027.4	1031.4	1031.4
37.5°	979.4	987.4	986.0	991.4	990.0
40°	935.3	946.0	944.7	950.0	952.7
42.5°	887.3	902.0	906.0	912.6	912.6
45°	841.9	856.6	863.3	872.6	873.9
47.5°	795.2	808.6	819.2	832.6	835.3
50°	747.2	761.9	776.5	791.2	795.2
52.5°	696.5	715.2	733.8	749.9	752.5
55°	647.1	668.5	689.8	704.5	709.8
57.5°	596.4	621.8	645.8	661.8	665.8
60°	545.7	572.4	599.1	619.1	623.1
62.5°	496.3	523.0	552.4	575.1	580.4
65°	445.6	476.3	508.4	528.4	533.7
67.5°	398.9	428.3	460.3	484.3	491.0
70°	346.9	377.6	412.3	437.6	445.6
72.5°	296.2	328.2	366.9	394.9	400.3
75°	245.5	280.2	322.9	349.6	356.2
77.5°	196.1	236.2	276.2	305.5	310.9
80°	150.8	190.8	236.2	265.5	270.9
82.5°	109.4	152.1	198.8	226.8	237.5
85°	73.4	117.4	164.1	193.5	204.1
87.5°	46.7	89.4	134.8	165.4	174.8
90°	22.5	74.4	127.9	164.4	177.1
92.5°	40.6	68.9	122.6	157.7	168.2
95°	83.1	114.4	115.9	151.1	160.4
97.5°	139.6	178.5	112.9	143.2	153.7
100°	207.6	239.0	286.4	142.3	145.7
102.5°	276.6	306.6	350.3	379.3	290.2
105°	351.5	377.6	417.6	444.3	452.4
107.5°	428.8	447.5	488.4	516.2	519.6
110°	503.6	519.7	559.3	581.2	591.7

TEST NUMBER: P1026702

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.2	590.7	627.9	647.3	654.3
115°	645.5	660.6	696.4	715.9	717.0
117.5°	719.3	725.9	763.9	779.7	786.6
120°	788.6	791.4	825.6	845.9	848.2
122.5°	848.4	855.5	886.0	905.1	906.2
125°	911.9	918.7	945.4	962.1	965.3
127.5°	971.8	976.3	997.8	1015.5	1014.3
130°	1027.2	1031.7	1051.5	1066.7	1067.6
132.5°	1081.4	1088.3	1098.1	1116.8	1116.4
135°	1133.3	1138.9	1146.0	1160.9	1160.7
137.5°	1181.8	1187.4	1190.5	1206.5	1206.0
140°	1227.8	1230.1	1230.3	1247.3	1245.7
142.5°	1270.5	1270.4	1272.7	1284.7	1283.1
145°	1312.1	1313.1	1313.1	1321.0	1319.3
147.5°	1347.8	1347.8	1348.9	1352.8	1347.3
150°	1382.4	1380.1	1382.4	1384.7	1376.8
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)