

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026704

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026704
REPORT IS A COMBINATION OF REPORTS P1001298 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9151.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026704

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026704

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10775	10775	10775
5°	10775	10525	10545
10°	10686	10284	10251
15°	10546	9995	9905
20°	10356	9660	9508
25°	10152	9295	9084
30°	9907	8915	8636
35°	9644	8517	8135
40°	9373	8095	7688
45°	9080	7684	7215
50°	8757	7218	6663
55°	8437	6705	6155
60°	8056	6164	5564
65°	7600	5537	4954
70°	7136	4816	4249
75°	6356	3965	3436
80°	5416	2962	2528
85°	4185	1752	1393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9080 cd/sqm

TEST NUMBER: P1026704

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	1.7
10°-20°	448.2	4.9
20°-30°	661.7	7.2
30°-40°	772.1	8.4
40°-50°	775.4	8.5
50°-60°	680.7	7.4
60°-70°	507.0	5.5
70°-80°	289.6	3.2
80°-90°	85.9	0.9
90°-100°	52.7	0.6
100°-110°	350.6	3.8
110°-120°	631.3	6.9
120°-130°	810.4	8.9
130°-140°	871.6	9.5
140°-150°	818.0	8.9
150°-160°	661.7	7.2
160°-170°	427.9	4.7
170°-180°	147.6	1.6
0°-30°	1268.7	13.9
0°-40°	2040.7	22.3
0°-60°	3496.8	38.2
0°-90°	4379.3	47.9
90°-120°	1034.6	11.3
90°-150°	3534.5	38.6
90°-180°	4772.0	52.1
0°-180°	9151.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1679	1676	1663	1675	1674	159
15°	1600	1596	1582	1588	1588	451
25°	1453	1446	1429	1432	1428	668
35°	1255	1249	1231	1224	1213	785
45°	1027	1022	1006	990	986	791
55°	782	778	760	748	738	698
65°	528	526	511	499	494	524
75°	281	278	271	267	262	299
85°	73	74	74	73	70	80
90°	1	10	18	24	28	8
95°	66	62	18	24	24	80
105°	338	343	343	343	342	359
115°	636	641	642	638	631	630
125°	904	912	912	907	904	807
135°	1127	1134	1132	1130	1123	869
145°	1307	1309	1309	1310	1304	817
155°	1439	1432	1435	1438	1429	663
165°	1519	1512	1513	1520	1511	429
175°	1553	1546	1548	1557	1546	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1026704

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1681.7	1681.7	1681.7	1681.7	1681.7
2.5°	1687.0	1683.0	1669.7	1683.0	1681.7
5°	1679.0	1676.4	1663.1	1675.0	1673.7
7.5°	1667.0	1664.4	1649.7	1661.7	1660.4
10°	1649.7	1647.1	1632.5	1643.1	1641.8
12.5°	1628.5	1623.1	1609.8	1617.8	1617.8
15°	1600.5	1596.5	1581.9	1588.5	1588.5
17.5°	1571.3	1564.6	1550.0	1557.9	1551.3
20°	1532.7	1530.0	1512.7	1522.0	1515.4
22.5°	1494.1	1488.8	1472.8	1478.1	1474.1
25°	1452.8	1446.2	1428.9	1431.6	1427.6
27.5°	1404.9	1401.0	1383.7	1385.0	1381.0
30°	1358.4	1354.4	1334.4	1331.8	1327.8
32.5°	1307.8	1301.2	1283.9	1278.6	1270.6
35°	1254.6	1249.3	1230.7	1224.0	1213.4
37.5°	1200.1	1193.4	1176.1	1166.8	1160.1
40°	1144.2	1137.5	1118.9	1106.9	1102.9
42.5°	1084.3	1079.0	1060.4	1049.7	1043.1
45°	1027.1	1021.8	1005.8	989.8	985.9
47.5°	964.6	965.9	945.9	930.0	920.7
50°	904.7	900.7	884.7	867.4	858.1
52.5°	843.5	840.8	823.5	808.9	798.3
55°	782.3	778.3	759.7	747.7	738.4
57.5°	717.1	715.8	699.8	683.8	679.9
60°	655.9	650.6	636.0	622.6	613.3
62.5°	592.0	588.1	576.1	561.4	554.8
65°	528.2	525.5	510.9	498.9	493.6
67.5°	465.7	460.3	449.7	439.0	436.4
70°	407.1	400.5	388.5	380.5	375.2
72.5°	343.3	339.3	332.6	323.3	318.0
75°	280.7	278.1	271.4	267.4	262.1
77.5°	222.2	220.9	216.9	214.2	210.2
80°	167.6	167.6	165.0	163.6	161.0
82.5°	119.7	117.1	117.1	114.4	114.4
85°	73.2	74.5	74.5	73.2	70.5
87.5°	35.9	35.9	34.6	34.6	31.9
90°	1.2	10.4	18.4	24.2	27.6
92.5°	21.9	11.5	18.4	24.2	25.3
95°	65.6	62.2	18.4	24.2	24.2
97.5°	123.2	130.1	20.7	23.0	24.2
100°	192.3	195.8	200.4	28.8	24.2
102.5°	262.5	267.2	269.5	271.8	175.0
105°	338.5	343.2	343.2	343.2	342.0
107.5°	416.8	416.8	419.2	420.3	415.7
110°	492.8	492.8	495.2	491.7	492.8

TEST NUMBER: P1026704

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.2	567.7	568.8	564.2	561.9
115°	635.6	641.4	642.5	637.9	631.0
117.5°	710.5	710.5	715.1	708.2	705.9
120°	779.6	778.4	781.9	779.6	773.8
122.5°	840.6	846.4	847.5	845.2	838.3
125°	903.9	912.0	912.0	907.4	903.9
127.5°	965.0	970.7	969.6	967.3	958.1
130°	1020.2	1026.0	1027.2	1023.7	1017.9
132.5°	1075.5	1082.4	1079.0	1079.0	1073.2
135°	1127.3	1134.2	1131.9	1129.6	1122.7
137.5°	1175.7	1182.6	1180.3	1180.3	1174.5
140°	1222.9	1225.2	1224.1	1226.4	1219.5
142.5°	1265.5	1266.7	1269.0	1269.0	1262.1
145°	1307.0	1309.3	1309.3	1310.4	1303.5
147.5°	1343.8	1343.8	1345.0	1346.1	1338.1
150°	1378.4	1376.1	1378.4	1380.7	1371.5
152.5°	1411.8	1406.0	1408.3	1410.6	1402.5
155°	1439.4	1432.5	1434.8	1438.2	1429.0
157.5°	1461.3	1457.8	1457.8	1461.3	1452.1
160°	1484.3	1477.4	1478.5	1483.2	1473.9
162.5°	1502.7	1495.8	1497.0	1503.9	1493.5
165°	1518.8	1511.9	1513.1	1520.0	1510.8
167.5°	1531.5	1524.6	1525.8	1533.8	1523.5
170°	1541.9	1533.8	1535.0	1544.2	1533.8
172.5°	1548.8	1540.7	1543.0	1551.1	1540.7
175°	1553.4	1546.5	1547.6	1556.8	1546.5
177.5°	1556.8	1549.9	1551.1	1559.2	1549.9
180°	1553.4	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)