

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026705

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026705
REPORT IS A COMBINATION OF REPORTS P1001299 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9230.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026705

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026705

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34	34	34
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33	28	28	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24	21	21	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22	19	19	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	16	16	16
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1026705

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	1.7
10°-20°	452.1	4.9
20°-30°	667.5	7.2
30°-40°	778.8	8.4
40°-50°	782.2	8.5
50°-60°	686.6	7.4
60°-70°	511.4	5.5
70°-80°	292.1	3.2
80°-90°	86.7	0.9
90°-100°	53.2	0.6
100°-110°	353.6	3.8
110°-120°	636.8	6.9
120°-130°	817.3	8.9
130°-140°	879.0	9.5
140°-150°	825.0	8.9
150°-160°	667.3	7.2
160°-170°	431.6	4.7
170°-180°	148.8	1.6
0°-30°	1279.7	13.9
0°-40°	2058.4	22.3
0°-60°	3527.2	38.2
0°-90°	4417.3	47.9
90°-120°	1043.5	11.3
90°-150°	3564.9	38.6
90°-180°	4813.0	52.1
0°-180°	9230.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	10	19	24	28	8
95°	66	63	19	24	24	81
105°	342	346	346	346	345	362
115°	641	647	648	643	636	636
125°	912	920	920	915	912	814
135°	1137	1144	1142	1139	1132	877
145°	1318	1320	1320	1322	1315	824
155°	1452	1445	1447	1451	1441	669
165°	1532	1525	1526	1533	1524	433
175°	1567	1560	1561	1570	1560	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1026705

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	1.2	10.5	18.6	24.4	27.9
92.5°	22.1	11.6	18.6	24.4	25.6
95°	66.2	62.7	18.6	24.4	24.4
97.5°	124.3	131.2	20.9	23.2	24.4
100°	194.0	197.4	202.1	29.0	24.4
102.5°	264.8	269.4	271.8	274.1	176.5
105°	341.5	346.1	346.1	346.1	344.9
107.5°	420.4	420.4	422.8	423.9	419.3
110°	497.1	497.1	499.4	495.9	497.1

TEST NUMBER: P1026705

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	569.1	572.6	573.7	569.1	566.8
115°	641.1	646.9	648.1	643.4	636.4
117.5°	716.6	716.6	721.2	714.3	711.9
120°	786.3	785.1	788.6	786.3	780.5
122.5°	847.8	853.6	854.8	852.5	845.5
125°	911.7	919.8	919.8	915.2	911.7
127.5°	973.3	979.1	977.9	975.6	966.3
130°	1029.0	1034.8	1036.0	1032.5	1026.7
132.5°	1084.8	1091.7	1088.2	1088.2	1082.4
135°	1137.0	1144.0	1141.7	1139.3	1132.4
137.5°	1185.8	1192.8	1190.4	1190.4	1184.6
140°	1233.4	1235.7	1234.6	1236.9	1229.9
142.5°	1276.4	1277.5	1279.9	1279.9	1272.9
145°	1318.2	1320.5	1320.5	1321.7	1314.7
147.5°	1355.4	1355.4	1356.5	1357.7	1349.6
150°	1390.2	1387.9	1390.2	1392.5	1383.2
152.5°	1423.9	1418.1	1420.4	1422.7	1414.6
155°	1451.8	1444.8	1447.1	1450.6	1441.3
157.5°	1473.8	1470.3	1470.3	1473.8	1464.5
160°	1497.0	1490.1	1491.2	1495.9	1486.6
162.5°	1515.6	1508.7	1509.8	1516.8	1506.3
165°	1531.9	1524.9	1526.1	1533.1	1523.8
167.5°	1544.7	1537.7	1538.9	1547.0	1536.5
170°	1555.1	1547.0	1548.2	1557.4	1547.0
172.5°	1562.1	1554.0	1556.3	1564.4	1554.0
175°	1566.7	1559.8	1560.9	1570.2	1559.8
177.5°	1570.2	1563.2	1564.4	1572.5	1563.2
180°	1566.7	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)