

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026707

Luminaire Tested: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026707
REPORT IS A COMBINATION OF REPORTS P1001301 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9178.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026707

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026707

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	85	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	22
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10807	10807	10807
5°	10807	10556	10576
10°	10717	10314	10281
15°	10577	10024	9935
20°	10387	9689	9537
25°	10183	9322	9111
30°	9936	8941	8662
35°	9673	8542	8159
40°	9401	8119	7711
45°	9107	7707	7237
50°	8783	7240	6683
55°	8462	6724	6174
60°	8081	6181	5582
65°	7623	5553	4969
70°	7157	4830	4262
75°	6376	3977	3446
80°	5432	2971	2535
85°	4197	1756	1397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9107 cd/sqm

TEST NUMBER: P1026707

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	1.7
10°-20°	449.6	4.9
20°-30°	663.7	7.2
30°-40°	774.4	8.4
40°-50°	777.7	8.5
50°-60°	682.7	7.4
60°-70°	508.5	5.5
70°-80°	290.4	3.2
80°-90°	86.1	0.9
90°-100°	52.9	0.6
100°-110°	351.6	3.8
110°-120°	633.2	6.9
120°-130°	812.7	8.9
130°-140°	874.1	9.5
140°-150°	820.4	8.9
150°-160°	663.6	7.2
160°-170°	429.2	4.7
170°-180°	148.0	1.6
0°-30°	1272.4	13.9
0°-40°	2046.8	22.3
0°-60°	3507.2	38.2
0°-90°	4392.3	47.9
90°-120°	1037.7	11.3
90°-150°	3544.9	38.6
90°-180°	4786.0	52.1
0°-180°	9178.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1687	1687	1687	1687	1687	
5°	1684	1681	1668	1680	1679	160
15°	1605	1601	1587	1593	1593	453
25°	1457	1450	1433	1436	1432	670
35°	1258	1253	1234	1228	1217	787
45°	1030	1025	1009	993	989	794
55°	785	781	762	750	741	700
65°	530	527	512	500	495	525
75°	282	279	272	268	263	300
85°	73	75	75	73	71	80
90°	1	10	18	24	28	8
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1026707

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1686.7	1686.7	1686.7	1686.7	1686.7
2.5°	1692.0	1688.0	1674.7	1688.0	1686.7
5°	1684.0	1681.3	1668.0	1680.0	1678.7
7.5°	1672.0	1669.3	1654.6	1666.7	1665.3
10°	1654.6	1652.0	1637.3	1648.0	1646.6
12.5°	1633.3	1628.0	1614.6	1622.6	1622.6
15°	1605.3	1601.3	1586.6	1593.3	1593.3
17.5°	1575.9	1569.2	1554.6	1562.6	1555.9
20°	1537.2	1534.6	1517.2	1526.5	1519.9
22.5°	1498.5	1493.2	1477.2	1482.5	1478.5
25°	1457.2	1450.5	1433.1	1435.8	1431.8
27.5°	1409.1	1405.1	1387.8	1389.1	1385.1
30°	1362.4	1358.4	1338.4	1335.7	1331.7
32.5°	1311.7	1305.0	1287.7	1282.4	1274.3
35°	1258.3	1253.0	1234.3	1227.6	1217.0
37.5°	1203.6	1197.0	1179.6	1170.3	1163.6
40°	1147.6	1140.9	1122.2	1110.2	1106.2
42.5°	1087.5	1082.2	1063.5	1052.8	1046.2
45°	1030.2	1024.8	1008.8	992.8	988.8
47.5°	967.4	968.8	948.8	932.7	923.4
50°	907.4	903.4	887.4	870.0	860.7
52.5°	846.0	843.3	826.0	811.3	800.6
55°	784.6	780.6	761.9	749.9	740.6
57.5°	719.2	717.9	701.9	685.9	681.9
60°	657.9	652.5	637.8	624.5	615.2
62.5°	593.8	589.8	577.8	563.1	556.4
65°	529.8	527.1	512.4	500.4	495.1
67.5°	467.0	461.7	451.0	440.4	437.7
70°	408.3	401.7	389.6	381.6	376.3
72.5°	344.3	340.3	333.6	324.3	318.9
75°	281.6	278.9	272.2	268.2	262.9
77.5°	222.8	221.5	217.5	214.8	210.8
80°	168.1	168.1	165.5	164.1	161.5
82.5°	120.1	117.4	117.4	114.8	114.8
85°	73.4	74.7	74.7	73.4	70.7
87.5°	36.0	36.0	34.7	34.7	32.0
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1026707

CATALOG NUMBER: S125DIP-B1090D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)