

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026474

Luminaire Tested: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026474
REPORT IS A COMBINATION OF REPORTS P999544 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D590UB27-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4424.2 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026474

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026474

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	42
3	82	73	66	60	76	68	62	56	58	53	50	49	46	43	41	39	36
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6845 cd/sqm

TEST NUMBER: P1026474

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	2.1
10°-20°	263.0	5.9
20°-30°	379.7	8.6
30°-40°	430.4	9.7
40°-50°	415.5	9.4
50°-60°	345.5	7.8
60°-70°	238.4	5.4
70°-80°	120.5	2.7
80°-90°	31.7	0.7
90°-100°	214.3	4.8
100°-110°	435.8	9.9
110°-120°	388.4	8.8
120°-130°	326.3	7.4
130°-140°	272.3	6.2
140°-150°	207.9	4.7
150°-160°	146.2	3.3
160°-170°	86.0	1.9
170°-180°	28.0	0.6
0°-30°	737.1	16.7
0°-40°	1167.5	26.4
0°-60°	1928.5	43.6
0°-90°	2319.1	52.4
90°-120°	1038.5	23.5
90°-150°	1845.0	41.7
90°-180°	2105.0	47.6
0°-180°	4424.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	1	4	10	11	12	4
95°	19	59	462	229	138	21
105°	66	96	372	800	797	71
115°	117	146	332	637	766	116
125°	163	193	330	542	611	145
135°	193	230	327	481	546	149
145°	223	255	325	406	446	140
155°	253	273	316	358	374	117
165°	276	284	303	321	326	78
175°	288	288	291	295	294	27
180°	288	288	288	288	288	

TEST NUMBER: P1026474

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	0.6	4.5	10.2	11.3	11.9
92.5°	7.9	43.6	222.1	73.4	51.6
95°	18.7	58.9	461.9	228.6	138.3
97.5°	31.2	65.2	494.2	467.0	332.1
100°	43.1	73.6	455.6	646.0	519.7
102.5°	54.4	83.9	407.5	758.2	682.9
105°	66.3	96.0	371.8	800.4	797.4
107.5°	79.3	108.5	348.5	787.7	851.8
110°	92.4	121.0	337.8	742.4	852.9

TEST NUMBER: P1026474

CATALOG NUMBER: S124RDIP-B575D590UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.8	133.4	332.7	686.8	819.5
115°	116.7	146.4	331.5	637.0	765.6
117.5°	129.2	158.6	331.0	597.9	712.9
120°	141.7	170.6	331.0	571.5	669.8
122.5°	153.0	182.2	330.4	554.2	635.8
125°	162.6	193.2	329.8	542.0	610.9
127.5°	171.7	203.4	328.7	530.4	595.0
130°	179.1	213.4	328.1	516.6	581.4
132.5°	186.4	221.8	327.6	500.1	566.1
135°	193.2	230.0	327.0	481.2	546.3
137.5°	200.0	237.2	327.0	460.8	523.1
140°	207.4	243.7	326.4	440.9	497.6
142.5°	215.3	249.6	326.4	422.5	470.4
145°	222.7	255.0	325.3	405.8	446.0
147.5°	231.2	260.1	323.6	391.9	423.3
150°	239.1	264.9	321.9	379.1	404.6
152.5°	246.5	269.5	319.1	368.4	387.6
155°	253.3	273.4	316.2	358.2	373.5
157.5°	260.1	277.1	313.4	348.5	360.4
160°	266.4	280.2	310.0	338.9	348.5
162.5°	272.0	282.8	306.6	329.6	337.2
165°	276.0	284.5	303.2	321.0	325.9
167.5°	280.5	285.9	299.8	313.6	316.8
170°	283.4	287.0	296.4	306.4	308.3
172.5°	286.2	287.9	293.0	299.8	299.8
175°	287.9	288.5	290.7	294.7	293.6
177.5°	289.0	288.5	289.0	291.0	289.0
180°	288.5	288.5	288.5	288.5	288.5

(END OF REPORT)