

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026509

Luminaire Tested: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026509
REPORT IS A COMBINATION OF REPORTS P999599 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D810UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5080.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026509

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026509

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	89	86	89	85	82	79	72	69	67	59	57	56	47	46	45
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	40	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1026509

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.9
10°-20°	265.4	5.2
20°-30°	383.2	7.5
30°-40°	434.3	8.5
40°-50°	419.3	8.3
50°-60°	348.6	6.9
60°-70°	240.6	4.7
70°-80°	121.6	2.4
80°-90°	33.0	0.6
90°-100°	64.3	1.3
100°-110°	192.7	3.8
110°-120°	327.4	6.4
120°-130°	431.8	8.5
130°-140°	485.0	9.5
140°-150°	476.7	9.4
150°-160°	400.9	7.9
160°-170°	266.7	5.3
170°-180°	93.4	1.8
0°-30°	743.8	14.6
0°-40°	1178.0	23.2
0°-60°	1945.9	38.3
0°-90°	2341.1	46.1
90°-120°	584.5	11.5
90°-150°	1977.9	38.9
90°-180°	2739.0	53.9
0°-180°	5080.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	2	11	17	21	23	6
95°	46	53	58	60	60	50
105°	178	179	182	184	186	189
115°	333	333	331	331	330	328
125°	485	485	484	482	481	432
135°	625	630	630	628	626	484
145°	760	763	763	763	760	475
155°	870	870	870	873	870	401
165°	947	945	944	948	945	267
175°	986	982	981	986	981	94
180°	987	987	987	987	987	

TEST NUMBER: P1026509

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	2.3	10.7	16.8	21.4	22.9
92.5°	19.8	29.8	33.6	35.9	36.6
95°	45.8	52.7	58.0	60.3	60.3
97.5°	73.3	79.4	85.5	88.6	88.6
100°	106.9	109.9	116.8	118.3	118.3
102.5°	142.0	142.8	148.9	151.2	151.9
105°	177.9	178.6	181.7	184.0	186.3
107.5°	215.3	216.1	216.8	219.9	219.1
110°	253.5	255.0	254.2	252.7	255.0

TEST NUMBER: P1026509

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	293.2	291.6	291.6	291.6
115°	332.9	332.9	331.3	330.6	329.8
117.5°	370.3	370.3	369.5	367.2	364.9
120°	407.7	410.7	408.4	404.6	406.1
122.5°	446.6	447.4	446.6	444.3	440.5
125°	484.8	484.8	484.0	482.5	481.0
127.5°	519.1	521.4	519.9	518.4	517.6
130°	555.8	558.1	558.1	556.5	553.5
132.5°	593.2	594.7	594.0	592.4	591.7
135°	625.3	629.8	629.8	628.3	626.0
137.5°	661.1	663.4	664.9	662.7	663.4
140°	697.0	698.5	698.5	697.8	697.0
142.5°	729.8	731.4	730.6	730.6	730.6
145°	759.6	762.7	763.4	762.7	760.4
147.5°	790.2	794.0	793.2	792.4	791.7
150°	817.6	820.7	820.7	820.7	819.9
152.5°	843.6	845.1	845.9	848.2	845.9
155°	870.3	870.3	869.5	872.6	869.5
157.5°	893.2	891.7	891.7	894.0	891.7
160°	913.1	912.3	911.5	913.8	910.0
162.5°	931.4	929.1	928.3	932.9	929.1
165°	947.4	945.1	943.6	948.2	945.1
167.5°	960.4	957.3	957.3	961.9	957.3
170°	971.1	967.3	968.0	972.6	967.3
172.5°	978.7	975.7	975.7	981.0	975.7
175°	985.6	981.8	981.0	986.4	981.0
177.5°	988.6	984.8	984.8	990.2	984.1
180°	987.1	987.1	987.1	987.1	987.1

(END OF REPORT)